

# MC812PA Terminal Block Markers

Catalogue Page 1SNK 160 010 S0201

## Pre-printed marker card for horizontal terminal block assembly



8 mm 0.315 in spacing



### Features and Benefits

Save printing time with our large pre-printed cards offer with pre-printed numbers, letters or symbols.

### Main Technical Data

| Material  | Flammability | Maximum printed digits |          | Dimensions |               |
|-----------|--------------|------------------------|----------|------------|---------------|
|           |              |                        |          | mm         | inches        |
| Polyamide | V2           | Horizontal             | Vertical | 7.6 x 12   | 0.299 x 0.472 |

### Ordering Details

| Description    | Number of markers per unit | Color | Type    | Order Code         | Pack <sup>(ing)</sup> pieces | Weight (1 pce) g |
|----------------|----------------------------|-------|---------|--------------------|------------------------------|------------------|
| 0->9 (x10)     | 100                        | White | MC812PA | 1SNK 160 091 R0000 | 1                            | 14.00            |
| 1->10 (x10)    | 100                        | White | MC812PA | 1SNK 160 011 R0000 | 1                            | 14.00            |
| 11->20 (x10)   | 100                        | White | MC812PA | 1SNK 160 021 R0000 | 1                            | 14.00            |
| 21->30 (x10)   | 100                        | White | MC812PA | 1SNK 160 031 R0000 | 1                            | 14.00            |
| 31->40 (x10)   | 100                        | White | MC812PA | 1SNK 160 041 R0000 | 1                            | 14.00            |
| 41->50 (x10)   | 100                        | White | MC812PA | 1SNK 160 051 R0000 | 1                            | 14.00            |
| 51->60 (x10)   | 100                        | White | MC812PA | 1SNK 160 061 R0000 | 1                            | 14.00            |
| 61->70 (x10)   | 100                        | White | MC812PA | 1SNK 160 071 R0000 | 1                            | 14.00            |
| 71->80 (x10)   | 100                        | White | MC812PA | 1SNK 160 081 R0000 | 1                            | 14.00            |
| 81->90 (x10)   | 100                        | White | MC812PA | 1SNK 160 083 R0000 | 1                            | 14.00            |
| 91->100 (x10)  | 100                        | White | MC812PA | 1SNK 160 101 R0000 | 1                            | 14.00            |
| 101->110 (x10) | 100                        | White | MC812PA | 1SNK 160 111 R0000 | 1                            | 14.00            |
| 111->120 (x10) | 100                        | White | MC812PA | 1SNK 160 121 R0000 | 1                            | 14.00            |
| 121->130 (x10) | 100                        | White | MC812PA | 1SNK 160 131 R0000 | 1                            | 14.00            |
| 131->140 (x10) | 100                        | White | MC812PA | 1SNK 160 141 R0000 | 1                            | 14.00            |
| 141->150 (x10) | 100                        | White | MC812PA | 1SNK 160 151 R0000 | 1                            | 14.00            |
| 151->160 (x10) | 100                        | White | MC812PA | 1SNK 160 161 R0000 | 1                            | 14.00            |
| 161->170 (x10) | 100                        | White | MC812PA | 1SNK 160 171 R0000 | 1                            | 14.00            |
| 171->180 (x10) | 100                        | White | MC812PA | 1SNK 160 181 R0000 | 1                            | 14.00            |
| 181->190 (x10) | 100                        | White | MC812PA | 1SNK 160 191 R0000 | 1                            | 14.00            |
| 191->200 (x10) | 100                        | White | MC812PA | 1SNK 160 201 R0000 | 1                            | 14.00            |
| 1->100         | 100                        | White | MC812PA | 1SNK 165 011 R0000 | 1                            | 14.00            |
| 101->200       | 100                        | White | MC812PA | 1SNK 165 021 R0000 | 1                            | 14.00            |
| 201->300       | 100                        | White | MC812PA | 1SNK 165 031 R0000 | 1                            | 14.00            |
| 301->400       | 100                        | White | MC812PA | 1SNK 165 041 R0000 | 1                            | 14.00            |
| 401->500       | 100                        | White | MC812PA | 1SNK 165 051 R0000 | 1                            | 14.00            |
| 501->600       | 100                        | White | MC812PA | 1SNK 165 061 R0000 | 1                            | 14.00            |
| 601->700       | 100                        | White | MC812PA | 1SNK 165 071 R0000 | 1                            | 14.00            |
| 701->800       | 100                        | White | MC812PA | 1SNK 165 081 R0000 | 1                            | 14.00            |
| 801->900       | 100                        | White | MC812PA | 1SNK 165 091 R0000 | 1                            | 14.00            |
| A (x100)       | 100                        | White | MC812PA | 1SNK 166 011 R0000 | 1                            | 14.00            |
| B (x100)       | 100                        | White | MC812PA | 1SNK 166 021 R0000 | 1                            | 14.00            |
| C (x100)       | 100                        | White | MC812PA | 1SNK 166 031 R0000 | 1                            | 14.00            |
| D (x100)       | 100                        | White | MC812PA | 1SNK 166 041 R0000 | 1                            | 14.00            |
| E (x100)       | 100                        | White | MC812PA | 1SNK 166 051 R0000 | 1                            | 14.00            |
| F (x100)       | 100                        | White | MC812PA | 1SNK 166 061 R0000 | 1                            | 14.00            |
| G (x100)       | 100                        | White | MC812PA | 1SNK 166 071 R0000 | 1                            | 14.00            |
| H (x100)       | 100                        | White | MC812PA | 1SNK 166 081 R0000 | 1                            | 14.00            |
| I (x100)       | 100                        | White | MC812PA | 1SNK 166 091 R0000 | 1                            | 14.00            |
| J (x100)       | 100                        | White | MC812PA | 1SNK 166 101 R0000 | 1                            | 14.00            |
| K (x100)       | 100                        | White | MC812PA | 1SNK 166 111 R0000 | 1                            | 14.00            |
| L (x100)       | 100                        | White | MC812PA | 1SNK 166 121 R0000 | 1                            | 14.00            |
| M (x100)       | 100                        | White | MC812PA | 1SNK 166 131 R0000 | 1                            | 14.00            |
| N (x100)       | 100                        | White | MC812PA | 1SNK 166 141 R0000 | 1                            | 14.00            |
| O (x100)       | 100                        | White | MC812PA | 1SNK 166 151 R0000 | 1                            | 14.00            |
| P (x100)       | 100                        | White | MC812PA | 1SNK 166 161 R0000 | 1                            | 14.00            |
| Q (x100)       | 100                        | White | MC812PA | 1SNK 166 171 R0000 | 1                            | 14.00            |
| R (x100)       | 100                        | White | MC812PA | 1SNK 166 181 R0000 | 1                            | 14.00            |
| S (x100)       | 100                        | White | MC812PA | 1SNK 166 191 R0000 | 1                            | 14.00            |
| T (x100)       | 100                        | White | MC812PA | 1SNK 166 201 R0000 | 1                            | 14.00            |
| U (x100)       | 100                        | White | MC812PA | 1SNK 166 211 R0000 | 1                            | 14.00            |
| V (x100)       | 100                        | White | MC812PA | 1SNK 166 221 R0000 | 1                            | 14.00            |
| W (x100)       | 100                        | White | MC812PA | 1SNK 166 231 R0000 | 1                            | 14.00            |

All the technical data for UL/CSA standard and dimensions in inches are in *italic*.

# MC812PA Terminal Block Markers

Catalogue Page 1SNK 160 010 S0201

## Pre-printed marker card for horizontal terminal block assembly



8 mm 0.315 in spacing



### Ordering Details

| Description                                 | Number of markers per unit | Color | Type    | Order Code         | Pack <sup>(ing)</sup> pieces | Weight (1 pc) g |
|---------------------------------------------|----------------------------|-------|---------|--------------------|------------------------------|-----------------|
| X (x100)                                    | 100                        | White | MC812PA | 1SNK 166 241 R0000 | 1                            | 14.00           |
| Y (x100)                                    | 100                        | White | MC812PA | 1SNK 166 251 R0000 | 1                            | 14.00           |
| Z (x100)                                    | 100                        | White | MC812PA | 1SNK 166 261 R0000 | 1                            | 14.00           |
| 0 (x100)                                    | 100                        | White | MC812PA | 1SNK 167 001 R0000 | 1                            | 14.00           |
| 1 (x100)                                    | 100                        | White | MC812PA | 1SNK 167 011 R0000 | 1                            | 14.00           |
| 2 (x100)                                    | 100                        | White | MC812PA | 1SNK 167 021 R0000 | 1                            | 14.00           |
| 3 (x100)                                    | 100                        | White | MC812PA | 1SNK 167 031 R0000 | 1                            | 14.00           |
| 4 (x100)                                    | 100                        | White | MC812PA | 1SNK 167 041 R0000 | 1                            | 14.00           |
| 5 (x100)                                    | 100                        | White | MC812PA | 1SNK 167 051 R0000 | 1                            | 14.00           |
| 6 (x100)                                    | 100                        | White | MC812PA | 1SNK 167 061 R0000 | 1                            | 14.00           |
| 7 (x100)                                    | 100                        | White | MC812PA | 1SNK 167 071 R0000 | 1                            | 14.00           |
| 8 (x100)                                    | 100                        | White | MC812PA | 1SNK 167 081 R0000 | 1                            | 14.00           |
| 9 (x100)                                    | 100                        | White | MC812PA | 1SNK 167 091 R0000 | 1                            | 14.00           |
| + (x100)                                    | 100                        | White | MC812PA | 1SNK 168 001 R0000 | 1                            | 14.00           |
| (x100)                                      | 100                        | White | MC812PA | 1SNK 168 011 R0000 | 1                            | 14.00           |
| ~ (x100)                                    | 100                        | White | MC812PA | 1SNK 168 021 R0000 | 1                            | 14.00           |
| = (x100)                                    | 100                        | White | MC812PA | 1SNK 168 031 R0000 | 1                            | 14.00           |
| ± (x100)                                    | 100                        | White | MC812PA | 1SNK 168 041 R0000 | 1                            | 14.00           |
| L1 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 051 R0000 | 1                            | 14.00           |
| L2 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 061 R0000 | 1                            | 14.00           |
| L3 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 071 R0000 | 1                            | 14.00           |
| PE (x100)                                   | 100                        | White | MC812PA | 1SNK 168 091 R0000 | 1                            | 14.00           |
| U1 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 101 R0000 | 1                            | 14.00           |
| U2 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 111 R0000 | 1                            | 14.00           |
| U3 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 121 R0000 | 1                            | 14.00           |
| V1 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 131 R0000 | 1                            | 14.00           |
| V2 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 141 R0000 | 1                            | 14.00           |
| V3 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 151 R0000 | 1                            | 14.00           |
| W1 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 161 R0000 | 1                            | 14.00           |
| W2 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 171 R0000 | 1                            | 14.00           |
| W3 (x100)                                   | 100                        | White | MC812PA | 1SNK 168 181 R0000 | 1                            | 14.00           |
| L1-L2-L3-N-PE (x20)                         | 100                        | White | MC812PA | 1SNK 169 001 R0000 | 1                            | 14.00           |
| U1-U2-U3-V1-V2-V3-W1-W2-W3 (x10) + U1 (x10) | 100                        | White | MC812PA | 1SNK 169 011 R0000 | 1                            | 14.00           |

All the technical data for UL/CSA standard and dimensions in inches are in *italics*.