



Declaration of Conformity, RoHS

This declaration of conformity is issued under the sole responsibility of the manufacturer

ABB STOTZ-KONTAKT GmbH
Eppelheimer Str. 82
D-69123 Heidelberg

Object of declaration

Interface relay and optocoupler, R600
RB...
OB...

Manufactured after
2016-04-15

The object of the declaration described above is in conformity with

DIRECTIVE 2011/65/EU OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL on the restriction of the use of certain hazardous substances in electrical and electronic equipment (recast) listed in Annex II, 8 June 2011

EN 50581:2012

ABB STOTZ-KONTAKT GmbH,
Heidelberg, April 15, 2016

Markus Klein
Local Product Group Manager

Frank Brenk
R&D / Technology Manager

Document No.: 1SVD982016-4400

ABB STOTZ KONTAKT GmbH



Addendum to Declaration of Conformity

No. 1SVD982016-4400

Products covered:

ABB Order Code	Type
1SNA206754R0000	BJ 612-20
1SNA290488R0100	BJ 612-10
1SNA645001R0300	RB121A 24vac/dc
1SNA645002R0400	RB121A 48-60vac/dc
1SNA645003R0500	RB121A 115vac/dc
1SNA645004R0400	RB121A 230vac/dc
1SNA645005R0700	RB121A 24vac/dc
1SNA645006R0000	RB121A 48-60vac/dc
1SNA645007R0100	RB121A 115vac/dc
1SNA645008R1200	RB121A 230vac/dc
1SNA645011R2400	RB121AR 230vac/dc
1SNA645012R2500	RB122A 24vac/dc
1SNA645013R2600	RB122A 230vac/dc
1SNA645014R2700	RB111A 24vac/dc
1SNA645016R2100	RB111A 115vac/dc
1SNA645017R2200	RB111A 230vac/dc
1SNA645018R0300	RB111AR 24vac/dc
1SNA645019R0400	RB101AR 24vac/dc
1SNA645020R0100	RB121A 60 à 230vac/dc
1SNA645021R2600	OBIC0100 24vdc
1SNA645022R2700	OBIC0100 115/230vac/dc
1SNA645024R2100	OB0C5000 24vdc
1SNA645025R2200	OB0C1500 24vac/dc
1SNA645026R2300	OB0C1000 230vac/dc
1SNA645027R2400	OBOA1000 24vdc
1SNA645028R0500	OBOA1000 230vac/dc
1SNA645029R0600	OBOA2000 24vdc
1SNA645034R2300	RB121 5vdc
1SNA645035R2400	RB121 12vdc
1SNA645036R2500	RB121 5vdc
1SNA645040R1500	RB122A 48-60vac/dc
1SNA645041R0200	RB122A 115vac/dc
1SNA645046R0700	RB121AR 115vac/dc
1SNA645047R0000	OBIC0100 5-12vdc
1SNA645049R1200	OBIC0100 48-60vac/dc
1SNA645050R1700	OB0C1000 5-12vdc
1SNA645051R0400	OB0C1000 24vdc
1SNA645053R0600	OB0C1000 48-60vac/dc
1SNA645054R0700	OB0C1000 115vac/dc
1SNA645058R1300	OB0C5000 115vac/dc
1SNA645059R1400	OB0C5000 230vac/dc
1SNA645061R0600	OBOA1000 48-60vac/dc
1SNA645062R0700	OBOA1000 115vac/dc
1SNA645071R0000	RB121 24vdc
1SNA645072R0000	RB121 Au 24vdc

ABB Order Code	Type
1SNA645073R0000	RB121 12vdc
1SNA645075R0000	RB121 Au 12vdc
1SNA645501R0500	RBR121A 24vac/dc
1SNA645502R0600	RBR121A 48-60vac/dc
1SNA645503R0700	RBR121A 115vac/dc
1SNA645504R0000	RBR121A 230vac/dc
1SNA645505R0100	RBR121A 24vac/dc
1SNA645506R0200	RBR121A 48-60vac/dc
1SNA645507R0300	RBR121A 115vac/dc
1SNA645508R1400	RBR121A 230vac/dc
1SNA645511R2600	RBR121AR 230vac/dc
1SNA645512R2700	RBR122A 24vac/dc
1SNA645513R2000	RBR122A 230vac/dc
1SNA645514R2100	RBR111A 24vac/dc
1SNA645518R0500	RBR111AR 24vac/dc
1SNA645519R0600	RBR101AR 24vac/dc
1SNA645520R0300	RBR121A 60 à 230vac/dc
1SNA645521R2000	OB0C0100 24vdc
1SNA645522R2100	OB0C0100 115/230vac/dc
1SNA645524R2300	OB0C5000 24vdc
1SNA645525R2400	OB0C1500 24vac/dc
1SNA645526R2500	OB0C1000 230vac/dc
1SNA645527R2600	OB0A1000 24vdc
1SNA645528R0700	OB0A1000 230vac/dc
1SNA645529R0000	OB0A2000 24vdc
1SNA645534R2500	RBR121 5vdc
1SNA645535R2600	RBR121 12vdc
1SNA645536R2700	RBR121 5vdc
1SNA645540R1700	RBR122A 48-60vac/dc
1SNA645541R0400	RBR122A 115vac/dc
1SNA645546R0100	RBR121AR 115vac/dc
1SNA645547R0200	OB0C0100 5-12vdc
1SNA645549R1400	OB0C0100 48-60vac/dc
1SNA645550R1100	OB0C1000 5-12vdc
1SNA645551R0600	OB0C1000 24vdc
1SNA645553R0000	OB0C1000 48-60vac/dc
1SNA645554R0100	OB0C1000 115vac/dc
1SNA645558R1500	OB0C5000 115vac/dc
1SNA645559R1600	OB0C5000 230vac/dc
1SNA645561R0000	OB0A1000 48-60vac/dc
1SNA645562R0100	OB0A1000 115vac/dc
1SNA645571R0000	RBR121 24vdc
1SNA645572R0000	RBR121 Au 24vdc
1SNA645573R0000	RBR121 12vdc
1SNA645575R0000	RBR121 Au 12vdc



Addendum to Declaration of Conformity

No. 1SVD982016-4400

Products covered:

ABB Order Code	Type
1SNA206754R0000	BJ 612-20
1SNA290488R0100	BJ 612-10
1SNA645001R0300	RB121-24VUC
1SNA645002R0400	RB121-48-60VUC
1SNA645003R0500	RB121-115VUC
1SNA645004R0400	RB121-230VUC
1SNA645005R0700	RB121G-24VUC
1SNA645006R0000	RB121G-48-60VUC
1SNA645007R0100	RB121G-115VUC
1SNA645008R1200	RB121G-230VUC
1SNA645011R2400	RB121R-230VUC
1SNA645012R2500	RB122G-24VUC
1SNA645013R2600	RB122G-230VUC
1SNA645014R2700	RB111-24VUC
1SNA645016R2100	RB111-115VUC
1SNA645017R2200	RB111-230VUC
1SNA645018R0300	RB111R-24VUC
1SNA645019R0400	RB101R-24VUC
1SNA645020R0100	RB121-60-230VUC
1SNA645021R2600	OBIC0100-24VDC
1SNA645022R2700	OBIC0100-115-230
1SNA645024R2100	OB0C 5000-24VDC
1SNA645025R2200	OB0C2000-24VUC
1SNA645026R2300	OB0C2000-230VUC
1SNA645027R2400	OBOA1000-24VDC
1SNA645028R0500	OBOA1000-230VUC
1SNA645029R0600	OBOA2000-24VDC
1SNA645034R2300	RB121P-5VDC
1SNA645035R2400	RB121P-12VDC
1SNA645036R2500	RB121PG-5VDC
1SNA645040R1500	RB122G-48-60VUC
1SNA645041R0200	RB122G-115VUC
1SNA645046R0700	RB121R-115VUC
1SNA645047R0000	OBIC0100-5-12VDC
1SNA645049R1200	OBIC0100-48-60VUC
1SNA645050R1700	OB0C2000-5-12VDC
1SNA645051R0400	OB0C2000-24VDC
1SNA645053R0600	OB0C2000-48-60VUC
1SNA645054R0700	OB0C2000-115VUC
1SNA645058R1300	OB0C5000-115VUC
1SNA645059R1400	OB0C5000-230VUC
1SNA645061R0600	OBOA1000-48-60VUC
1SNA645062R0700	OBOA1000-115VUC
1SNA645071R0000	RB121-24VDC
1SNA645072R0000	RB121G-24VDC

ABB Order Code	Type
1SNA645073R0000	RB121-12VDC
1SNA645075R0000	RB121G-12VDC
1SNA645501R0500	RBR121-24VUC
1SNA645502R0600	RBR121-48-60VUC
1SNA645503R0700	RBR121-115VUC
1SNA645504R0000	RBR121-230VUC
1SNA645505R0100	RBR121G-24VUC
1SNA645506R0200	RBR121G-48-60VUC
1SNA645507R0300	RBR121G-115VUC
1SNA645508R1400	RBR121G-230VUC
1SNA645511R2600	RBR121R-230VUC
1SNA645512R2700	RBR122G-24VUC
1SNA645513R2000	RBR122G-230VUC
1SNA645514R2100	RBR111-24VUC
1SNA645518R0500	RBR111R-24VUC
1SNA645519R0600	RBR101R-24VUC
1SNA645520R0300	RBR121-60-230VUC
1SNA645521R2000	OBRIC0100-24VDC
1SNA645522R2100	OBRIC0100-115-230
1SNA645524R2300	OBROC5000-24VDC
1SNA645525R2400	OBROC2000-24VUC
1SNA645526R2500	OBROC2000-230VUC
1SNA645527R2600	OBROA1000-24VDC
1SNA645528R0700	OBROA1000-230VUC
1SNA645529R0000	OBROA2000-24VDC
1SNA645534R2500	RBR121P-5VDC
1SNA645535R2600	RBR121P-12VDC
1SNA645536R2700	RBR121PG-5VDC
1SNA645540R1700	RBR122G-48-60VUC
1SNA645541R0400	RBR122G-115VUC
1SNA645546R0100	RBR121R-115VUC
1SNA645547R0200	OBRIC0100-5-12VDC
1SNA645549R1400	OBRIC0100-48-60VUC
1SNA645550R1100	OBROC2000-5-12VDC
1SNA645551R0600	OBROC2000-24VDC
1SNA645553R0000	OBROC2000-48-60VUC
1SNA645554R0100	OBROC2000-115VUC
1SNA645558R1500	OBROC5000-115VUC
1SNA645559R1600	OBROC5000-230VUC
1SNA645561R0000	OBROA1000-48-60VUC
1SNA645562R0100	OBROA1000-115VUC
1SNA645571R0000	RBR121-24VDC
1SNA645572R0000	RBR121G-24VDC
1SNA645573R0000	RBR121-12VDC
1SNA645575R0000	RBR121G-12VDC