



中国国家强制性产品认证证书

证书编号: 2010010307445320

委托人名称、地址

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

生产者(制造商)名称、地址

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

生产企业名称、地址

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

产品名称和系列、规格、型号

塑料外壳式断路器

S20..P, S20..U, S20..UP; 型号参数详见附录

产品标准和技术要求

GB 14048.2-2008

上述产品符合强制性产品认证实施规则
CNCA-C03-02: 2014的要求, 特发此证。

发证日期: 2015年08月05日

有效期至: 2020年08月05日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2010年11月23日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>



Q 1206337



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2010010307445320

NAME AND ADDRESS OF THE APPLICANT

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

NAME AND ADDRESS OF THE MANUFACTURER

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

NAME AND ADDRESS OF THE FACTORY

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

NAME, MODEL AND SPECIFICATION

Moulded Case Circuit-breaker
S20..P, S20..U, S20..UP; See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.2-2008

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification (REF NO. CNCA-C03-02:2014).

Date of issue: Aug. 05, 2015 Date of expiry: Aug. 05, 2020

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Nov. 23, 2010

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China

<http://www.cqc.com.cn>



Q 1206337



中国国家强制性产品认证证书

附录:

第 1 页 共 2 页

证书编号: 2010010307445320

纸号: 1206337

S20..P, S20..U, S20..UP

Ue: AC230/400V (1P), AC230V (1P+N), AC400V (2P, 3P, 3P+N, 4P);

In:

S20..P, S20..U: K 型: 0.2A, 0.3A, 0.5A, 0.75A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A*;

Z 型: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 16A, 20A, 25A, 32A, 40A, 50A, 63A*;

*仅适用于极数为 1P, 1P+N, 2P。

S20..UP: K 型: 0.2A, 0.3A, 0.5A, 0.75A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A;

Z 型: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 16A, 20A, 25A;

过电流脱扣器类型: 热磁式;

Ics: 12.5kA ($I_n \leq 25A$); 11.25kA ($I_n=32A, 40A$); 7.5kA ($I_n=50A, 63A$);

Icu: 25kA ($I_n \leq 25A$); 15kA ($I_n > 25A$);

使用类别: A 类; 1P、1P+N、2P、3P、3P+N、4P

注: 此附录与证书同时使用时有效。



主 任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 2 页 共 2 页

证书编号: 2010010307445320

纸号: 1206337

型号的解释:

$\frac{S20}{I} \frac{1}{II} \frac{P}{I} \frac{-NA}{III} \frac{K}{IV} \frac{10}{V}$

- I: S20 ..P - Basic Type 基本型号
S20 ..U - Same as basic type, just with small barriers
与基本型号一样, 仅边上有小的栅栏
S20 ..UP - Same as basic type, just with large barriers
与基本型号一样, 仅边上有大的栅栏

II: Number of Pole 极数

- 1- 1 Pole 1极
2- 2 Pole 2极
3- 3 Pole 3极
4- 4 Pole 4极

III: blank: without N Pole 空缺: 没有N极
-NA: with N Pole NA: 具有N极

IV: Instantaneous Tripping Type K, Z 瞬时脱扣类型 K, Z

- K: Short circuit tripping 10In - 14In 短路脱扣倍数 10In - 14In
Z: Short circuit tripping 2In - 3 In 短路脱扣倍数 2In - 3 In

V: Rated Current 额定电流

- K: 0,2 - 63A, Z: 0,2 - 63A for S20..P and S20..U 针对 S20..P, S20..U 型号
K: 0,2 - 25A, Z: 0,2 - 25A for S20..UP 针对 S20..UP 型号

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国 · 北京 · 南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

