



中国国家强制性产品认证证书

证书编号: 2012010307538957

委托人名称、地址

ABB-Stotz-Kontakt GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, 德国

生产者(制造商)名称、地址

ABB-Stotz-Kontakt GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, 德国

生产企业名称、地址

北京ABB低压电器有限公司
北京市北京经济技术开发区康定街17号

产品名称和系列、规格、型号

微型断路器

SH20. L; Ue: AC230/400V (1P), AC230V (1P+N), AC400V (2P, 3P, 3P+N, 4P); B: In:
6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A; C: In: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A,
13A, 16A, 20A, 25A, 32A, 40A; 瞬时脱扣类型: B, C型; Icn=Ics: 4.5kA; 1P, 1P+N (N极可开
闭), 2P, 3P, 3P+N (N极可开闭), 4P; 型号详见附件

产品标准和技术要求

GB 10963.1-2005

上述产品符合强制性产品认证实施规则

CNCA-C03-02: 2014的要求, 特发此证。

发证日期: 2017年04月25日

有效期至: 2022年04月25日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书, 证书首次颁发日期: 2012年04月25日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>



Q 1675679



中国国家强制性产品认证证书

附录:

第 1 页 共 1 页

证书编号: 2012010307538957

纸号: 1675679

型号的解释:

SH20	1	L	-NA	C	□
1	2	3	4	5	6

1——产品系列:SH20

2——保护极数, 1-1pole, 2-2pole, 3-pole, 4-4pole

3——分断能力, L-4.5 kA

4——无中性极, NA 为带有中性极

5——瞬时脱扣特性, B-B 特性; C-C 特性;

6——额定电流, B: 6 A; 8 A; 10 A; 13 A; 16 A; 20 A; 25 A; 32 A, 40 A

C: 0,5 A; 1 A; 1,6 A; 2 A; 3 A; 4 A; 6 A; 8 A; 10 A; 13 A; 16 A; 20 A; 25 A; 32 A, 40 A

注: 此附录与证书同时使用时有效。



主 任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2012010307538957

NAME AND ADDRESS OF THE APPLICANT

ABB-Stotz-Kontakt GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

NAME AND ADDRESS OF THE MANUFACTURER

ABB-Stotz-Kontakt GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

NAME AND ADDRESS OF THE FACTORY

ABB LV Installation Materials Co. Ltd., Beijing
No.17 Kangding Street, Beijing Economic-Technological Development Area
100176, P.R.China

NAME, MODEL AND SPECIFICATION

Miniature Circuit-breaker

SH20. L; Ue: AC230/400V (1P), AC230V (1P+N), AC400V (2P, 3P, 3P+N, 4P); B: In:
6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A; C: In: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A,
13A, 16A, 20A, 25A, 32A, 40A; Type B, Type C; Icn=Ics: 4.5kA; 1P, 1P+N (Switched
neutral pole), 2P, 3P, 3P+N (Switched neutral pole), 4P; See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 10963.1-2005

This is to certify that the above mentioned products have met the
requirements of implementation rules for compulsory certification (REF
NO. CNCA-C03-02:2014).

Date of issue: Apr.25, 2017 Date of expiry: Apr.25, 2022

Validity of this certificate is subject to positive result of the regular
follow up inspection by issuing certification body until the expiry date.

Date of original certification: Apr.25, 2012

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China

<http://www.cqc.com.cn>



Q 1675679