

Accessories for enclosures SDC and SDCM

3



SLUS 48-98

Door with outlet opening at the bottom for temporary connections. The outlet opening measures 60 mm x 240 mm.



GOLV-S 48-98

Complete foundation when the enclosure is installed on a floor.



BPF-S 48-98

Base plate with 4, 6 or 10 FL 21 flange openings.



MARK-S 48-98

MARK-S 73-98 LD

Complete foundation when the enclosure is installed in the ground.



VF-S 30

Wall bracket. Two required per cabinet.
Gives 30 mm free space behind the cabinet.

Designation	ID No.	Fits enclosure	Dimensions			Weight
			Height	Width	Depth	
			mm			kg/pcs
SLUS 48	2CGX0 53310666	SDC/SDCM 48	288	626	22	5
SLUS 73	2CGX0 53310684	SDC/SDCM 73	288	940	22	7.5
SLUS 98	2CGX0 53310668	SDC/SDCM 98	288	1254	22	10.0
MARK-S 48	2CGX0 63300439	SDC/SDCM 48	940	672	303	30
GOLV-S 48	2CGX0 63300441	SDC/SDCM 48	400	672	303	23
GOLV-S 73	2CGX0 63300550	SDC/SDCM 73	400	986	303	30
GOLV-S 98	2CGX0 63300442	SDC/SDCM 98	400	1300	303	36
BPF-S 48	2CGX0 53310629	SDC/SDCM 48	30	672	282	4
BPF-S 73	2CGX0 53310682	SDC/SDCM 73	30	986	282	5
BPF-S 98	2CGX0 53310630	SDC/SDCM 98	30	1300	282	6
MARK-S 73	2CGX0 63300549	SDC/SDCM 73	940	986	303	36
MARK-S 73 LD	2CGX0 63300636	SDC 73 LD	940	986	233	34
MARK-S 98	2CGX0 63300440	SDC/SDCM 98	940	1300	303	42
MARK-S 98 LD	2CGX0 63300572	SDC 98 LD	940	1300	233	40
VF-S 30	2CGX0 53310643	SDC/SDCM	500	40	40	0.5