



**RMD<sup>fsd</sup>**

Cost effective solution for projects with very constant ore grade throughout life cycle of the mine or for small ball mills that do not require variable speed.



**RMD<sup>vsd</sup>**

Variable speed solution, including softstarting and optimum torque control for entire speed range. Suitable for any kind of grinding mill.



**RMD<sup>plus</sup>**

Full variable speed solution, additionally including mill application features providing highest operational flexibility and optimizing maintenance actions.



**SmartMill**

Combines all features from RMD<sup>plus</sup> with the advanced process control, providing the ultimate control strategy. Ideal to increase productivity and energy efficiency.

fsd: fixed speed drive, vsd: variable speed drive