

Flood light

Flood light premium weatherproof



Image indicative only

Range


Non-standard range

Product group

Flood light

Features

- 3 year warranty
- Weatherproof rating IP65
- Adjustable lamp heads in azimuth and elevation to customise light coverage



Standard products

Catalogue no.	Description
WPFL212	Premium flood light weatherproof 2x12W non-maintained
WPFL235	Premium flood light weatherproof 2x35W non-maintained

Spare parts

Catalogue no.	Description
14-00061	Battery sealed lead acid 12V 7Ah (suits 12W)
14-00063	Battery sealed lead acid 12V 10Ah (suits 35W)

Dimensions

Catalogue no.	Length	Width	Height (excl. lamps)	Height (incl. lamps)
WPFL212	360mm	170mm	270mm	400mm
WPFL235	360mm	170mm	360mm	500mm

Construction

Part	Construction
Base and cover	GRP
Lamp	Halogen 12V 12W (suits 12W) Halogen 12V 35W (suits 35W)
Housing	Chrome plated aluminium
Lens	Glass

Power consumption

Model	Power consumption
Standard	240Vac 50Hz 0.13A

Note: Designed to comply with AS2293 and meet relevant Australian EMC standards

For more information please contact:

ABB Australia Pty Limited

Phone: 1300 666 595

Fax: 1300 666 594

E-mail: AU-ABB-Stanilite@abb.com

www.stanilite.com.au

Note: We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilisation of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright © 2016 ABB
All rights reserved