



中国国家强制性产品认证证书

证书编号: 2007010307238782

申请人名称及地址

ABB Switzerland Ltd CMC Low Voltage Products
Fulachstrasse 150, CH-8201 Schaffhausen, Switzerland

商标: ABB

制造商名称及地址

ABB Switzerland Ltd CMC Low Voltage Products
Fulachstrasse 150, CH-8201 Schaffhausen, Switzerland

生产企业名称及地址

ABB Switzerland Ltd CMC Low Voltage Products
Fulachstrasse 150, CH-8201 Schaffhausen, Switzerland

产品名称和系列、规格、型号

塑料外壳式断路器

S400 系列, S450 系列 (详见参数附件); U_e =AC230/254V (1P, 1P+N), AC400/440V (2P, 3P, 3P+N);
In: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A; AC230V/400V: I_{cs} =50kA
($I_n=0.5\sim 2A$), 15kA ($I_n=3\sim 20A$), 7.5kA ($I_n=25\sim 63A$); I_{cu} =50kA ($I_n=0.5\sim 2A$), 25kA ($I_n=3\sim 20A$), 10kA
($I_n=25\sim 63A$); AC254V/440V: I_{cs} =15kA ($I_n=0.5\sim 2A$), 6kA ($I_n=3\sim 10A$), 3kA ($I_n=13\sim 63A$); I_{cu} =15kA
($I_n=0.5\sim 2A$), 10kA ($I_n=3\sim 10A$), 6kA ($I_n=13\sim 63A$); 使用类别: A; 1P, 1P+N, 2P, 3P, 3P+N

产品标准和技术要求

GB14048.2-2001

上述产品符合强制性产品认证实施规则的要求, 特发此证。

发证日期: 2007年07月03日

本证书的有效性依据发证机构的定期监督获得保持。



主任:

李怀林

中国质量认证中心

中国·北京·南四环西路188号9区 100070

网址: www.cqc.com.cn



A 0376009



中国国家强制性产品认证证书

附录:

共 1 页, 第 1 页

证书编号: 2007010307238782

纸号: 376009

S400 系列

S401M-C..,S402M-C..,S403M-C..,S401M-C..NP,S403M-C..NP

S401M-K..,S402M-K..,S403M-K..,S401M-K..NP,S403M-K..NP

S450 系列

S451M-C..,S452M-C..,S453M-C..,S453M-C..NP

S451M-K..,S452M-K..,S453M-K..,S453M-K..NP

型号中的..表示电流: 0.5, 1, 1.6, 2, 3, 4, 6, 8, 10, 13, 16, 20, 25, 32, 40, 50, 63A

注: 此附录与证书同时使用时有效。



主 任:

李怀林





CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2007010307238782

NAME AND ADDRESS OF THE APPLICANT

ABB Switzerland Ltd CMC Low Voltage Products
Fulachstrasse 150, CH-8201 Schaffhausen, Switzerland

TRADE MARK: ABB

NAME AND ADDRESS OF THE MANUFACTURER

ABB Switzerland Ltd CMC Low Voltage Products
Fulachstrasse 150, CH-8201 Schaffhausen, Switzerland

NAME AND ADDRESS OF THE FACTORY

ABB Switzerland Ltd CMC Low Voltage Products
Fulachstrasse 150, CH-8201 Schaffhausen, Switzerland

NAME, MODEL AND SPECIFICATION

Moulded Case Circuit-breaker

S400 Series, S450 Series (See the Appendix): $U_e = AC230/254V(1P, 1P+N), AC400/440V$
(2P, 3P, 3P+N); $I_n: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A$;
AC230V/400V: $I_{cs} = 50kA(I_n = 0.5 \sim 2A), 15kA(I_n = 3 \sim 20A), 7.5kA(I_n = 25 \sim 63A)$; $I_{cu} = 50kA$
($I_n = 0.5 \sim 2A$), $25kA(I_n = 3 \sim 20A), 10kA(I_n = 25 \sim 63A)$; AC254V/440V: $I_{cs} = 15kA(I_n = 0.5 \sim 2A), 6kA$
($I_n = 3 \sim 10A$), $3kA(I_n = 13 \sim 63A)$; $I_{cu} = 15kA(I_n = 0.5 \sim 2A), 10kA(I_n = 3 \sim 10A), 6kA(I_n = 13 \sim 63A)$;
Utilization Category: A; 1P, 1P+N, 2P, 3P, 3P+N

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB14048.2-2001

THIS IS TO CERTIFY THAT THE ABOVE MENTIONED PRODUCTS HAVE QUALIFIED FOR THE
REQUIREMENTS OF IMPLEMENTATION RULES FOR COMPULSORY CERTIFICATION

ISSUED DATE: Jul. 03, 2007

THE VALIDITY OF THE CERTIFICATE DEPEND ON THE FOLLOW UP INSPECTION BY THE
CERTIFICATION BODY AT REGULAR INTERVALS



President:

李怀林

Li Huailin

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China

<http://www.cqc.com.cn>



A 0376009



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

Appendix:

Page 1 of 1

No.: 2007010307238782

Paper: 376009

S400 Series

S401M-C..., S402M-C..., S403M-C..., S401M-C..NP, S403M-C..NP

S401M-K..., S402M-K..., S403M-K..., S401M-K..NP, S403M-K..NP

S450 Series

S451M-C..., S452M-C..., S453M-C..., S453M-C..NP

S451M-K..., S452M-K..., S453M-K..., S453M-K..NP

“..” for In: 0.5, 1, 1.6, 2, 3, 4, 6, 8, 10, 13, 16, 20, 25, 32, 40, 50, 63A

NOTE:

This appendix forms a part of the certificate for china compulsory product certification, and must be used together with the certification.



President:

李怀林

