Tmax molded case circuit-breakers Tmax T5

Compliance with Standards
UL489
CSA C22.2 No. 5.1
IEC 60947-2
EC Directive: - "Low voltage directives" (LVD) no. 73/23
EEC
 "Electromagnetic compatibility directive"

(EMC) no. 89/336 EEC



Type of circuit-breaker						Tmax T5					
Frame					400 / 600 (1)						
Rated ultima	ate short-circuit bre	aking capacity,	lcu		N	S	Н	L	٧		
	(AC) 50-60 Hz 2	.		[kA]	65	100	150	200	200		
	(AC) 50-60 Hz 2	· · · · · · · · · • · · · · · · · · · ·		[kA]	_	-	-	-	_		
	(AC) 50-60 Hz 3		.	[kA]	<u> —</u>	_	_				
	(AC) 50-60 Hz 4		·····•	[kA]	25	35	65	100	150		
	(AC) 50-60 Hz 6	· · · · · · · · · • · · · · · · · · · ·	.	[kA]							
	(AC) 50-60 Hz 6	· · · · · · · · · · • · · · · · · · · ·	· · · · · · · · · · · · · · · · · · ·	[kA]	18	25	35	65	100		
	(DC) 250 V-2 po			[kA]		-	-	-	-		
	(DC) 500 V-2 po		·····•	[kA]	25	35	50	65	100		
	(DC) 500 V-3 po			[kA]	16	_ 25	- 35	- 50	- 65		
(DC) 600 V-3 poles in series [kA] [16	25	33	: 50	65			
mp units.	T fixed M fixed (10vIn) TMF									
	T fixed, M fixed (10xln) TMF T adj., M fixed (10xln) TMD										
ThermomagneticT adj., M adj. (510xln) TMA					•						
	T adj., M fixed (3		·····•			•••••		•	• · · · · · · · · · · · · · · · · · · ·		
	T adj., M adj. (2.5					•••••		• • • • • • • • • • • • • • • • • • • •	• · · · · · · · · · · · · · · · · · · ·		
Magnetic only M adjustable (612xln) MA				•••••		•••••	• · · · · · · · · · · · · · · · · · · ·				
	PR221DS						•	•	•		
Electronic	PR222DS/P				•						
<u></u>	PR222DS/PD-A		· · · · · · · · · · · · · · · · · · ·		•				*		
Versions							F-P-W		•		
	Fixed (F)				F-P-V F-FC C		-FC Cu	Al			
Terminals	Plug-in (P)	Plug-in (P)					F-FC CuAl EF-ES-R				
	Withdrawable (W)				F-FC CuAl EF-ES-R						
Fixing on DIN	l rail		•				_		•		
Mechanical li	Mechanical life [No. operation			oper.]	20000/120						
Electrical life	(at 415 V)	[No. operatio	ns /hourly	oper.]	oper.] 7000/60 (5000/60 for 600A)				0A)		
•••••			W	[mm]			140/184	4	• · · · · · · · · · · · · · · · · · · ·		
Basic fixed d	Basic fixed dimensions		D	[mm]	103.5/103.5						
<u></u>			Н	[mm]			205/20	5	•		
Weights	fixed	3/4 pole		[kg] 3.25/4.15							
	plug-in	3/4 pole		[kg] 5.15/6.65				• · · · · · · · · · · · · · · · · · · ·			
	Withdrawable	3/4 pole		[kg]	5.4/6.9						

(1) T5 600 only available with electronic trip unit and 3P

Tmax molded case circuit-breakers Dimensions T5 series

112.5

4.43

103.5

4.07


107 *4.21*

> 139 *5.47*

59.5 2.34

0.08


Overall dimensions T5



- Overall dimensions with cabled accessories mounted (SOR-C, UVR-C, RC222)

 Overall dimensions with
- 2 Overall dimensions with cabled auxiliary contacts mounted (only 3Q 1SY)

Drilling template for support sheet



Contact us

Canada

ABB Inc.
Low Voltage Products
2117 – 32nd Avenue
Lachine, QC, CANADA H8T 3J1
Tel: 514-420-3100

Tel.: 514-420-3100 Fax: 514-420-3137

Toll Free: 1-800-567-0283

www.abb.ca

While all care has been taken to ensure that the information contained in this publication is correct, no responsibility can be accepted for any inaccuracy. The Company reserves the right to alter or modify the information contained herein at any time in the light of technical or other developments. Technical specifications are valid under normal operating conditions only. The Company does not accept any responsibility for any misuse of the product and cannot be held liable for indirect or consequential damages.

© Copyright 2011 ABB Inc. All rights reserved.



