
 TECHNICAL DATA SHEET

Terminals, piggy back disconnects

Nylon-insulated, double crimp

Spec-Kon®



Nylon-insulated piggy back disconnects for wire termination of copper conductors ranging from 0.5mm² to 6mm²

Certifications / Standards:


Features:

- Easy entry double crimp
- Corrosive resistant plating
- Color coded to wire size range

Maximum rating:

- 105°C Max
- 600 volts
- Copper conductors only

Application:

- ERG9003

Conforms to:

- IEC 60352-2 & IEC 61210

Materials / Finishes:

- Brass disconnect
- Electro-Tin plated
- Nylon insulation

Product selection

Drawing	Part no:	Wire size range (mm ²)	Color	Tab size (mm)	Dimensions (mm)				Crimping tool
					L	F	W	D	
	PBD1.5-638NDC	0.5-1.5	Red	0.8x6.35	6.7	22	8	3.8	ERG9003
	PBD2.5-638NDC	1.5-2.5	Blue	0.8x6.35	6.7	22	8	4.7	
	PBD6-638NDC	4-6	Yellow	0.8x6.35	6.7	25.2	8	6.2	

Note: Products must be installed in accordance with applicable national and local electrical codes.