

TECHNICAL DATA SHEET

Terminals, receptacle disconnects

Vinyl-insulated, double crimp

Spec-Kon®



Features:

- · Easy entry double crimp
- · Corrosive resistant plating
- Color coded to wire size range

Maximum rating:

- 75°C Max
- 600 volts
- · Copper conductors only

Vinyl-insulated receptacle disconnects for wire termination of copper conductors ranging from 0.5mm² to 6mm²

Certifications / Standards:



Application tool:

• ERG9003

Conforms to:

• IEC 60352-2

Materials / Finishes:

- Brass disconnect
- · Electro-Tin plated
- · Vinyl insulation

Drawing	Part no:	Wire size range (mm²)	Color	Dimensions (mm)				Crimping tool
				L	F	w	D	
	RD1.5-39VDC	0.5-1.5	Red 📕	19.8	7.3	3.9	3.3	ERG9003
	RD2.5-39VDC	1.5-2.5	Blue 📕	19.8	7.3	3.9	4.1	
	RD2.5-49VDC	1.5-2.5	Blue 📕	21.5	8.5	4.9	4.1	
	RD6-49VDC	4.0-6.0	Yellow	24.5	8.5	4.9	5.6	

 $Note: Products\ must\ be\ installed\ in\ accordance\ with\ applicable\ national\ and\ local\ electrical\ codes.$

tnb.abb.com (US/Latin America) tnb.ca.abb.com (Canada) abb.com We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction – in whole or in part – is forbidden without prior written consent of ABB.

Copyright© 2019 ABB. All rights reserved.