
Ligne de rub: Rubrique No Ligne de pos: Quantite	Position	Texte	Numero d'identification	Masse unitaire



Dimensions 1-pole CE5 on	A	B	C	D
AF09/12/16..-30-xx 1-stack AF09/16..-40/22-00 NF..E 1-stack	91,5	103,5	7,5	45
AF26/30/38..-30-00	100,5	112,5	7,5	45
AF26/38..-40/22-00	115,5	127,5	7,5	45
AF40/52/65-30-00	125	137	12,5	55
AF40/52/65-40/22-00	128	140	20	70
AF80..96-30-00	130	142	20	70
AF80..96-40/22-00	130	142	30	90

Tolerances generales selon ISO 2768
Degre de precision
f m c v H K L
Tolerances generales sur pieces moulees selon DIN 16901 (FPTC 407364)
130 140

Ce document,propriete exclusive de notre Societe, est strictement confidentiel. Il ne peut etre communique, copie ou reproduit sans son autorisation ecrite.

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express autority is strictly forbidden.

Modif.	Version	DESCRIPTION	DATE	N° EO	Author	control
	A	Creation	13/03/14	501811	JP.R	V.P

First EO 501811
Echelle 1
Control V. Parniere
Author JP. Reverdy
Nb.Page 1

ABB FRANCE | Owner : Design Department | Running Number | Doc | Format | Type | N° Page | Version

Title AF09..96.. + CE5-10/01
ENCOMBREMENT / DIMENSIONS

1SBB505149 | D | 4 | 5 | 01 | A