中国国家强制性产品认证证书

证书编号：2013010304604054

委托人名称、地址

ABB AB, Control Products
Motorgrand 20, 72161 Vasteras, Sweden

生产者（制造商）名称、地址

ABB AB, Control Products
Motorgrand 20, 72161 Vasteras, Sweden

生产企业名称、地址

ABB AB, Control Products
Motorgrand 20, 72161 Vasteras, Sweden

产品名称和系列、规格、型号

接触器

AF2650-30-*-*, AF2650T-30-*-*, AF2850-30-*-*, AF2850T-30-*-*; Ui:1000V; Uimp: 8kV; Ith: 2650A(AF2650*),2850A(AF2850*); AC-1:Ue/Ie:1000V/2650A(AF2650*),1000V/2850A(AF2850*); Us: AF2650/AF2850: 100-250VAC/DC,50Hz/60Hz, AF2650T/ AF2850T: 230-240VAC,50Hz/60Hz; 极数：3P；配用辅助触头： CAL18-11,CAL18-11B,CAL18-11RT:1NO1NC,2NO2NC;Ith：16A； AC-15：Ue/Ie：24-127V/6A，220-240V/4A，280-440V/3A，500-690V/2A； DC-13：Ue/Ie：24V/6A，48V/2.8A，72V/1A，125V/0.55A，250V/0.3A; CEL18-10,CEL18-01: 1NO,1NC; Ith：0.1A; AC-14:Ue/Ie:24-125V/0.1A,DC-12:Ue/Ie:24-110V/0.1A；型号解释见附件

产品标准和技术要求

GB/T14048.4-2010

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求，特发此证。

发证日期：2018 年 08 月 31 日　　有效期至：2023 年 02 月 01 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书，证书首次颁发日期：2013 年 03 月 21 日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询

主　任：

中国质量认证中心

http://www.cqc.com.cn　　中国・北京・南四环西路188号9区 100070　　电话：+86 10 83886666

Q 2031327

CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2013010304604054

NAME AND ADDRESS OF THE APPLICANT

ABB AB, Control Products

Motorgrand 20, 72161 Vasteras, Sweden

NAME AND ADDRESS OF THE MANUFACTURER

ABB AB, Control Products

Motorgrand 20, 72161 Vasteras, Sweden

NAME AND ADDRESS OF THE FACTORY

ABB AB, Control Products

Motorgrand 20, 72161 Vasteras, Sweden

PRODUCT NAME, MODEL AND SPECIFICATION

Contactor

AF2650-30-*-*, AF2650T-30-*-*, AF2850-30-*-*, AF2850T-30-*-*: Ui:1000V; Uimp: 8kV; Ith: 2650A(AF2650*),2850A(AF2850*); AC-1:Ue/Ie:1000V/2650A(AF2650*),1000V/2850A(AF2850*); Us: AF2650/AF2850: 100-250VAC/DC,50Hz/60Hz, AF2650T/ AF2850T: 230-240VAC,50Hz/60Hz; Poles: 3P; Attached Auxiliary Contacts: CAL18-11,CAL18-11B,CAL18-11RT:1NO1NC,2NO2NC;Ith: 16A; AC-15: Ue/Ie: 24-127V/6A, 220-240V/4A, 280-440V/3A, 500-690V/2A; DC-13: Ue/Ie: 24V/6A, 48V/2.8A, 72V/1A, 125V/0.55A, 250V/0.3A; CEL18-10,CEL18-01: 1NO,1NC; Ith: 0.1A; AC-14:Ue/Ie:24-125V/0.1A,DC-12:Ue/Ie:24-110V/0.1A

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T14048.4-2010

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO.CNCA-C03-02:2014).

Valid from: Aug.31,2018 **Valid until:** Feb.01,2023

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Mar.21,2013

The certificate information is available through CNCA's website: www.cnca.gov.cn

President: Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

http://www.cqc.com.cn Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China Tel: +86 10 83886666

Q 2031327

中国国家强制性产品认证证书

附　　录

证书编号：2013010304604054　　纸　号：2031327

型号的解释：

AF2650　　-30　-11　-70
-1　　-2　-3　-4

1 = Name of series and size of contactor
AF2650　= Basic model
AF2650T　= Basic model with delayed drop-out
AF2850　= Basic model
AF2850T　= Basic model with delayed drop-out

2: Number of main contacts
30　= 3 NO- and 0 NC-contacts

3: Number of NO and NC auxiliary contacts (CAL18-11, CEL18-01 or CEL18-10)
00　= without auxiliary contact
11　= 1 NO- and 1 NC-contacts (side mounted CAL18-11)
22　= 2 NO- and 2 NC-contacts (side mounted, 2 pieces CAL18-11)
01　= 0 NO- and 1 NC-contacts (side-mounted CEL18-01)
10　= 1 NO- and 0 NC-contacts (side-mounted CEL18-10)

4: Control supply voltage code
70: Us = 100-250V a.c./d.c. with PLC-control
91: Us = 230-240V ac (only for T-version)

注：此附录与证书同时使用时有效。

主　任：

中国质量认证中心