中国国家强制性产品认证证书

证书编号：2013010307600255

委托人名称、地址

ABB Stotz-Kontakt GmbH

Eppelheimer Strasse 82 69123 Heidelberg Germany

生产者（制造商）名称、地址

ABB Stotz-Kontakt GmbH

Eppelheimer Strasse 82 69123 Heidelberg Germany

生产企业名称、地址

ABB Stotz-Kontakt GmbH

Eppelheimer Strasse 82 69123 Heidelberg Germany

产品名称和系列、规格、型号

用于交流和直流的断路器

S20...UC(型号解释详见附件); Ue:AC230/400V,DC220V(1P),AC400V(2P,3P,4P),DC440V(2P); In(B型):6A,10A,13A,16A,20A,25A,32A,40A,50A,63A; In(C型):0.5A,1A,1.6A,2A,3A,4A,6A,8A,10A,13A,16A,20A,25A,32A, 40A,50A,63A;瞬时脱扣类型:B型,C型;Icn=10000A;Ics=7500A; 1P,2P,3P,4P

产品标准和技术要求

GB/T10963.1-2005;GB/T10963.2-2008

上述产品符合强制性产品认证实施规则 CNCA-C03-02:2014 的要求，特发此证。

发证日期：2018 年 02 月 01 日 有效期至：2023 年 02 月 01 日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书，证书首次颁发日期：2013 年 03 月 01 日

本证书的相关信息可通过国家认监委网站 www.cnca.gov.cn 查询

主 任：

中国质量认证中心

Q 1893412

CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

CERTIFICATE NO.: 2013010307600255

NAME AND ADDRESS OF THE APPLICANT

ABB Stotz-Kontakt GmbH

Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND ADDRESS OF THE MANUFACTURER

ABB Stotz-Kontakt GmbH

Eppelheimer Strasse 82 69123 Heidelberg Germany

NAME AND ADDRESS OF THE FACTORY

ABB Stotz-Kontakt GmbH

Eppelheimer Strasse 82 69123 Heidelberg Germany

PRODUCT NAME, MODEL AND SPECIFICATION

circuit-breakers for AC and DC operation

S20...UC; Ue:AC230/400V,DC220V(1P),AC400V(2P,3P,4P),DC440V(2P); In(Type B):6A,10A,13A,16A,20A,25A,32A,40A,50A,63A; In(Type C):0.5A,1A,1.6A,2A,3A,4A,6A,8A,10A,13A,16A,20A,25A,32A, 40A,50A,63A;Type B,Type C;Icn=10000A;Ics=7500A;1P,2P,3P,4P

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB/T10963.1-2005;GB/T10963.2-2008

This is to certify that the above mentioned product(s) complies with the requirements of implementation rules for compulsory certification(REFNO.CNCA-C03-02:2014).

Valid from: Feb.01,2018 **Valid until:** Feb.01,2023

The validity of the certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original issued: Mar.01,2013

The certificate information is available through CNCA's website: www.cnca.gov.cn

President: Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE 中国质量认证中心

CHINA QUALITY CERTIFICATION CENTRE

http://www.cqc.com.cn Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P. R. China Tel: +86 10 83886666

Q 1893412

中国国家强制性产品认证证书

附录：　　第 1 页 共 1 页

证书编号：2013010307600255　　纸号：1893412

型号的解释：

S20...UC	2	M	C	16	UC
1	2	3	4	5	6

1——产品系列 Product series　S20...UC-S20...UC0MUC, 交流和直流通用 Applicable for both AC and DC current

2——保护极数，Number of protect pole 1-1pole，2-2pole，3-3pole，4-4pole

3——分断能力，Breaking capacity　M 为分断能力为 10kA

4——脱扣特性，Tripping characteristic　B-B 特性；C-C 特性;

5——额定电流 Rated current ，0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A

6——交流和直流通用 Applicable for both AC and DC current

注：此附录与证书同时使用时有效。

主　任：

中国质量认证中心

http://www.cqc.com.cn　　中国・北京・南四环西路188号9区 100070　　电话：+86 10 83886666