

MEDIUM VOLTAGE PRODUCTS CATALOG

# MH Switchgear types MH 12-24 C/M

Spare parts, accessories and kits



# MH Switchgear types MH 12-24 C/M

## Spare parts, accessories and kits

### Cubicle doors

Ordering code	Type	Description	Details
80000254	AAC08A8	Door for 800 mm wide cubicle, VD4	Complete assembly without hinges, CB compartment window adjusted for VD4 breaker
80000274	K/AAC10A8	Door for 1000 mm wide cubicle, VD4	Complete assembly without hinges, CB compartment window adjusted for VD4 breaker
80000247	K/AAC08A16	Door for 800 mm wide cubicle, HD4	Complete assembly without hinges, CB compartment window adjusted for HD4 breaker
80000267	K/AAC10A18	Door for 1000 mm wide cubicle, HD4	Complete assembly without hinges, CB compartment window adjusted for HD4 breaker
42003537	K/AAC08A17	Door for 800 mm wide cubicle, HPA and HD4	Complete assembly without hinges, CB compartment window adjusted for HPA and HD4 breakers
42003735	K/AAC08A18	Door for 1000 mm wide cubicle, HPA and HD4	Complete assembly without hinges, CB compartment window adjusted for HPA and HD4 breakers
42003496	Kit	MH Door handle kit containing: handle, lever, pin and ring	For CB compartment door, kit contains: handle, lever, pin and ring

### Cubicle transfer mechanism

Ordering code	Type	Description	Details
21140520	UERZ4/08	Transfer mechanism for circuit breaker	Complete transfer mechanism for 800 mm cubicle, manually operated , operation voltage to be specified
21138215	UERZ4/10	Transfer mechanism for circuit breaker	Complete transfer mechanism for 1000 mm cubicle, manually operated , operation voltage to be specified

### Cubicle spare parts

Ordering code	Type	Description	Details
23607557	MHZNA11	Cable support	For MV cable compartment in 800 mm wide cubicle
23607573	MHZNA12	Cable support	For MV cable compartment in 1000 mm wide cubicle
23607751	MHZNA14	Mounting bar	For mounting cable current transformer in 800 mm wide cubicle
23607760	MHZNA15	Mounting bar	For mounting cable current transformer in 1000 mm wide cubicle
23666308	MHZCF12	Apparatus flange	Standard secondary compartment door panel for 800 mm wide cubicle, mounting holes to be specified
23666316	MHZCF13	Apparatus flange	Standard secondary compartment door panel for 1000 mm wide cubicle, mounting holes to be specified
21295094	MHZCF18	Apparatus flange	Secondary compartment door panel for 800 mm wide cubicle, mounting hole for REF 5_
21295108	MHZCF19	Apparatus flange	Secondary compartment door panel for 1000 mm wide cubicle, mounting hole for REF 5_
21137812	OPZK1	Tulip contact 2000 A	Up to 2000 A
21137821	NLDX12A1	Bushing insulator	Includes Tulip contact 2000 A
21137855	NLDX24A1	Bushing insulator	Includes Tulip contact 2000 A
21254240	NLDX24A2	Bushing insulator	Includes 2 Tulip contacts 2000 A

—  
Tools

Ordering code	Type	Description	Details
23724405	MHZGA51	Lifting tool standard	For 640 mm wide circuit breaker frame, used together with transfer trolley
21279528	MHZGA136	Lifting tool wide	For 790 mm wide circuit breaker frame, used together with transfer trolley
80001285	K/AMHG12	Transfer trolley with standard lifting tool	To be used with 12 kV breakers, max. 2000 A
80001333	K/AMHG24	Transfer trolley with standard lifting tool	To be used with 24 kV breakers, max. 2000 A
80001319	K/AMHG12G	Transfer trolley with standard lifting tool	To be used with 12 kV breakers, all standard models
80001320	K/AMHG12G1	Transfer trolley with wide lifting tool	All wide models
21147346	UERZK2	Operating handle for selector	Suitable for all circuit breaker cubicles
21147320	UERZK	Operating handle for earthing switch	Suitable for all circuit breaker cubicles



—  
Lifting tools



—  
Bushing insulators and Tulip contact



—  
Door handle kit

**Remark:**

This catalogue doesn't include the circuit breakers and the relevant components.  
Send the equipment serial number to your local ABB contact for having a dedicated support.



—  
For more information, please contact

**[abb.com/mediumvoltage](http://abb.com/mediumvoltage)**  
**[abb.com/service](http://abb.com/service)**