

LH-R1 Label Holder

Markers and Marking Systems

Catalogue Page 1SNK 160 023 S0201



RoHS
RoHS

19.5 mm 0.768 in spacing

Features and Benefits

- Easily identify your terminal blocks assembly with white or yellow labels,
- Adjustable in height for best visibility,
- Compatible with all SNK end stops.

Ordering Details

Description	Color	Type	Order Code	Pack ^(ing) pieces	Weight (1 pce) g
19.5 mm 0.768 in width	Dark Grey	LH-R1	1SNK 900 607 R0000	50	1.08

Mounting Instructions

Rail	Tool	
		Flat screwdriver Ø 4 mm Ø 0.157 in
Material Specifications	Insulating material Flammability NF F 16 101	Polyamide V0 I2F2
Ambient temperature min/max	Service IEC 60068-2-1 Storage Installing	-55 +110 °C -55 +110 °C -5 +40 °C
		-67 +230 F -67 +230 F -23 +104 F

Accessories

Description	Color	Type	Order Code	Pack ^(ing) pieces	Weight (1 pce) g
Label for LH-R1 label holder	White	MCLH-R1	1SNK 900 631 R0000	25	10.00
	Yellow	MCLH-R1-YL	1SNK 900 634 R0000	25	10.00

Some accessories may modify the terminal block's ratings. See complete information in "Technical Datasheet".

LH Label Holder

Markers and Marking Systems

Catalogue Page 1SNK 160 023 S0201



RoHS
RoHS

10 mm 0.394 in spacing

Features and Benefits

- Easily identify your terminal blocks assembly with white or yellow labels,
- Adjustable in height for best visibility,
- Compatible with all SNK end stops.

Ordering Details

Description	Color	Type	Order Code	Pack ^(ing) pieces	Weight (1 pce) g
10 mm 0.394 in width	Dark Grey	LH	1SNK 900 605 R0000	50	0.60

Mounting Instructions

Rail	Tool	
		Flat screwdriver Ø 4 mm Ø 0.157 in
Material Specifications	Insulating material Flammability NF F 16 101	Polyamide V0 I2F2
Ambient temperature min/max	Service IEC 60068-2-1 Storage Installing	-55 +110 °C -55 +110 °C -5 +40 °C
		-67 +230 F -67 +230 F -23 +104 F

Accessories

Description	Color	Type	Order Code	Pack ^(ing) pieces	Weight (1 pce) g
Label for LH label holder	White	MCLH	1SNK 900 630 R0000	25	10.00
	Yellow	MCLH-YL	1SNK 900 633 R0000	25	10.00

Some accessories may modify the terminal block's ratings. See complete information in "Technical Datasheet".

All the technical data for UL/CSA standard and dimensions in inches are in *italic*.