

PRODUCT GUIDE


Snap-it® nonmetallic fitting



With a superior pullout performance and cost efficiency, the Snap-it nonmetallic fitting is available in 1/2 and 3/4 in.

Features and benefits

- Easy “Snap-it” installation in knockouts, no tools needed
- Snug fit eliminates movement within knockout
- Exceeds pullout requirements, better cable secureness
- Insertion from inside or outside of enclosures increases installation flexibility
- Distinctive colours to differentiate both sizes; grey for 1/2 in. and blue for 3/4 in.
- Certified for one or two cables
- Designed and manufactured in Canada




Cat. no.	Description	Trade size (in.)	Clamping range (in.)		Suggested application	Packaging	
			Min.	Max.		Inner.	Outer.
CI4004-FP5	Nonmetallic fitting 1/2 in. - FLIP-PAK 350	1/2"	0.21"	0.42"	14/2 - 12/2 - 10/2	350	-
CI4004-FP3	Nonmetallic fitting 1/2 in. - FLIP-PAK 175	1/2"	0.21"	0.42"	14/3 - 12/3 - 10/3	175	-
CI4004	Nonmetallic fitting 1/2 in.	1/2"	0.21"	0.42"	2 CABLES: 2 X 14/2 - 2 X 12/2 1 X 14/2 + 1 X 12/2	100	400
CI4006-JAR200	Nonmetallic fitting 3/4 in. - JAR 200	3/4"	0.22"	0.65"	12/2 - 10/2 - 8/2 - 6/2	200	1200
CI4006-JAR80	Nonmetallic fitting 3/4 in. - JAR 80	3/4"	0.22"	0.65"	14/3 - 12/3 - 10/3 - 8/3 - 6/3	80	960
CI4006-JAR40	Nonmetallic fitting 3/4 in. - JAR 40	3/4"	0.22"	0.65"	2 CABLES: 2 X 12/2 - 2 X 10/2 1 X 12/2 + 1 X 10/2	40	640

01
Align the flat surface or opening with the burr of the knockout for easier insertion.


02 et 03
Insert the fitting into the knockout without the cables, from the inside or the outside of the enclosure.

04
For two cables installation: both cables may be inserted at once or one after the other.


Quick and easy installation




01



02



03



04

ABB Installation Products Ltd.
Electrification Products division
700 Thomas Avenue
Saint-Jean-sur-Richelieu, Quebec J2X 2M9
Tel.: +1 (450) 347 5318
Toll Free: +1 (800) 362 2952
Fax: +1 (450) 347 1976

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB Inc. does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG. Copyright © 2018 ABB
All rights reserved