







35mm EN/IEC 60715



Products reference	Dimensions		
	R (mm)	P (mm)	Q (mm)
AF26..38(Z)-xx-xx-xx	68.5	38	86
AF26..38Z-xx-xx-30	88.5	58	106

(*) : Minimum distance to grounded component

Code article		Material		Heat treatment	Surface treatment	Finish
Created by		Andre Imperato		Checked by	Approved by	Hugo Guilhem
Created on		2018-02-07		Checked on	Approved on	2018-02-07
	Comments					Folio: 1/1
	ECN number	Approuvé	Language: FR/EN	Format: A3	Scale: 1:1	PRUFRFRA_EPP
Title		AF26....38 + LH38-4 DIMENSIONS + DRILLING		PRT	1SBB910504R3501 B.2	
Title (en)		AF26....38 + LH38-4 DIMENSIONS + DRILLING		DRW	1SBB910504D3501 B	