

Continuous-line Recorder LineMaster 200
Continuous-line Recorder Minicomp LK
Consumables and accessories

Ordering information									
	Catalog Number	Code							
Scale plate for LineMaster 200 and Minicomp LK	0319171V-								
Numeral height 2 mm									
Without graduation (start and end marked)		3	4	0					
With graduation as specified (Klartext)		3	4	2					
Ruler for LineMaster 200 and Minicomp LK	1882197V-								
Graduation as specified (clear text)		4	1	2					
Tag name plate									
for Minicomp LK	0319489V-								
(train of colours from down up: violet, blue, red, green)									
for LineMaster 200	0319796V-								
(train of colours from down up: violet, blue, red, green)									
(Character height 3 mm; max. 64 characters per channel)									
Label as specified									
for measuring channel blue (clear text)		5	7	2					
for measuring channel red (clear text)		5	7	5					
for measuring channel green (clear text)		5	7	8					
for measuring channel violet (clear text)		5	8	2					
Fibre-tip insert									
for Minicomp LK 4. and LineMaster 200 without printer channel									
blue	43482-0319133								
red	43482-0319132								
green	43482-0319131								
violet	43482-0319134								
for Minicomp LK 3. and LineMaster 200P with printer channel									
blue	43482-0319133								
red	43482-0319132								
green	43482-0319131								
Ink head (the same for all versions "with printer channel")									
violet	43481-0319135								
Bag with 4 pieces of a zener diode combination	43483-0745641								
Protection against interruption of unipolar and bipolar current signals when removing a slide-in module									

The three-digit Code-Numbers should be appended to the Catalog Number - separated by a slash

Continuous-line Recorder LineMaster 200, Minicomp LK

Consumables and Accessories

10/43-2.15 EN

Ordering information				
	Catalog Number			
PARALINE 200 parameter definition program for LineMaster 200 / Minicomp LK ¹⁾	43095-3100448			
Adapter set²⁾	43083-0745566			
Bag with bus terminal resistors $R_u = 390 \Omega$; $R_d = 390 \Omega$; $R_t = 150 \Omega$	43483-0319229			

¹⁾ User guidance in German, English and French

Hardware preconditions:

Operating system DOS	as from Version 3.20
Free working memory, min.	540 KByte
Diskette drive 3.5 inch.	storage density 1.44 MByte
For graphics mode	VGA card
Serial interface	RS 232C or RS 485 to COM1/2/3/4
Printer optionally on	LPT1...LPT3

²⁾ Consisting of:

RS 232/RS 485 adapter
Mains unit to RS 232/RS 485 adapter
Connection cable (3 m), with plugs at both ends
Adapter 9-pin to 25-pin

Contact us

ABB Ltd.

Process Automation

Howard Road, St. Neots
Cambridgeshire, PE19 8EU
UK

Phone: +44 (0)1480 475321

Fax: +44 (0)1480 217948

ABB Inc.

Process Automation

125 E. County Line Road
Warminster PA 18974
USA

Phone: +1 215 674 6000

Fax: +1 215 674 7183

ABB Automation Products GmbH

Process Automation

Borsigstr. 2
63755 Alzenau
Germany

Phone: +49 551 905-534

Fax: +49 551 905-555

www.abb.com

Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

Copyright© 2011 ABB

All rights reserved

3KXR091103R1001

10/43-2,15-EN 01.2011