


OS200-250PD-LR


Installation instruction

1




4

OS200-250_12_





5

OS200-250_21_




7





10



OS200-250 12



OS200B12BL
OS200B12BR
OS200B12DL
OS200B12LR
OS200B12UR

OS250B12BL
OS250B12BR
OS250B12DL
OS250B12LR
OS250B12UR


OS250D12BL
OS250D12BR
OS250D12DL
OS250D12LR
OS250D12UR



M00120/OS250_12BL-BR A / KA00031



11

OS200-250 21



OS200B21BL
OS200B21BR
OS200B21DL
OS200B21LR
OS200B21UR
OS250B21BL
OS250B21BR
OS250B21DL
OS250B21LR
OS250B21UR

OS250D21BL
OS250D21BR
OS250D21DL
OS250D21LR
OS250D21UR



M00119/OS250_21BD-BR A / KA00032

Diagram of the rear view of the device. It shows a vertical stack of components. On the right side, there are two ports labeled 'BR' (top) and 'BL' (bottom), connected by a bracket. The device has a grey and black color scheme.

A / KA00033








Diagram illustrating the rear view of the device, showing the BR (Blue) and BL (Black) ports.



M00122/OS250_22BL-BRN2 A / KA00034




Phase terminals




OSV250DK





KA00084











M8 | 15...22 Nm
M10 | 30...44 Nm



Connections

18

OZXB17








KA00013



Connections

19





OEZXU14



M8 | 15...22 Nm
M10 | 30...44 Nm




OZXB1L
OZXB2L
OZXB3
OZXB4
OZXB5
OZXB7L
OZXB8











OZXB1L
OZXB2L
OZXB8
OZXB9

OZXB3+OZXB3K
OZXB4+OZXB3K
OZXB5+OZXB4K
OZXB7L+OZXB5K




OZXB1L
OZXB2L

OZXB3+OZXB3K
OZXB5+OZXB4K
OZXB7L+OZXB5K





OA_

A




Test indication contact




NO: OA1G10
NC: OA3G01



B




Test contact



C






Remove




KA00086

OA1G10 (NO)
OA3G01 (NC)

max 2






max 2














BS type

KA00011







DPMM_





Phase barriers






Cutting width 55 mm








KA00015




OSS250^G1SH_

OSS250G1SH_

OSS250^G1LHOSS400^G3SS OSS400^G4SSL OSS400^G4SSROSS400^G3LS OSS400^G4LSL OSS400^G4LSR

OSS400G4SSL

OSS400T4LSL





BG	Внимание! Опасно напряжение! Да се монтира само от лице с електротехническа квалификация.
FR	Avertissement! Tension électrique dangereuse! Installation uniquement par des personnes qualifiées en électrotechnique.
MT	Twissija! Vultaġġ perikoluż! Għandu jiġi installat biss minn persuna b'kompetenza elettroteknika.
HR	Upozorenje! Opasan napon! Postavljati smije samo elektrotehnički stručnjak.
DE	Warnung! Gefährliche Spannung! Installation nur durch elektrotechnische Fachkraft.
PL	Ostrzeżenie! Niebezpieczne napięcie! Instalacji może dokonać wyłącznie osoba z fachową wiedzą w dziedzinie elektrotechniki.
CZ	Varování! Nebezpečné napětí! Montáž smí provádět výhradně elektrotechnik!
EL	Προειδοποίηση! Υψηλή τάση! Η εγκατάσταση πρέπει να γίνεται μόνο από εξειδικευμένους ηλεκτροτεχνικούς.
PT	Aviso! Tensão perigosa! A instalação só deve ser realizada por um electricista especializado.
DA	Advarsel! Farlig elektrisk spænding! Installation må kun foretages af personer med elektroteknisk ekspertise.
HU	Figyelmeztetés! Veszélyes feszültség! Csak elektrotechnikai tapasztalattal rendelkező szakember helyezheti üzembe.
RO	Avertizare! Tensiune periculoasă! Instalarea trebuie efectuată numai de către o persoană cu experiență în electrotehnică.
NL	Waarschuwing! Gevaarlijke spanning! Mag alleen geïnstalleerd worden door een deskundige elektrotechnicus.
IE	Rabhadh! Voltas guaiseach! Ba chóir do dhuine ag a bhfuil saineolas leictreicniúil, agus an té sin amháin, é seo a shuiteáil.
SK	Varovanie! Nebezpečné napätie! Montáž môže vykonávať iba skúsený elektrotechnik.
EN	Warning! Hazardous voltage! Installation by person with electrotechnical expertise only.
IT	Avvertenza! Tensione pericolosa! Fare installare solo da un elettricista qualificato.
SL	Opozorilo! Nevarna napetost! Vgradnjo lahko opravi le oseba z elektrotehničnim strokovnim znanjem.
ET	Hoiatus! Ohtlik pinge. Paigaldada võib ainult elektrotehnika-alane ekspert.
LV	Uzmanību! Bīstami - elektrība! Montāžas darbus drīkst veikt tikai personas, kurām ir atbilstošas elektrotehniskās zināšanas.
ES	¡Advertencia! ¡Tensión peligrosa! La instalación deberá ser realizada únicamente por electricistas especializados.
FI	Varoituis! Vaarallinen jännite! Asennuksen voi tehdä vain sähköalan ammattihenkilö.
LT	Dėmesio! Pavojinga įtampa! Dirbti leidžiama tik elektrotechniko patirties turintiems asmenims.
SE	Varning! Farlig spänning! Installation får endast utföras av en elektriker.
CN	警告！电压危险！只能由专业电工进行安装。
RU	Осторожно! Опасное напряжение! Монтаж должен выполняться только специалистом-электриком.

For more information please contact:

ABB Oy, Protection and Connection
P.O. Box 622, FI-65101 Vaasa, Finland
new.abb.com/low-voltage

Power and productivity
for a better world™

