

MC612PA Terminal Block Markers

Pre-printed marker card for vertical terminal block assembly

Catalogue Page 1SNK 160 008 S0201



6 mm 0.236 in spacing

Features and Benefits

Save printing time with our large pre-printed cards offer with pre-printed numbers, letters or symbols.

Main Technical Data

Material	Flammability	Maximum printed digits		Dimensions	
				mm	inches
Polyamide	V2	Horizontal	Vertical	5.6 x 12	0.220 x 0.472

Ordering Details

Description	Number of markers per unit	Color	Type	Order Code	Pack ^(ing) pieces	Weight (1 pce) g
0->9 (x10)	100	White	☐ MC612PA	1SNK 150 092 R0000	1	11.00
1->10 (x10)	100	White	☐ MC612PA	1SNK 150 012 R0000	1	11.00
11->20 (x10)	100	White	☐ MC612PA	1SNK 150 022 R0000	1	11.00
21->30 (x10)	100	White	☐ MC612PA	1SNK 150 032 R0000	1	11.00
31->40 (x10)	100	White	☐ MC612PA	1SNK 150 042 R0000	1	11.00
41->50 (x10)	100	White	☐ MC612PA	1SNK 150 052 R0000	1	11.00
51->60 (x10)	100	White	☐ MC612PA	1SNK 150 062 R0000	1	11.00
61->70 (x10)	100	White	☐ MC612PA	1SNK 150 072 R0000	1	11.00
71->80 (x10)	100	White	☐ MC612PA	1SNK 150 082 R0000	1	11.00
81->90 (x10)	100	White	☐ MC612PA	1SNK 150 084 R0000	1	11.00
91->100 (x10)	100	White	☐ MC612PA	1SNK 150 102 R0000	1	11.00
101->110 (x10)	100	White	☐ MC612PA	1SNK 150 112 R0000	1	11.00
111->120 (x10)	100	White	☐ MC612PA	1SNK 150 122 R0000	1	11.00
121->130 (x10)	100	White	☐ MC612PA	1SNK 150 132 R0000	1	11.00
131->140 (x10)	100	White	☐ MC612PA	1SNK 150 142 R0000	1	11.00
141->150 (x10)	100	White	☐ MC612PA	1SNK 150 152 R0000	1	11.00
151->160 (x10)	100	White	☐ MC612PA	1SNK 150 162 R0000	1	11.00
161->170 (x10)	100	White	☐ MC612PA	1SNK 150 172 R0000	1	11.00
171->180 (x10)	100	White	☐ MC612PA	1SNK 150 182 R0000	1	11.00
181->190 (x10)	100	White	☐ MC612PA	1SNK 150 192 R0000	1	11.00
191->200 (x10)	100	White	☐ MC612PA	1SNK 150 202 R0000	1	11.00
1->100	100	White	☐ MC612PA	1SNK 155 012 R0000	1	11.00
101->200	100	White	☐ MC612PA	1SNK 155 022 R0000	1	11.00
201->300	100	White	☐ MC612PA	1SNK 155 032 R0000	1	11.00
301->400	100	White	☐ MC612PA	1SNK 155 042 R0000	1	11.00
401->500	100	White	☐ MC612PA	1SNK 155 052 R0000	1	11.00
501->600	100	White	☐ MC612PA	1SNK 155 062 R0000	1	11.00
601->700	100	White	☐ MC612PA	1SNK 155 072 R0000	1	11.00
701->800	100	White	☐ MC612PA	1SNK 155 082 R0000	1	11.00
801->900	100	White	☐ MC612PA	1SNK 155 092 R0000	1	11.00
901->1000	100	White	☐ MC612PA	1SNK 155 102 R0000	1	11.00
A (x100)	100	White	☐ MC612PA	1SNK 156 012 R0000	1	11.00
B (x100)	100	White	☐ MC612PA	1SNK 156 022 R0000	1	11.00
C (x100)	100	White	☐ MC612PA	1SNK 156 032 R0000	1	11.00
D (x100)	100	White	☐ MC612PA	1SNK 156 042 R0000	1	11.00
E (x100)	100	White	☐ MC612PA	1SNK 156 052 R0000	1	11.00
F (x100)	100	White	☐ MC612PA	1SNK 156 062 R0000	1	11.00
G (x100)	100	White	☐ MC612PA	1SNK 156 072 R0000	1	11.00
H (x100)	100	White	☐ MC612PA	1SNK 156 082 R0000	1	11.00
I (x100)	100	White	☐ MC612PA	1SNK 156 092 R0000	1	11.00
J (x100)	100	White	☐ MC612PA	1SNK 156 102 R0000	1	11.00
K (x100)	100	White	☐ MC612PA	1SNK 156 112 R0000	1	11.00
L (x100)	100	White	☐ MC612PA	1SNK 156 122 R0000	1	11.00
M (x100)	100	White	☐ MC612PA	1SNK 156 132 R0000	1	11.00
N (x100)	100	White	☐ MC612PA	1SNK 156 142 R0000	1	11.00
O (x100)	100	White	☐ MC612PA	1SNK 156 152 R0000	1	11.00
P (x100)	100	White	☐ MC612PA	1SNK 156 162 R0000	1	11.00
Q (x100)	100	White	☐ MC612PA	1SNK 156 172 R0000	1	11.00
R (x100)	100	White	☐ MC612PA	1SNK 156 182 R0000	1	11.00
S (x100)	100	White	☐ MC612PA	1SNK 156 192 R0000	1	11.00
T (x100)	100	White	☐ MC612PA	1SNK 156 202 R0000	1	11.00
U (x100)	100	White	☐ MC612PA	1SNK 156 212 R0000	1	11.00
V (x100)	100	White	☐ MC612PA	1SNK 156 222 R0000	1	11.00

All the technical data for UL/CSA standard and dimensions in inches are in italic.

MC612PA Terminal Block Markers

Catalogue Page 1SNK 160 008 S0201

Pre-printed marker card for vertical terminal block assembly



6 mm 0.236 in spacing



Ordering Details

Description	Number of markers per unit	Color	Type	Order Code	Pack ^(ing) pieces	Weight (1 pcs) g
W (x100)	100	White	MC612PA	1SNK 156 232 R0000	1	11.00
X (x100)	100	White	MC612PA	1SNK 156 242 R0000	1	11.00
Y (x100)	100	White	MC612PA	1SNK 156 252 R0000	1	11.00
Z (x100)	100	White	MC612PA	1SNK 156 262 R0000	1	11.00
0 (x100)	100	White	MC612PA	1SNK 157 002 R0000	1	11.00
1 (x100)	100	White	MC612PA	1SNK 157 012 R0000	1	11.00
2 (x100)	100	White	MC612PA	1SNK 157 022 R0000	1	11.00
3 (x100)	100	White	MC612PA	1SNK 157 032 R0000	1	11.00
4 (x100)	100	White	MC612PA	1SNK 157 042 R0000	1	11.00
5 (x100)	100	White	MC612PA	1SNK 157 052 R0000	1	11.00
6 (x100)	100	White	MC612PA	1SNK 157 062 R0000	1	11.00
7 (x100)	100	White	MC612PA	1SNK 157 072 R0000	1	11.00
8 (x100)	100	White	MC612PA	1SNK 157 082 R0000	1	11.00
9 (x100)	100	White	MC612PA	1SNK 157 092 R0000	1	11.00
+ (x100)	100	White	MC612PA	1SNK 158 002 R0000	1	11.00
- (x100)	100	White	MC612PA	1SNK 158 012 R0000	1	11.00
~ (x100)	100	White	MC612PA	1SNK 158 022 R0000	1	11.00
= (x100)	100	White	MC612PA	1SNK 158 032 R0000	1	11.00
≡ (x100)	100	White	MC612PA	1SNK 158 042 R0000	1	11.00
L1 (x100)	100	White	MC612PA	1SNK 158 052 R0000	1	11.00
L2 (x100)	100	White	MC612PA	1SNK 158 062 R0000	1	11.00
L3 (x100)	100	White	MC612PA	1SNK 158 072 R0000	1	11.00
PE (x100)	100	White	MC612PA	1SNK 158 092 R0000	1	11.00
U1 (x100)	100	White	MC612PA	1SNK 158 102 R0000	1	11.00
U2 (x100)	100	White	MC612PA	1SNK 158 112 R0000	1	11.00
U3 (x100)	100	White	MC612PA	1SNK 158 122 R0000	1	11.00
V1 (x100)	100	White	MC612PA	1SNK 158 132 R0000	1	11.00
V2 (x100)	100	White	MC612PA	1SNK 158 142 R0000	1	11.00
V3 (x100)	100	White	MC612PA	1SNK 158 152 R0000	1	11.00
W1 (x100)	100	White	MC612PA	1SNK 158 162 R0000	1	11.00
W2 (x100)	100	White	MC612PA	1SNK 158 172 R0000	1	11.00
W3 (x100)	100	White	MC612PA	1SNK 158 182 R0000	1	11.00
+24V (x100)	100	White	MC612PA	1SNK 158 192 R0000	1	11.00
+48V (x100)	100	White	MC612PA	1SNK 158 202 R0000	1	11.00
- 24V (x100)	100	White	MC612PA	1SNK 158 212 R0000	1	11.00
-48V (x100)	100	White	MC612PA	1SNK 158 222 R0000	1	11.00
L1-L2-L3-N-PE (x20)	100	White	MC612PA	1SNK 159 002 R0000	1	11.00
U1-U2-U3-V1-V2-V3-W1-W2-W3 (x10) + U1 (x10)	100	White	MC612PA	1SNK 159 012 R0000	1	11.00

All the technical data for UL/CSA standard and dimensions in inches are in *italic*.