



中国国家强制性产品认证证书

证书编号: 2016010307839861

委托人名称、地址

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg, Germany

生产者(制造商)名称、地址

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg, Germany

生产企业名称、地址

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg, Germany

产品名称和系列、规格、型号

塑料外壳式断路器

S201, S201-NA, S202, S203, S203-NA, S204; 型号解释详见附件

产品标准和技术要求

GB 14048.2-2008

上述产品符合强制性产品认证实施规则
CNCA-C03-02: 2014的要求, 特发此证。

发证日期: 2016年01月25日

有效期至: 2021年01月25日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询



主任:

中国质量认证中心

中国·北京·南四环西路188号9区 100070

<http://www.cqc.com.cn>



Q 1283308



CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No. : 2016010307839861

NAME AND ADDRESS OF THE APPLICANT

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg, Germany

NAME AND ADDRESS OF THE MANUFACTURER

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg, Germany

NAME AND ADDRESS OF THE FACTORY

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82 69123 Heidelberg, Germany

NAME, MODEL AND SPECIFICATION

Moulded Case Circuit-breaker
S201, S201-NA, S202, S203, S203-NA, S204;

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 14048.2-2008

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification (REF NO. CNCA-C03-02:2014).

Date of issue: Jan. 25, 2016 Date of expiry: Jan. 25, 2021

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

This certificate can be verified through CNCA's website: www.cnca.gov.cn



President:

Wang Kejiao



CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188, Nansihuan Xilu, Beijing 100070 P.R. China

<http://www.cqc.com.cn>

Q 1283308



中国国家强制性产品认证证书

附录:

第 1 页 共 2 页

证书编号: 2016010307839861

纸号: 1283308

S201, S201-NA, S202, S203, S203-NA, S204

Ui: 440V;

Uimp: 4kV;

Ue: AC133/230V(1P, 1P+N), AC230/400/440V(2P, 3P, 3P+N, 4P);

In:

B 特性: 1A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A;

C, D 特性: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A;

K 特性: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 5A, 6A, 8A, 10A, 13A, 15A, 16A, 20A, 25A, 30A, 32A, 40A, 50A, 60A, 63A;

Z 特性: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A;

Ics=7.5kA(AC230V/400V, 440V), 15 kA(AC133V/230V);

Icu=10kA(AC230V/400V, 440V), 20 kA(AC133V/230V);

使用类别: A;

过电流脱扣器类型: 热磁式;

适用频率: 50Hz;

适用隔离;

极数: 1P, 1P+N(N 极可开闭), 2P, 3P, 3P+N(N 极可开闭), 4P

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国·北京·南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>





中国国家强制性产品认证证书

附录:

第 2 页 共 2 页

证书编号: 2016010307839861

纸号: 1283308

型号的解析:

$\frac{S20}{I} \frac{1}{II} \frac{-NA}{III} \frac{K}{IV} \frac{0.5}{V}$

I: S20 ... - Basic Type 基本型号

II: Number of Pole 极数

1- 1 Pole

2- 2 Pole

3- 3 Pole

4- 4 Pole

III: blank: without N Pole 不带中性极

-NA: with N Pole 带中性极

IV: Setting current 电流设定

B: Setting current Ii: 12 In

C: Setting current Ii: 6,5 In

D: Setting current Ii: 4 In

K: Setting current Ii: 12 In

Z: Setting current Ii: 2,5 In

V: Rated Current 额定电流

B: 1A; 2A; 3A; 4A; 6A; 8A; 10A; 13A; 16A; 20A; 25A; 32A; 40A;
50A; 63A

C and D: 0.5A; 1A; 1.6A; 2A; 3A; 4A; 6A; 8A; 10A; 13A; 16A; 20A; 25A;
32A; 40A; 50A; 63A

K and Z: 0.5A; 1A; 1.6A; 2A; 3A; 4A; 5A(only K); 6A; 8A; 10A; 13A;
15A(only K); 16A; 20A; 25A; 30A(only K); 32A; 40A; 50A;
60A(only K); 63A

注: 此附录与证书同时使用时有效。



主任:

中国质量认证中心

中国 · 北京 · 南四环西路 188 号 9 区 100070

<http://www.cqc.com.cn>

