中国国家强制性产品认证证书

证书编号：2012010307584585

委托人名称、地址

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

生产者(制造商)名称、地址

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

生产企业名称、地址

北京ABB低压电器有限公司
北京市北京经济技术开发区康定街17号

产品名称和系列、规格、型号

微型断路器

S201, S201-NA, S202, S203, S203-NA, S204; Ue:AC230/400V(1P), AC230V(1P+N), AC400V(2P, 3P, 3P+N, 4P);
B:In:1A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A;
C:In:0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A;
D:In:0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A;瞬时脱扣类型:B, C, D型;Icn=Ics:6kA;防护等级:IP20;极数:1P, 1P+N(N极可开闭), 2P, 3P, 3P+N(N极可开闭), 4P;型号详见附录

产品标准和技术要求

GB 10963.1-2005

上述产品符合强制性产品认证实施规则
CNCA-C03-02:2014的要求，特发此证。

发证日期：2016年11月29日　　有效期至：2021年11月29日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

本证书为变更证书，证书首次颁发日期：2012年12月05日

本证书的相关信息可通过国家认监委网站www.cnca.gov.cn查询

主　任：

中国质量认证中心

中国 · 北京 · 南四环西路188号9区 100070

http://www.cqc.com.cn

Q 1520580

中国国家强制性产品认证证书

附录：　　第 1 页 共 1 页

证书编号：2012010307584585　　纸号：1520580

型号解释：

S20 □ □ □ □
1 2 3 4 5

1——产品系列，S201,S201-NA,S202,S203,S203-NA,S204
2——保护极数，1-1P，2-2P，3-3P，4-4P
3——中性极，空白为无中性极，-NA 为带有中性极
4——瞬时脱扣特性，B-B 特性；C-C 特性；D-D 特性
5——额定电流，B: 1A; 2A; 3A; 4A; 6A; 8A; 10A; 13A; 16A; 20A; 25A; 32A; 40A, 50A, 63A;
C: 0.5A; 1A; 1,6A; 2A; 3A; 4A; 6A; 8A; 10A; 13A; 16A; 20A; 25A; 32A; 40A, 50A, 63A;
D: 0.5A; 1A; 1,6A; 2A; 3A; 4A; 6A; 8A; 10A; 13A; 16A; 20A; 25A; 32A; 40A, 50A, 63A.

注：此附录与证书同时使用时有效。

主　任：

中国质量认证中心

中国 · 北京 · 南四环西路 188 号 9 区 100070
http://www.cqc.com.cn

CERTIFICATE FOR CHINA COMPULSORY PRODUCT CERTIFICATION

No.: 2012010307584585

NAME AND ADDRESS OF THE APPLICANT

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

NAME AND ADDRESS OF THE MANUFACTURER

ABB Stotz-Kontakt GmbH
Eppelheimer Strasse 82, 69123 Heidelberg, Germany

NAME AND ADDRESS OF THE FACTORY

ABB LV Installation Materials Co. Ltd., Beijing
No. 17, Kangding Street, Beijing Economic-Technological Development Area, 100176, P. R. China

NAME, MODEL AND SPECIFICATION

Miniature Circuit-breaker

S201, S201-NA, S202, S203, S203-NA, S204; Ue: AC230/400V(1P), AC230V(1P+N), AC400V (2P, 3P, 3P+N, 4P);
B: In: 1A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A;
C: In: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A;
D: In: 0.5A, 1A, 1.6A, 2A, 3A, 4A, 6A, 8A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A; Type of Instantaneous Tripping Current: B, C, D; Icn=Ics: 6kA; IP20; Poles: 1P, 1P+N (Switched N pole), 2P, 3P, 3P+N(Switched N pole), 4P; See the Appendix

THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB 10963.1-2005

This is to certify that the above mentioned products have met the requirements of implementation rules for compulsory certification(REF NO. CNCA-C03-02:2014).

Date of issue: Nov. 29, 2016 Date of expiry: Nov. 29, 2021

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

Date of original certification: Dec. 05, 2012

This certificate can be verified through CNCA's website: www.cnca.gov.cn

President: Wang Kejiao

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China
http://www.cqc.com.cn

Q 1520580