## OVR T2-T3 3L 20-275 P TS QS 2CTB803873R3500

EAN: 3660308520661 FR: B752066

6/03/2015

Type

T2-T3

7 7

Imax: 20 kA

Up: 0,85 kV

System

TNC: 230/400 V

TF'

IEC 61643-11 EN 61643-11 Type 2 + 3 SPD's have characteristics of type 2 but also type 3, they are capable of discharging the currents generated by indirect lightning strikes (T2 8/20 $\mu$ s), but also they have a low residual voltage (Up), who is compatible with the withstand voltage of sensitive electronic equipment.

They are generally less powerful than a pure Type 2 SPD. Higher is the Imax, more powerful they are.

They are installed in sub-distribution boards or close to sensitive equipment.

They can be used on their own.



• Din rail mounting

Pluggable

• Excellent technical features

• Improved safety

• Pro M compact design

• Back up protection up to 125 A Fuse or Mcb

Key characteristics			
Protection mode			L-PEN
Number of protected lines			3
Test class			-
Integrated thermal disconnector			Yes
End of life indicator			Yes
Safety reserve			No
Electrical characteristics			
Nominal discharge current	In (8/20)	kA	5
Maximal discharge current	I <sub>max</sub> (8/20)	kA	20
Impulse current	I <sub>imp</sub> (10/350)	kA	2
Maximal continuous operating voltage	Uc	V	275
Type of current / frequency		Hz	a.c. 47-63
Voltage protection level at In	U <sub>P</sub> (L-PE)	kV	0,85
Voltage protection level at In	U <sub>P</sub> (L-N)	kV	-
Voltage protection level at In	U <sub>P</sub> (N-PE)	kV	-
Short circuit withstand	/sccr	kA	100
Total current	/TOTAL	kA	60
Follow current interrupted	I fi	kA	-/-
Ground residual current	/PE	μΑ	< 210
TOV withstand (L-N: 5s / N-PE: 200 ms)	Uτ	V	337 / -
Voltage Combination Wave	Uoc	kV	6
Required thermal/back up protection			
Curve B or C Circuit breaker		Α	≤ 125
gG - gL fuse		Α	≤ 125
Comments			
Mechanical characteristics			
Dimensions	HxWxD	mm	95 x 53,4 x 58
Wire range : Solid wire		mm²	2.525
Wire range : Stranded wire		mm²	2.516
Stripping length		mm	12.5
Packing quantities		piece	Per 1
Miscellaneous characteristics			
Maximal altitude		m	2000
Weight		g	360
Response time		ns	< 25
Fire resistance according to UL 94			V-0
Replacement cartridges			
Phase / Product ID	OVR T2-T3 20	-275 C QS	2CTB803876R1200
Neutral / Product ID		-	

















