OVR T2-T3 20-440 P TS QS 2CTB803871R1300

EAN: 3660308519610 FR : B751961

Type

T2-T3



Imax: 20 kA

Up: 1,4 kV

System

TT/TNC/TNS: 400/690 V IT: 230/400 V

IEC 61643-11 EN 61643-11

Type 2 + 3 SPD's have characteristics of type 2 but also type 3, they are capable of discharging the currents generated by indirect lightning strikes (T2 8/20µs), but also they have a low residual voltage (Up), who is compatible with the withstand voltage of sensitive electronic equipment.

They are generally less powerful than a pure Type 2 SPD. Higher is the Imax, more powerful they are.

They are installed in sub-distribution boards or close to sensitive equipment.

They can be used on their own.



• Din rail mounting

- Pluggable
- Excellent technical features
- Improved safety
- Pro M compact design
- Back up protection up to 125 A Fuse or Mcb

Key characteristics			
Protection mode			L-N/N-PE/L-PE
Number of protected lines			1
Test class			-
Integrated thermal disconnector			Yes
End of life indicator			Yes
Safety reserve			No
Electrical characteristics			
Nominal discharge current	In (8/20)	kA	5
Maximal discharge current	I _{max} (8/20)	kA	20
Impulse current	/ _{imp} (10/350)	kA	2
Maximal continuous operating voltage	Uc	V	440
Type of current / frequency		Hz	a.c. 47-63
Voltage protection level at In	U _P (L-PE)	kV	1,4
Voltage protection level at In	U _P (L-N)	kV	-
Voltage protection level at In	U _P (N-PE)	kV	-
Short circuit withstand	/sccr	kA	100
Total current	/TOTAL	kA	20
Follow current interrupted	/fi	kA	-/-
Ground residual current	/PE	μA	< 70
TOV withstand (L-N : 5s / N-PE : 200 ms)	UT	'V	581 / -
Voltage Combination Wave	Uoc	kV	6
Required thermal/back up protection			
Curve B or C Circuit breaker		А	≤ 125
gG - gL fuse		Α	≤ 125
Comments			
Mechanical characteristics			
Dimensions	HxWxD	mm	95 x 17,8 x 58
Wire range : Solid wire		mm²	2.525
Wire range : Stranded wire		mm²	2.516
Stripping length		mm	12.5
Packing quantities		piece	Per 1
Miscellaneous characteristics			
Maximal altitude		m	2000
Weight		g	120
Response time		ns	< 25
Fire resistance according to UL 94			V-0
Replacement cartridges			
Phase / Product ID	OVR T2-T3 20-440 C QS		2CTB803876R0600
Neutral / Product ID	-		-

















