



Test Report				Date of issue: 1.6.2015					
				Serial No.:					
				Type: M3GP 160MLB 6					
				Product Code: 3GGP163420-ADL					
				Protection type: Ex tb IIIB/C T125C Db					
				Cert. No.: LCIE 13 ATEX 3067 X /					
				IECEX LCIE 13.0047 X					
Rating:									
	V	Hz	kW	r/min	A	cos φ	Duty		
3~Motor	690	Y 50	11,0	975	13,1	0,78	S1		
Insul.cl.F	400	D 50	11,0	975	22,5	0,78	S1		
IP65	415	D 50	11,0	977	22,0	0,77	S1		
Eff class IE3	440	D 60	11,0	1177	20,4	0,77	S1		
	460	D 60	11,0	1179	19,8	0,76	S1		
50Hz: IE3-90,3%(100%)-91,1%(75%)-91,1%(50%)									
60Hz: IE3-91,7%(100%)									
Resistance				Insulation resistance at 82 °C		Overload			
Line	Ambient: 26 °C			2000 MΩ 1000 V		Torque 160% 15s			
U ₁ - V ₁	0,53230 Ω					Speed 120% 120s			
U ₁ - W ₁	0,53120 Ω					Current 150% 15s			
V ₁ - W ₁	0,53250 Ω								
				High-voltage test winding 1900 V		60 s			
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	η[r/min]	cos φ	η [%]
No load test		400,5 D	50	10,8	0,35		998	0,05	
Locked rotor test		94,2 D	50	22,4	1,16		0	0,32	
Thermal test (100% load)	107,4	399,8 D	50	22,5	12,2	11,0	975	0,78	90,2
Partial load points:									
~75% load	80,7	400,8 D	50	18,2	9,1	8,3	982	0,72	91,1
~50% load	53,9	400,9 D	50	14,5	6,1	5,5	989	0,60	91,0
~25% load	26,8	401,3 D	50	11,7	3,1	2,8	994	0,39	87,5
Temperature rise at rated load.				°C	[K]	Method	Measurement method		
Stator winding :				52	1		1 Resistance		
Frame :				27	2		2 Thermocouples		
Bearing D-end :				31	2		3 Thermometer		
Rotor:				73	3				
Ambient Temperature :				25	2				
These tests have been carried out on motor no. 3G1P141700176, on date 2014-07-23 which is identical in design with the above.									
Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.									
On behalf of customer									
On behalf of manufacturer				Date of test					
Tested by Asea Brown Boveri, S.A., Fabrica Motores, 08192 Sant Quirze del Valles, Spain						Telephone +34 93 728 85 00 Telefax +34 93 728 85 33			

Computer print-out valid without signature.