

V_{DRM} = 8000 V
 $I_{T(AV)M}$ = 2000 A
 $I_{T(RMS)}$ = 3150 A
 I_{TSM} = $47.5 \cdot 10^3$ A
 V_{TO} = 1.25 V
 r_T = 0.48 mΩ

Phase Control Thyristor

5STP 20N8500


Doc. No. 5SYA1072-04 Dec. 13

- Patented free-floating silicon technology
- Low on-state and switching losses
- Designed for traction, energy and industrial applications
- Optimum power handling capability
- Interdigitated amplifying gate

Blocking

Maximum rated values ¹⁾

Parameter	Symbol	Conditions	5STP 20N8500	Unit
Max. surge peak forward and reverse blocking voltage	V_{DSM}, V_{RSM}	$t_p = 10$ ms, $f = 5$ Hz $T_{vj} = 5 \dots 115$ °C, Note 1	8500	V
Max repetitive peak forward and reverse blocking voltage	V_{DRM}, V_{RRM}	$f = 50$ Hz, $t_p = 10$ ms, $t_{p1} = 250$ µs, $T_{vj} = 5 \dots 115$ °C, Note 1, Note 2	8000	V
Max crest working forward and reverse voltages	V_{DWM}, V_{RWM}		5340	V
Critical rate of rise of commutating voltage	dv/dt_{crit}	Exp. to $0.67 \cdot V_{DRM}$, $T_{vj} = 115$ °C	2000	V/µs



Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
Forward leakage current	I_{DRM}	V_{DRM} , $T_{vj} = 115$ °C			1000	mA
Reverse leakage current	I_{RRM}	V_{RRM} , $T_{vj} = 115$ °C			1000	mA

Note 1: Voltage de-rating factor of 0.11% per °C is applicable for T_{vj} below +5 °C.

Note 2: Recommended minimum ratio of V_{DRM} / V_{DWM} or $V_{RRM} / V_{RWM} = 2$. See App. Note 5SYA 2051.

Mechanical data

Maximum rated values ¹⁾

Parameter	Symbol	Conditions	min	typ	max	Unit
Mounting force	F_M		81	90	108	kN
Acceleration	a	Device unclamped			50	m/s ²
Acceleration	a	Device clamped			100	m/s ²

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
Weight	m				2.9	kg
Housing thickness	H	$F_M = 90$ kN, $T_a = 25$ °C	35.3		36	mm
Surface creepage distance	D_S		56			mm
Air strike distance	D_a		22			mm

1) Maximum rated values indicate limits beyond which damage to the device may occur

ABB Switzerland Ltd, Semiconductors reserves the right to change specifications without notice.



On-state*Maximum rated values¹⁾*

Parameter	Symbol	Conditions	min	typ	max	Unit
Average on-state current	$I_{T(AV)M}$	Half sine wave, $T_c = 70^\circ C$			2000	A
RMS on-state current	$I_{T(RMS)}$				3150	A
Peak non-repetitive surge current	I_{TSM}	$t_p = 10 \text{ ms}, T_{vj} = 115^\circ C$, sine half wave, $V_D = V_R = 0 \text{ V}$, after surge			$47.5 \cdot 10^3$	A
Limiting load integral	I^2t				$11.28 \cdot 10^6$	A^2s
Peak non-repetitive surge current	I_{TSM}	$t_p = 10 \text{ ms}, T_{vj} = 115^\circ C$, sine half wave, $V_R = 0.6 \cdot V_{RRM}$, after surge			$31.5 \cdot 10^3$	A
Limiting load integral	I^2t				$4.96 \cdot 10^6$	A^2s

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
On-state voltage	V_T	$I_T = 1500 \text{ A}, T_{vj} = 115^\circ C$			2	V
Threshold voltage	$V_{(T0)}$				1.25	V
Slope resistance	r_T	$I_T = 700 \text{ A} - 2100 \text{ A}, T_{vj} = 115^\circ C$			0.48	$\text{m}\Omega$
Holding current	I_H	$T_{vj} = 25^\circ C$			150	mA
		$T_{vj} = 115^\circ C$			125	mA
Latching current	I_L	$T_{vj} = 25^\circ C$			600	mA
		$T_{vj} = 115^\circ C$			500	mA

Switching*Maximum rated values¹⁾*

Parameter	Symbol	Conditions	min	typ	max	Unit
Critical rate of rise of on-state current	di/dt_{crit}	$T_{vj} = 115^\circ C, I_{TRM} = 2000 \text{ A},$ $V_D \leq 0.67 \cdot V_{DRM}, I_{FG} = 2 \text{ A}, t_r = 0.5 \mu\text{s}$	Cont. $f = 50 \text{ Hz}$		250	$\text{A}/\mu\text{s}$
			Cont. $f = 1 \text{ Hz}$		1000	$\text{A}/\mu\text{s}$
Circuit-commutated turn-off time	t_q	$T_{vj} = 115^\circ C, I_{TRM} = 2000 \text{ A},$ $V_R = 200 \text{ V}, di_T/dt = -1.5 \text{ A}/\mu\text{s},$ $V_D \leq 0.67 \cdot V_{DRM}, dv_D/dt = 20 \text{ V}/\mu\text{s}$			1080	μs

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
Reverse recovery charge	Q_{rr}	$T_{vj} = 115^\circ C, I_{TRM} = 2000 \text{ A},$ $V_R = 200 \text{ V}, di_T/dt = -1.5 \text{ A}/\mu\text{s}$	4000		8000	μAs
			50		125	A
Gate turn-on delay time	t_{gd}	$T_{vj} = 25^\circ C, V_D = 0.4 \cdot V_{RM},$ $I_{FG} = 2 \text{ A}, t_r = 0.5 \mu\text{s}$			3	μs

Triggering

Maximum rated values¹⁾

Parameter	Symbol	Conditions	min	typ	max	Unit
Peak forward gate voltage	V_{FGM}				12	V
Peak forward gate current	I_{FGM}				10	A
Peak reverse gate voltage	V_{RGM}				10	V
Average gate power loss	$P_{G(AV)}$		see Fig. 7			W

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
Gate-trigger voltage	V_{GT}	$T_{vj} = 25^\circ\text{C}$			2.6	V
Gate-trigger current	I_{GT}	$T_{vj} = 25^\circ\text{C}$			400	mA
Gate non-trigger voltage	V_{GD}	$V_D = 0.4 \cdot V_{DRM}, T_{vjmax} = 115^\circ\text{C}$			0.3	V
Gate non-trigger current	I_{GD}	$V_D = 0.4 \cdot V_{DRM}, T_{vjmax} = 115^\circ\text{C}$			10	mA

Thermal

Maximum rated values¹⁾

Parameter	Symbol	Conditions	min	typ	max	Unit
Operating junction temperature range	T_{vj}				115	°C
Storage temperature range	T_{stg}		-40		140	°C

Characteristic values

Parameter	Symbol	Conditions	min	typ	max	Unit
Thermal resistance junction to case	$R_{th(j-c)}$	Double-side cooled $F_m = 81 \dots 108 \text{ kN}$			5.7	K/kW
	$R_{th(j-c)A}$	Anode-side cooled $F_m = 81 \dots 108 \text{ kN}$			11.4	K/kW
	$R_{th(j-c)C}$	Cathode-side cooled $F_m = 81 \dots 108 \text{ kN}$			11.4	K/kW
Thermal resistance case to heatsink	$R_{th(c-h)}$	Double-side cooled $F_m = 81 \dots 108 \text{ kN}$			1	K/kW
	$R_{th(c-h)}$	Single-side cooled $F_m = 81 \dots 108 \text{ kN}$			2	K/kW

Analytical function for transient thermal impedance:

$$Z_{th(j-c)}(t) = \sum_{i=1}^n R_i (1 - e^{-t/\tau_i})$$

i	1	2	3	4
$R_i(\text{K/kW})$	3.400	1.260	0.680	0.350
$\tau_i(\text{s})$	0.8685	0.1572	0.0219	0.0078




Fig. 1 Transient thermal impedance (junction-to-case) vs. time




Fig. 2 On-state voltage characteristics




Fig. 3 On-state voltage characteristics




Fig. 4 On-state power dissipation vs. mean on-state current, turn-on losses excluded




Fig. 5 Max. permissible case temperature vs. mean on-state current, switching losses ignored




Fig. 6 Recommended gate current waveform




Fig. 7 Max. peak gate power loss




Fig. 8 Reverse recovery charge vs. decay rate of on-state current




Fig. 9 Peak reverse recovery current vs. decay rate of on-state current

Turn-on and Turn-off losses




Fig. 10 Turn-on energy, half sinusoidal waves




Fig. 11 Turn-on energy, rectangular waves




Fig. 12 Turn-off energy, half sinusoidal waves




Fig. 13 Turn-off energy, rectangular waves




Fig. 14 Current and voltage waveforms at turn-off




Fig. 15 Relationships for power loss




Fig. 16 Device Outline Drawing

Related documents:

- | | |
|-----------|---|
| 5SYA 2020 | Design of RC-Snubber for Phase Control Applications |
| 5SYA 2049 | Voltage definitions for phase control thyristors and diodes |
| 5SYA 2051 | Voltage ratings of high power semiconductors |
| 5SYA 2034 | Gate-Drive Recommendations for PCT's |
| 5SYA 2036 | Recommendations regarding mechanical clamping of Press Pack High Power Semiconductors |
| 5SZK 9104 | Specification of environmental class for pressure contact diodes, PCTs and GTO, STORAGE available on request, please contact factory |
| 5SZK 9105 | Specification of environmental class for pressure contact diodes, PCTs and GTO, TRANSPORTATION available on request, please contact factory |

Please refer to <http://www.abb.com/semiconductors> for current version of documents.

ABB Switzerland Ltd, Semiconductors reserves the right to change specifications without notice.



**ABB Switzerland Ltd
Semiconductors**
Fabrikstrasse 3
CH-5600 Lenzburg, Switzerland

Doc. No. 5SYA1072-04 Dec. 13

Telephone +41 (0)58 586 1419
Fax +41 (0)58 586 1306
Email abbsem@ch.abb.com
Internet www.abb.com/semiconductors