



Test Report				Date of issue: 25.5.2015						
Customer:				Serial No.:						
Customer ref.:				Order No.:						
				Type: M3GP 180MLA 2						
				Product Code: 3GGP181410-ADK						
				Protection type: Ex nA IIC T3 Gc						
				Cert. No.: LCIE 13 ATEX 1034 X / IECEx LCIE 13.0047 X						
Rating:										
		V	Hz	kW	r/min	A	cos φ	Duty		
3-Motor		690	Y 50	22,0	2957	21,7	0,91	S1		
Insul.cl.F		400	D 50	22,0	2957	37,4	0,91	S1		
IP55		660	Y 50	22,0	2952	22,9	0,91	S1		
		380	D 50	22,0	2952	39,5	0,91	S1		
		415	D 50	22,0	2961	36,0	0,91	S1		
		460	D 60	22,0	3563	32,5	0,91	S1		
Eff class IE3		50Hz : IE3-93,2(100%)-93,9(75%)-93,8(50%) 60Hz : IE3-92,9(100%)								
Resistance				Insulation resistance at 22 °C		Overload				
Line				R > 2000 Mohm 1000 V		Current 150 % 120s				
U ₁ - V ₁				Ambient: 21,9 °C		Torque 160 % 15s				
U ₁ - W ₁				0,18800 Ω		Speed 120 % 120s				
V ₁ - W ₁				0,18680 Ω						
				0,18660 Ω						
				High-voltage test winding 2400 V		60 s				
Test		Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	η[r/min]	cos φ	η [%]
No load test			401 D	50	9,4	0,41		3000	0,06	
Locked rotor test			65 D	50	39,2	1,69		0	0,38	
Thermal test (100% load)		71,1	400 D	50	37,3	23,44	22,00	2957	0,91	93,85
Partial load points:										
~75% load		78,6	400 D	50	28,1	17,16	16,20	1969	0,88	94,41
~50% load		34,9	400 D	50	20,2	11,54	10,88	2980	0,83	94,27
~25% load		17,2	400 D	50	13,2	5,86	5,38	2991	0,64	91,82
Temperature rise at rated load.				°C	[K]	Method		Measurement method		
Stator winding :				43,0	1			1 Resistance		
Frame :				22,5	2			2 Thermometer		
Bearing D-end :				24,3	2			3 Thermocouples		
Ambient Temperature :				22	2					
These tests have been carried out on motor no. 3GV1110796867001, on date 2011-09-30 which is identical in electrical design with the above. Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss. On behalf of customer On behalf of manufacturer Date of test Tested by ABB AB, LV Motors, 721 70 Västerås, Sweden Telephone +46 (0)21 32 90 00 Telefax +46 (0)21 32 90 22										

Computer print-out valid without signature.