



Test Report				Date of issue: 29.5.2015						
Customer:				Serial No.:						
				Order No.:						
Customer ref.:				Type: M3GP 250SMA 2						
				Product Code: 3GGP251210-ADK						
				Protection type: Ex tb IIIB/C T125C Db						
				Cert. No.: LCIE 13 ATEX 3067 X/ IECEx LCIE 13.0047 X						
Rating:				V	Hz	kW	r/min	A	cos φ	Duty
3-Motor				690	Y 50	55,0	2975	54,3	0,89	S1
Insul.cl.F				400	D 50	55,0	2975	93,6	0,89	S1
IP65				660	Y 50	55,0	2973	56,4	0,90	S1
				380	D 50	55,0	2973	97,9	0,90	S1
				415	D 50	55,0	2977	91,3	0,88	S1
				460	D 60	55,0	3578	81,5	0,89	S1
Eff class IE3				50Hz : IE3-95,2(100%)-95,4(75%)-95,0(50%) 60Hz : IE3-94,4(100%)						
Resistance				Insulation resistance at 24 °C				Overload		
Line				R > 2000 Mohm 1000 V				Current 150 % 120s		
U ₁ - V ₁				Ambient: 24,0 °C				Torque 160 % 15s		
U ₁ - W ₁				0,04292 Ω				Speed 120 % 120s		
V ₁ - W ₁				0,04191 Ω						
				0,04293 Ω						
				High-voltage test winding 2400 V 60 s						
Test	Torque [Nm]	Line U[V]	f[Hz]	Input I[A]	P1 [kW]	Output P2 [kW]	η[r/min]	cos φ	η [%]	
No load test		400,3 D	50	24,8	0,92		3000	0,05		
Locked rotor test		70,4 D	50	106,7	4,67		0	0,36		
Thermal test (100% load)	176,5	400 D	50	92,9	57,46	55,00	2976	0,89	95,72	
Partial load points:										
~75% load	134,6	400 D	50	72,8	43,83	42,02	2982	0,87	95,87	
~50% load	90,8	400 D	50	53,2	29,74	28,41	2989	0,81	95,52	
~25% load	46,2	400 D	50	35,4	15,55	14,51	2996	0,63	93,31	
Temperature rise at rated load.				°C	K	Method		Measurement method		
Stator winding :				53,9	1			1 Resistance		
Frame :				29,1	2			2 Thermometer		
Bearing D-end :				31,4	2			3 Thermocouples		
Ambient Temperature :				25	2					
These tests have been carried out on motor no. 3GV1110782971002, on date 2011-09-08 which is identical in electrical design with the above. Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss. On behalf of customer On behalf of manufacturer Date of test Tested by ABB AB, LV Motors, 721 70 Västerås, Sweden Telephone +46 (0)21 32 90 00 Telefax +46 (0)21 32 90 22										

Computer print-out valid without signature.