


ROBOT SYSTEMS

MS-55 Conveyor

Transport solutions



The ABB MS-55 Conveyor System provides quality, durability and versatility based on a similar conveyor in production for over 20 years and counting.

Description

The ABB MS-55 conveyor solution is a friction, power roller conveyance capable of transporting palletized assemblies. This product offers a full line of conveyor modules necessary for any major assembly system with a proven track record of durability to provide years of dependable service. Primary applications include engine assembly, transmission assembly, and larger axle assembly.


The conveyor system can be used in synchronous and non-synchronous modes at a speed of 18 meters/minute. Versions are available with a 350 mm height—from top of roller to floor—and can be raised to any practical height.

Customer Benefits

MS-55 conveyor is a highly durable and dependable solution, based on a similar conveyor in production for over 20 years. Our conveyor offers novel solutions such as: internal drive packages, bevel gear driven driveshafts, and a fully open-center design that allows for a greater level of flexibility in placement of operations.

Available Modules


- Transport modules (1, 2 and 3 meters)
- Integral 1HP drive motor package capable of driving 9 m of conveyor for either non-sync or synchronous operation.
- Available $\frac{3}{4}$ HP motor, capable of driving 6 m of conveyor at speeds up to 18 m/minute
- Integral electric pallet stop units capable of staging up to 3 pallets with a max load of 2,100 Kg.
- Integral powered curve units with slaved drives to simplify controls expense.
- Rotate units capable of rotation from 0°-180°



01

01 conveyor drive motor

02 Pallet stop units



02

Conveyor Design Parameters

Description	Values	Units
Load-transport load capacity of this conveyor per meter	100 Kg minimum-550 Kg Max	Kg
Roller Pitch	250 mm standard	mm
Height of conveyor from machine floor	350 mm minimum; 550 mm-800 mm standard; no max height. Custom available	mm
Modular lengths	1 m, 2 m, 3 m, standard; custom lengths available; 3 m max	meters
Speed-operating speed limits of this conveyor	18 m/min. max	meters
Delivery time	12 weeks minimum; 15 weeks standard; 20 weeks max	weeks
Conveyor width/pallet width	500 mm minimum; 600 mm wide X 850 mm long (standard);	mm
Span for legs design-conveyor is supported by the legs with these spans	2 m standard; variable based on surrounding equipment and pallet weight.	meters

ABB Ltd.
1250 Brown Rd.
Auburn Hills, Mi 48326
United States

abb.com/robotics

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG.
Copyright© 2017 ABB
All rights reserved