

Battery Information Sheet

Industrial Nickel-Cadmium cells, modules and battery systems

According to REACH regulation (EC 1907/2006, Art 31) and to OSHA regulation (29 CFR 1910.1200), batteries are **ARTICLES** with no intended release. As such, they are not covered by legal requirements to generate and supply an SDS or an MSDS.

This Battery Information Sheet is provided solely as an information document for the purpose of assisting our customers.

1. IDENTIFICATION

1.1 Product

Industrial Ni-Cd cells and modules or battery systems composed of these cells

1.2 Supplier

Headquarters	Saft S.A.S.						
Address	12 rue Sadi Carnot, 93170 BAGNOLET – France						
Phone/Fax	Phone/Fax: +33 (0)1 49 93 19 18 /+33 (0)1 49 93 19 50						
Factory	Saft Bordeaux						
Address	111-113, boulevard Alfred Daney, 33074 BORDEAUX - France						
Phone/Fax	+33 (0)5 57 10 64 00 /+33 (0)5 57 10 68 77						
Factory	Saft AB						
Address	Jungnergatan – Box 709 SE-572 28 OSKARSHAMN – Sweden						
Phone/Fax	+46 491 68 000/ + 46 491 68 180						
Factory	Saft Nersac						
Address	Zone industrielle, 16440 NERSAC - France						
Phone/Fax	+33 (0)5 45 90 50 26 /+33 (0)5 45 90 50 71						
Factory	Saft Ferak a.s.						
Address	Raskovice 247, 73904 PRAZMO - Czech Republic						
Phone/Fax	+420 558 426 257/+420 558 426 300						
Factory	Saft Valdosta						
Address	711, Industrial Boulevard, VALDOSTA, GA 31601 - USA						
Phone/Fax	Tel/Fax: +1 229 247 2331/+1 229 247 8486						
Factory	Saft Batteries Co., Ltd.						
Address	Zhuhai Free Trade Zone, Lianfeng Road, ZHUHAI 519030, Guangdong Province – China						
Phone/Fax	+86 756 881 9318/+86 756 881 9328						
Factory	Amco Saft India Ltd.						
Address	Hebbal, Bellary – Jakkur Road, Byatarayanapura, BANGALORE 560092 – India						
Phone/Fax	+86 756 881 9318/+86 756 881 9328						

1.3 Emergency contact

Chemtrec US Service within the USA: +800 424 93 00/outside: +1-202-483-7616 for English INRS Orfila: +33(0) 1 45 42 59 59 for French



2. HAZARD IDENTIFICATION

2.1 At cell level

Not chemically dangerous with normal use, where the electrode materials and the electrolyte are enclosed within the cell. In particular, the battery should not be opened or burned. Exposure to /Ingestion of the ingredients contained within could be harmful.

EYE CONTACT: contents of an opened cell (electrolyte) within a battery can cause severe burns.

SKIN CONTACT: Electrolyte solution inside cells can cause severe burns

2.2 At module and battery system level

HIGH VOLTAGE: Always use the large battery systems in a restricted access area. Only authorized people aware of high voltage hazards and trained to work on such systems are allowed to enter in the battery area.

TEMPERATURE: Do not place the batteries on or near fires or other high-temperature locations (> 70°C).

3. COMPOSITION, INFORMATION OR INGREDIENTS

3.1 At cells and modules level

Component	CAS Number	EINECS/ELINCS	Content (wt. %)*
Active nickel**	12054-48-7	235-008-5	4-15
Active cadmium***	21041-95-2	244-168-5	7-12
Cobalt	21041-93-0	244-166-4	0-2
Alkaline electrolyte (pH=14)	N/A	N/A	14-40
Plastics	N/A	N/A	5-20
Steel	N/A	N/A	10-40
Nickel	7440-02-0	231-111-4	5-20
Copper	7440-50-8	231-159-6	0-10

^{*} Quantities may vary with cell model

3.2 At battery system level

Depending on the application and on customers' requirements, modules are assembled either in a plastic, wood or steel container.

4. HANDLING AND STORAGE

STORAGE: Store in a dry place. Since short circuit can cause burn hazard, keep batteries in original packaging until use and do not jumble them.

HANDLING:

- Do not short (+) or (-) terminal with conductors/conductive materials.
- Do not reverse the polarity
- Do not open the battery system or modules

^{**} Active nickel present as Ni(OH)₂ and NiOOH

^{***}Active cadmium present as Cd(OH)₂ and Cd



Do not submit to excessive mechanical stress.

CHARGING/DISCHARGING: Refer to Saft Instructions.

5. PHYSICAL AND CHEMICAL PROPERTIES

The Nickel-Cadmium cell or battery described by this Battery Information Sheet is a manufactured "article" and does not expose the user to hazardous chemicals when used in accordance with manufacturer specifications.

Boiling Point – Not applicable

Vapor Pressure – Not applicable

Vapor Density – Not applicable

Specific Gravity – Not applicable

Physical shape and colour as supplied

6. STABILITY AND REACTIVITY – the battery system is stable when handled and stored according to section 4

MATERIALS TO AVOID: Do not fill cells with acidic electrolyte for e.g. lead/acid battery

CONDITIONS TO AVOID: Avoid exposing battery to fire or temperature over 85°C. Do not disassemble, crush or short-circuit the electrode connections or install with incorrect polarity. Avoid deformation/crushing of cells

7. TOXICOLOGICAL INFORMATION

If the cell is mechanically, thermally or electrically abused to the point of compromising the enclosure toxic and hazardous internal components may be exposed.

- ACUTE TOXICITY

The electrolyte:

Potassium hydroxide LD50/oral/rat: 365 mg/kg

Lithium hydroxide No data available

Fumes containing cadmium compounds:

Cadmium oxide LD50/oral/rat: 1,3 mg/m³ (30 minutes)
Cadmium oxide LD50/oral/mouse: 0,7 mg/m³ (30 minutes)

HEALTH HAZARD

Skin contact can cause severe injury.

Eye contact rapidly causes severe damage. Risk of permanent damage. Ingestion usually results in severe injury. Risk of permanent injuries.

8. ECOLOGICAL INFORMATION

There is no ecological harm when batteries are used correctly and recycled after use has ended.

Spilled/Released electrolyte: The sharp pH rise may cause harmful impact on fish, plankton and stationary organisms. If released to water bodies, the electrolyte contained in the product can be toxic for aquatic organisms because of alkalinity.



9. DISPOSAL CONSIDERATIONS

As with all battery systems, Ni-Cd cells must be collected separately from other waste and recycled – contact your local Saft dealer for information

Never incinerate Ni-Cd cells

Never dispose of Ni-Cd cells in landfills

Europe: End-of-life management must be performed according to directive 2006/66/EC on batteries and accumulators and waste batteries, accumulators and their transposition into each European Union's Member State national legislation. Check with Saft or with your national or local environment authority for details.

Saft has implemented a network of collection and recycling partners for waste industrial Ni-Cd batteries, See:

http://www.saftbatteries.com/TheSaftGroup/Environment/Takebackpolicy/tabid/104/Language/en-US/Default.aspx http://www.saftbatteries.com/TheSaftGroup/Environment/BringBackPoints/tabid/435/Language/en-US/Default.aspx

10. TRANSPORT INFORMATION

10.1 UNITED NATIONS

- UN N° : 2795

10.2 INTERNATIONAL CONVENTIONS

Air : IATASea : IMDG

- Land: ADR (road) or RID (rail) Batteries exempted acc to special paragraph no 598.

UN N ⁰	NAME	RAIL & ROAD (ADR)			SEA (IMDG)			AIR (IATA)						
	Proper	CL	Code	Packing	Labelling	CL	Risk	EmS	Packing	Labelling	CL	Risk	Packing	Labelling
	shipping			group					group				group	
	name													
2795	BATTERIES	8	C 11	None	None	8	None	F-A,	None	8	8	None	None	8
	WET,							S-B						
	FILLED WITH													
	ALKALI													
	Electric storage													

11. REGULATORY INFORMATION

11.1 PRODUCT MARKING (EU)



11.2 PRODUCT MARKING (US)

Regulated marking includes the three pointed chasing arrows symbol, the abbreviation Ni-Cd, and the phrase BATTERY MUST BE RECYCLED OR DISPOSED OF PROPERLY.



12. FIRST AID MEASURES (not anticipated under normal use)

For contact with electrolyte:

EYE CONTACT: Rinse immediately with plenty of water during at least 15-30 minutes, **seek** immediate medical attention/ treatment

SKIN CONTACT: Rinse immediately with plenty of water and seek medical attention/treatment

INHALATION: Remove to fresh air, rinse mouth and nose with water and seek immediate medical attention/treatment.

INGESTION: If the injured is fully conscious, clear mouth with water and afterwards drink plenty of water. Do not induce vomiting. Send immediately to hospital for medical attention/treatment.

13. FIRE FIGHTING MEASURES (not anticipated under normal use)

ESTINGUISHING MEDIA:

Use Class D-Dry chemical and/or sand Do not use water

SPECIAL FIRE FIGHTING PROCEDURES:

Fire fighters should wear self-contained breathing apparatus and full fire-fighting protective clothing.

If overheated by an external source or by internal shorting, the cell may give off potassium hydroxide mist and/or hydrogen gas.

In fire situations, fumes containing cadmium and nickel compounds may develop; danger of serious acute damage to health by inhalation of fumes.

14. EXPOSURE CONTROLS AND PERSONAL PROTECTION* (not necessary under normal use)

Handle an opened battery only in a well ventilated place.

Respiratory protection	Fire fighters should wear self-contained breathing apparatus.
Hand protection	Use polypropylene, polyethylene, rubber or Viton gloves when handling leaking or ruptured cells.
Eye protection	In case of incident or after an abusive use, in case of a leak or cell opening, wear safety glasses with protected side shields or a mask covering the whole face when handling leaking or ruptured cells
Other	In the event of leakage or ruptured cells, wear a rubber apron and protective clothes.

^{*}AFNOR pictograms



15. ACCIDENTAL RELEASE MEASURES (not anticipated under normal use)

INDIVIDUAL PRECAUTIONS:

In case of fire, evacuate the employees from the area until fumes dispersal.

In case of electrolyte leakage, flush electrolyte spillage with plenty of water and beware risk of slipping/falling.

In case of skin or eye contact, inhalation or ingestion, follow the measures described in section 12.

ENVIRONMENTAL PRECAUTION: Avoid sewage, surface water and underground water contamination. Avoid ground and atmosphere contamination.

WAYS OF CLEANING: Using protective glasses and gloves, use absorbent material (sand, earth or vermiculite) to absorb any exuded material. Seal leaking battery (unless hot) and contaminated absorbent material in plastic bag or suitable leak proff container and send for recycling in accordance with local regulations.

16. OTHER INFORMATION

This information has been compiled from sources considered to be dependable and is, to the best of our knowledge and belief, accurate and reliable as of the date compiled. However, neither exhaustively nor perfect reliability can be granted. Information does not imply implicit or specific warranty of it.

This information relates to the specific products designated and may not be valid for such products used in combination with any other materials or in any process. It is the user's responsibility to satisfy himself as to the suitability and completeness of this information for his particular use.

Saft does not accept liability for any loss or damage that may occur, whether direct, indirect, incidental or consequential, from the use of this battery information sheet provided as a service to our customers. Saft does not offer warranty against patent infringement.



12, rue Sadi Carnot 93170 Bagnolet – France Tel.: +33 (0)1 49 93 19 18 Fax: +33 (0)1 49 93 19 69

www.saftbatteries.com

Doc N° BIS06-12-12 Edition: December 2012 Version 1.1

Data in this document is subject to change without notice and becomes contractual only after written confirmation.