

GP50

Vibrating fork level switch

KTEK products

Measurement made easy



Features

- Accepts universal input voltage
- Acceptable for most bulk materials
- Modular & simple design
- Maintenance free
- No calibration required
- Self-cleaning
- Robust fork design with patented piezo crystal sensing element

Options

- Mounting plate/flange
- Extensions to 156 in./3962 mm
- General purpose indicator light

The Model GP50 is a vibrating level switch that detects the absence or presence of dry bulk solids in bins, silos or hoppers. The GP50 provides a contact output indicating a high or low level alarm. Typical Products include lime, styrofoam, flour and plastic pellets. The GP50 can detect products with densities as low as 1.3 pcf (20 kg/m³).

The GP50 is a compact and robust design, suitable for top or side mounting. The constant vibration of the fork tines provides self-cleaning characteristics for products that do not coat or cake. The unique design of the fork and crystal assembly eliminates false level readings.


The GP50 sends a signal from the electronic circuitry to excite a patented piezo element in the probe. This causes the fork to vibrate at a frequency of 125 Hz. If the fork is covered by material, the change in vibration is detected by the circuitry which causes the relay to change state after a one second delay. When the fork is free from material, full vibration resumes and the relay reverts to its normal condition.

APPLICATIONS

The Model GP50 can be used in products that do not have heavy build up on forks. The Model GP50 can handle dense materials such as cement (80 pcf) to extremely light products like styrene (2 pcf). A wide range of applications are also found in dry food processing.

SPECIFICATIONS

Enclosure	Single Compartment Cast Aluminum, Powder Coated
Electrical Connection	(2) 3/4 in. FNPT Connections
Power Supply	Universal Input Voltage: 19 - 253 VAC, 50/60 Hz, 19 - 60 VDC
Fork Material	316 Stainless Steel
Material Specification	Granular bulk solids and powders that do not cake or coat; Minimum density 1.3 pcf (20 kg/m ³); maximum grain size 0.40 in (10mm)
Process Connection	1-1/2 in MNPT
Temperature Range	Sensor: -13 to 302°F / -25 to 150°C Electronics: -13 to 140°F / -25 to 60°C
Output	1 ea SPDT Relay, Maximum Contact Ratings: AC: 253 VAC, 4 A, 500 VA, Resistive DC: 253 VDC, 4 A, 60 W Switch Status Display via Integral LED Signal Delay: Probe free to covered: 1 second Probe covered to free: 1 to 2 seconds Sensitivity: Adjustable in 2 levels
Pressure	Maximum 232 psi / 16 bar
Classification	General Purpose 




ORDERING INFORMATION


GP50/a/b/c/d:

Notes:	1. Accessories must be ordered separately.
/a Insertion Length	
X	Standard length 9 in. / 229 mm
Lxxx	Custom Length; xxx from 10 - 156 in. / 254 to 3962 mm
/b Process Connection	
P	1.5 MNPT (Standard)
WP	Welded Flange, 2" minimum; (Specify Type & Size from SLG-0001-1 Flange Guide)
FL	Flange Shipped Loose with 1-1/2" FNPT Process Connection Drilled & Tapped; 2" minimum; (Specify Type & Size from SLG-0001-1 Flange Guide)
Tnn	Tri-Clamp; Specify 'nn' as follow: 20 = 2.0", 25 = 2.5" up to 6"
/c Approvals	
X	None (Housing is FM Approved)
/d Options	
X	None
L2	120 VAC - Indicating Lamp (General Purposes Only)
L3	240 VAC - Indicating Lamp (General Purposes Only)
R	Remote Housing (20 ft. / 6.1m) max.

GENERAL INSTALLATION GUIDELINES




WIRING CONNECTIONS



DS/GP50-EN Rev. J 04.2014

MP6 MOUNTING PLATE DETAIL REQUIRED FOR PADDLE SWITCH REPLACEMENT



For more information, please contact:

ABB US
18321 Swamp Road
Prairieville, LA 70769
USA
Tel: +1 225 673 6100
Fax: +1 225 637 2525

www.abb.com/level

Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents - in whole or in parts - is forbidden without prior written consent of ABB.

Copyright© 2014 ABB
All rights reserved