Specification sheet

600T EN Series Pressure Transmitters

Model 624EG Gauge Model 624EA Absolute

- Base accuracy : $\pm 0.075\%$
- Reliable inductive sensing system coupled with the very latest digital technologies
 - ensures high performance at all process conditions
- Wide selection of materials and choice of fill fluids including "process-inert"
 - meet virtually all process requirements also protecting application integrity
- HART 4-20 mA, Profibus PA, FF versions with plug-and-play electronics replacement
 - provides interchangeability for upgrading transmitter
- Local snap calibration and full management via hand terminal or PC-running software
- HART®, Profibus PA, FF communications
 - allows integration with standard process bus
- CoMeter display option
 - offers HART Configuration capabilities combined with local indication
- **Ecoefficient life cycle**
 - -ensures low environmental impact in compliance with LCA assessment to ISO 14040 standard



The all new 600T Series transmitter The first choice pressure transmitter is now an even bigger choice



FUNCTIONAL SPECIFICATIONS

Range and span limits

Sensor	Upper	Lower	1	Turndown 624EG			ratio (TD) 624EA		
code	Range Limit (URL)	Range Limit (LRL)	Normal	Extended	Maximum	Normal	Extended	Maximum	
D	160 kPa 1600 mbar 642 inH2O	0.07 kPa abs 0.7 mbar abs 0.5 mmHg	15	60	100	10	20	60	
E	600 kPa 6 bar 87 psi	0.07 kPa abs 0.7 mbar abs 0.5 mmHg	15	60	100	10	20	60	
F	2400 kPa 24 bar 348 psi	0.07 kPa abs 0.7 mbar abs 0.5 mmHg	15	60	100	10	20	60	
W	8000 kPa 80 bar 1160 psi	0.07 kPa abs 0.7 mbar abs 0.5 mmHg	15	60	100	10	20	60	
U	16000 kPa 160 bar 2320 psi	0.07 kPa abs 0.7 mbar abs 0.5 mmHg	15	60	100	10	20	60	
S	42000 kPa 420 bar 6090 psi	1 kPa abs 10 mbar abs 0.15 psia	10	20	30	10	20	30	

Span limits

Maximum span = URL

Minimum recommended span = URL/TD extended (can be further turndown to URL/TD maximum at no stated performances)

Zero suppression and elevation

Zero and span can be adjusted to any value within the range limits detailed in the table as long as:

- calibrated span ≥ minimum span

Damping

Selectable time constant: 0, 0.25, 0.5, 1, 2, 4, 8 or 16 sec.

Volume of process chamber

16 cm³ approx (1 in³)

Volumetric displacement

< 0.020 cm³ (0.0015 in³) for max span.

Electromagnetic compatibility (EMC)

Comply with EN 50081-2 for emission and EN 50082-2 for immunity requirements and test; CE marking.

Turn on time

Operation within specification in less than 2 sec. with minimum damping.

Insulation resistance

 $> 100 \text{ M}\Omega$ @ 1000 Vdc (terminals to earth)

Temperature limits °C (°F):

Ambient (is the operating temperature)

Filling	Model 624EG	Model 624EA
Silicone oil	-40 and +85	-40 and +85
Silicone oil	(-40 and +185)	(-40 and +185)
Inert	-20 and +85	-10 and +65
men	(-4 and +185)	(+14 and +150)
KTFILL-1	-40 and +85	-10 and +85
IXII ILL I	(-40 and +185)	(+14 and +185)

Lower ambient limit for LCD indicators: -20°C (-4°F) Upper ambient limit for CoMeter: +70°C (+158°F)

• Process (1)

Lower limit

- refer to lower ambient limits

Upper limit

- Silicone oil and KTFILL-1 filling: 120°C (248°F) (2)
- Inert fluid filling: 100°C (212°F) (3)
- Process temperature above 85°C (185 °F) requires derating the ambient limits by 1.5: 1 ratio.
- (2) 100°C (212°F) for application below atmospheric pressure
- (3) 65°C (150°F) for application below atmospheric pressure

Storage

Lower limit: -50°C (-58°F); -40°C (-40°F) for LCD indicators Upper limit: +120°C (+248°F); +85°C (+185°F) for LCD indicators

Overpressure limits (without damage to the transmitter)

- Lower: 0.07 kPa abs, 0.7 mbar abs, 0.5 mmHg (double the value with inert filling)
- Upper
 - sensor code D, E, F, W: 14 MPa, 140 bar, 2030 psi
- sensor code U: 25 MPa, 250 bar, 3620 psi
- sensor code S: 65 MPa, 650 bar, 9400 psi

Proof pressure

The transmitter meets SAMA PMC 27.1 requirements and can be exposed without leaking to line pressure of up to

- 31.5 MPa, 315 bar, 4500 psi for sensor codes D, E, F, W, U
- 80 MPa, 800 bar, 11600 psi for sensor code S


ELECTRICAL CHARACTERISTICS AND OPTIONS

HART digital communication and 4 to 20 mA output Power Supply


The transmitter operates from 10.5 to 42 Vdc with no load and is protected against reverse polarity connection (additional load allows operations over 42 Vdc).

For EEx ia and intrinsically safe (FM, CSA and SAA) approval power supply must not exceed 30 Vdc.

MINIMUM OPERATING VOLTAGES



Load limitations - 4-20 mA and HART total loop resistance :



Optional indicators

Output meter (user adjustable)

LCD: 3 1/2-digit with 10 mm (3/8 in) high, 7-segment characters. Engineering unit labels are provided. LCD output meter may be calibrated within the range -1999 to + 1999 with a span adjustable between 100 and 3998 units. (Display of decimal point, if required, is switch selectable)

- analog: 36 mm (1.4 in) scale on 90°

Integral display

LCD: 4-digit with 8 mm. (5/16 in) high, 9-segment alphanumeric characters.

User-definable display mode with HART communication :

- process variable in engineering units, or
- percent of range, or
- process variable in engineering units and percent of range alternating every 3 seconds, or
- process variable in engineering units and digital output (4 to 20 mA) alternating every 3 seconds.

Factory selectable display mode with 4 to 20 mA output :

- percent of range
- percent of range and 4 to 20 mA output alternating every 3 seconds

Display also indicates diagnostic messages.

CoMeter

- 5-digit (± 99999 counts) programmable with 7.6 mm. high (3 in), 7-segment numeric characters plus sign and digital point
- 10-segment bargraph display (10% per segment)
- 7-digit LCD with 6 mm. high (2.3 in), 14-segment alphanumeric characters.

Optional surge protection

Up to 2.5 kV (5 kA discharge current) of 8 μs rise time/20 μs decay.

Output signal

Two-wire 4 to 20 mA dc, user-selectable for linear or square root output, power of 3/2 or 5/2, 5th order or two 2nd order switching point selectable programmable polynomial output.

HART® communication provides digital process variable (%, mA or engineering units) superimposed on 4 to 20 mA signal, with protocol based on Bell 202 FSK standard.

Output current limits (to NAMUR standard)

Overload condition
- Lower limit: 3.8 mA dc
- Upper limit: 20.8 mA dc

Transmitter failure mode (to NAMUR standard)

The output signal can be user-selected to a value of 3.6 or 21.6 mA on gross transmitter failure condition, detected by self-diagnostics.

In case of CPU failure the output is driven <3.6 mA or >21.6 mA.

• Profibus PA output

Power supply

The transmitter operates from 10.5 to 32 Vdc with no polarity. For EEx ia approval power supply must not exceed 15 Vdc. Intrinsic safety installation according to FISCO model.

Current consumption

- operating (quiescent): 10.5 mA

- communicating: 20.5 mA

- fault current limiting: 16 mA max.

Output signal

Physical layer in compliance to IEC 1158-2/EN 61158-2 with transmission to Manchester II modulation, at 31.25 kbit/sec.

Output interface

Profibus PA communication according to Profibus DP50170 Part 2/DIN 19245 part 1-3 compliant to Profiles 3.0 Class A & B for pressure transmitter; ident. number 052B HEX.

Output update time: 25 ms

Function blocks

2 analog input, 1 transducer, 1 physical

Optional indicator

Integral display

- LCD: 4 digit characters, displaying process variable in engineering units or as percentage value.

Display also indicates diagnostic messages.

Transmitter failure mode

On gross transmitter failure condition, detected by self-diagnostics, the output signal can be driven to defined conditions, selectable by the user as safe, last valid or calculated value.

• FOUNDATION fieldbus output

Device type

Link Active Scheduler (LAS) capability implemented

Power supply

The transmitter operates from 9 to 32 Vdc with no polarity. For EEx ia approval power supply must not exceed 24 Vdc. Intrinsic safety installation according to FF application guide

Current consumption

operating (quiescent): 10.5 mAcommunicating: 20.5 mAfault current limiting: 16 mA max.

Output signal

Physical layer in compliance to IEC 1158-2/EN 61158-2 with transmission to Manchester II modulation, at 31.25 kbit/sec.

Function blocks/execution period

2 standard Analog Input blocks / 25 msec. max (each) 1 standard PID block / 70 msec. max.

Additional blocks

Transducer block, 1 standard Resource block, 1 custom Pressure with calibration block

Number of link objects: 25

Number of VCRs: 24

Output interface

FOUNDATION fieldbus digital communication protocol to standard H1, compliant to specification V. 1.4; FF registration IT011000.

Optional indicator

Integral display

- LCD: 4 digit characters, displaying process variable in engineering units or as percentage value.

Display also indicates diagnostic messages.

Transmitter failure mode

The output signal is "frozen" to the last valid value on gross transmitter failure condition, detected by self-diagnostics which also indicate a BAD conditions. If electronic failure or short circuit occur the transmitter consumption is electronically limited at a defined value (16 mA approx), for safety of the network.

PERFORMANCE SPECIFICATIONS

Stated at ambient temperature of 23°C \pm 3K (75°F \pm 5), relative humidity of 50% \pm 20%, atmospheric pressure, zero based range for transmitter with isolating diaphragms in AISI 316 L ss or Hastelloy and silicone oil fill or KTFILL-1 and HART digital trim values equal to 4-20 mA span end points, in linear mode. Unless otherwise specified, errors are quoted as % of span. Some performance data are affected by the actual turndown (TD) as ratio between Upper Range Limit (URL) and calibrated span. IT IS RECOMMENDED TO SELECT THE TRANSMITTER SENSOR CODE PROVIDING THE TURNDOWN VALUE AS LOWEST AS POSSIBLE TO OPTIMIZE PERFORMANCE CHARACTERISTICS.

Accuracy rating

% of calibrated span, including combined effects of terminal based linearity, hysteresis and repeatability.

For fieldbus versions SPAN refer to analog input function block outscale range

Model 624EG

- \pm 0.075% for TD from 1:1 to 15:1 (\pm 0.10% for sensor code S for TD from 1:1 to 10:1)

for TD from 10:1 to 20:1)

$$-\pm 0.005\%$$
 x $\frac{\text{URL}}{\text{Span}}$ for TD from 15:1 to 60:1
($\pm 0.01\%$ x $\frac{\text{URL}}{\text{URL}}$ for sensor code S

Model 624EA

 $-\pm$ 0.075% for TD from 1:1 to 10:1 (\pm 0.10% for TD for sensor code S from 1:1 to 10:1)

$$-\pm 0.0075\%$$
 x $\frac{URL}{Span}$ for TD from 10:1 to 20:1
 $(\pm 0.01\%$ x $\frac{URL}{Span}$ for sensor code S for TD from 10:1 to 20:1)

Optional indicators accuracy

• integral display (microprocessor driven) : no error

ullet analog output meter : \pm 2% full scale deflection

• LCD output meter : \pm 0.1% of calibrated span \pm 1 unit

CoMeter

-digital: \pm 0.10% of max span(16 mA) \pm 1 digit

-analog (bargraph): 10%

Operating influences

Ambient temperature per 20 K (36° F) change between the limits of - 20° C to + 65° C (-4 to + 150° F) :

Model	Sensor code	for TD up to	
624EG	D,E,F,W,U	15:1	± (0.08% URL + 0.15% span)
02420	S	10:1	± (0.10% URL + 0.15% span)
624FA	D,E,F,W,U	10:1	± (0.08% URL + 0.15% span)
02 12/1	S	10:1	± (0.10% URL + 0.15% span)

Multiply by 1.5 the above coefficients for 20 K (36° F) change between the limits of -40 to -20°C (-40 to -4°F) and of +65 to +85°C (+150 to 185°F)

Optional LCD output meter ambient temperature

per 1 K (1.8°F) change between the limits of -20 and +80°C (-4 and + 176°F)

Total effect: \pm (0.0002 x span units + 0.1) of reading.

Optional CoMeter ambient temperature

Total reading error per 20K (36°F) change between the ambient limits of -20 and +70°C (-4 and +158°F) : \pm 0.15% of max span (16 mA).

Supply voltage

Within voltage/load specified limits the total effect is less than 0.005% of URL per volt.

Load

Within load/voltage specified limits the total effect is negligible.

Radio frequency interference

Total effect: less than 0.10% of span from 20 to 1000 MHz and for field strengths up to 30 V/m when tested with shielded conduit and grounding, with or without meter. Meets IEC 801.

Common mode interference

No effect from 100 V rms @ 50 Hz, or 50 Vdc.

Series mode interference

No effect from 1 V rms @ 50 Hz.

Mounting position

No effect.

Stability

± 0.15% of URL over a thirty-six-month period

PHYSICAL SPECIFICATIONS

(Refer to ordering information sheets for variant availability related to specific model or versions code)

Materials

Process isolating diaphragms (*)

AISI 316 L ss, Hastelloy C276 ◊; Tantalum; Hastelloy C276 ◊ on AISI 316 L ss gasket seat.

Process connection (*)

AISI 316 L ss; Hastelloy C ◊.

Sensor fill fluid

Silicone oil (DC200) or inert fill (perfluorinated polyethers Galden \Diamond) or "process-inert" fill (KTFILL-1).

Mounting bracket (**)

Zinc plated carbon steel with chrome passivation; AISI 316 Lss.

Sensor housing: AISI 316 L ss

Electronic housing and covers

Barrel version

- Low-copper content aluminium alloy with baked epoxy finish;
- AISI 316 L ss.

Covers O-ring: Buna N.

Local zero and span adjustments:

Glass filled polycarbonate plastic (removable)

Tagging

AISI 316 ss data plate attached to the electronics housing.

Calibration

- Standard: at maximum span, zero based range, ambient temperature and pressure
- Optional: at specified range and ambient conditions; or at operating temperature.

Optional extras

Mounting brackets

For 60 mm. (2 in) pipes or wall mounting.

Output indicator:

plug-in rotatable type, LCD or analog.

Standard LCD output meter scale is 0 to 100% linear; special linear scale to specified range and engineering unit is available. Standard analog output meter scale is 0 to 100% linear; special graduation is available.

Supplemental customer tag

AISI 316 ss tag screwed/fastened to the transmitter for customer's tag data up to a maximum of 20 characters and spaces on one line for tag number and tag name, and up to a maximum of 3 spaced strings of 10 characters each for calibration details (lower and upper values plus unit). Special typing evaluated on request for charges.

Surge protection (not available with Profibus PA and FF output)

Cleaning procedure for oxygen service

Material traceability; manifold

Environmental protection

Wet and dust-laden atmospheres

The transmitter is dust and sand tight and protected against immersion effects as defined by IEC 529 (1989) to IP 67 (IP 68 on request) or by NEMA to 4X or by JIS to C0920

Hazardous atmospheres

With or without output meter/integral display

INTRINSIC SAFETY/EUROPE:

ATEX/BASEEFA approval

EC-Type Examination Certificate no. BAS 99ATEX 1180
 (HART)

II 1 GDT50°C, EEx ia IIC T6/T5 (-40°C \leq Ta \leq +40°C) T95°C, EEx ia IIC T4 (-40°C \leq Ta \leq +85°C)

- (FOUNDATION Fieldbus)

II 1 GD T70°C, EEx ia IIC T4 (-40°C \leq Ta \leq +60°C)

- EC-Type Examination Certificate no. BAS 00ATEX 1241
- (PROFIBUS-PA)

II 1 GD T70°C, EEx ia IIB T4 (-40°C \leq Ta \leq +60°C)

TYPE "N"/EUROPE :

ATEX/BASEEFA type examination

- Design compliance by Certificate no. BAS 01ATEX 3380X
 (HART)
 - II 3 GD T50°C, EEx nL IIC T5 (-40°C \leq Ta \leq +40°C) T95°C, EEx nL IIC T4 (-40°C \leq Ta \leq +85°C)
- (FOUNDATION Fieldbus)

II 3 GD T70°C, EEx nL IIC T4 (-40°C \leq Ta \leq +60°C)

Design compliance by Certificate no. BAS 01ATEX 3384X
 (PROFIBUS-PA)

II 3 GD T70°C, EEx nL IIB T4 (-40°C \leq Ta \leq +60°C)

FLAMEPROOF/EUROPE:

ATEX/CESI approval;

• EC-Type Examination Certificate no. CESI 00 ATEX 035 II 1/2 GD T80°C, EEx d IIC T6 (-40°C \le Ta \le +70°C) T95°C, EEx d IIC T5 (-40°C \le Ta \le +85°C)

CANADIAN STANDARDS ASSOCIATION and FACTORY MUTUAL:

- Explosionproof: Class I, Div. 1, Groups A, B, C, D
- Dust ignitionproof: Class II, Div. 1, Groups E, F, G
- Suitable for : Class II, Div. 2, Groups F, G; Class III, Div. 1, 2
- Nonincendive: Class I, Div. 2, Groups A, B, C, D
- Intrinsically safe: Class I, II, III, Div. 1, Groups A, B, C,D,E, F, G STANDARDS AUSTRALIA (SAA)

TS/WCA Approval (HART only)

Conformity Certificate no. AUS Ex 3117X
 Ex d IIC T5 (Tamb +85°C)/T6 (Tamb +70°C) Class 1 Zone 1;
 Ex ia IIC T4 (Tamb +85°C) /T5 (Tamb +55°C) T6 Class 1 Zone 0

Process connections

1/2 NPT-f or DIN-EN837-1 - G 1/2"B

Electrical connections

Two 1/2 NPT or M20x1.5 or PG 13.5 or 1/2 GK threaded conduit entries, direct on housing; straight or angle Harting HAN connector and one plug, on request.

Terminal block

HART version

Three terminals for signal/external meter wiring up to 2.5 mm² (14 AWG) and three connection points for test and communication purposes.

Fieldbus versions

Two terminals for signal wiring (bus connection) up to 2.5 mm² (14 AWG)

Grounding

Internal and external 6 mm² (10 AWG) ground termination points are provided.

Mounting position

Transmitter can be mounted in any position.

Electronics housing may be rotated to any position. A positive stop prevents over travel.

Mass (without options)

1.7 kg approx (4 lb); add 1.5 kg (3.4 lb) for AISI housing. Add 650 g (1.5 lb) for packing.

Packing

Carton 26 x 26 x 18 cm approx (10 x 10 x 7 in).

◊ Hastelloy is a Cabot Corporation trademark

♦ Galden is a Montefluos trademark

Wetted parts of the transmitter.

(*) Wetted parts of the transmitter.
 (**) U-bolt material: AISI 400 ss; screws material: high-strength alloy steel or AISI 316 ss.

CONFIGURATION

• Transmitter with HART communication and 4 to 20 mA Standard configuration

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and configured as follows:

Engineering Unit: Specify code option

4 mA:

20 mA: Upper Range Limit (URL)

Output: Linear Damping: 1 sec. Transmitter failure mode: Upscale Software tag characters: Blank

Optional LCD output indicator: 0 to 100.0% linear

Any or all the above configurable parameters, including Lower range-value and Upper range-value which must be the same unit of measure, can be easily changed using the HART hand-held communicator. The transmitter database is customized with specified flange type and material, O-ring and drain/vent materials and meter code option.

Custom configuration (option)

The following data may be specified in addition to the standard configuration parameters:

Descriptor: 16 alphanumeric characters Message: 32 alphanumeric characters

Date: Day, month, year

Damping: Seconds

· Transmitter with Profibus PA communication

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and configured as follows:

Measure Profile: Pressure **Engineering Unit:** kPa

Lower Range Limit (LRL) Output scale 0%: Output scale 100%: Upper Range Limit (URL)

Output:

Hi-Hi Limit: Upper Range Limit (URL) Hi Limit: Upper Range Limit (URL) Low Limit: Lower Range Limit (LRL) Low-Low Limit: Lower Range Limit (LRL) Limits hysteresis: 0.5% of output scale

PV filter: 0 sec. Address (settable by local key): 126

32 alphanumeric characters

Any or all the above configurable parameters, including Lower range-value and Upper range-value which must be the same unit of measure, can be easily changed by a PC running the configuration software Smart Vision with DTM for 600T or 600T template for Siemens Simatic PDM System. The transmitter database is customized with specified flange type and material, Oring and drain/vent materials and meter code option.

Custom configuration (option)

The following data may be specified in addition to the standard configuration parameters:

Descriptor: 32 alphanumeric characters Message: 32 alphanumeric characters

Date: Day, month, year

PV filter: Seconds

Transmitter with FOUNDATION fieldbus communication

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and configured as follows:

Measure Profile: Pressure **Engineering Unit:** kPa

Output scale 0%: Lower Range Limit (LRL) Output scale 100%: Upper Range Limit (URL)

Output: Linear

Hi-Hi Limit: Upper Range Limit (URL) Upper Range Limit (URL) Hi Limit: Low Limit: Lower Range Limit (LRL) Low-Low Limit: Lower Range Limit (LRL) Limits hysteresis: 0.5% of output scale

PV filter time: 0 sec.

Tag: 32 alphanumeric

characters

Any or all the above configurable parameters, including the range values, can be changed using any host compliant to FOUNDA-TION fieldbus. The transmitter database is customized with specified flange type and material, O-ring and drain/vent materials and meter code option.

Available engineering units of pressure measure are:

Pa. kPa. MPa

inH2O@4°C, mmH2O@4°C, psi

inH2O@20°C, ftH2O@20°C, mmH2O@20°C


inHg, mmHg, Torr g/cm², kg/cm², atm


mbar, bar

MOUNTING DIMENSIONS


(not for construction unless certified)


• Sensor codes D, E, F, W, U






• Sensor code S






ELECTRICAL CONNECTIONS

HART Version



• FIELDBUS Versions



HART hand-held communicator may be connected at any wiring termination point in the loop, providing the minimum resistance is 250 ohm. If this is less than 250 ohm, additional resistance should be added to allow communications.

ORDERING INFORMATION model 624EG Gauge Pressure Transmitter

Select one character or set of characters from each category and specify complete catalog number.

Refer to supplementary code and specify another number for each transmitter if additional options are required.

PR	ODUCT CODE	abcde fg	h i j k l	lm n op		
		<u> </u>	\top \top \top \top			
D.4.0	T MODEL					
	SE MODEL		0 0			
вот	TOM WORKS —					
	JNTING BRACKET ——					
	PUTCTRICAL CERTIFICATION					
TOP	WORKS					
ELE	CTRICAL OPTIONS					
					Ī	
abc	de BASE MODEL - 1st to	5th characters				Code
	Gauge pressure transm					624EG
	Cauge pressure transm	iittoi				V
	SENSOR					
f	Span limits - 6th charact	ter				
	2.67 and 160 kPa	26.7 and 1600 mbar	10.7 and 642 inH ₂ O			D
	10 and 600 kPa 40 and 2400 kPa	0.1 and 6 bar 0.4 and 24 bar	1.45 and 87 psi 5.8 and 348 psi			E F
	133 and 8000 kPa	1.33 and 80 bar	19.3 and 1160 psi			W
	267 and 16000 kPa	2.67 and 160 bar	38.7 and 2320 psi			Ü
	2100 and 42000 kPa	21 and 420 bar	305 and 6090 psi			S
	7th character					
g	Diaphragm material (*)			Fill fluid		
٣	AISI 316 L ss			Silicone oil (**)		2
	Hastelloy C276 ◊ (AISI sea	at)		Silicone oil (**)	(Note)	6
	Hastelloy C276 ◊			Silicone oil (**)		3
	Tantalum			Silicone oil (**) Inert fluid		5
	AISI 316 L ss Hastelloy C276 ◊ (AISI sea	at)		Inert fluid	(Note)	A 7
	Hastelloy C276 ◊	aty		Inert fluid	(**************************************	В
	Tantalum			Inert fluid		D
	AISI 316 L ss	-4\		KTFILL-1 (**) KTFILL-1 (**)	(Note)	L
	Hastelloy C276 ◊ (AISI sea	at)		KTFILL-1 (**)	(Note)	P N
·	•	sensor code S at position "f"				
	BOTTOM WORKS	04h				
h	Process connection (*) - Material	· otii ciiaiactei		Connection		
ш	AISI 316 L ss			1/2" NPT-f		1
		um diaphragm code 5 and D at p	position "g")	DIN-EN837-1 - G 1/2"B		3
	Hastelloy C ◊	2401 11 1 0 4	11	1/2" NPT-f DIN-EN837-1 - G 1/2"B		A
	(Not applicable with AISI 3	316 L ss diaphragm code 2, A an	id L at position "g")	DIN-EN837-1 - G 1/2"B		С
Γ.	9th character					
i						
	Use code					0
	MOUNTING BRACKET -	10th character				
L	Material					
	None Carbon steel Not avail	able with AISI 316 L ss housing	material code A. C. D. F	at position "n"		2
	AISI 316 L ss	able will 7 (101 0 10 E 33 floading	material code 71, 0, D, 1	at position in		3
	Lazar III.					
k	11th character					
	Use code					0
	12th character					
T	OUTPUT					
	HART digital communication	on and 4 to 20 mA				G
	Profibus PA communication	on				P
	FOUNDATION Fieldbus C	communication				F
	Compliance to NACE class !! h	olting according to appoint the MPO	175 latest revision ^	Hastallov is a Cabat Carrer	ation tradomark	
(*)	Process wetted-parts	olting, according to specification MR0	113, Ialest Tevision V	Hastelloy is a Cabot Corpora	auon uduemdik	
(**)	Not available for oxygen service	e				

ORDERING INFORMATION model 624EG Gauge Pressure Transmitter

m ELECTRICAL CERTIFICATION - 13th character

1
F
L
N
8
W

Note: not available with output code P and F at position "I"

TOP WORKS - 14th character

n Housing material	Electrical connection	
	1/2" NPT	1
	M20 x 1.5 (CM 20)	2
Aluminium alloy	Pg 13.5	3
(Barrel version)	1/2" GK	4
	Harting HAN connector - straight entry (Note 1, 2)	5
	Harting HAN connector - angle entry (Note 1, 2)	6
	1/2" NPT	Α
AISI 316 L ss	M20 x 1.5 (CM 20)	С
(Barrel version)	Pg 13.5	D
	1/2" GK	F

Note 1 : requires certification code 1 at position "m"

Note 2 : not available with output code P and F at position "I"

ELECTRICAL OPTIONS - 15th character

O Internal meter type

None		1
Digital LCD output indicator linear 0-100%, user scalable	(Note)	3
Digital LCD output indicator linear scale (specify range and engineering units)	(Note)	5
Analog output indicator linear 0-100% scale	(Note)	7
Analog output indicator, special graduation (to be specified for linear scale)	(Note)	9
Digital LCD integral display		Α
Digital LCD integral display and digital LCD output indicator linear 4-20 mA	(Note)	С
Digital LCD integral display and analog output indicator linear 0-100% scale	(Note)	E
Programmable signal meter and HART configurator (CoMeter)	(Note)	Р
Programmable signal meter and HART configurator (CoMeter) and digital LCD integral display	(Note)	R

Note: not available with output code P and F at position "I"

16th character

р	Electrical options	Labels language	
		English	1
	Standard terminal block	German	2
		Italian	7
		English	3
	Surge protector (Note)	German	4
		Italian	8
		English	5
	Terminal block for external meter (Note)	German	6
		Italian	9

Note: not available with output code P and F at position "I"

ORDERING INFORMATION model 624EA Absolute Pressure Transmitter

Select one character or set of characters from each category and specify complete catalog number.

Refer to supplementary code and specify another number for each transmitter if additional options are required.

PR	ODUCT CODE	abcde fg	h i j k l	m n op	·
SEN BOT MOL OUT	E MODEL SOR TOM WORKS INTING BRACKET PUT		0 0		
	CTRICAL CERTIFICATION WORKS				
	CTRICAL OPTIONS				
abco	de BASE MODEL - 1st to	5th characters			Code
	Absolute pressure trans				624EA
	7 isociate procedio tranc				
	SENSOR				
f	Span limits - 6th charact				
	8 and 160 kPa 30 and 600 kPa	80 and 1600 mbar 0.3 and 6 bar	60 and 1200 mmHg 4.35 and 87 psi		<u>D</u>
	120 and 2400 kPa	1.2 and 24 bar	17.4 and 348 psi		
	400 and 8000 kPa	4 and 80 bar	58 and 1160 psi		W
	800 and 16000 kPa	8 and 160 bar	116 and 2320 psi		U
	2100 and 42000 kPa	21 and 420 bar	305 and 6090 psi		S
	7th character				
g	Diaphragm material (*)			Fill fluid	
\neg	AISI 316 L ss			Silicone oil (**)	2
	Hastelloy C276 ◊ (AISI sea	at)		Silicone oil (**) (Note)	6
-	Hastelloy C276 ◊ AISI 316 L ss			Silicone oil (**) Inert fluid	3 A
	Hastelloy C276 ◊ (AISI sea	at)		Inert fluid (Note)	7
	Hastelloy C276 ◊			Inert fluid	В
	AISI 316 L ss			KTFILL-1 (**)	L
-	Hastelloy C276 ◊ (AISI sea Hastelloy C276 ◊	at)		KTFILL-1 (**) (Note) KTFILL-1 (**)	P N
L	·	ensor code S at position "f"		100 EE 1 ()	· ·
	11010 . Hot available with c	onder dede e at position 1			
	BOTTOM WORKS				
h	Process connection (*) -	8th character			
Ln_	Material			Connection	
	AISI 316 L ss			1/2" NPT-f DIN-EN837-1 - G 1/2"B	<u>1</u>
	Hastelloy C ◊			1/2" NPT-f	A
	(Not applicable with AISI 3	16 L ss diaphragm code 2, A ar	d L at position "g")	DIN-EN837-1 - G 1/2"B	С
i	9th character				
	Use code				0
$\overline{}$	MOUNTING BRACKET - 1	0th character			
Ĺ	Material				
-	None Not avail	able with AICL 24C Lee beviews	material and A. C. D. F	at position "p"	1
ł	Carbon steel Not availa AISI 316 L ss	able with AISI 316 L ss housing	material code A, C, D, F	- at position in	3
L					- J
k	11th character				
	Use code				0
	12th character				
П	OUTPUT				
لنا	HART digital communication	on and 4 to 20 mA			G
	Profibus PA communicatio	n			P
	FOUNDATION Fieldbus Co	ommunication	-		F

Compliance to NACE class II bolting, according to specification MR0175, latest revision

^(*) Process wetted-parts

^{**)} Not available for oxygen service

ORDERING INFORMATION model 624EA Absolute Pressure Transmitter

m ELECTRICAL CERTIFICATION - 13th character

П	General Purpose	1
	ATEX Group II Category 1/2 GD - Flameproof EEx d CESI approval	F
	ATEX Group II Category 1 GD - Intrinsic Safety EEx ia BASEEFA approval	L
	ATEX Group II Category 3 GD - Type of protection "N" EEx nL design compliance	N
	Factory Mutual (FM) and Canadian Standard Association (CSA) approvals (only with 1/2" NPT and M20 electrical connection)	8
Г	Intrinsic Safety and Flameproof to Standards Australia SAA approval Ex ia IIC T6/T5/T4 + Ex d IIC T6/T5 (Note)	W
ᆫ		

Note: not available with output code P and F at position "I"

TOP WORKS - 14th character

n	Housing material	Electrical connection	
		1/2" NPT	1
		M20 x 1.5 (CM 20)	2
	Aluminium alloy	Pg 13.5	3
	(Barrel version)	1/2" GK	4
	,	Harting HAN connector - straight entry (Note 1, 2)	5
		Harting HAN connector - angle entry (Note 1, 2)	6
		1/2" NPT	Α
	AISI 316 L ss	M20 x 1.5 (CM 20)	С
	(Barrel version)	Pg 13.5	D
	·	1/2" GK	F

Note 1 : requires certification code 1 at position "m"

Note 2 : not available with output code P and F at position "I"

ELECTRICAL OPTIONS - 15th character

o Internal meter type

,		
None		1
Digital LCD output indicator linear 0-100%, user scalable	(Note)	3
Digital LCD output indicator linear scale (specify range and engineering units)	(Note)	5
Analog output indicator linear 0-100% scale	(Note)	7
Analog output indicator, special graduation (to be specified for linear scale)	(Note)	9
Digital LCD integral display		Α
Digital LCD integral display and digital LCD output indicator linear 4-20 mA	(Note)	С
Digital LCD integral display and analog output indicator linear 0-100% scale	(Note)	E
Programmable signal meter and HART configurator (CoMeter)	(Note)	Р
Programmable signal meter and HART configurator (CoMeter) and digital LCD integral display	(Note)	R

Note: not available with output code P and F at position "I"


16th character

р	Electrical options	Labels language	
		English	1
	Standard terminal block	German	2
		Italian	7
	Surge protector (Note)	English	3
		German	4
		Italian	8
		English	5
	Terminal block for external meter (Note)	German	6
		Italian	9

Note : not available with output code P and F at position "I" $\,$

ORDERING INFORMATION

Select one character or set of characters from each category and specify complete catalog number in addition to each transmitter code, if required.



ab	BASE MODEL - 1st to 2nd characters	Code	
	Supplementary code	SC]

c CONFIGURATION - 3rd charact	er
-------------------------------	----

Standard - Pressure = kPa; Temperature = deg. C	1	
Standard - Pressure = inH2O/psi (@ 20°C); Temperature = deg. F	2	
Standard - Pressure = inH2O/psi (@ 4°C); Temperature = deg. F	3	
Standard - Pressure = inH2O/psi (@ 20°C); Temperature = deg. C		
Standard - Pressure = inH2O/psi (@ 4°C); Temperature = deg. C	5	
Custom	С	

CALIBRATION - 4th character

	CALIBRATION - 4th character			
d	Calibration range	Calibration	Certificate	
	Standard (max span = 0 to URL)	Reference temperature	None	1
		Telefence temperature	Yes (3 copies)	2
		Operating temperature	None	3
			Yes (3 copies)	4
	At specified range	Reference temperature	None	5
		received temperature	Yes (3 copies)	6
		Operating temperature	None	7
		Operating temperature	Yes (3 copies)	8

5th character

е	PROCEDURE	Material traceability	
	None	None	0
		To EN10204 - 3.1.B (certificates for flanges, adapters, diaphragms)	Α
		To EN10204 - 2.1 (declaration for instrument)	В
	Oxygen service cleaning (Note 1)	None	2
		To EN10204 - 3.1.B (certificates for flanges, adapters, diaphragms)	С
		To EN10204 - 2.1 (declaration for instrument)	F

Note 1 : not applicable to transmitter model 624EG/EA (sensor code S)

f	f INTEGRAL MOUNTING OF ASSOCIATED INSTRUMENTATION - 6th character			
	None		0	١
	For valve manifold	Ιľ	1	İ



The Company's policy is one of continuous product improvement and the right is reserved to modify the specifications contained herein without notice.

ABB Instrumentation spa

Via Statale 113 22016 Lenno (Como) Italia Tel. 0344 58111 Facsimile 0344 56278

ABB Automation Ltd.

Howard Road St. Neots, Cambs. England PE19 3EU Tel. (01480) 475321, Facsimile (01480) 217948

ABB Automation Inc.

125 East County Line Road Warminster, Pa. 18974-4995 USA Tel. (215) 674-6693/6320/6777 Facsimile (215) 674-7184