

ABB MEASUREMENT & ANALYTICS | DATA SHEET

LevelMaster

Level sensor



Introduction

The Totalflow LevelMaster uses a patented multilayer transformer technology to provide high precision liquid level measurements.

In service at thousands of production and gathering sites, Totalflow's digital level sensors can be used to:

- Prevent spills & detect leaks
- Manage production inventories
- Ensure accurate custody transfer
- · Generate Run-Tickets automatically
- · Automate pumps & disposal systems
- · Schedule haul-off trucks
- · Minimize time on tanks

Floats are available for measuring oil, water and emulsion levels up to 25 feet in depth with a relative accuracy of 0.1 inch. The floats can be installed to measure only the top surface level (single float) or both surface and interface levels (dual floats). In addition to level measurement, an RTD measures the liquid temperature at the load line.

Data from the level sensors can be accessed locally, near the tank, or remotely via wired or wireless networking.

In-field interfaces and software options

- Push-to-Read display near the tank in a Totalflow XSeries
- MasterLink software on PC connected directly to the LevelMaster sensor
- PCCU software on PC connected to Totalflow XSeries

Remote interface software options

- WinCCU software on a PC connected to an XSeries or LMC7100 device
- TF.NET software on a PC in a web browser for multiple client access to level data
- SCADAvantage software on a PC for multiple client access to dashboard views for comprehensive tank management
- Automated Voice Alarm System calls you when an alarm sets

Communications options

- RS-485 port with open ASCII protocol
- Licensed and spread spectrum radio
- · Microwave and leased lines
- · Cellular and cellular digital packet data
- · LAN/WAN and satellite

Automation

Powerful and highly adaptable level measurement applications can be configured in PCCU and deployed on Totalflow XSeries flow computers for standalone operation. These applications can measure inputs, compute control logic and drive output channels to automate the management of liquids at a tank battery. SCADAvantage can gather data from multiple tank batteries and automate business processes for optimal production and disposal of liquids for your enterprise.

Features

- · High-precision level measurement
- · Both surface and interface level sensing
- Customizable alarms & reports
- Ultra low power consumption
- Highly adaptable data collection and automation capabilities
- Works with your existing Totalflow computers and RTUs
- Simple one-time installation & calibration (set it and forget it)
- Same, familiar trending tool as other Totalflow applications
- Meets or exceeds requirements for Federal Bureau of Land Management (BLM)
- Optional high level switch for failsafe shutdown
- Dynamic temperature correction during transfer

Specifications

| Measurement | |
|-----------------------------|---|
| Length (depth) | 2-25 feet (0.6 to 7.6 meters) in 1 foot (0.31 meters) increments |
| Relative level accuracy | Standard: ± 0.1 inches (2.5 mm) High: ± 0.05 inches (1.25 mm) |
| Level resolution | ± 0.01 inches (0.25 mm) |
| Level repeatability | ± 0.05 inches (1.25 mm) |
| Temperature sensor accuracy | ± 1.8° F (1.0° C) |
| Temperature sensor range | 0° F to 185° F (–17.7° C to 85° C) |
| Pressure | Single or dual floats: Non-pressurized tanks Single float: Up to 200 psig (standard) - (higher pressure on request) |

| Materials and dimensions | | |
|---|--|--|
| Casing material | Fiberglass or stainless steel (pressurized tanks | |
| Casing outer diameter | 1.95 inches (48.5 mm) | |
| Float material | PPS material with Nitrophyl Gravity of the oil | |
| Float outer diameter | 3.17 inches (80.5 mm) (2.83 inch single float on request) | |
| Reducer bushing and compression fitting | Fits standard 3 and 4 inch (10.16 mm) tank port | |
| Temperature sensor location | 12 inches (300 mm) from bottom | |

| Power | | |
|----------------|--|--|
| Supply voltage | 9-15.5 V DC | |
| Current | 40 mA transmitting; 1 mA standby | |
| Power cycling | Available for optimal power management | |

| Environmental/Safety | | |
|---|---|--|
| Operating temperature | Non-submerged: -20° F to 185° F (-29° C to +85° C) Submerged, single float: 26° F to 185° F (-3° C to +85° C) Submerged, dual floats: 26° F to 140° F (-3° C to +60° C) | |
| CSA approved for intrinsically safe operation | Class I, Div 1, Group D: 4 level sensors max / barrier Class I, Div 1, Group C & D: 3 level sensors max / barrier | |

| Communications | 5 |
|----------------|--|
| Output | Standard digital serial half duplex RS485, ASCII protocol |
| Speed | 1200 or 9600 bps |



ABB Inc.

Measurement & Analytics

Quotes: totalflow.inquiry@us.abb.com
Orders: totalflow.order@us.abb.com
Training: totalflow.training@us.abb.com
Support: totalflowsupport@us.abb.com

+1 800 442 3097 (opt. 2)

Main Office

7051 Industrial Boulevard Bartlesville, OK 74006 Ph: +1 918 338 4888

www.abb.com/upstream

California Office

4300 Stine Road Suite 405-407 Bakersfield, CA 93313 Ph: +1 661 833 2030

Kansas Office

2705 Centennial Boulevard Liberal, KS 67901 Ph: +1 620 626 4350

Texas Office - Odessa

8007 East Business 20 Odessa, TX 79765 Ph: +1 432 272 1173

Texas Office - Houston

3700 West Sam Houston Parkway South, Suite 600 Houston, TX 77042 Ph: +1 713 587 8000

Texas Office - Pleasanton

150 Eagle Ford Road Pleasanton, TX 78064 Ph: +1 830 569 8062

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.

© Copyright 2019 ABB. All rights reserved.