# AT200VP Specialty Level Instrument

# Valve positioner K-TEK Products



#### Introduction

The AT200 Valve Positioner is a compact, high accuracy valve position transmitter that uses ABB's patented Magnetostrictive sensing technology. In the valve positioning application, the transmitter is bolted to the yoke of the actuator with two mounting brackets that are supplied with the transmitter. A third bracket is secured to the stem connector. This bracket holds the magnet that provides the signal to the transmitter. The clearance between the magnet and the sensing tube of the AT200 is approximately 1/4" (6.35mm). This dimension is not critical and can vary slightly along the length of the transmitter. The magnet should not contact the sensing tube at any point in its travel. The brackets supplied with the transmitter do not include mounting holes. These will be drilled in the field to accommodate the various sizes of actuators that will be encountered. The transmitter is calibrated in place by using either the integral pushbuttons or LCD. The vertical alignment of the transmitter is not critical and the zero and span can be set anywhere along the active portion of the transmitter. There is an unusable range of 2" (50.8 mm) at the transmitter and 3.5" (88.9 mm) on the bottom end of the sensing tube.

#### Features

- High accuracy .01 % of full scale with patented magnetostrictive sensing technology
- No direct connection between valve stem and transmitter
- Microprocessor based
- Simple calibration: pushbutton or HART Protocol
- Never requires recalibration
- Dual compartment housing with separate field terminal compartment
- Field replaceable module
- Built-in RFI/EMI filter

#### Options

- Local indication with scrolling LCD display
- HART protocol output
- Honeywell DE output
- Foundation Fieldbus output
- Glass viewing window
- 316L SS enclosure
- 21-segment strapping table



# SPECIFICATIONS

Electronic Transmitter Housing Type

Electrical Connection Mounting Measuring Range Repeatability Non-Linearity Accuracy Loop Supply Voltage Polarity Protection Output

Dampening Burnout Temperature Humidity **Sensor Tube** Material Approvals

Explosion Proof Powder Coated Cast Aluminum, Dual Compartment Standard Optional 316L Stainless Steel, Dual Compartment 1/2" FNPT Includes magnet with valve stem bracket and two (2) activator yoke mounting brackets 0.5 - 30 ft. (0.15 - 9.1 m) 0.005% of full scale or 0.015", whichever is greater 0.01% of full scale or 0.35", whichever is greater 0.01% of full scale or 0.050", whichever is greater 13.5 to 36 VDC Diode in series with loop Standard 4-20 mAdc; Manual field calibration via pushbuttons; Optional: HART protocol, Honeywell DE, Foundation Fieldbus ITK4.01 Compliant Field Adjustable by means of pushbuttons. Range: 0.1 to 36 seconds Jumper selectable upscale (21 mAdc) or downscale (3.6 mAdc) -40 to 170°F (-40 to 77°C) ambient 0 to 100% R.H., non-condensing 316L Stainless Steel standard FM Factory Mutual Research Corp and CSA Canadian Standards Association Hazardous XP/ I /1/ ABCD / T6; DIP / II, III / 1 / EFG / T6 IS / I / 1 / CD / T4—ELE0001 / A [excludes RI (secondary analog output) & Honeywell DE option] NI / I / 2 / ABCD / T4 Type 4X ATEX: € II 1/2 GD EEx d IIC T6 T80°C; 002 ATEX 132659 Flameproof: D 02 ATEX 132658 € II 1/2 GD EEx ia IIB T6; Intrinsically Safe:

[excludes RI secondary analog output) & Honeywell DE option] Ingress protection classification: IP67

#### **ORDERING INFORMATION**

# AT200/a/b/c/d/e/f/g/h:

/a Mounting

L

A S

- B Bottom Connected Electronic Housing
- BW Bottom Connected Electronic Housing with Window cover
- T Top Connected Electronic Housing
- TW Top Connected Electronic Housing with Window Cover
- /b Transmitter Configuration
  - Standard Local Transmitter
    - Process Temperature up to 200°F (93°C)
- /c Transmitter Housing
  - Standard Dual Compartment Aluminum Housing
  - Dual Compartment Stainless Steel Housing

### /d Probe Type

R1 5/8" OD Probe Standard

- /e Electronic Module with One Analog Output
  - X N M4A C
    - One Level, LCD Indicator. HART Protocol or Honeywell DE Protocol (Default is HART) Add "D" suffix to module option for Honeywell DE (class 0 support) Add "F" suffix to module option for Foundation Fieldbus ITK 4.01 compliant
      - Add "S" suffix to module option for 21 segment strapping table (not available with "D" suffix)
- /f Second Analog Output (Hart protocol only)

#### X None

- RI Second Electronic Module with One Analog Output and LCD Indicator
  - Notes: 1. Available only with HART Protocol module M4A
    - 2. Housing type will be the same as primary transmitter housing (/c above)


### /g Approvals

- FM Factory Mutual and CSA Canadian Standard Association
- CEX ATEX Flameproof, NEPSI
- CEI ATEX I.S., NEPSI
- /h Measuring Length
  - ML Specify the measuring length in inches or mm



# Available Accessories:

- VP: Valve Positioning Transmitter (This ordering code is required to order AT200 with positioning capabilities)
- MGT: Magnet Assembly (includes magnet with valve stem bracket and two actuator yoke mounting brackets) Note: <u>This accesory is required</u>. Please specify the following: Valve Type/Size, Actuator Type/Size, and Valve
  - Stem length and O.D. dimensions.
- VI-Transmitter: Vibration Isolator (One Isolator includes: one rubber grommet one (1) split ring collar and one mounting bracket)
- M20 ISO Fitting: M20 Female Electrical Connection



# Contact us

### ABB Inc.

18321 Swamp Road Prairieville, LA 70769 USA Phone: +1 225 673 6100 Service: +1 225 677 5836 Fax: +1 225 673 2525 Service e-mail: service@us.abb.com

#### www.abb.com/level

# Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents - in whole or in parts - is forbidden without prior written consent of ABB.

Copyright© 2012 ABB All rights reserved



