

2TMD041800D0014 | 23.11.2022

# Product manual ABB-Welcome IP

H8138.K-. IP keypad outdoor station



| 1  | Notes                  | Notes on the instruction manual |                                                  |    |  |  |
|----|------------------------|---------------------------------|--------------------------------------------------|----|--|--|
| 2  | Safety4                |                                 |                                                  |    |  |  |
| 3  | Intend                 | Intended use5                   |                                                  |    |  |  |
| 4  | Environment            |                                 |                                                  |    |  |  |
| 4  |                        |                                 |                                                  |    |  |  |
|    | 4.1                    | ABB devi                        | ices                                             | 6  |  |  |
| 5  |                        | •                               | tion                                             |    |  |  |
|    | 5.1                    | Device ty                       | /pe                                              | 7  |  |  |
|    | 5.2                    | Control e                       | elements                                         | 8  |  |  |
|    | 5.3                    | Terminal                        | description.                                     | 9  |  |  |
|    | 5.4                    | Lock type                       | e and connection                                 | 10 |  |  |
| 6  | Techr                  | nical data                      |                                                  | 11 |  |  |
| 7  | Moun                   | ting/Installa                   | ation                                            | 12 |  |  |
|    | 7.1                    | Requirem                        | nent for the electrician                         | 12 |  |  |
|    | 7.2                    | Mounting                        | ]                                                | 13 |  |  |
|    |                        | 7.2.1                           | Preparation                                      | 13 |  |  |
|    |                        | 7.2.2                           | Installation height                              | 13 |  |  |
|    |                        | 7.2.3                           | Surface-mounted installation                     | 15 |  |  |
|    |                        | 7.2.4                           | Flush-mounted installation                       | 16 |  |  |
|    |                        | 7.2.5                           | Cavity wall installation                         | 18 |  |  |
|    |                        | 7.2.6                           | Dismantling                                      | 19 |  |  |
| 8  | Comr                   | nissioning.                     |                                                  | 20 |  |  |
|    | 8.1                    | Accessin                        | g the "Menu" screen                              | 20 |  |  |
|    | 8.2                    | 8.2 Engineering settings        |                                                  |    |  |  |
|    | 8.3                    | Access c                        | control settings                                 | 22 |  |  |
|    | 8.4                    | System s                        | settings                                         | 23 |  |  |
|    | 8.5                    | Logical a                       | ddress settings                                  | 25 |  |  |
| 9  | Opera                  | ation                           |                                                  | 26 |  |  |
|    | 9.1 Calling a resident |                                 |                                                  | 26 |  |  |
|    | 9.2                    | Calling a                       | guard unit                                       | 26 |  |  |
|    | 9.3                    |                                 |                                                  |    |  |  |
|    |                        | 9.3.1                           | Releasing a lock by swiping cards                |    |  |  |
|    |                        | 9.3.2                           | Releasing a lock by pressing the exit button     |    |  |  |
|    |                        | 9.3.3                           | Releasing a lock by entering the public password | 28 |  |  |
|    |                        | 9.3.4                           | Releasing a lock by entering a private password  | 29 |  |  |
| 10 | Cybei                  | security                        |                                                  | 30 |  |  |
|    | 10.1 Disclaimer        |                                 |                                                  | 30 |  |  |
|    | 10.2                   | Performa                        | ance and service                                 | 30 |  |  |
|    | 10.3                   |                                 |                                                  |    |  |  |
|    |                        |                                 | d                                                |    |  |  |

# Table of contents

|      | 9                           |     |
|------|-----------------------------|-----|
|      | Password rule               |     |
| 10.6 | Malware prevention solution | .31 |
| 10.5 | Backup/Restore              | .31 |

# 1 Notes on the instruction manual

Please read through this manual carefully and observe the information it contains. This will assist you in preventing injuries and damage to property and ensure both reliable operation and a long service life for the device.

Please keep this manual in a safe place. If you pass the device on, also pass on this manual along with it. ABB accepts no liability for any failure to observe the instructions in this manual.

# 2 Safety



#### Warning

Electric voltage!

Dangerous currents flow through the body when coming into direct or indirect contact with live components.

This can result in electric shock, burns or even death.

- Disconnect the mains power supply prior to installation and/or disassembly!
- Permit work on the 100-240 V supply system to be performed only by specialist staff!

## 3 Intended use

As part of the ABB-Welcome IP system, this device can only be used with accessories from that system.

#### Security mode

This outdoor station runs in "Security mode" by default to guarantee high security.

In "Security mode", this outdoor station requires a certificate issued by the management software before it can function normally.

#### Compatible mode

If there is no management software, this outdoor station needs to run in "Compatible mode" to function normally. It can be set on indoor station. Please refer to the product manual for IP touch 7".

#### Video privacy



#### Video privacy

Making and saving video recordings can infringe on personal rights! Always observe the applicable legal and labeling requirements for the placement and operation of video components!

#### 4 Environment



#### Consider the protection of the environment!

Used electric and electronic devices must not be disposed of with household waste.

 The device contains valuable raw materials that can be recycled. Therefore, dispose of the device at the appropriate collecting facility.

#### 4.1 ABB devices

All packaging materials and devices from ABB bear the markings and test seals for proper disposal. Always dispose of the packing materials and electric devices and their components via an authorized collection facility or disposal company.

ABB products meet the legal requirements, in particular the laws governing electronic and electrical devices and the REACH ordinance.

(EU-Directive 2012/19/EU WEEE and 2011/65/EU RoHS)


(EU-REACH ordinance and law for the implementation of the ordinance (EG) No.1907/2006)

# 5 Product description

# 5.1 Device type


| Article<br>number | Product ID      | Product name                           | Colour             | Size (HxWxD)<br>Unit: mm |
|-------------------|-----------------|----------------------------------------|--------------------|--------------------------|
| H81383K-S         | 2TMA130010X0037 | OS, IPkeypad, with display, ID         | Stainless<br>steel | 135 x 349 x 29           |
| H81384K-S         | 2TMA130010X0038 | OS, IPkeypad, with display, Desfire/IC | Stainless<br>steel | 135 x 349 x 29           |
| H81381K-W         | 2TMA130010W0033 | OS, IPkeypad, with display, ID         | White              | 135 x 349 x 29           |
| H81382K-W         | 2TMA130010W0037 | OS, IPkeypad, with display, Desfire/IC | White              | 135 x 349 x 29           |

#### 5.2 Control elements



| No. | Function                              |
|-----|---------------------------------------|
| 1   | Camera                                |
| 2   | Speaker and microphone integration    |
| 3   | Display module with ID/IC card reader |
| 4   | Keypad                                |
| 5   | End strip                             |


### 5.3 Terminal description



| No. | Function                                                      |  |  |
|-----|---------------------------------------------------------------|--|--|
| 1   | Reset button                                                  |  |  |
| 2   | Micro USB update connector                                    |  |  |
| 3   | Plug-in clamps (DC+-GND) for standalone power supply          |  |  |
| 4   | Plug-in clamps (LOCK-GND) for door opener                     |  |  |
| 5   | Plug-in clamps (COM-NC-NO) for floating output, door opener   |  |  |
| 6   | LAN (PoE)                                                     |  |  |
| 7   | Connector for next module                                     |  |  |
| 8   | Connector for exit button                                     |  |  |
| 9   | Connector for the sensor used for door status detection       |  |  |
| 10  | Connector for 5" display module                               |  |  |
| 11  | Connector for previous module                                 |  |  |
| 12  | Connector for Wiegand output It supports 26 bits and 34 bits. |  |  |
| 13  | Connector for device software updating                        |  |  |

#### 5.4 Lock type and connection

| Lock type                   | Pic   | Operation type    | Voltage             | Wiring type |
|-----------------------------|-------|-------------------|---------------------|-------------|
| Electrical strike lock, 12V | 0 0 0 | Power on to open  | 12 V ==/~           | Type A/B    |
| Electrical strike lock, 24V | 0 0 0 | Power on to open  | 24 V ==/~           | Type B      |
| Electrical rim lock, 12 V   |       | Power on to open  | 12 V =              | Type A/B    |
| Electrical<br>mortise lock  | 1/4   | Power off to open | 12 V =              | Type C      |
| Magnetic lock               |       | Power off to open | 12/24 V <del></del> | Type C      |



# 6 Technical data

| Designation                     | Value                                           |
|---------------------------------|-------------------------------------------------|
| Rating voltage                  | 24 VDC                                          |
| Operating voltage range         | 20-27 V DC                                      |
| Rating current                  | 27 V DC, 455 mA<br>24 V DC, 500 mA              |
| Operating temperature           | -40 °C+55 °C                                    |
| Product dimensions              | 135 mm x 348.9 mm x 17.6 mm                     |
| Display type                    | LCD                                             |
| Display size                    | 57.8 mm × 31.9 mm                               |
| Camera type                     | CMOS                                            |
| Camera viewing angle            | 130°                                            |
| Resolution ratio                | HD (1280 x 720 pixel)                           |
| Power supply for door opener    | 18 V, 4A impulse, max. 250 mA holding           |
| Floating output for door opener | 230 V AC, 3 A<br>30 V DC, 3 A                   |
| Video codec                     | H.264                                           |
| Audio codec                     | G.711                                           |
| IP level                        | IP54                                            |
| IK level                        | IK07                                            |
| Network connection standard     | IEEE 802.3, 10Base-T/100Base-TX, auto MDI/MDI-X |

# 7 Mounting/Installation



#### Warning

Electric voltage!

Dangerous currents flow through the body when coming into direct or indirect contact with live components.

This can result in electric shock, burns or even death.

- Disconnect the mains power supply prior to installation and/or disassembly!
- Permit work on the 100-240 V supply system to be performed only by specialist staff!

#### 7.1 Requirement for the electrician



#### Warning

Electric voltage!


Install the device only if you have the necessary electrical engineering knowledge and experience.

- Incorrect installation endangers your life and that of the user of the electrical system.
- Incorrect installation can cause serious damage to property, e.g. due to fire.
   The minimum necessary expert knowledge and requirements for the installation are as follows:
- Apply the "five safety rules" (DIN VDE 0105, EN 50110):
  - 1. Disconnect
  - 2. Secure against being re-connected
  - 3. Ensure there is no voltage
  - 4. Connect to earth and short-circuit
  - 5. Cover or barricade adjacent live parts.
- Use suitable personal protective clothing.
- Use only suitable tools and measuring devices.
- Check the type of supply network (TN system, IT system, TT system) to secure the following power supply conditions (classic connection to ground, protective grounding, necessary additional measures, etc.).


# 7.2 Mounting

# 7.2.1 Preparation

Use gloves to protect yourself against cuts.



## 7.2.2 Installation height






#### Note

The following installation situations must be avoided without fail to ensure picture quality:


- Direct light
- Direct sunlight
- Extremely bright picture background
- Highly reflective walls on the opposite side of the door station

### 7.2.3 Surface-mounted installation




#### 7.2.4 Flush-mounted installation


1. Flush-mounted without pre-installation box




#### 2. Flush-mounted with pre-installation box



# 7.2.5 Cavity wall installation



# 7.2.6 Dismantling



# 8 Commissioning

#### 8.1 Accessing the "Menu" screen

In standby mode, press [#\*] + system password + [#] to access the "Menu" screen.



#### Note

The system password must be changed the first time you access "Menu" screen. (The system default is 345678. This password should only be used for initial setting work and should be changed to another password. It cannot be used as the actual password)

# $\bigcap_{i=1}^{\infty}$

#### Note

If an incorrect system password is entered 10 times within 5 minutes, no further attempts are permitted for the next 5 minutes.

# $\prod_{i=1}^{\infty}$

#### Password rule

The password must not include continuously increasing or decreasing numbers (e.g. 123456, 654321), and three consecutive identical numbers are similarly not permitted (e.g. 123444, 666888).

Please see the "Engineering settings overview" chapter for more details on changing the system password.

#### 8.2 Engineering settings

On the "Menu" screen, click "Engineering settings" to access the corresponding screen.

#### **Engineering settings overview**

| Level 1              | Level 2          | Level 3                     | Option                                                             |
|----------------------|------------------|-----------------------------|--------------------------------------------------------------------|
|                      | Device attribute | Device type                 | <ul><li>OS = Outdoor station</li><li>GS = Gate station</li></ul>   |
|                      | Device attribute | Device no.                  | <ul><li>Outdoor station: 0164</li><li>Gate station: 0132</li></ul> |
|                      |                  | IS digits                   | <ul><li>3 digits</li><li>4 digits (default)</li></ul>              |
|                      |                  | Block no. (outdoor station) | 001999                                                             |
| Engineering settings |                  | Block digits (gate station) | <ul><li>1 digit</li><li>2 digits</li><li>3 digits</li></ul>        |
|                      | System attribute | Default GU                  | 0132                                                               |
|                      |                  | Digits of indoor station    | 3 digits     4 digits                                              |
|                      |                  | Change system password      | Input new password                                                 |
|                      |                  | (1) Mode select             | <ul><li>Compatible mode</li><li>Security mode</li></ul>            |
|                      |                  | Call mode                   | <ul><li>Physical address</li><li>Logical address</li></ul>         |

#### (1) Mode select

This outdoor station is used in "Security mode" by default to guarantee high security. It requires the certificate issued from the management software before use.

#### 8.3 Access control settings

On the "Menu" screen, click "Access control" to access the corresponding screen.

#### Access control overview

| Level 1        | Level 2          | Level 3                                   | Option                                                     |
|----------------|------------------|-------------------------------------------|------------------------------------------------------------|
|                | Password setting | Change public password                    | The system default is 123456                               |
|                |                  | <sup>(1)</sup> Enable public<br>password  | On Off (default)                                           |
|                |                  | <sup>(2)</sup> Enable private<br>password | On Off (default)                                           |
| Access control |                  | User card                                 | <ul><li>Add</li><li>Delete</li><li>Clear all</li></ul>     |
|                | Card setting     | (3) Copy to                               | Destination OS no.                                         |
|                |                  | (4) Card mode (only for H81382K)          | <ul><li>Standard</li><li>Customization (default)</li></ul> |

#### (1) Public password

This password is used by everyone for access via the entrance. It is set on the local outdoor station.

#### (2) Private password

This password is used by each resident for access via the entrance. It is set on indoor station. Please see the product manual for IP touch 7" for more details.



#### Password rule

The password must not include continuously increasing or decreasing numbers (e.g. 123456, 654321), and three consecutive identical numbers are similarly not permitted. (e.g. 123444, 666888)

#### (3) Copy to

Card information can only be copied from an outdoor station to the other outdoor station, or a gate station to another gate station.

#### (4) Card mode

If the card mode is set to "Customization" (default), this outdoor station will only support IC cards with a correct token.

#### 8.4 System settings

On the "Menu" screen, click "System settings" to access the corresponding screen.

#### System settings overview

| Level 1         | Level 2             | Level 3                                                         | Option                                                                                                         |
|-----------------|---------------------|-----------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------|
|                 |                     | Voice volume                                                    | <ul><li>Low</li><li>Relatively low</li><li>Medium</li><li>Relatively high (default)</li><li>High</li></ul>     |
|                 | Sound               | Key tone                                                        | Off On (default)                                                                                               |
| System settings |                     | (1) Voice prompt                                                | <ul><li>Off (default)</li><li>On</li></ul>                                                                     |
|                 |                     | Ringtone volume                                                 | <ul><li>Off</li><li>Low</li><li>Medium (default)</li><li>High</li></ul>                                        |
|                 | Date and time       | Local setting                                                   | Date and time setting                                                                                          |
|                 |                     | Management software sync                                        |                                                                                                                |
|                 | Language            |                                                                 |                                                                                                                |
|                 | Wiegand<br>settings | <ul><li>Off (default)</li><li>26 bits</li><li>34 bits</li></ul> |                                                                                                                |
|                 | Choose door         | Default lock                                                    | <ul> <li>L1 LOCK-GND</li> <li>L2 NO-NC-COM</li> <li>IPA LOVK-GND (132)</li> <li>IPA NO-NC-COM (132)</li> </ul> |
| Choose door     |                     | Auxiliary lock                                                  | <ul> <li>L1 LOCK-GND</li> <li>L2 NO-NC-COM</li> <li>IPA LOVK-GND (132)</li> <li>IPA NO-NC-COM (132)</li> </ul> |

#### (1) Voice prompt

If this function is enabled, the outdoor station will play the sound for "Call in progress" during the operation. The language of the voice prompt will be the same as the language setting.

| Level 1         | Level 2                      | Level 3                                         | Option                                         |
|-----------------|------------------------------|-------------------------------------------------|------------------------------------------------|
|                 | Unlock time                  | L1 LOCK-GND                                     | 110 s                                          |
|                 |                              | L2 NO-NC-COM                                    | 110 s                                          |
|                 | Door status                  | Off (default)                                   |                                                |
|                 | alarm                        | On                                              | <ul><li>Off</li><li>On (alarm sound)</li></ul> |
|                 | Temper alarm                 | Off (default) On                                |                                                |
|                 | Call forward (to guard unit) | Off (default)                                   |                                                |
| System settings |                              | On                                              |                                                |
| -               | Lift settings Anti-flicker   | Enable lift                                     | Off (default) On                               |
|                 |                              | Floor no. (outdoor station)                     | -7+63                                          |
|                 |                              | (2) Block no.                                   | 001999                                         |
|                 |                              | <ul><li>50 Hz</li><li>60 Hz (default)</li></ul> |                                                |
|                 | Reset factory default        | Press [#]                                       |                                                |
|                 | Help                         | Version                                         |                                                |

<sup>(2)</sup> Block no.

This block no. means the number of the lift control module. It must be the same as the number of the connecting outdoor station.

### 8.5 Logical address settings

The call mode should be set to "logical address" before use.

On the "Menu" screen, click "Logical address settings" to access the corresponding screen.

#### Add

Enter "Logical address" + [V] + "Physical address" + [#] to add a new one.

#### Modify

Enter "Logical address" + [#], then enter new "Logical address" + [ $\lor$ ] + "Physical address" + [#] to change it.

#### **Delete**

Enter "Logical address" + [#] to delete it.

#### Clear all

Enter [#] to clear all logical address.

# 9 Operation

#### 9.1 Calling a resident

[1] Device type = OS

In standby mode, enter the room no. (e.g. 0101), press [\*] to end the call.

[2] Device type = GS

In standby mode, enter the building no. + room no. (e.g. 020101), press [\*] to end the call.

# $\int_{0}^{\infty}$

#### Forward to GU

If "Call forward" is enabled, all calls will be transferred to the guard unit.

#### 9.2 Calling a guard unit


In standby mode, press  $\, 8 \,$  to call the default guard unit. Press [\*] to end the call.

#### 9.3 Releasing a lock

## 9.3.1 Releasing a lock by swiping cards

Please enroll the ID/IC cards before use. Please see the "Access control overview" chapter for more details.

Swipe registered ID/IC cards near the area (see diagram below) to release the lock.



#### IC card specification


| Operating frequency | 13.56 MHz                                           |
|---------------------|-----------------------------------------------------|
| Standard            | ISO 14443A                                          |
| Support card        | EM4100, EM4205, EM4305, EM4450, TK4100, T5567/T5577 |
| Output format       | Wiegand 26/34 bit                                   |

### **ID** card specification

| Operating frequency | 125 KHz                                    |
|---------------------|--------------------------------------------|
| Standard            | ISO 18000-2                                |
| Support card        | Mifare one S50/S70, Mifare desfire EV1/EV2 |
| Output format       | Wiegand 26/34 bit                          |

#### 9.3.2 Releasing a lock by pressing the exit button





#### 9.3.3 Releasing a lock by entering the public password

The "public password" must be enabled before use. Please see the "Access control overview" chapter for more details.

In standby mode, press [#] + public password + [#] to release the lock.

In standby mode, press [#] [2] [#]+ public password + [#] to release the second lock.

#### 9.3.4 Releasing a lock by entering a private password

The "private password" must be enabled before use. Please see the "Access control overview" chapter for more details.

In standby mode,

[1] Device type = Outdoor station

Release default lock: [\*1#] + room no. + [#] + private password + [#] Release auxiliary lock: [\*2#] + room no. + [#] + private password + [#]

[2] Device type = Gate station

Release default lock: [\*1#] + building no. + [#] + room no. + [#] + private password + [#] Release auxiliary lock: [\*2#] + building no. + [#] + room no. + [#] + private password + [#]

# $\frac{\circ}{1}$

#### Incorrect password

If an incorrect password is entered 10 times within 5 minutes, no further attempts are permitted for the next 5 minutes.

# 10 Cyber security

#### 10.1 Disclaimer

H8138.K-. products are designed to be connected and to communicate information and data via a network interface, which should be connected to a secure network. It is customer's sole responsibility to provide and continuously ensure a secure connection between the product and customer's network or any other network (as the case may be) and to establish and maintain appropriate measures (such as but not limited to the installation of firewalls, application of authentication measures, encryption of data, installation of antivirus programs, etc.) to protect the H8138.K-. product, the network, its system and interfaces against any kind of security breaches, unauthorized access, interference, intrusion, leakage and/or theft of data or information. ABB and its affiliates are not liable for damages and/or losses related to such security breaches, unauthorized access, interference, intrusion, leakage and/or theft of data or information.

Although ABB provides functionality testing on the products and updates that we release, you should institute your own testing program for any product updates or other major system updates (to include but not limited to code changes, configuration file changes, third party software updates or patches, hardware change out, etc.) to ensure that the security measures that you have implemented have not been compromised and system functionality in your environment is as expected.

#### 10.2 Performance and service

#### **Network performance**

| Туре     | Value                        |
|----------|------------------------------|
| Ethernet | 24 Mbps (37,449 packets/sec) |
| ARP      | 12 Mbps (18,724 packets/sec) |
| ICMP     | 22 Mbps (34,328 packets/sec) |
| IP       | 22 Mbps (34,328 packets/sec) |

#### Port and service

| Port  | Service | Purpose                                                             |
|-------|---------|---------------------------------------------------------------------|
| 5070  | UDP     | To be used by SIP client.                                           |
| 7777  | TCP/UDP | To be used for device management.                                   |
| 10777 | TLS     | Secure channel for device management                                |
| 7005  | TCP     | To be used for connectivity detection when this feature is enabled. |
| 8887  | TCP     | To be used for firmware update.                                     |

#### 10.3 Deployment guideline

All devices need to work in security mode by default and. all devices in one system shall be signed by a public CA at commissioning stage, normally management software works as CA.

It's suggested that compatible mode only to be used when device needs to communicate with previous generation products. In this mode, data transmission between devices are not encrypted, it may lead to data leaks and has the risk of being attacked.

When user decide to remove the device from system, user shall reset the device to factory setting in order to remove all the configuration data and sensitive data in the device. This will prevent sensitive data leak.

It is recommended to apply "MAC filter" and "Rate limiter" in the switch to prevent DOS attack.

#### 10.4 Upgrading

Device supports firmware updates via management software, a signature file will be used to verify the authentication and integrity of firmware.

#### 10.5 Backup/Restore

None.

#### 10.6 Malware prevention solution

The H8138.K-. device is not susceptible to malware, because custom code cannot be executed on the system. The only way to update the software is by firmware upgrades. Only firmware signed by ABB can be accepted.

#### 10.7 Password rule

The user must change the engineering password when accessing the engineering settings for the first time. This engineering password must not include continuously increasing or decreasing numbers (e.g. 123456, 654321), and three consecutive identical numbers are similarly not permitted (e.g. 123444, 666888).

# 11 Notice

We reserve the right to at all times make technical changes as well as changes to the contents of this document without prior notice.

The detailed specifications agreed to at the time of ordering apply to all orders. ABB accepts no responsibility for possible errors or incompleteness in this document.

We reserve all rights to this document and the topics and illustrations contained therein. The document and its contents, or excerpts thereof, must not be reproduced, transmitted or reused by third parties without prior written consent by ABB.



#### Contact us

ABB Xiamen Smart Technology Co., Ltd. No. 881, FangShanXiEr Road, Xiang'An Industrial Area, Torch Hi-Tech Industrial Development Zone, Xiamen

Tel: +86 592 295 9000 Fax: +86 592 562 5072

www.abb.com

Approvals and Compliances

#### Notice

We reserve the right to at all times make technical changes as well as changes to the contents of this document without prior notice.

The detailed specifications agreed upon apply for orders. ABB accepts no responsibility for possible errors or incompleteness in this document.

We reserve all rights to this document and the topics and illustrations contained therein. The document and its contents, or extracts thereof, must not be reproduced, transmitted or reused by third parties without prior written consent by ABB.