

ABB MEASUREMENT & ANALYTICS | DATA SHEET

# Industrial tablet PC

## Field device management tools



---

## Measurement made easy

Highly flexible industrial tablet PC for harsh environments

---

**Install and run ABB Field Information Manager and other ABB software on a rugged tablet**

---

### Key features

- Brilliant, high-resolution, bonded 10.1 touch LED display, also sunlight readable
- Powerful processor for high working speed and long battery life
- Rugged design for industrial use, including hazardous area
- Integrated Bluetooth 4.0, WLAN and optional LTE radio module and HART modem
- Freely configurable expansion interface for customer specific charging
- Extensive accessories
- Tool-less battery hot-swap

## Agile / Agile × 10.1 in industrial tablet PC



Figure 1: Agile / Agile × 10.1 in industrial tablet PC

### Specification

#### CPU

Intel BayTrail-M Quad-Core 1.8 GHz  
(turbo frequency up to 2.2 GHz)

#### Memory

System memory: 8 GB SODIMM DDR3L-1600  
Storage: 128 GB mSATA MLC SSD

#### Operating system

Windows® 10 IoT Enterprise (64 bit)

#### Display

Size	10.1 in
Resolution	1920 × 1200 pixel
Brightness	700 cd/m <sup>2</sup> (nits)
Contrast ratio	800:1
Touch	Projective capacitive touch (min. 4 points)
Front glass	Gorilla Glass®, 3 mm with hardness of 8H

#### Audio

1 × built-in microphone, 2 × 1 W speaker

#### Sensors

Light sensor, G sensor, Gyrometer, E-compass

#### Camera

- 5 MP auto-focus camera with LED flash on rear
- 2 MP camera on front

#### Network specifications

Wireless LAN	IEEE 802.11 a/b/g/n
Bluetooth	Bluetooth 4.0 (Class I)
GPS	u-Blox Neo-6Q, up to 2.5 m accuracy
Optional LTE Module	EU: LTE, HSPA+, GSM/GPRS

#### Interface

Under protective cover – for use only in safe area:

- 1 × Micro HDMI
- 1 × 30-pin connector (Giga-LAN or RS232)
- 1 × USB 3.0
- 1 × Audio connector (Mic in/Line Out)
- 1 × Power jack (DC)
- 1 × Micro SD slot

### Power supply

Input voltage	12 to 19 V DC
Adapter	100 to 240 V AC, 50 to 60 Hz / 19 V DC
Battery	Standard: Up to 6 h run time, 7.4 V, min. 5300 mAh Extended: Up to 13 h run time, 7.4 V, min. 10600 mAh


### Dimensions

W × L × H	271.8 × 197.2 × 9 mm (10.7 × 7.76 × 0.35 in)
Weight	1.5 kg (3.3 lb) with standard battery

### Ambient conditions

Shock resistance	Military grade device (MIL-STD-810G)
IP rating	IP 65 (IEC 60529)
Storage temperature	–30 to 70 °C (–22 to 158 °F)
Operating temperature	–20 to 60 °C (–4 to 140 °F) For hazardous area: –20 to 50 °C (–4 to 122 °F)
Humidity	30 to 90 % (non-condensing)

## ... Agile / Agile × 10.1 in industrial tablet PC



- |                              |                              |
|------------------------------|------------------------------|
| ① I/O ports                  | ⑪ Home button                |
| ② Volume buttons             | ⑫ Function button            |
| ③ Function button            | ⑬ Touch screen               |
| ④ Expansion port             | ⑭ Microphone                 |
| ⑤ Rear camera                | ⑮ Front camera               |
| ⑥ Battery                    | ⑯ Light sensor               |
| ⑦ Strap fixture              | ⑰ Indicators                 |
| ⑧ Tool-less battery hot swap | ⑱ LTE module / SIM card slot |
| ⑨ Stylus                     | ⑲ Speaker                    |
| ⑩ Power button               |                              |

Figure 2: Overview

## Ex marking

Ex marking – zone 2	
ATEX	II 3G Ex ic IIA/IIC T5 Gc II 3D Ex ic IIIB T90 °C Dc IP 54 (IIA when using hand strap Type 03-9849-0130) Ex certification: EPS 15 ATEX 1 823 X
IECEX	Ex ic IIA/IIC T5 Gc Ex ic IIIB T90 °C Dc IP 54 (IIA when using hand strap Type 03-9849-0130) Ex certification: IECEX EPS 15.0010X
UL	Class I Div. 2 Groups A, B, C, D T4 A Ex certification: UL File E321557

## Ordering information

Model	Bartec order number
Agile 10.1 in industrial tablet PC, non Ex, 5.3 Ah	G7-A031-4051/11110000
Agile × 10.1 in industrial tablet PC, Ex Zone 2, 5.3 Ah	B7-A234-4051/11110000
Agile × 10.1 in industrial tablet PC, EX Zone 2, 10.6 Ah	B7-A234-4051/11120000

## Agile × IS 10.1 in industrial tablet PC



Figure. 3: AGILE × IS 10.1 in industrial tablet PC

### Specification

#### CPU

Intel N3710 1.6 GHz (turbo 2.56 GHz)

#### Memory

System memory: 8 GB SODIMM DDR3L-1600

Storage: 128 GB SATA uSSD

#### Operating system

Windows® 10 IoT Enterprise CBB

#### Display

Size	10.1 in
Resolution	1920 × 1200 pixel
Brightness	700 cd/m <sup>2</sup> (nits)
Contrast ratio	800:1
Touch	10 points multi touch
Front glass	LCD display, 2 × bonded Gorilla Glass®

#### Audio

2 microphones with integrated noise cancellation system;  
2 speakers (2 × 0.5 W)

#### Sensors

Light sensor, G sensor, E-compass

#### Camera

- 5 MP auto-focus camera with LED flash on rear
- 2 MP camera on front

### Network specifications

Wireless LAN	IEEE 802.11 a/b/g/n/ac on board 2 antennas
Bluetooth	BT 4.1 LE Class I
GPS	u-Blox Neo-M8N
Optional LTE Module	LTE, UMTS/HSPA+, GSM/GPRS/EGDE

### Interface

Interfaces tablet PC	1 × USB 2.0 1 × MicroSD card slot 1 × Micro SIM card slot 1 × Charging port 1 × Expansion port for add-on module 1 × Docking station
Interfaces docking station	4 × USB 2.0, 1 × RS232, 1 × Ethernet 10/100 Mbps, 1 × HDMI, 1 × Charging port

### Power supply

Input voltage	19 V DC, 3.41 A
Adapter	100 to 240 V AC, 50 to 60 Hz / 19 V DC
Battery	Internal battery: 7.4 V typ. 4200 mAh External battery: 7.4 V typ. 4200 mAh
Run Time	up to 2:45 h with internal battery only up to 5:40 h with internal and external battery

### Dimensions

W × L × H	290 × 209 × 33 mm (11.42 × 8.23 × 1.30 in)
Weight	2.3 kg (5.07 lb) with internal battery only

### Ambient conditions

Drop	4 feet to concrete (including add-on module and battery)
IP rating	IP 65 (IEC 60529)
Storage temperature	−20 to 50 °C (−4 to 122 °F)
Operating temperature	−20°C to 50 °C (−4 to 122 °F) (exclude cold start)
Humidity	5 to 90 % (non-condensing)

## ... Agile × IS 10.1 in industrial tablet PC





Figure 4: Overview front



- ⑪ I/O ports (USB 2.0 port, MicroSD card slot, Micro SIM card slot, Charging port)
- ⑫ Volume (+/-)
- ⑬ Function key
- ⑭ Expansion port for add on modules

- ⑮ High quality 5 MP camera with flash
- ⑯ Multi-stage battery compartment locking mechanism
- ⑰ Empty module / external battery (can be changed during active operations) for battery compartment
- ⑱ Docking station connection

Figure 5: Overview rear

## Ex marking

Ex marking - zone 1	
ATEX	II 2G Ex ia op is IIC T4 Gb -20 °C ≤ Ta ≤ 50 °C Ex certification: DEMKO 16 ATEX 1803
IECEX	Ex ia op is IIC T4 Gb -20 °C ≤ Ta ≤ 50 °C Ex certification: IECEX UL 16.0160
UL	Class I, Division 1, Groups A, B, C and D Class I, Zone 1, AEx ia IIC T4 Gb -20 °C ≤ Ta ≤ 50 °C Ex certification: E226123

## Ordering information

Model	Bartec order number
Agile x IS Industrial Tablet PC without external battery	17-A1B4-1031/22101000

# HART® add-on module




Figure 1: HART® add-on module

The HART® add-on module is a new extension module for the Agile series and offers a HART modem function.

It may be connected to a HART loop as secondary master and facilitates applications such as configuring the HART devices. Due to the Windows operating system, the user can deploy many current software solutions in particular FDI based Field Information Manager by ABB and other software to make measurement easy.

The Agile series equipped with HART add-on module is the new safe solution when working in the Ex and in the non-Ex area:

Parameterization, configuration, measurement and office tasks can be carried out much easier, faster and more safely.

## Features

- Integrated HART modem function on an industry tablet PC.
- Supports FDI technology for easy field device management.
- Mixed operation between Ex and non-Ex area possible.

## Electrical data HART® interface

$U_i$ :  $\leq 30$  V DC,  $I_i$ :  $\leq 130$  mA,  $P_i$ :  $\leq 1$  W,  $U_o$ :  $\leq 3$  V DC,  $I_o$ :  $\leq 10$  mA,  
 $P_o$ :  $\leq 5$  mW,  $U_m$ : 60 V DC  
 Maximum cable length: 1.8 m (5.9 ft)

## Explosion protection

### Ex marking – zone 1

ATEX	II 2G Ex ia [ia Ga] IIC T4 Gb EX certification: EPS 15 ATEX 1 069 X
IECEx	Ex ia [ia Ga] IIC T4 Gb Ex certification: IECEx EPS 15.0065X
NEC	Class I Div 1 Groups A, B, C, D T4 Ex certification: CSA 70045374

### Ex marking – zone 2

ATEX	II 3G Ex ic [ia Ga] IIC T4 Gc II 3D Ex ic [ia Da] IIIB T135 °C Dc Ex certification: EPS 15 ATEX 1 823 X
IECEx	Ex ic [ia Ga] IIC T4 Gc Ex ic [ia Da] IIIB T135 °C Dc4 Ex certification: IECEx EPS 15.0010X
NEC	Class I Division 2 Groups A, B, C and D Ex certification: UL File E321557

### Ex marking – for non-Ex areas with intrinsically safe outputs


ATEX	II (2)G [Ex ia Ga] IIC Ex certification: EPS 15 ATEX 1 069 X
IECEx	[Ex ia] IIC Ga Ex certification: IECEx EPS 15.0065X
NEC	Use with intrinsically safe outputs in non-Ex areas


## Ordering information


### Model


Non Ex for Agile	G7-A0Z0-0007
Ex Zone 2 for Agile X	B7-A2Z0-0033
Ex Zone 1 for Agile × IS	17-A1Z0-0005


## Accessories for Agile / Agile X

Li-Polymer battery (EX)	Description	Type	Order number
	Maximum use is 1 battery per Tablet PC	7.4 V / 5300 mAh	B7-A2Z0-0028
	Change battery only in non-Ex area	(39.22 Whr)	
	Ex Certification:	7.4 V / 10600 mAh	B7-A2Z0-0029
	<ul style="list-style-type: none"> <li>• ATEX Zone 2 / 22</li> <li>• IECEx Zone 2 / 22</li> <li>• UL Class I Division 2</li> </ul>	(78.44 Whr)	

Battery lock (EX)	Description	Type	Order number
	Prevents the accidental un-locking and remove of the battery.	Battery lock	03-9827-0004




Charging power supply	Description	Type	Order number
	① Charging power supply	Charging power supply	03-9911-0040
	<ul style="list-style-type: none"> <li>• For non-hazardous area.</li> <li>• Input voltage: 100 to 240 V AC</li> <li>• Output voltage: 19 V DC, 3,42 A</li> <li>• Available with correct line cord for EU, UK, US and other.</li> <li>• Country specific AC-line cord ② must be ordered separately.</li> </ul>		
	② Country specific AC-line cord	Version EU	03-9609-0022
	<ul style="list-style-type: none"> <li>• For non-hazardous area.</li> <li>• AC Line cord – 3 wired with IEC 320-C5 connector.</li> </ul>	Version US	03-9609-0023
		Version UK	03-9609-0024

Vehicle charging cable	Description	Type	Order number
	<ul style="list-style-type: none"> <li>• For non-hazardous area.</li> <li>• Input voltage: 11 to 16 V DC and 22 to 32 V DC</li> <li>• Output voltage: DC 19 V (±5%), 3.42 A</li> <li>• Operating temperature: 0 to 40 °C (32 to 104 °F)</li> </ul>	Vehicle charging cable	03-9914-0011




Cover for expansion port	Description	Type	Order number
	Suitable for tablet PC series Agile.	Standard cover	03-9827-0011
	Must be changed only outside potentially explosive atmosphere.	Cover for vehicle docking station	03-9827-0005

## ... Accessories for Agile / Agile X



### Docking stations

Desktop docking station	Description	Type	Order number
	<p>For non-hazardous area.</p> <p>Input voltage: 12 V DC, optional 9 to 36 V DC</p> <p>Charging of the Agile x with inserted battery</p> <p>Interfaces:</p> <ul style="list-style-type: none"> <li>• 4 × USB 2.0</li> <li>• 1 × RS232</li> <li>• 1 × Ethernet 10/100 Mbit/s, 1 × VGA</li> </ul> <p>Useable with standard and extended battery.</p> <p>Further required components, must be ordered separately:</p> <ul style="list-style-type: none"> <li>• Charging power Supply: 03-9911-0040</li> <li>• Country-specific AC-line cord</li> </ul>	Desktop docking station	03-9915-0017
Vehicle docking station			
	<p>For non-hazardous area.</p> <p>Input: 9 to 36 V DC</p> <p>Charging of the Agile x with inserted battery.</p> <p>Interfaces:</p> <ul style="list-style-type: none"> <li>• 2 × USB 2.0</li> <li>• 1 × RS232</li> <li>• 1 × Ethernet 10/100 Mbit/s</li> <li>• 1 × SMA for external GPS antenna</li> </ul> <p>Useable with standard and extended battery.</p> <p>Further required components, must be ordered separately:</p> <ul style="list-style-type: none"> <li>• Vehicle charging cable: 03-9914-0011</li> </ul>	Vehicle docking station	03-9915-0019
Table-top charger dual			
	<p>For non-hazardous area</p> <p>Input voltage: 10 to 20 V DC (50 W)</p> <p>Two-slot charging dock.</p> <p>Power level LED indicators.</p> <p>Buzzer to indicate battery is inserted.</p> <p>Supports up to 2 set of dock interconnected.</p> <p>Items supplied:</p> <ul style="list-style-type: none"> <li>• Charging power supply: 03-9911-0040</li> <li>• AC-line cord (EU): 03-9609-0022</li> <li>• AC-line cord (US): 03-9609-0023</li> </ul> <p>Information: Other AC line cord must order separately.</p>	Table-top charger dual	03-9914-0010

## Adapter cable




LAN-Adapter	Description	Type	Order number
	For non-hazardous area. For LAN from 30 pin extension port. Connector: RJ45, female.	LAN-Adapter	03-9919-0022
<b>RS232 cable</b>			
	For non-hazardous area. For RS232 from 30 pin extension port. DB9 Serial RS232 cable, male.	RS232 cable	03-9919-0023
<b>Micro HDMI cable</b>			
	For non-hazardous area. Micro HDMI (male) to HDMI (male).	Micro HDMI cable	03-9919-0024



## Radio modules

LTE radio modules (Ex)	Description	Type	Order number
	Ex certification: <ul style="list-style-type: none"> <li>• ATEX Zone 2 / 22</li> <li>• IECEx Zone 2 / 22</li> <li>• UL Class I Division 2</li> </ul> 4G / LTE Sierra MC7305-EU (Gobi5000) LTE, HSPA+, GSM / GPRS	LTE radio module EU	03-9826-0128
	Ex certification: <ul style="list-style-type: none"> <li>• ATEX Zone 2 / 22</li> <li>• IECEx Zone 2 / 22</li> <li>• UL Class I Division 2</li> </ul> 4G / LTE Sierra MC7355-US (Gobi5000) LTE, HSPA+, GSM / GPRS / EDGE, EV-DO Rev. A, 1 × RTT	LTE radio module US	03-9826-0127

## ... Accessories for Agile / Agile X

### Additional accessories

Carry system	Description	Type	Order number
	Ex certification: <ul style="list-style-type: none"> <li>• ATEX Zone 2 / 22</li> <li>• IECEx Zone 2 / 22</li> <li>• UL Class I Division 2</li> </ul> <ul style="list-style-type: none"> <li>• Simplified handling</li> <li>• Ergonomic back trace with shoulder pad for safe carrying in front of the body</li> <li>• Easy access of the battery and add-on module integration possible</li> <li>• with holder for stylus</li> <li>• adjustable strap length</li> </ul> The carry system includes: <ul style="list-style-type: none"> <li>• Leather carry case</li> <li>• 4-point belt</li> <li>• Shoulder strap</li> </ul>	Carry system	03-9829-0100
<b>Leather carry case</b>			
	<ul style="list-style-type: none"> <li>• with practical stand function and holder for stylus</li> <li>• Easy access of the battery and add-on module integration possible</li> <li>• upgradable with shoulder strap and 4-point belt</li> <li>• robust industry quality leather</li> </ul>	Leather carry case  Ex certification ATEX Zone 2 / 22 IECEx Zone 2 / 22 UL Class I Division 2	03-9829-0090
<b>4-point belt</b>			
	Suitable for leather carry case of tablet PC Agile series. <ul style="list-style-type: none"> <li>• Ergonomic back trace with shoulder pad for safe carrying in front of the body</li> <li>• Easy and secure fitting at leather carry case via colored press buttons</li> <li>• Adjustable strap length</li> </ul>	4-point belt  Ex certification ATEX Zone 2 / 22 IECEx Zone 2 / 22 UL Class I Division 2	03-9829-0092
<b>Shoulder strap</b>			
	Suitable for leather carry case of tablet PC Agile series. Ex certification: <ul style="list-style-type: none"> <li>• ATEX Zone 2 / 22</li> <li>• IECEx Zone 2 / 22</li> <li>• UL Class I Division 2</li> </ul> <ul style="list-style-type: none"> <li>• ergonomic and soft shoulder pad</li> <li>• adjustable strap length</li> </ul>	Shoulder strap	03-9829-0091




Hand strap (Ex)	Description	Type	Order number
	<p>Ex certification:</p> <ul style="list-style-type: none"><li>• ATEX Zone 2 / 22</li><li>• IECEx Zone 2 / 22</li><li>• UL Class I Divison 2</li><li>• Only suited for gas group IIA</li></ul> <p>• 1 piece per package</p> <p>• To be mounted on the back side</p>	Hand strap	03-9849-0130
<b>Spare stylus (Ex)</b>			
	<p>Ex certification:</p> <ul style="list-style-type: none"><li>• ATEX Zone 2 / 22</li><li>• IECEx Zone 2 / 22</li><li>• UL Class I Divison 2</li></ul> <p>Suitable for capacitive touchscreen.</p> <ul style="list-style-type: none"><li>• 1 piece</li><li>• With spiral cord</li><li>• Up to S/N 3B or higher</li></ul>	Dual stylus	03-9849-0151
<b>Screen Protector (Ex)</b>			
	<p>Ex certification:</p> <ul style="list-style-type: none"><li>• ATEX Zone 2 / 22</li><li>• IECEx Zone 2 / 22</li><li>• UL Class I Divison 2</li><li>• For gas group IIA, IIB and IIC</li></ul> <p>• 1 piece per package</p> <p>• 10.1 in widescreen</p>	Screen protector	B7-A2Z0-0031

## Accessories for Agile × IS





### Accessories for use in potentially explosive atmospheres

#### Certification

- ATEX: Zone 1 (DEMKO 16 ATEX 1803)
- IECEx: Zone 1 (IECEx UL 16.0160)
- UL: Class I Div 1 (File E226123)

External battery	Description	Type	Order number
	Certified in combination with Agile × IS. <ul style="list-style-type: none"> <li>• Lithium-ion battery</li> <li>• Hot-swappable</li> </ul> Can be changed in potentially explosive atmosphere.	7.4 V / 4200 mAh (31.08 Wh)	17-A1Z0-0006
	<ul style="list-style-type: none"> <li>• Cover module for battery compartment</li> <li>• Hot-swappable</li> </ul> Can be changed in potentially explosive atmosphere.	Cover module	03-9849-0150
MicroSD card			
	Certified in combination with Agile × IS.	Storage capacity: 8 GB	17-A1Z0-0008
	Can be changed in potentially explosive atmosphere.	Storage capacity: 16 GB	17-A1Z0-0009
		Storage capacity: 32 GB	17-A1Z0-0010
USB stick			
	Certified in combination with Agile × IS <ul style="list-style-type: none"> <li>• Intrinsically safe</li> </ul> Can be changed in potentially explosive atmosphere.	Storage capacity: 8 GB	17-A1Z0-0007
Cover for expansion port			
	Suitable for tablet PC series Agile. Must be changed only outside potentially explosive atmosphere.	Cover for expansion port	03-9827-0011
Screen protector			
	Certified in combination with Agile × IS. <ul style="list-style-type: none"> <li>• 1 piece</li> </ul> Must be changed only outside potentially explosive atmosphere.	Screen protector	17-A1Z0-0011


## Accessories for use in potentially explosive atmospheres


Dual stylus	Description	Type	Order number
	<p>Suitable for capacitive touchscreen.</p> <ul style="list-style-type: none"> <li>• 1 piece</li> <li>• With spiral cord</li> <li>• Up to S/N 3B or higher</li> </ul>	Dual stylus	03-9849-0151
Carry system			
	<p>Suitable with Agile × IS.</p> <ul style="list-style-type: none"> <li>• Simplified handling</li> <li>• Ergonomic back trace with shoulder pad for safe carrying in front of the body</li> <li>• Easy access of the battery and add-on module integration possible</li> <li>• With holder for stylus</li> <li>• Adjustable strap length</li> </ul> <p>The carry system includes:</p> <ul style="list-style-type: none"> <li>• Leather carry case</li> <li>• 4-point belt</li> <li>• Shoulder strap</li> </ul>	Carry system	03-9829-0101
Leather carry case			
	<p>Suitable with Agile × IS</p> <ul style="list-style-type: none"> <li>• With practical stand function and holder for stylus</li> <li>• Easy access of the battery and add-on module integration possible</li> <li>• Upgradable with shoulder strap and 4-point belt</li> <li>• Robust industry quality leather</li> </ul>	Leather carry case	03-9829-0089
4-point belt			
	<p>Suitable for leather carry case of tablet PC Agile series.</p> <ul style="list-style-type: none"> <li>• Ergonomic back trace with shoulder pad for safe carrying in front of the body</li> <li>• Easy and secure fitting at leather carry case via colored press buttons</li> <li>• Adjustable strap length</li> </ul>	4-point belt	03-9829-0092
Shoulder strap			
	<p>Suitable for leather carry case of tablet PC Agile series.</p> <ul style="list-style-type: none"> <li>• Ergonomic and soft shoulder pad</li> <li>• Adjustable strap length</li> </ul>	Shoulder strap	03-9829-0091

## ... Accessories for Agile × IS


### Accessories for use outside potentially explosive atmospheres

#### Docking stations

2-slot battery charging station	Description	Type	Order number
	<p>Suitable with Agile × IS.</p> <p>For charging of 2 batteries.</p> <p>Input voltage: 10 to 20 V DC (50 W).</p> <p>Charge indicator by LED and buzzer.</p> <p>Two plugged charging stations can be supplied with one power supply.</p>	2-slot battery charging station	03-9914-0021
	<p>Items supplied:</p> <ul style="list-style-type: none"> <li>• 2-slot battery charging station</li> <li>• Power supply</li> <li>• AC power cable (EU + US)</li> </ul>		

Docking station	Description	Type	Order number
	<p>Suitable with Agile × IS.</p> <p>Input voltage: 12 V DC.</p> <p>Charging with inserted battery.</p> <p>Interfaces:</p> <ul style="list-style-type: none"> <li>• 4 × USB 2.0</li> <li>• 1 × RS232</li> <li>• 1 × Ethernet 10/100 Mbit/s</li> <li>• 1 × HDMI</li> <li>• 1 × Charging port</li> </ul>	Docking station	03-9914-0022
	<p>Items supplied:</p> <ul style="list-style-type: none"> <li>• Docking Station</li> <li>• Mounting bracket</li> <li>• Screws for mounting bracket (6 pieces)</li> <li>• Fixation elements (2 pieces)</li> <li>• Inserts for Agile × (2 pieces)</li> <li>• Screws for insert (2 pieces)</li> <li>• Rubber pads (4 pieces)</li> <li>• Power supply</li> <li>• Power cable (EU + US)</li> <li>• Quick start guide (DE + EN)</li> </ul>		

#### Power supply

Charging power supply for Agile × IS	Description	Type	Order number
	<p>① Charging power supply</p> <ul style="list-style-type: none"> <li>• For non-hazardous area.</li> <li>• Input voltage: 100 to 240 V AC</li> <li>• Output voltage: 19 V DC, 3.42 A</li> <li>• Available with correct line cord for EU, UK, US and other.</li> <li>• Country-specific AC-line cord ② must be ordered separately.</li> </ul>	Charging power supply	03-9911-0040
	<p>② Country specific AC-line cord</p>	Version EU	03-9609-0022
	<ul style="list-style-type: none"> <li>• For non-hazardous area.</li> </ul>	Version US	03-9609-0023
	<ul style="list-style-type: none"> <li>• AC Line cord – 3 wired with IEC 320-C5 connector.</li> </ul>	Version UK	03-9609-0024

---

## Trademarks

HART is a registered trademark of FieldComm Group, Austin, Texas, USA

Windows is a registered trademark of Microsoft Corporation.

Gorilla Glass is a registered trademark of Corning Incorporated (USA).

Sales





**Notes**



---

To find your local ABB contact visit:  
**[abb.com/contacts](http://abb.com/contacts)**

For more information visit:  
**[abb.com/fieldinfo](http://abb.com/fieldinfo)**

---

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail.  
ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.