

Electrical installation solutions for buildings – Technical details


SMISLINE TP plug-in system

Index

Busbar system 125 A Overview	9/2
Busbar system 250 A Overview	9/4
Socket/additional socket/busbars	9/5
Incoming terminal block/Incoming terminal components	9/6
Power supply	9/8
Incoming Power Bar System 250 A and 400 A	9/9
Incoming UL 508 – Industrial Control Equipment	9/10
Busbar system accessories	9/11
Combi module: starting solutions in kit form	9/12
Definitions	9/13
Approvals according to IEC/EN 61439-6	
Busbar system 125 A	9/14
Technical data IEC and technical data UL508A	
Busbar system 125 A	9/15
Technical data according to IEC/EN 61439-6	
Power Bar System 250 A	9/16
Miniature circuit breaker Properties	9/18
S400M	9/19
S400UC	9/20
Trip characteristics	9/21
Internal resistances at rated voltage and power losses	9/23
Limitation of specific let-through energy I^2	9/24
Limitation curves – Peak current values I_p	9/25
Power supply: overload and short-circuit protection	9/26
Back-up and selectivity dates	9/27
Back-up protection with fuses, S800	9/28
Back-up protection with Tmax and XT	9/29
Influence of ambient temperature	9/30
Protection of circuits with fluorescent lamps	9/32
S400UC	9/33
F402, F404 Properties	9/34
F402, F404 Standard, short-time delayed and selective type	9/36
F402, F404 Technical data	9/38
FS401	9/40
FS403	9/42
Switch disconnecter	9/45
Surge arrester OVR	9/46
Auxiliary switches and signal contacts	9/49
Accessory mounting	9/50
Auxiliary switches and signal contacts	9/51
Contact arrangements to auxiliary busbars	9/52

SMISLINE TP technical details


Busbar system 125A Overview



- | | | | |
|---|---|----|--------------------------|
| 1 | Supply terminal | 10 | Cover for socket |
| 2 | Incoming terminal block with a max. current rating of 160 A 50 mm² (2 x 25 mm²) + 2 x 10 mm² (LA, LB) | 11 | Socket |
| 3 | Cover for incoming terminal block | 12 | End piece |
| 4 | Supply cable | 13 | Additional socket |
| 5 | Residual current operated circuit breaker with overcurrent protection RCBO FS401 and FS403 | 14 | Outgoing cable |
| 6 | Residual-current circuit breaker F404 | | |
| 7 | Miniature circuit breaker S401 M | | |
| 8 | Signal contact | | |
| 9 | Plug contacts | | |

SMISLINE TP technical details


Busbar system 125A Overview



- | | | | |
|----|---|----|--|
| 1 | 6 and 8-module socket | 12 | Incoming terminal block 63A |
| 2 | end piece on left and right | 13 | Incoming terminal block 160A |
| 3 | 6 and 8 module additional socket | 14 | Incoming terminal component, centre power supply 200 A, maximum 95 mm² |
| 4 | Busbar LA 40A | 15 | Isolator |
| 5 | Busbar LB 40A | 16 | DIN adapter |
| 6 | Busbar 125A N | 17 | Spare way cover |
| 7 | Busbar 125A L1 or DC +,- | 18 | Adapter for DIN rail components |
| 8 | Busbar 125A L2 or DC +,- | 19 | Combi module with a current rating of 32 A |
| 9 | Busbar 125A L3 or DC +,- | | |
| 10 | Busbar 125A PE | | |
| 11 | Busbar 125A N | | |

SMISLINE TP technical details


Busbar system 250 A Overview



- | | | | |
|---|---|----|--|
| 1 | 6 and 8-module socket | 10 | Busbar 250 A PE |
| 2 | end piece on left and right | 11 | Busbar 250 A N |
| 3 | 6 and 8 module additional socket | 12 | Incoming block, supply 250 A, M8 bolt on maximum 150 mm² |
| 4 | Busbar LA 40 A | 13 | Incoming terminal component, supply 250 A, maximum 120 mm² |
| 5 | Busbar LB 40 A | 14 | Isolator |
| 6 | Busbar 250 A N | 15 | Spareway cover |
| 7 | Busbar 250 A L1 or DC +,- | 16 | Adapter for DIN rail components |
| 8 | Busbar 250 A L2 or DC +,- | 17 | Adapter for Motor starter MS116/132 |
| 9 | Busbar 250 A L3 or DC +,- | 18 | Combi module with a current rating of 32 A |

SMISLINE TP technical details

Socket/additional socket/busbars



Socket bases ZLS906, ZLS908

The SMISLINE socket system is a totally new kind of assembly and connection technology for the construction of distributions. Besides the classic method of snapping the devices onto 35-mm mounting rails, the new family of devices can be directly attached to the socket bases with integrated busbars. The time-consuming process of connecting up the supply is thereby no longer needed. In addition, in the event of rearrangement or expansion, the replacement of devices in existing systems is made significantly easier.



The socket sections and the wide range of accessories make it possible to plan with the capability for expansion and to construct distribution systems of any desired size in a short period of time.

6- and 8-module sockets are installed either by screwing them onto any flat surface or by snapping them onto a 35 mm DIN mounting rail. Lateral movement or detachment of the sockets again is possible before final fixing.

In order to determine the required socket length, the space necessary for

- the devices required
- the incoming terminal block and
- any reserve spaces needed must be determined.

Snap mounting

Pull down the slide with a screwdriver until it latches (socket can be moved).



Press on front of slid:

Fixed position
(Sockets fixed)

The key features

- System of any desired length (even number of poles)
- Integrated busbars
- Simple device change
- Long-term planning and problem free extension possible
- Significant time savings during assembly and connection



Busbars for the sockets and additional socket ZLS200

The busbars of size 10x3mm can be loaded with currents up to 100A. They are plated for perfect contact with the devices plug-in contacts. The maximum available busbar length is 1979 mm. The same busbar type is used, regardless whether it is fitted in the socket (L1, L2, L3, N) or in the additional socket (N, PE). The busbars are inserted in to the socket from the front.



Auxiliary busbars for the socket ZLS202

The 5x2mm auxiliary busbars are intended for a common power supply of auxiliary switches and signal contacts. They are also plated and their max. delivery length is 1979 mm.

Like the main busbars, the auxiliary busbars are inserted in holders LA and LB from the front. Of course, only on auxiliary busbar can be fitted.

SMISLINE TP technical details

Incoming terminal block/Incoming terminal components

General

The incoming terminal block is used to connect cables directly to the busbars. The terminals act directly on the busbars and therefore fix the incoming terminal block. Removable terminal tops permit the connection of continuous conductors (risers) while horizontal or vertical cable entry is also possible.

Instead of using the incoming terminal block, the power supply can also be realized via a device (e.g. residual current operated circuit breaker, miniature circuit breaker or switch disconnector).


Power supply left or right, maximum 125 A.

Max. 35 °C Ambient air temperature for 125 A continuously.



Power supply in centre, maximum 160 A.

A maximum of 125 A is permitted on either side. A total of 160 A must not be exceeded.



Incoming terminal blocks ZLS224, 225

A standard incoming terminal block whose cover provides protection against accidental contact. Construction height 50 mm. The base plate can be fitted with a maximum of 4 main terminals L1, L2, L3 and N for the busbars, and 2 auxiliary terminals LA and LB for the auxiliary busbars.



Incoming terminal blocks, low ZLS228, 229

Incoming terminal block with construction height of 36 mm.


SMISLINE TP technical details

Incoming terminal block/Incoming terminal components



Incoming terminal blocks ZLS260 to 262

Compact terminal block with the construction width of 18 mm for 2 poles. The maximum rated current is 63 A for L1, L2, L3N and 6 A for LA, LB.



Incoming maximum 63 A.



Incoming terminal component ZLS250 to 255

The incoming terminal component, with an installation width of 36 mm is available as a single-pole component for the line conductors L1, L2, L3 and as neutral. The terminals act directly on the busbars and thereby fix the incoming terminal component. The incoming terminal component, L1, L2, L3 and N can be combined to meet specific needs. A maximum cable cross-section of 95 mm² can be connected to the incoming terminal component.



Incoming terminal component, in centre, maximum 200 A.
But on each side not more than 125 A.




Incoming bolt-on solution M8 50 mm² up to 150 mm² or 4/0AWG for UL

This Incoming block can be used for side feed Incoming with 250A for IEC and UL applications. It is an bolt-on solution for a connection up to 150 mm². For a safe and strong connection to Incoming molded case circuit breaker upstream. Can only used for the 250 A Power Bar System.


SMISLINE TP technical details

Power supply



Indirect supply via residual current operated circuit breaker (RCCB) (or switch disconnector)


The supply cable is connected at the top of the RCCB. This supply variant gives the busbars and therefore all subsequent devices RCCB protection. If several RCCB groups are planned, the busbars should be separated and spaced using the dark grey busbar insulator ZLS938. Attention must then be paid to the regulations governing protection of the residual current circuit breaker by subsequent miniature circuit breakers. The supply can also be fed in through the switch disconnector.



Direct supply to residual current operated circuit breaker (or switch disconnector)


Instead of using the incoming terminal block, the power can also be supplied via a device

In this case, the supply cable is connected to the lower terminal of the device. The residual current operated circuit breaker or switch disconnector can be supplied with 63A regardless of its rated current, since the plug-in connection arrangement of the device is suitable for this amount of current. For current in excess of 63A, the incoming terminal block or the incoming terminal component should be used.



Supply of auxiliary busbars LA and LB

The two auxiliary busbars LA and LB can be supplied using the additional terminal ZLS 233 via an incoming terminal block. The maximum operating current of the auxiliary busbars is 40A.




Incoming block for two auxiliary busbars LA, LB

The pluggable incoming block is especially for the two auxiliary busbars LA, LB. The maximum rated current is 6A.

SMISLINE TP technical details

Incoming Power Bar System 250A and 400A IEC

- 01 Power supply side feed, maximum 250A.
- 02 Central feed 250A, 400A total. The cables in the connections must have the same length. Incoming terminal blocks ZLP25X.



SMISLINE TP technical details

Incoming UL 508 – Industrial Control Equipment

—
01, 02 Max. 250 A Incoming Power Bar System
250 A any side 600 V AC





—
03 Max. 250A Incoming 125A each side
600VAC

—
04 Max. 125A 600VAC

—
05 Max. 125A 600VAC

CSA C22.2 No. 14 – Industrial Control Equipment File E222110

Rated voltage:	277 Y/480V, 480V, 347 Y/600V and 600V
Rated current:	ZLS200 bus bar 125A, ZLSP200 250A
Maximum current for supply:	250A



SMISLINE TP technical details

Busbar system accessories



Socket end piece ZLS920

To prevent displacement of sockets and busbars (particularly when installed vertically) end pieces can be fitted at the start and finish of each row of sockets. These simultaneously ensure electrically protected covering of the busbar end faces and mechanical fixing of the sockets on the mounting rail.



Intermediate piece ZLS725

The light grey intermediate piece matches the device profile and fills empty module spaces.




Busbar insulator ZLS938

The dark grey busbar insulator electrically isolates the separated busbar ends from each other (e.g. when using several RCD protected groups) and also identifies the isolation point from outside. It conforms with the device profile and its space requirement is 1 module.



Busbar cover ZLS100

If component modules or spare modules are not required, the busbar cover ensures electrically protected covering of the main and auxiliary busbars. The cover (4 modules) can be divided anywhere. The openings allow voltage measurements on the busbars without removing the cover.



Extension adapter ZLS101

The extension adapter, single or several side by side, can be plugged into the busbar cover via the built-in holding device. This enables conventional DIN devices with 45 mm cap size to be snapped onto the SMISLINE socket. By plugging in several extension adapters one on top of the other, heights can be adjusted in multiples of 7 mm

SMISLINE TP technical details

Combi module: starting solutions in kit form

Direct-On-Line Starters

- MS116
- + BEA16-4
- + AF09, AF12, AF16

- MS116 up to 16 A
- + BEA26-4
- + AF26, AF30, AF38

- MS116 > 16 A
- + BEA38-4
- + AF26, AF30, AF38

- MS132
- + BEA16-4
- + AF09, AF12, AF16


- MS132 up to 10 A
- + BEA26-4
- + AF26, AF30, AF38

- MS132 > 10 A
- + BEA38-4
- + AF26, AF30, AF38



Mounting possibilities on the combi module:

The following combinations of contactor, motor circuit breaker and connector are possible on the combi module.



Reversing Starters

- MS116
- + BEA16-4, BER16-4, VEM4
- + AF09, AF12, AF16


- MS116 up to 16 A
- + BEA26-4, BER38-4, VEM4
- + AF26, AF30, AF38

- MS116 > 16 A
- + BEA38-4, BER38-4, VEM4
- + AF26, AF30, AF38

- MS132
- + BEA16-4, BER16-4, VEM4
- + AF09, AF12, AF16

- MS132 up to 10 A
- + BEA26-4, BER38-4, VEM4
- + AF26, AF30, AF38

- MS132 > 10 A
- + BEA38-4, BER38-4, VEM4
- + AF26, AF30, AF38



SMISLINE TP technical details

Definitions

Rated short-circuit breaking capacity I_{cn}

According to EN 60898-1

The maximum current which a switching device can switch off without damage at a rated operational voltage and rated operational frequency. It is specified as an effective value.

Rated ultimate short-circuit breaking capacity I_{cu}

According to EN 60947-2

Ultimate short-circuit breaking capacity that a circuit breaker can switch off without damage at a rated operational voltage and rated operational frequency. It is specified as an effective value.

Rated service short-circuit breaking capacity I_{cs}

According to EN 60947-2

Service short-circuit breaking capacity that a circuit breaker can switch off without damage at a rated operational voltage and rated operational frequency. It is specified as an effective value.

Rated insulation voltage U_i

The rated insulation voltage (U_i) is the voltage to which dielectric checks and creepage distances refer. The maximum rated operational voltage must not exceed its rated insulation voltage.

Rated impulse withstand voltage U_{imp}

Peak of a withstand voltage of a specified form and polarity with which the circuit can be loaded under specified test conditions without a breakdown and to which clearances relate. The rated impulse withstand voltage must be equal to or greater than the values of the withstand over-voltages (transient overvoltages) which occur in the system in which the device is used.

Rated short-time withstand current I_{cw}

The rated short-time withstand current is the effective value of the short-circuit current, as specified by the manufacturer for this circuit, that the circuit can conduct without damage. Unless otherwise specified, a time of 1 s shall apply.

Rated conditional short-circuit current I_{cc}

The rated conditional short-circuit current is the value of the prospective short-circuit current, as specified by the manufacturer, for a switching device combination that the latter can conduct during the total break time. The information about the specified short-circuit device must be given by the manufacturer.

Rated fused short-circuit current I_{cf}

The rated fused short-circuit current is the conditional rated short-circuit current if the short-circuit device is a fuse in accordance with IEC 60269 [IEV 441-17-21, modified].

Rated peak withstand current I_{pk}

The rated peak withstand current is the peak value of the withstand current of the circuit of a combination of switching devices, as specified by the manufacturer.

Back-up protection

Assignment of two overcurrent protective devices in series, where the protective device, generally but not necessarily on the supply side, effects the overcurrent protection with or without the assistance of the other protective device and prevents excessive stress on the latter [IEC 60947-1, definition 2.5.24].

Total selectivity

Overcurrent discrimination where, in the presence of two overcurrent protective devices in series, the protective device on the load side effects the protection without causing the other protective device to operate [IEC 60947-2, definition 2.17.2].

Partial selectivity

Overcurrent discrimination where, in the presence of two overcurrent protective devices in series, the protective device on the load side effects the protection up to a given level of overcurrent, without causing the other protective device to operate [IEC 60947-2, definition 2.17.3].

SMISLINE TP technical details

Approvals according to IEC/EN 61439-6. Busbar system 125 A.

Busbar system touch proof:

Use only for wall mounted application (horizontal or vertical).

When installed correctly the requirements of EN/IEC 61439-2 are met.

Number of poles	max. 6 to 110 3p+N / 2 additional bars PE+N
Rated operational voltage (U_e)	690 V AC, 1000 V DC (400 V AC, 250 V DC when used for load-free snap on and off under power)
Rated insulation voltage (U_i)	690 V AC, 1000 V DC
IP Code	IP20B
Mounting position	horizontal or vertical, direct mounting or mounting on DIN rail acc. to EN 60715 35 mm
Pollution degree	3 (690 V AC) 2 (1000 V DC)
Rated impulse voltage (U_{imp})	8 kV (L1L2L3N)
Rated current of the assembly (I_n)	Max. 125 A side feeding Max. 200 A (center feeding) Max. 250 A (Double feed side or center)
Auxiliary circuit	max. 40 A
Rated current of a circuit (I_{nc})	Main circuit: Max. 125 A
Rated current of Auxiliary circuit	40 A
Rated short-time withstand current (I_{cw})	10 kA / 300 ms
Auxiliary circuit	4 kA / 50 ms
Rated peak withstand current (I_{pk})	Main circuit: 30 kA
Auxiliary circuit	6 kA
Rated frequency (f)	50/60 Hz
Rated conditional short-circuit current (I_{cc})	100 kA (415 V, 50 kA)
Ambient air temperature	max. 60°C
Size of CU bars 3P+N+PE	3x10 mm (30 mm ²)
Size of CU auxiliary bars La Lb	2x5 mm (10 mm ²)

Rated conditional short-circuit current (I_{cc})	Incoming current of main busbars (L1, L2, L3, N)	Short circuit protection device (SCPD)	
		Fuse	MCCB
50 kA (690 V)	250 A		ABB T _{max} 250 A
	200 A	NH1 gG 690 V/200 A	ABB T _{max} 250 A
	160 A	NH1 gG 690 V/160 A	ABB T _{max} 250 A
	63 A	NH00 gG 690 V/63 A	ABB Type S803S in combination with Type S803S-SCL63-SR
	Incoming current of auxiliary busbars (La Lb)		
50 kA (415 V)	40 A	NH00 gG 690 V/40 A	ABB Type S800 with 240V/415 V

Rated Voltage (U_e)	Rated conditional short-circuit current (I_{cc})	Incoming current of main busbars (L1, L2, L3, N)	Short circuit protection device (SCPD)	
			Fuse	MCCB
415 V	100 kA	250 A	NH1 gG 690V/250A	ABB T _{max} T4/XT4 250 A
690 V	25 kA	250 A	NH1 gG 690V/250A	ABB T _{max} T4/XT4 250 A
		Incoming current of auxiliary busbars (La Lb)		
	25 kA	40 A	NH00 gG 415 V/40 A	ABB Type S800 with (240V/415 V AC)

SMISLINE TP technical details

Busbar system 125A

**SMISLINE TP system for UL 508 – Industrial Control Equipment,
CSA C22.2 No. 14 – Industrial Control Equipment UL File E222110**

Technical data UL508 Industrial Control Equipment SMISLINE TP busbar system

Rated Voltage: 600 VAC

Rated Current (End feed, left and right): 125A left, 125A right

Rated Current (Center Feed): 250A max. if used with two feeder blocks.

Short Circuit Ratings: 50kA, max. 480VAC and 480Y/277V and 240VAC or 35 kA. max. 600VAC and 600Y/347V

Technical data UL508 Industrial Control Equipment (ZLS906, ZLS908, ZLS920, ZLS926, ZLS928)

	Busbar ZLS200	Feeder block ZLS924 ZLS25X	Combimodule ZLS840X, 842X	Universal- adpter ZLS97X	Terminals ZLS95XUL, 91XUL	Combi modul ZMS132X	Adapter moter strater ZMS93X
Maximum rated voltage	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC
Maximum rated current	125 A	150A	30 A	32 A, 63 A	32 A, 100 A, 150 A	32 A	32 A

Terminals for 125A SMISLINE TP System

ZLS954UL - Terminal 150A (Neutral)

ZLS959UL - Terminal (PE)

ZLS913UL - Terminal 63A (Neutral)

ZLS918UL – Terminal 32A (Neutral)

ZLS919UL - Terminal (PE)

ZLS929UL - Terminal (PE)

Circuit breaker accessories UL489 universal adapter

	970UL, 971UL, 972UL or 973UL
Maximum nominal voltage	600 V
Maximum nominal current	25 A, 45 A

SMISLINE TP technical details

Technical data according to IEC/EN 61439-6

Power Bar System 250 A

Busbar system touch proof:

Use only for wall mounted application (horizontal or vertical).

When installed correctly the requirements of EN/IEC 61439-2 are met.

Number of poles:	6 to 110 3p+N / 2 additional bars PE+N
Rated operational voltage (U_o):	690VAC, 1000VDC (400VAC, 250VDC when used for load-free snap on and off under power)
Rated insulation voltage (U_i) Main circuit:	690VAC, 1000VDC
Rated insulation voltage (U_i) Auxiliary circuit:	415VAC
IP Code:	IP20B
Mounting position:	horizontal or vertical, direct mounting or mounting on DIN rail acc. to EN 60715 35mm
Pollution degree:	3 (690V a.c.) 2 (1000V d.c.)
Rated impulse voltage (U_{imp}):	8 kV Main circuit; 6 KV Auxiliary circuit
Rated current of the assembly ($I_n A$):	max. 250 A side feeding
Rated current of a circuit (I_{nc}):	Main circuit: Max. 100A
Rated current of Auxiliary circuit:	40A
Rated short-time withstand current (I_{cw}):	15kA/100 ms Main circuit 4 kA / 50 ms Auxiliary circuit
Rated peak withstand current Main circuit (I_{pk}):	Main circuit: 30kA
Rated peak withstand current Auxiliary circuit (I_{pk}):	6kA
Rated frequency (f):	50/60 Hz
Rated conditional short-circuit current (I_{cc}):	see table below
Ambient air temperature:	max. 60°C
Size of CU bars 3P+N+PE:	3x25mm (75 mm ²)
Size of CU auxiliary bars La Lb:	2x5 mm (10 mm ²)

Rated Voltage (U_o)	Rated conditional short-circuit current (I_{cc})	Incoming current of main busbars (L1, L2, L3, N)	Short circuit protection device (SCPD)	
			Fuse	MCCB
415 V	100 kA	250 A	NH1 gG 690V/250A	ABB T _{max} T4/XT4 250 A
690 V	25 kA	250 A	NH1 gG 690V/250A	ABB T _{max} T4/XT4 250 A
Incoming current of auxiliary busbars (La Lb)				
	25 kA	40 A	NH00 gG 415 V/40 A	

SMISLINE TP technical details

Busbar system 250 A

Technical data data UL508; Approvals for US and CA: cULus
SMISLINE TP system for UL 508 – Industrial Control Equipment,
CSA C22.2 No. 14 – Industrial Control Equipment UL File E222110

Technical data UL508 Industrial Control Equipment SMISLINE TP busbar system

Rated Voltage: 600 V AC

Rated Current: 250 A

Short Circuit Ratings: 50 kA, max. 480 V AC, 480 Y/277 V and 240 V AC or 30 kA, max. 600 V AC and 600 Y/347 V

Technical data UL508 Industrial Control Equipment (ZLSP906, ZLSP908, ZLSP920)

	Busbar ZLSP200	Feeder ZLS934	Feeder block ZLS924, 95X	Combimodule ZLS840X, 842X	Universal- adapter ZLS97X	Terminals ZLS95XUL, 91XUL	Combi modul ZMS132X	Adapter moter strater ZMS93X
Maximum rated voltage	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC
Maximum rated current	250 A	250 A	150A	30 A	32 A, 63 A	32 A, 100 A, 150 A	32 A	32 A

Circuit breaker accessories UL489 universal adapter

	970UL, 971UL, 972UL or 973UL
Maximum nominal voltage	600 V
Maximum nominal current	25 A, 45 A

SMISLINE TP technical details

Miniature circuit breaker Properties



General Information

The SMISLINE miniature circuit-breaker is an energy-restricting circuit-breaker that has high performance values and that is equally suitable for the industrial sector, for commercial use and for installation at home.

If a short-circuit occurs, it guarantees excellent selectivity conditions to upstream overcurrent circuit breakers while the load on equipment that is connected downstream is limited to a minimum amount.

The most important features

- High rated breaking capacity of 10 kA or 6 kA
- Optimum ease of installation and connection
- The pole conductors are protected against accidental contact
- Tripping characteristic on B, C, D, K, UCZ/UCC

Miniature circuit-breaker in accordance with standard EN 60898-1

This standard is for electrical installation material for household installations and for similar purposes. It regulates the use of miniature circuit-breakers by the layman up to a maximum of 125 A, a voltage of 440 VAC and up to a maximum of 25 kA.

Miniature circuit-breaker in accordance with standard EN60947-2

This standard is for low-voltage material used for industrial purposes. It regulates the use of circuit-breakers (and not miniature circuit-breakers) by qualified personnel up to a maximum voltage of 1000 VAC or 1500 VDC. This standard does not recognise any maximum values when it comes to current and breaking capacity. In practice, the standard is also applied to miniature circuit-breakers.

Brief description of tripping


The SMISLINE miniature circuit breakers have a current-limiting operation. They have two different releases acting on the mechanism.

1. Thermal release, operating with a time delay, for overload protection
2. Electro-magnetic release plunger operated for short-circuit protection.

They offer:

- high short-circuit breaking capacity
- high selectivity to the back-up fuse
- In the event of short-circuits, low electrodynamic and heating effects on the cable and the point of fault location due to the drastically limited let through energy $\int i^2 dt$.

Oscillogram of a short-circuit current interruption



- $I_k \cdot \sqrt{2}$ = peak value of prospective short-circuit current
- i_D = Max. peak let through current of circuit breaker S 400
- U_n = Supply voltage
- U_b = Arc voltage of circuit breaker
- t_k = Total interruption time

SMISLINE TP technical details

S400M

With a expert working the requirements of EN/IEC 61439-2 are as well covered

	S400E, S400M
General data	
Tripping characteristics	B,C,D,K
Standards	IEC/EN 60898-1 IEC/EN 60947-2
Poles	1P, 1P+NP, 2P, 3P, 3P+NP
Rated current I_n	0.5A ... 63A
Rated frequency f	50/60Hz
Rated insulation voltage U_i acc. to DIN EN 60664-1	440 VAC
Rated impulse withstand voltage U_{imp} (1.2/50 μ s)	4 kV
Overvoltage category	III
Pollution degree	2
Data acc. to IEC/EN 60898-1	
Rated operational voltage U_e	1P: 230/400 VAC; 1P+N: 230 VAC; 2 ... 4P: 400 VAC; 3P+N: 400 VAC
Min. operating voltage	12 VAC–12 VDC
Rated short-circuit capacity I_{cn}	10 kA S400M
Energy limiting class	3
Reference Ambient Air Temperature for Overload Tripping	C, D: 30 °C
Electrical and Mechanical Endurance	10 000 ops.
Data acc. to IEC/EN 60947-2	
Rated operational voltage U_e	1P: 240 VAC; 1P+N: 240 VAC; 2 ... 4P: 415 VAC; 3P+N: 415 VAC
Min. operating voltage	12 V AC–12 V DC
Rated ultimate short-circuit capacity I_{cu}	25 kA (0,5 up to 16 A, 240/415 V) 15 kA (20 up to 63 A, 240/415 V) 15 kA (0,5 up to 16 A, 254/440 V) 6 kA (20 up to 63 A, 254/440 V)
Rated service short-circuit capacity I_{cs}	15 kA (0,5 up to 16 A, 240/415 V) 7,5 kA (20 up to 63 A, 240/415 V) 6 kA (0,5 up to 16 A, 254/440 V) 3 kA (20 up to 63 A, 254/440 V)
Reference Ambient Air Temperature for Overload Tripping B, C, D: 30 °C K: 40 °C	
Electrical and Mechanical Endurance	$I_n < 32A$: 20 000 operating cycles $I_n \geq 32A$: 10 000 operating cycles
Mechanical Data	
Housing	RAL 7035
Toggle	black
Classification acc. To NF F 126-101, NF F 16-102	acc. to I2/F3
Protection degree acc. to EN 60529	IP20, IP40 in enclosure with cover
Mechanical endurance	20 000 ops.
Shock resistance acc. to IEC/EN 60068-2-30	30g–3 shocks–11ms
Vibration resistance acc. to IEC/EN 60068-2-6	5g–20 cycles at 5 ... 150 ... 5 Hz with load 0.8 I_n
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	2 cycles with 55 °C/90–96% and 25 °C/95–100%
Ambient temperature	–25 ... +55 °C
Storage temperature	–40 ... +70 °C
Installation	
Standed Cross-section of conductors (top/bottom)	upper terminal section: 0,75–25 mm ² lower terminal section: 0,75–10 mm ²
Tightening torque	2.8 Nm
Screwdriver	No. 2 Pozidrive
Mounting	plug in on bus bar system SMISLINE
Mounting position	any
Supply	any
Dimensions and weight	
Pole dimensions (HxDxW)	91x18x82
Pole weight	110 g


SMISLINE TP technical details

Miniature circuit breaker S400UC


S400UC	
General data	
Tripping characteristics	UCC, UCZ
Standards	IEC/EN 60947-2
Poles	1P, 2P
Rated current I_n	0.5 A ... 63 A
Rated frequency f	50/60 Hz
Rated insulation voltage U_i acc. to DIN EN 60664-1	440 V AC
Rated impulse withstand voltage $U_{imp.}$ (1.2/50 μ s)	4 kV
Overvoltage category	III
Pollution degree	2
Data acc. to IEC/EN 60947-2	
Rated operational voltage U_e	110 V d.c. (1pole) 220 V d.c. (poles 1; 2) 440 V d.c. (2pole) 230/400 V (poles 1;2)
Min. operating voltage	12 V AC–12 V DC
Rated ultimate short-circuit capacity I_{cu}	10 kA (0,5 up to 63 A, 220 V d.c. 1pole) 20 kA (0,5 up to 63 A, 110 V d.c. 1pole) 25 kA (0,5 up to 63 A, 220 V d.c. 2pole) 10 kA (0,5 up to 63 A, 440 V d.c. 2pole) 10 kA (0,5 up to 63 A, 230/400 V) a.c.
Rated service short-circuit capacity I_{cs}	10 kA (0,5 up to 63 A, 220 V d.c. 1pole) 10 kA (0,5 up to 63 A, 110 V d.c. 1pole) 20 kA (0,5 up to 63 A, 220 V d.c. 2pole) 10 kA (0,5 up to 63 A, 440 V d.c. 2pole) 6 kA (0,5 up to 63 A, 230/400 V) a.c.
Reference Ambient Air Temperature for Overload Tripping	30 °C
Electrical and Mechanical Endurance	$I_n < 32$ A: 20 000 operating cycles $I_n \geq 32$ A: 10 000 operating cycles
Mechanical Data	
Housing	RAL 7035
Toggle	black
Protection degree acc. to EN 60529	IP20*, IP40 in enclosure with cover
Mechanical endurance	20 000 ops.
Shock resistance acc. to IEC/EN 60068-2-30	30 g–3 Shocks–11 ms
Vibration resistance acc. to IEC/EN 60068-2-6	5 g–20 cycles at 5 ... 150 ... 5 Hz with load $0.8 I_n$
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	2 cycles with 55 °C/90–96 % and 25 °C/95–100 %
Ambient temperature	–25 ... +55 °C
Storage temperature	–40 ... +70 °C
Installation	
Standed Cross-section of conductors (top/bottom)	upper terminal section: 0,75–25 mm ² lower terminal section: 0,75–10 mm ²
Tightening torque	2.8 Nm
Screwdriver	No. 2 Pozidrive
Mounting	plug in on bus bar system SMISLINE
Mounting position	any
Supply	any
Dimensions and weight	
Pole dimensions (H x D x W)	91 x 18 x 82
Pole weight	110 g

SMISLINE TP technical details


Miniature circuit breaker Trip characteristics




Trip characteristics: B
 Thermal trip
 $1.13...1.45 \times I_n$
 Electromagnetic trip
 $3...5 \times I_n$ AC
 $4...7 \times I_n$ DC
 Calibration temperature 30°C




Trip characteristics: C
 Thermal trip
 $1.13...1.45 \times I_n$ acc. to EN60898-1
 Thermal trip
 $1.05...1.3 \times I_n$ acc. to EN60947-2
 Electromagnetic trip
 $5...10 \times I_n$ AC
 $7...14 \times I_n$ DC
 Calibration temperature 30°C



Trip characteristics: D
 Thermal trip
 $1.13...1.45 \times I_n$
 Electromagnetic trip
 $10...20 \times I_n$ AC
 $15...30 \times I_n$ DC
 Calibration temperature 30°C



Trip characteristics: K
 Thermal trip
 $1.05...1.3 \times I_n$
 Electromagnetic trip
 $10...14 \times I_n$ AC
 $14...20 \times I_n$ DC
 Calibration temperature 40°C



Trip characteristics: UC


Z	C
$1.05...1.35 \times I_n$	$1.13...1.45 \times I_n$
$3...5 \times I_n$ DC	$7...14 \times I_n$ DC
$2...3 \times I_n$ AC	$5...10 \times I_n$ AC
Calibration temperature 30°C	

SMISLINE TP technical details

Miniature circuit breaker Trip characteristics

Trip characteristics example of trip curve interpretation of B-characteristics

- a Thermal trip characteristics:**
 Lower test current I_1 = defined as non-tripping current.
 The circuit breaker withstands 1.13 times the rated current for at least 60 minutes.
 Upper test current I_2 = defined as trip current.
 The circuit breaker trips at 1.45 times the rated current within 60 minutes.
- b Electro-magnetic trip characteristics AC:**
 The circuit breaker withstands 3 times the rated current for more than 0.1 sec. (in this example, up to around 2 sec.).
 The circuit breaker trips in less than 0.1 sec. at 5 times the rated current.



Trip behaviour of different trip characteristics

Trip characteristics and current ratings	Thermal release Test currents:		Trip time	Electromagnetic release Test currents:		Trip time
	lower test current I_1	upper test current I_2		lower test current	upper test current	
B 4 to 63 A	$1.13 \times I_n$	$1.45 \times I_n$	> 1 h < 1 h	$3 \times I_n$	$5 \times I_n$	> 0.1 s < 0.1 s
C 0.5 to 63 A	$1.13 \times I_n$	$1.45 \times I_n$	> 1 h < 1 h	$5 \times I_n$	$10 \times I_n$	> 0.1 s < 0.1 s
D 6 to 63 A	$1.13 \times I_n$	$1.4 \times I_n$	> 1 h < 1 h	$10 \times I_n$	$20 \times I_n$	> 0.1 s < 0.1 s
K 0.5 to 63 A	$1.05 \times I_n$	$1.2 \times I_n$	> 2 h	$8 \times I_n$	$12 \times I_n$	> 0.2 s
		$1.5 \times I_n$	< 2 h			< 0.2 s
		$6.0 \times I_n$	< 2 min > 2 s			

Application characteristics: B
 Miniature circuit breaker for circuits supplying loads generating no or only minor inrush currents (boilers, electric heaters, cookers).

Application characteristics: C
 The 'standard' miniature circuit breaker for circuits supplying loads producing inrush currents particular to inductive loads (TV sets, fluorescent and discharge lamps) and for socket outlets.

Application characteristics: D
 Miniature circuit breaker for circuits supplying loads producing very high inrush currents (transformers, capacitor banks).
 Main circuit breaker for the back-up protection of downstream connected circuit breakers.

Application characteristics: K
 Circuit breaker for equipment: The characteristics of these types enable the close protection requirements for equipment to be met.

Application characteristics: UC
 Device protection in DC systems of up to 250V = with a time constant of <15ms (emergency networks, electroplating, etc.).

SMISLINE TP technical details

Miniature circuit breaker

Internal resistances at rated voltage and power losses

Internal resistances and power loss per pole (cold resistance at room temperature)

Rated current I_n A	S400 M B, C, D ¹		K		S400 M-UCZ		S400 M-UCC	
	R_i Ω	P_v W	R_i Ω	P_v W	R_i Ω	P_v W	R_i Ω	P_v W
0.5	5.5	1.4	4.906	1.2	6.34	1.6	6.34	2.6
1	1.44	1.5	1.505	1.5	1.55	1.6	1.55	3.5
1.6	0.63	1.6	0.594	1.5	0.695	1.8	0.695	2.9
2	0.460	1.8	0.415	1.7	0.46	1.9	0.46	3.9
3	0.150	1.4	0.181	1.6	0.165	1.5	0.165	4.5
4	0.123	1.9	0.150	2.4	0.12	1.9	0.12	2.4
6	0.051	1.8	0.080	2.9	0.052	1.9	0.052	3.5
8	0.029	1.9	0.043	2.7	0.038	2.4	0.038	3.5
10	0.012	1.2	0.0165	1.7	0.0126	1.3	0.013	1.3
13	0.0112	1.9	0.0153	2.6	0.0101	1.7	0.010	2.2
16	0.0074	1.9	0.0095	2.4	0.0077	1.8	0.007	1.8
20	0.004	1.6	0.0073	2.9	0.0067	2.7	0.0067	2.5
25	0.0032	2	0.0053	3.3	0.0046	2.9	0.005	3.1
32	0.0026	2.7	0.0034	3.4	0.0025	3.6	0.0025	3.7
40	0.0026	4.2	0.0028	4.5	0.0028	4.5	0.003	4.8
50	0.0017	4.3	0.0021	5.3	0.0012	3.0	0.0012	3.0
63	0.0014	5.6	0.0015	5.9	0.0007	2.8	0.0007	3.6

¹ Currents 0.5–4 A only apply to C and K characteristics.

SMISLINE TP technical details



Miniature circuit breaker

Limitation of specific let-through energy I^2t



I^2t diagrams - Specific let-through energy value I^2t

The I^2t curves give the values of the specific let-through energy expressed in A^2s (A=amps; s=seconds) in relation to the prospective short-circuit current (I_{rms}) in kA.

S400 characteristics B-C



S400 characteristics D-K



SMISLINE TP technical details


MCBs technical details

Limitation curves – Peak current values I_p


Limitation curves – Peak current values

The I_p curves give the values of the peak current, expressed in kA, in relation to the perspective symmetrical short-circuit current (kA).

Characteristics B–C



Characteristics K–D



SMISLINE TP technical details

Power supply: overload and short-circuit protection

Overload and short-circuit protection of the plug-in socket system

Protection of the busbar system without upstream overcurrent protection

An important factor for the protection of the busbar system (sockets, incoming terminal block, incoming terminal component, adapter, combi module or terminals) is the characteristic of the rated peak withstand current I_{pk} . The rated peak withstand current I_{pk} of the SMISLINE busbar system is 17 kA.

Protection of the busbar system with upstream overcurrent protection

The rated short-circuit current I_{cf} of the SMISLINE busbar system is 50 kA.

If, on the power supply side, a circuit breaker of the type Sace Tmax 200A, a high performance circuit breaker S800 or a NH fuse is positioned upstream of the busbar system, then due to the short-circuit current limiting effect of this protection device, a larger prospective short-circuit current of up to 50 kA for the plug-in socket system is permissible.

Overload and short-circuit protection of devices on the busbar system

The rated short-circuit breaking capacity (or rated breaking capacity) of the protective devices, together with the maximum short-circuit current at the installation location of the devices on the busbar system, must be taken into consideration.

This is not only relevant for the SMISLINE busbar system, but is also applicable to the distribution construction.

Miniature circuit breaker

If the prospective short-circuit current at the installation location of a miniature circuit breaker is not greater than its rated breaking capacity, no back-up protection via an upstream overcurrent protection device is necessary.

If the prospective short-circuit current at the installation location of a miniature circuit breaker is greater than its rated short-circuit breaking capacity, the current ratings of the upstream overcurrent protection device must not exceed the table values in the back-up tables (catalogue, page 2/20 onwards).

Residual-current circuit breaker

A back-up fuse with max. 100A gL/gG or a high performance circuit breaker S800 100A is required for short-circuit protection upstream or downstream (see Coordination table, page 2/42). A back-up fuse is not required up to the level of the internal short-circuit withstand rating. Thermal protection can be ensured by means of downstream miniature circuit breakers, but only if the rated currents do not exceed the value of the current rating of the residual-current circuit breaker in consideration of a utilisation factor.

Surge arrester OVR

An upstream overcurrent protection device with max. 160A gL/gG is necessary for short-circuit protection (in the case of non-independent interruptions of the secondary current).

Back-up fuses for devices with a universal adapter

In principle, the same requirements apply as for directly plugged-in devices.

SMISLINE TP technical details

Back-up and selectivity dates

SOC - Selected Optimized Coordination

See as well ABB on <https://applications.it.abb.com/SOC/>



SOC - SELECTED OPTIMIZED COORDINATION

- Motor protection
- Selectivity
- Back-up
- Other devices protection

SOC - Selected Optimized Coordination



SMISLINE TP technical details

Miniature circuit breaker

Back-up protection with fuses, S800

- a) If the short-circuit current at the point of installation of the circuit breaker is not greater than the nominal breaking capacity of the MCB, an upstream fuse is not needed. If a fuse is fitted upstream for installation reasons, any nominal current may be selected for the fuse.
- b) If the short-circuit current at the point of installation of the circuit breaker is greater than its nominal breaking capacity, the nominal currents of the upstream fuses must not exceed the values specified in the table (back-up protection of the circuit breaker).

Upstream: Fuse NH..gL/gG

L.	S.		NH gL/gG							
	I_{cu} [kA]	I_n [A]	25	40	63	80	100	125	160	200
S400M/S450M FS401M/FS451M FS403M/ FS453M	I_{cn} [kA] 10	all types	100	100	100	100	80	50	30	20
S400E/S450E FS401E/FS451E FS403E/FS453E	I_{cn} [kA] 6	all types	100	100	70	40	25	15	10	-

E. = Upstream
L. = Downstream
Selectivity limits are specified in kA

S800S – S400M (SMISLINE) @ 230/400 V

L.	Char.	I_{cu} [kA]	S.										
			S800S										
			B, C, D, K										
S400M FS401M FS403M	B, D	10	50										
			I_n [A]	25	32	40	50	63	80	100	125		
			I_{cn} [kA]	4*...16	50	50	50	50	50	50	50	50	50
				20	50	50	50	50	50	50	50	50	50
				25		50	50	50	50	50	50	50	50
				32			50	50	50	50	50	50	50
				40				50	50	50	50	50	50
	50					50	50	50	50	50			
	63						50	50	50	50			

L.	Char.	I_{cu} [kA]	S.										
			S800S										
			B, C, D, K										
S400M	C, K	15	50										
			I_n [A]	25	32	40	50	63	80	100	125		
			I_{cn} [kA]	50	0.5...2	50	50	50	50	50	50	50	50
				25	3...20	50	50	50	50	50	50	50	50
				25		50	50	50	50	50	50	50	50
				32			50	50	50	50	50	50	50
				40				50	50	50	50	50	50
	50					50	50	50	50	50			
	63						50	50	50	50			

S800N – S400M (SMISLINE) @ 230/400 V

L.	Char.	I_{cu} [kA]	S.										
			S800N										
			B, C, D										
S400M FS401M FS403M	B, D	10	36										
			I_n [A]	25	32	40	50	63	80	100	125		
			I_{cn} [kA]	4*...16	36	36	36	36	36	36	36	36	36
				20	36	36	36	36	36	36	36	36	36
				25		36	36	36	36	36	36	36	36
				32			36	36	36	36	36	36	36
				40				36	36	36	36	36	36
	50					36	36	36	36	36			
	63						36	36	36	36			

L.	Char.	I_{cu} [kA]	S.										
			S800 N										
			B, C, D										
S400M	C, K	15	36										
			I_n [A]	25	32	40	50	63	80	100	125		
			I_{cn} [kA]	50	0.5...2	36	36	36	36	36	36	36	36
				25	3...20	36	36	36	36	36	36	36	36
				25		36	36	36	36	36	36	36	36
				32			36	36	36	36	36	36	36
				40				36	36	36	36	36	36
	50					36	36	36	36	36			
	63						36	36	36	36			

E. = Upstream
L. = Downstream
Selectivity limits are specified in kA

Consulting the back-up table

This table provides the value (in kA) for which the back-up protection is ensured between a given combination of circuit breakers. The table covers possible combinations between the S800 or SACE series Tmax and between SMISLINE miniature circuit breakers 400M.

SMISLINE TP technical details

Miniature circuit breaker


Back-up protection with Tmax and XT

Sace Tmax – S400 @ 230/400 V

Downstream	Version	I _n [A]	Up-Stream Version	I _{cu} [kA]	T1	T1	T1	T2	T3	T4	T2	T3	T4	T2	T4	T2	T4	
					B	C	N	N	N	N	S	S	S	H	H	L	V	
S400E FS401E/403E	B, C	6...10 13...63	6	6	16	25	30	36	36	36	36	36	36	36	36	36	36	36
S400M FS401M/403M	C, K	0.5...10 13...63	10	10	16	25	30	36	36	36	36	36	36	36	36	36	36	36
S400M FS401M/403M	B, D	6...10 13...63	10	10	16	25	30	36	36	36	36	36	36	36	36	36	36	36

Sace XT – S400 @ 230/400 V

Downstream	Version	I _n [A]	Up-Stream Version	I _{cu} [kA]	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4	XT2	XT4	
					B	C	N	S	H	L	V									
FS400E S400E S450E	B, C	6...10 13...63	6	6	18	25	30	36	36	36	36	36	36	36	36	36	36	36	36	36
FS400M S400M S450M	C, K	0.5...10 13...63	10	10	18	25	30	36	36	36	36	36	36	36	36	36	36	36	36	36
FS400M S400M S450M	B, D	6...10 13...63	10	10	18	25	30	36	36	36	36	36	36	36	36	36	36	36	36	36



S800N - S400E @ 230/400 V

L.	Char.	I _{cu} [kA]	E. S800N B, C, D										
			36										
			I _n [A]	25	32	40	50	63	80	100	125		
S400E	B	6	6	36	36	36	36	36	36	36	36	36	
			10	36	36	36	36	36	36	36	36	36	
			13	36	36	36	36	36	36	36	36	36	
			16	36	36	36	36	36	36	36	36	36	
			20	36	36	36	36	36	36	36	36	36	
			25	36	36	36	36	36	36	36	36	36	
			32	36	36	36	36	36	36	36	36	36	
			40	36	36	36	36	36	36	36	36	36	
			36	36	36	36	36	36	36	36	36	36	
			63	36	36	36	36	36	36	36	36	36	

Example 1: With a S800 nominal current 50 A is a Back-up protection till a nominal current of 25 A to a S400 given. The Back-up protection ist till 36 kA.

Example 2: There is no Back-up protection between supply side and the load side given.

Back-up protection

The tables given provide the value (in kA, referring to the breaking capacity) for which the back-up protection among the combination of selected circuit breakers is verified. The tables cover the possible combinations between S800 and those between the above mentioned circuit breakers and the ABB series of modular circuit breakers S400.

The values indicated in the tables refer to the voltage:

- V_n of 230/400VAC

SMISLINE TP technical details

Miniature circuit breaker

Influence of ambient temperature

Allowable current of miniature circuit breakers depending on ambient temperature and max. load current for row mounted miniature circuit breakers.

Practical procedure

Conditions often arise which allow for simple consideration of the ambient temperature and thermal influences of row mounted circuit breakers according to EN 60898 and EN 60947-2. The following procedure has proven to be effective:

1. Selection of circuit breaker according to the rated current of the equipment or the current carrying capacity of the cable depending on which of these is the lower value.
2. Consideration of thermal factors
 - for an ambient temperature of 40°C: $I_b \leq 0,9 \times I_n$
 - for thermal influence of row mounted circuit breakers subject to the same loads: $I_b \leq 0,75 \times I_n$
3. This results in the rated current of the circuit breaker to be selected for $I_n \leq 1,5$ times the relevant current according to point 1.

This procedure considers all thermal influence factors and results in an optimum choice of the rated current for the circuit breaker.

Example: Current carrying capacity required of the cable: 4 A. Selected rated current of circuit breaker taking thermal influence into consideration: $I_n \geq 1,5 \times 4 A \geq 6 A$.

Basis for the simplified procedure

1. Different ambient temperature


The thermal releases are set to a reference ambient temperature. For trip characteristic K, this is 40°C, for trip characteristics B, C and D, this is 30°C. At different ambient temperatures, the specified current values change by around 6% per 10°C difference in temperature.

For more accurate calculations and very high or very low ambient temperatures, the following tables apply:

2. Influence of row mounted devices at continuous load

If the circuit breakers are lined up close to one another and have equally high load levels, a correction factor must be taken. This influence can be reduced if fillers and/or spacers (9 mm wide) are used.

Influence of adjacent devices S400



Influence of adjacent devices	
Correction factor Fm	
No. of adjacent devices	correction factor
1	1
2	0.95
3	0.9
4	0.86
5	0.82
6	0.8
7	0.78
8	0.77
9	0.76
>9	0.76

SMISSLINE TP technical details

Miniature circuit breaker

Influence of ambient temperature

Max. operating currents depending on ambient temperature for S400 miniature circuit breakers of trip characteristics B, C, D, UC-C and UC-Z

I _n (A)	Ambient temperature T (°C)										
	0	10	15	20	25	30	35	40	45	50	55
0.5*	0.58	0.55	0.53	0.52	0.51	0.50	0.48	0.47	0.46	0.44	0.43
1.0*	1.15	1.09	1.07	1.04	1.02	1.0	0.97	0.94	0.91	0.89	0.86
1.6*	1.85	1.75	1.71	1.67	1.63	1.6	1.55	1.50	1.46	1.42	1.38
2.0*	2.31	2.19	2.13	2.08	2.03	2.0	1.93	1.88	1.83	1.77	1.72
3.0*	3.5	3.32	3.24	3.16	3.09	3.0	2.93	2.85	2.77	2.69	2.61
4.0*	4.6	4.37	4.27	4.17	4.07	4.0	3.86	3.76	3.66	3.56	3.45
6.0	6.9	6.59	6.44	6.29	6.14	6.0	5.83	5.68	5.53	5.37	5.22
8.0	9.2	8.84	8.63	8.42	8.22	8.0	7.81	7.6	7.39	7.19	6.98
10.0	11.5	10.9	10.7	10.4	10.2	10.0	9.65	9.39	9.14	8.88	8.63
13.0	15.0	14.4	14.0	13.7	13.3	13.0	12.7	12.3	12.0	11.6	11.3
16.0	18.5	17.6	17.2	16.8	16.4	16.0	15.6	15.2	14.7	14.3	13.9
20.0	23.1	22.1	21.6	21.0	20.5	20.0	19.5	19.0	18.5	18.0	17.5
25.0	28.9	27.5	26.9	26.3	25.6	25.0	24.3	23.7	23.0	22.4	21.8
32.0	37.0	35.3	34.5	33.7	32.8	32.0	31.2	30.4	29.5	28.7	27.9
40.0	46.2	44.1	43.0	42.0	41.0	40.0	39.0	37.9	36.9	35.9	34.9
50.0	57.7	55	53.7	52.4	51.1	50.0	48.6	47.3	46.0	44.7	43.4
63.0	72.7	69.3	67.7	66.1	64.5	63.0	61.3	59.7	58.1	56.4	54.8

* only applies to C

Max. operating currents depending on ambient temperature for S400 miniature circuit breakers of trip characteristic K

I _n (A)	Ambient temperature T (°C)									
	10	15	20	25	30	35	40	45	50	55
0.5	0.54	0.52	0.51	0.50	0.49	0.47	0.5	0.45	0.43	0.42
1.0	1.14	1.12	1.09	1.07	1.0	1.02	1.0	0.96	0.94	0.91
1.6	1.85	1.81	1.77	1.73	1.7	1.65	1.6	1.56	1.52	1.48
2.0	2.29	2.23	2.18	2.13	2.1	2.03	2.0	1.93	1.87	1.82
3.0	3.48	3.40	3.32	3.25	3.2	3.09	3.0	2.93	2.85	2.77
4.0	4.58	4.48	4.38	4.28	4.2	4.07	4.0	3.87	3.77	3.66
6.0	6.91	6.76	6.61	6.46	6.3	6.15	6.0	5.85	5.69	5.54
8.0	9.24	9.03	8.82	8.62	8.4	8.21	8.0	7.79	7.59	7.38
10.0	11.5	11.2	11.0	10.7	10.5	10.2	10.0	9.69	9.43	9.18
13.0	15.1	14.7	14.4	14.0	13.7	13.4	13.0	12.7	12.3	12.0
16.0	18.4	18.0	17.6	17.2	16.8	16.4	16.0	15.6	15.2	14.8
20.0	23.0	22.5	22.0	21.5	20.9	20.4	20.0	19.4	18.9	18.4
25.0	28.9	28.3	27.6	27.0	26.3	25.7	25.0	24.4	23.8	23.1
32.0	36.9	36.1	35.3	34.4	33.6	32.8	32.0	31.1	30.3	29.5
40.0	46.2	45.1	44.1	43.1	42.1	41.1	40.0	39.0	38.0	37.0
50.0	57.7	56.4	55.1	53.8	52.5	51.3	50.0	48.7	47.4	46.1
63.0	72.5	70.9	69.3	67.7	66.1	64.5	63.0	61.3	59.6	58.0

SMISLINE TP technical details

Miniature circuit breaker

Protection of circuits with fluorescent lamps

Protection of circuits with fluorescent lamps

The following table gives the maximum permissible number of fluorescent lamps which can be protected by a single-pole circuit breaker of characteristic. The figure for multi-pole circuit breakers is reduced by 20%.


Rated current ballast	FL not compensated			FL compensated in parallel			FL with electronic		
	KVG 19/20 W	36/40 W	59/65 W	KVG 19/20 W	36/40 W	59/65 W	EVG ¹⁾ 19/20 W	36/40 W	59/65 W
13	35	30	19	41	41	27	21	21	10
16	43	37	24	51	51	33	26	26	12
20	53	46	30	64	64	41	33	33	15
25	66	58	37	82	82	53	42	42	19

¹⁾ EVG: Two-lamp version, lamps switched together, electronic ballast
 KVG: Conventional ballast


Use of miniature circuit breakers S400M for DC systems

A standard miniature circuit breaker type S400M and S400 E can be used in a DC system by observing the following conditions: Single pole miniature circuit breaker max. 60VDC. 2-pole miniature circuit breaker with 2-poles in series max. 125VDC. The polarity needs not to be taken into account. Load connection can either be at the top or at the bottom of the MCB.

Example of permissible DC voltages depending on the number of poles and the circuit configuration in earthed DC systems:



Examples for different voltages between a conductor and earth where voltages between conductors are identical:



SMISLINE TP technical details

Miniature circuit breaker

S400UC

UC = Universal Current = AC/DC

S400UC MCBs can be used in the one-pole version as 250V d.c., and in the 2-pole version with series connection of two poles up to 440V d.c..


For DC incoming supply from above

S400 UC-... MCBs have, in the area of arc chutes, permanent magnets, it is therefore necessary to take into account the polarity during the installation process. Doing so ensures that in the case of a short circuit the magnetic field of the permanent magnets corresponds with the electromagnetic field of the short-circuit current, therefore safely leading the short circuit into the arc chute. Incorrect polarities may cause damage to the MCB.

This is why – in the case of top-fed devices – terminal 1 must be connected to (-) and terminal 3 (+).

Example for permissible voltages between the conductors depending on the number of poles and circuit layout:


voltage U_N between conductors	250 V d.c.	440 V d.c.	440 V d.c.	440 V d.c.
voltage U_N between conductor and earth supply	250 V d.c.	250 V d.c.	440 V d.c.	250 V d.c.



SMISLINE TP technical details

Residual current operated circuit breaker F402, F404

Properties



General information about residual current operated circuit breakers

The residual current operated circuit breaker prevents personal injury and damage to property caused by electric current. Use of this circuit breaker is required in various national and international standards for electrical installations.

Modern residual current operated circuit breakers respond to small residual currents.

Interruption occurs in a fraction of a second even before a hazardous situation for people, animals and property can arise.


The principle of magnetic tripping independent of the supply voltage ensures perfect and safe operation even in the event of undervoltage and neutral interruptions.

The key features

- High short-circuit resistance 10 kA
- Sensitive for alternating and pulsating DC residual currents
- 2- and 4-pole types
- Nominal residual trip currents 10, 30, 100, 300 and 500 mA
- Snap-on auxiliary switches and signal contacts
- Nominal currents 25, 40, 63 A
- Double terminals

According to the wave form of the earth leakage currents they are sensitive to, the RCDs may be classed as:

- AC type (for alternating current only) AC are not in the Smisline portfolio
- A type (for alternating and/or pulsating current with DC components)
- B type (for alternating and/or pulsating current with DC components and continuous fault current).

Shape of the fault current	Correct RDC function		
		alternating current Type AC	pulsating current sensitiv Type A
sinusoidal a.c.	 rampant	 slowly rising	
pulsating d.c.	 rampant with or without overlapping DC components from 6 mA	 slowly rising	

Selectivity

RCDs raise similar issue to those surrounding the installation of MCBs, and in particular the need to reduce to a minimum the parts of the system out of order in the event of a fault.

For RCBOs the problem of selectivity in the case of short-circuit currents may be handled with the same specific criteria as for MCBs.


However, for correct residual current protection, the more important aspects are linked to tripping times. Protection against contact voltages is only effective if the maximum times indicated on the safety curve are not exceeded.

SMISLINE TP technical details


Residual current operated circuit breaker F402, F404

Properties

Partial selectivity



Total selectivity



Amperometric (partial) selectivity

Selectivity may be created by placing low-sensitivity RCDs upstream and higher-sensitivity RCDs downstream.

An essential condition which must be satisfied in order to achieve selective co-ordination is that the $I_{\Delta 1}$ value of the breaker upstream (main breaker) is more than double the $I_{\Delta 2}$ value of the breaker downstream. The operative rule to obtain an amperometric (partial) selectivity is $I_{\Delta n}$ of the upstream breaker = $3 \times I_{\Delta n}$ of the downstream breaker (e.g.: F404, 300 mA upstream; F402, 100 mA downstream).

In this case, selectivity is partial and only the downstream breaker trips for earth fault currents $I_{\Delta 2} < I_{\Delta m} < 0,5 \times I_{\Delta 1}$.

Chronometric (total) selectivity

To achieve total selectivity, delayed or selective RCDs must be installed.

The tripping times of the two devices connected in series must be co-ordinated so that the total interruption time t_2 of the downstream breaker is less than the upstream breaker's no-response limit time t_1 for any current value. In this way, the downstream breaker completes its opening before the upstream one.

To completely guarantee total selectivity, the I_{Δ} value of the upstream device must also be more than double that of the downstream device in accordance with IEC 64-9/563.3, comments. The operative rule to obtain an amperometric (partial) selectivity is $I_{\Delta n}$ of the upstream breaker = $3 \times I_{\Delta n}$ of the downstream breaker (e.g.: F404, S type, 300 mA upstream). For safety reasons, the delayed tripping times of the upstream breaker must always be below the safety curve.

SMISLINE TP technical details

Residual current operated circuit breaker F402, F404

Standard, short-time delayed and selective type

The use of multiple electronic reactors for the supply of fluorescent lamps instead generates permanent leakage currents and inrush currents that can provoke nuisance tripping of a standard residual current breaker.

IT system loads and other electronic equipment (e.g. dimmers, computers, inverters) with capacitive input filters connected between the phases and ground can also generate permanent earth leakage currents whose sum may provoke the nuisance tripping of a standard residual current breaker.

For these situations, the SHORT-TIME DELAY breakers allow a greater number of devices to be connected to the installation.

Soft-starters for motors are loads which can generate high-frequency capacitive currents (provoked by the harmonics) toward ground or fed into the network. Also in this case, the use of SHORT-TIME DELAY residual breakers reduces the sensibility to nuisance tripping.

Compared with standard type breakers, SHORT-TIME DELAY residual current breakers are therefore characterised, for any given sensibility, by:

- Higher residual trip current
- Tripping time delay
- Better resistance to overvoltages, harmonics and impulse disturbances.

Regulations

The tests set out in the IEC 61008 and IEC 61009 standards verify the resistance of residual current breakers to unwanted tripping provoked by operation overvoltages, using a ring wave impulse shape of $0.5\mu\text{s}/100\text{kHz}$. All residual current circuit-breakers are required to pass this test with a peak current value of 200A.


For what concerns atmospheric overvoltages, the IEC 61008 and 61009 standards prescribe the $9/20\mu\text{s}$ surge test with a 3000A peak current, but limit the requirement to residual current devices classified as selective; no test is required for other types.

The ABB range of SHORT-TIME DELAY anti- nuisance tripping breakers and blocks pass the general $0.5\mu\text{s}/100\text{kHz}$ ring wave test and also withstand the $9/20\mu\text{s}$ impulse test with the same peak current of 3000A prescribed for selective devices.

The F402 K and F404 K should therefore be used to prevent unwanted tripping.

Three different types of Residual current operated circuit breaker

- standard RCD 30 mA
- selective RCD 300 mA **S**
- short-time delay RCD 30 mA **K**



- The standard RCD 30 mA tripp after circa 22 mA and a release time of $\leq 35\text{ms}$.
- The selectiv RCD 300 mA tripp after circa 200 mA and a release time of circa 180 ms.
- The short-time delay RCD 30 mA tripp after circa 25 mA and a release time of 100 ... 120 ms.

SMISLINE TP technical details

Residual current operated circuit breaker F402, F404

Standard, short-time delayed and selective type

Unwanted tripping

In the event of disturbance in the mains, the RCDs normally present in the system are tripped, breaking the circuit even in the absence of a true earth fault.

Disturbances of this kind are most often caused by:

- operation overvoltages caused by inserting or removing loads (opening or closing protection of control devices, starting and stopping motors, switching fluorescent lighting systems on and off, etc.)
- overvoltages of atmospheric origin, caused by direct or indirect discharges on the electrical line.

Under these circumstances, breaker tripping is unwanted, since it does not satisfy the need to avoid the risks due to direct and indirect contacts. On the contrary, the sudden and unjustified interruption of the power supply may result in very serious problems.

SHORT-TIME DELAY RCDs

The ABB range of SHORT-TIME DELAY anti-disturbance residual current circuitbreakers and blocks was designed to overcome the problem of unwanted tripping due to overvoltages of atmospheric or operation origin.

The electronic circuit in these devices can distinguish between temporary leakage caused by disturbances on the mains and permanent leakage due to actual faults, only breaking the circuit in the latter case.

SHORT-TIME DELAY residual current circuit-breakers and blocks have a slight delay into the tripping time, but this does not compromise the safety limits set by the Standards in force (release time at $2 I_{\Delta n} = 150$ ms).

Guaranteeing conventional residual current protection, their installation in the electrical circuit therefore allows any unwanted tripping to be avoided in domestic and industrial systems in which service continuity is essential.

This delay makes the SHORT-TIME DELAY residual current devices especially suited for installations involving motor starters/variable speed drives, fluorescent lamps or IT/electronic equipment.

Table of RDC selectivity

Downstream $I_{\Delta n}$ [mA]	Upstream $I_{\Delta n}$	10		30		100		300		300		500		500	
		inst	inst	inst	inst	inst	inst	S	inst	S	inst	S			
10			■	■	■	■	■	■	■	■	■	■	■	■	■
30	inst				■	■	■	■	■	■	■	■	■	■	■
100	inst						■	■	■	■	■	■	■	■	■
300	inst														
300	S														
500	inst														

inst = instantaneous S = selective ■ = amperometric (partial) selectivity ■ = chronometric (total) selectivity

SMISLINE TP technical details

Residual current operated circuit breaker F402, F404

Technical data

	F402	F404
Rated voltage U_n :	230 V	230/400 V
Number of poles:	2	4
Rated frequency f_n :	50/60 Hz	50/60 Hz (for Type LF 16 ² / ₃ Hz)
Rated breaking capacity I_m :		1000 A
Total trip time (average value)		
– at $I_{\Delta n}$	≤ 300 ms	≤ 300 ms
– at $5 I_{\Delta n}$	≤ 40 ms	≤ 40 ms
Delay time at $5 I_{\Delta n}$:	–	–
Resistance to short circuits (kA):	in conjunction with an upstream fuse gL / gG 100 A or a high performance MCB S800, 100 A	10 kA 10 kA in conjunction with an upstream fuse gL / gG 100 A or a high performance MCB S800, 100 A
Connection	Double lift terminal touch finger-proof, suitable for connecting load side terminal	single-, multi- and fine-wire conductors of up to 25 mm ²
Degree of protection:	IP20 inside panel IP40	IP20 inside panel IP40
Endurance:	> 5000 operating cycles	> 5000 operating cycles
Resistance to climate acc. to:	EN 61008	EN 61008
Rated insulation voltage U_i	500 V	500 V
Rated impulse withstand voltage U_{imp}	4 kV	4 kV
Mounting position:	any	any
Ambient temperature:	–25°C ... +40°C	–25°C ... +55°C acc. to EN 61009
Vibration resistance:	5g 5 ... 150 ... 5 Hz	5g 5 ... 150 ... 5 Hz
Plastic parts:	halogen-free	halogen-free
Contacts:	cadmium-free	cadmium-free

	F402...K	F404...K	F404...S
Rated voltage U_n :	230 V	230/400 V	230/400 V
Number of poles:	2	4	4
Rated frequency f_n :	45 ... 60 Hz	45 ... 60 Hz	45 ... 60 Hz
Resistance to surge current:	3 kA 9/20 μs	3 kA 9/20 μs	5 kA 9/20 μs
Total trip time (average value)			
– at $I_{\Delta n}$	240 ms	120 ... 300 ms	150 ... 500 ms
– at $5 I_{\Delta n}$	≤ 40 ms		40 ... 150 ms
Delay time at $5 I_{\Delta n}$:	10 ms	10 ms	90 ms
Resistance to short circuits (kA):	10 kA in conjunction with an upstream fuse gL / gG 100 A or a high performance MCB S800 100 A	10 kA	10 kA
Connection	Double lift terminal touch finger-proof, suitable for connecting load side terminal single-, multi- and fine-wire conductors of up to 25 mm ²		
Degree of protection:	IP20 in panel IP40	IP20 in panel IP40	IP20 in panel IP40
Endurance:	> 5000 operating cycles	> 5000 operating cycles	> 5000 opera- ting cycles
Resistance to climate acc. to:	EN 61008	EN 61008	EN 61008
Mounting position:	any	any	any
Ambient temperature:	–25°C ... +40°C	–25°C ... +55°C	–25°C ... +40°C
Vibration resistance:	5g 5 ... 150 ... 5 Hz	5g 5 ... 150 ... 5 Hz	5g 5 ... 150 ... 5 Hz
Plastic parts:	halogen-free	halogen-free	halogen-free
Contacts:	cadmium-free	cadmium-free	cadmium-free

SMISSLINE TP technical details

Residual current operated circuit breaker F402, F404

Technical data

Coordination tables between Short Circuit Protection Devices (SCPD) and F404 RCCBs

If you are using an RCCB you must verify that the Short Circuit Protection Device (SCPD) protects it from the effects of high current that arise under short-circuit conditions. The IEC/EN 61008 provides some tests to verify the behaviour of RCCB in short-circuit conditions. The tables below provide the maximum withstanding short-circuit current expressed in eff. kA for which the RCCBs are protected thanks to the coordination with the SCPD with a rated current (thermal protection) less than or equal to the rated current of the associated RCCB.

	F404 25 A	F404 40 A	F404 63 A
gG fuse 25 A	100		
gG fuse 40 A	60	60	
gG fuse 63 A	20	20	20
gG fuse 100 A	10	10	10
S403M	10	10	10
S803N	20	20	20
S803S	25	25	25

Internal resistances and power losses of RCCBs and RCBOs

Internal resistances and power losses per pole (cold resistance at room temperature)

4-pole RCCB F404

2-pole RCCB F402

in A	R _i mΩ	P _v W	Type	R _i mΩ	P _v W
25	2.1	1.3	25 A/10 mA	8.8	5.5
40	2.0	3.2	25 A/30 mA	6.1	3.8
63	1.1	4.4	40 A/30 mA	5.8	9.3

SMISLINE TP technical details

Residual current operated circuit breaker FS401



Residual current operated circuit breakers with overcurrent protection (RCBO)

The SMISLINE residual current operated circuit breakers with overcurrent protection (RCBO) are ideal for protecting people and property in all new and existing distribution systems. The combination of standby current and cable protection in one single device greatly simplifies planning and offers cost benefits. Using a RCBO can e.g. satisfy the minimum level of protection required by regulations in an apartment or in a particular distribution system. Should a residual current arise, only the circuit directly affected is switched off while all other circuits remain in operation.

The short time-delayed residual current operated circuit breaker with overcurrent protection FS401 K is a version particularly suited to unfavourable distribution and load situations. Without limiting the personal protection function in any way, the electronic short time delay prevents nuisance tripping which may arise as a result of capacitive discharge currents.

	FS401	FS401K
Rated voltage U_n :	230 V ~	230 V ~
Upstream fuses and	For backup and selectivity, the details for the miniature circuit breakers S400 E	
Selectivity limits:	and S400 M Page 2/19 to 2/36	
Number of poles:	2-pole (1PN)	2-pole (1PN)
Rated frequency f_n :	50/60 Hz	50/60 Hz
Rated breaking capacity I_{cn} :	10 kA – 230 V ~ (10–16 A nominal current) 6 kA – 230 V ~ (20–32 A nominal current)	10 kA – 230 V ~ (10–16 A nominal current) 6 kA – 230 V ~ (20 A nominal current)
Current limitation class:	3	3
Total cut-off time (average value) acc. to		EN 61009-1 EN 61009-1
– at I_n	40 ms	240 ms
– at $5 I_{\Delta n}$	25 ms	35 ms
Delay time at $5 I_{\Delta n}$:	–	10 ms
Rated insulation voltage U_i	500 V	500 V
Rated impulse withstand voltage U_{imp}	4 kV	4 kV
Connection cross-sections	Opposing action stroke clamp on cylinder, touch finger-proof. Suitable for connecting Terminal at load end	single, multi- and fine-wire conductors of up to 25 mm ²
Degree of protection:	IP20 inside panel IP40	IP20 inside panel IP40
Endurance:	> 5000 operating cycles	> 5000 operating cycles
Resistance to climate, acc. to:	EN 61009	EN 61009
Mounting position:	any	any
Ambient temperature:	–25°C ... +40°C	–25°C ... +40°C
Vibration resistance:	5 g 5 ... 150 ... 5 Hz	5 g 5 ... 150 ... 5 Hz
Plastic parts:	halogen-free cadmium-free	halogen-free Contacts: cadmium-free

Please notice:

For the influence of the ambient temperature and the thermal influences of row mounted RCBO's it is necessary to calculate with the same correction factors like with MCB's.

SMISLINE TP technical details

Residual current operated circuit breaker FS401

Internal resistances and power losses, Derating

Max. operating currents depending on ambient temperature for RCBO of tip characteristics B and C.

Influence of adjacent devices

B,C	Ambient temperature T (°C)								Influence of adjacent devices	
	-25	-20	-10	0	10	20	30	40	No. of adjacent devices	correction factor
In (A)	-25	-20	-10	0	10	20	30	40	1	1
2	2.6	2.5	2.4	2.3	2.2	2.1	2	1.9	2	0.95
4	4.9	4.8	4.6	4.5	4.3	4.2	4	3.8	3	0.9
6	7.95	7.8	7.4	7.1	6.7	6.4	6	5.6	4	0.86
8	10.3	10.1	9.7	9.3	8.8	8.4	8	7.6	5	0.82
10	11.8	11.6	11.3	11	10.7	10.3	10	9.7	6	0.8
13	15.65	15.4	14.9	14.4	14	13.5	13	12.5	7	0.78
16	18.65	18.4	17.9	17.4	17	16.5	16	15.5	8	0.77
20	23.1	22.8	22.2	21.7	21.1	20.6	20	19.4	9	0.76
25	30.8	30.3	29.2	28.2	27.1	26.1	25	23.9	10	0.76
32	39.3	38.6	37.3	36	34.7	33.3	32	30.7		
40	50.7	49.7	47.8	45.8	43.9	41.9	40	38.1		

Internal resistances and power losses

Internal resistances and power losses per pole (cold resistance at room temperature)

Type	FS401 B Ri mΩ	PV [W]	FS401 C Type	Ri mΩ	PV [W]
FS401M-B6	53.8	1.9	S401M-C6	50.3	1.8
FS401M-B10	20.5	2.1	FS401M-C10	18.2	1.8
FS401M-B13	14.7	2.5	FS401M-C13	12.7	2.2
FS401M-B16	10.7	2.7	FS401M-C16	10.4	2.7
FS401M-B20	7.4	3.0	FS401M-C20	7.7	3.1
FS401M-B25	6.3	4.0	FS401M-C25	7.6	4.8
FS401M-B32	5.5	5.7	FS401M-C32	5.5	5.6

SMISLINE TP technical details

Residual current operated breaker RCBO FS403



4-pole RCBO from the ABB SMISLINE protective devices range

The combination of circuit protection and a residual current protection in one device as 4-pole RCBO simplifies both – planning and installation. It enables you to provide perfect protection in one device. This protection consists of:

- Short circuit protection
- Overload protection
- Residual current protection
- Preventive fire protection

High rated short-circuit breaking capacity of 10 kA, conforming to EN 61009-1

The I_{cn} 10 kA short-circuit breaking capacity of the RCBO complies with standard EN 61009-1. This standard specifies testing and usage of RCBO's for household and similar uses. The devices can also be used by non-professionals.

Features and benefits of the new devices:

- Overall width of 72 mm (4 modules)
- Rated sensitivity 30 mA
- Current rating 10 A to 32 A
- B and C tripping characteristics
- Easy Drive double deck terminals on the output side for connecting two conductors in one chamber. The two chambers can accommodate conductors with different cross sections.

	FS403
Rated voltage U_n :	240/415 V
Number of poles:	3PN
Rated frequency f_n :	50/60 Hz
Rated breaking capacity I_{cn} :	10 kA bzw. 6 kA
Current limitation class:	3
Total cut-off time (average time) acc. to IEC/EN 61009-1	EN61009
– at $I_{\Delta n}$	40 ms
– at $5I_{\Delta n}$	25 ms
Standard Cross-section of conductors (top/bottom)	Upper terminal part 0,75–35 mm ² Lower terminalpart 0,75–10 mm ²
Tightening torque:	2.8 Nm
Degree of protection:	IP20
Endurance:	> 5000
Resistance to climate:	according to EN61009
Ambient temperature:	–25 °C ... +40 °C
Vibration resistance:	EN 61009-1
Plastic parts:	halogen free, according
contacts:	IEC 61-249-2-21 cadmium free
Approvals and standards:	EN/IEC 61009-1, SEV

Accessory:

Auxiliary- and signal contacts are to attach on to the left of the device through the customer.

SMISLINE TP technical details

Residual current operated circuit breaker FS403

Internal resistances and power losses, Derating

Internal resistances and power losses

Internal resistances and power losses per pole (cold resistance at room temperature)

FS403

Typ	R _i mΩ	P _v W
6A B, C	50	3
10A B, C	17.6	2.69
13A B, C	11.9	2.96
16A B, C	9.8	3.52
20A B, C	7.3	3.94
25A B, C	4.8	5.19
32A B, C	3.6	6.38

Performances at different ambient temperatures

Max. operating current depending on the ambient temperature of a circuit-breaker in load circuit of characteristics type B, C

Influence of adjacent devices Correction factor Fm

B,C	Ambient temperature T (°C)									No. Of adjacent devices	correction factor
	-25	-20	-10	0	10	20	30	40	1		
In (A)											
6	7.95	7.8	7.4	7.1	6.7	6.4	6	5.6	4	0.86	
10	11.8	11.6	11.3	11	10.7	10.3	10	9.7	6	0.8	
13	15.65	15.4	14.9	14.4	14	13.5	13	12.5	7	0.78	
16	18.65	18.4	17.9	17.4	17	16.5	16	15.5	8	0.77	
20	23.1	22.8	22.2	21.7	21.1	20.6	20	19.4	9	0.76	
25	30.8	30.3	29.2	28.2	27.1	26.1	25	23.9	10	0.76	
32	39.3	38.6	37.3	36	34.7	33.3	32	30.7			

SMISLINE TP technical details



RCBO FS401, FS403

Limitation of specific let-through energy I^2t , peak current I_p

I^2t diagrams - Specific let-through energy value I^2t

The I^2t curves give the values of the specific let-through energy expressed in A^2s (A=amps; s=seconds) in relation to the perspective short-circuit current (I_{rms}) in kA.


FS400M characteristics B-C



Limitation curves – Peak current values

The I_p curves give the values of the peak current, expressed in kA, in relation to the perspective symmetrical short-circuit current (kA).

FS400M Characteristics B-C



S400 E S400M
DS400 DS400 M

6

SMISLINE TP technical details

Switch disconnecter



General switch disconnecter

When used in a smissline socket system, the switch disconnecter can be used instead of the incoming terminal block for up to 63 A. With the smissline IS404 switch disconnecter, individual loads, groups of loads or entire system parts can be separated or connected to the input supply.

The key features of the switch disconnecter


- Input supply switch
- On-Off function
- Clear indication of switching position
- Snap-on auxiliary switch available
- Uniform smissline design

Technical data for switch disconnecter IS404

Rated voltage U_n :	230/400 V ~
Rated current I_n :	63 A
Rated frequency f_n :	50 Hz
Number of poles:	4
Rated impulse withstand voltage:	6 kV
Connection cross-sections C_u :	At top, touch finger-proof. Suitable for connecting up single-, multi- and fine-wire conductors of up to 25 mm ²
Degree of protection:	IP40
Endurance, mechanical/electrical:	5000 operating cycles
Mounting position:	any
Ambient temperature:	-25 °C ... +40 °C
Specifications:	EN/IEC 60947-3
Approvals:	SEV
Weight (approx.):	250 g
Switching duty:	AC-22A
Plastic parts:	halogen-free
Contacts:	cadmium-free

SMISLINE TP technical details

Surge arrester OVR



Description of product

The 'OVR' surge protector is a 4-pole type II surge arrester meeting the requirements of IEC 61643-11.

The OVR is used to protect low voltage distribution systems and devices from overvoltages (DIN VDE 100) caused by remote lightning strikes or switching operations.

Typical sites of use are main and sub-distribution for low voltage systems where the arrester is plugged in directly on to the SMISLINE busbar system.

Display and maintenance

The protective elements (high-performance varistors) are monitored thermally. In the event of a defect, this monitor automatically disconnects the overloaded high-performance varistors from the power supply and the operating indication changes from green to red. This status is also indicated by the signalling contact. In such cases, the arrester should be replaced immediately because the downstream devices are no longer protected against overvoltages.

If the operating indication is neither green nor red, you should check whether the connections are correct. You must also check whether there is any supply voltage.

If the device is connected correctly, the operating display (LED) lights up green.

The surge arrester requires no maintenance. A regular visual check is recommended.

Warning: When taking insulation resistance measurements on the electrical system, the arrester should be disconnected from the power supply since otherwise the measurement may be affected by the arrester characteristics. The enclosed sticker with the corresponding note should be placed in a clear position on the distribution board.

Assembly

Site of installation and electrical connection

The 'OVR' surge arrester installed at the input supply of the system to be protected.

The OVR404 is plugged in directly on to the SMISLINE busbar system.

Earth conductor rating

The OVR should be linked to ground potential using the shortest route possible.

The earth conductor supplied with the device can be used for this purpose. The connection must be as short as possible. The minimum cross-section is 6 mm².

Running cables

Protected and unprotected cables (also including the earth conductor) must not be routed directly parallel to one another. They should be separated such that surge interference from unprotected to protected cables cannot occur. Cables should cross one another at right angles.


SMISLINE TP technical details

Surge arrester OVR


Coordination between surge arrester

In order to ensure a full and complete protection it is necessary to have coordination between different surge arrester types.


Configuration 1 15 kA ≤ I_p ≤ 50 kA




> 10 meters cable




> 10 meters cable




Configuration 2 7 kA ≤ I_p ≤ 15 kA



> 10 meters cable



> 10 meters cable




SMISLINE TP technical details

Surge arrester OVR

Rated voltage U_n :	230/400 V AC
Max. Continuous voltage U_c :	275 V AC
Number of poles:	4 (TN-S system)
Power consumption at U_n :	1.2 W per device
Requirement class according to IEC 61643-1:	Type 2
Rated leakage surge current I_n (9/20 μ s):	15 kA
Max. leakage surge current I_{smax} (9/20 μ s):	30 kA
Protection level U_p at I_{sn} :	≤ 1.5 kV
U_p at $I_s = 5$ kV:	≤ 1 kV
Max. leakage surge current I_{sg} (9/20 μ s):	100 kA 4-pole
Response time t_a :	≤ 25 ms
Connection cross-sections PE / L1/L2/L3/N:	Opposing action stroke clamp on cylinder, touch finger-proof. Suitable for connecting up single-, multi- and fine-wire conductors up to 25 mm ²
Max. Back-up fuse:	160 A gL/gG / 25 kA
Short-circuit withstandability with max. Back-up fuse:	25 kA
Signal contact max. operating voltage:	250 V AC
max. load current:	2 A
1 changeover contact:	11/12 normally closed contact, 11/14 normally open contact
Temperature range:	-25 ... +60 °C
Degree of protection:	IP 20
Plastic parts:	halogen-free
Contacts:	cadmium-free

Surge protection TN-S system



SMISLINE TP technical details

Auxiliary switches and signal contacts



General

The auxiliary switches and signal contacts are snapped on to the left of the protective devices. On the miniature circuit breakers an optional mounting on the right is also possible. For auxiliary switches and signal contacts supplied via SMISLINE auxiliary busbars LA or LB a version with integrated contacting pieces is available. Conventional supply via the terminals of the auxiliary devices is possible.

Function

The auxiliary switch works in the same way as the main contacts. The signal contact only operates when the protective device trips.

This can be simulated with the white test button. Each time the signal contact is tripped, it must be reset to its starting position using the orange-coloured reset button.

Auxiliary switch and signal contacts have special contacts which ensure high switching reliability even in systems with low voltages or low currents (PLC, signal systems etc.).

Auxiliary switch contacts operate at the same time as the contacts of the protective device (activated manually or automatically).

Normally open contact
NO (normally open) } 13
 } 14 joint operation with protective device

Normally open contact
NC (normally close) } 21
 } 22 opposing operation with protective device

Signal contacts only operate when the protective device is tripped electrically as a result of a short-circuit, a fault current or overcurrent (undervoltage for MS325).

Normally open contact
NO (normally open) } 97
 } 98 closes during automatic trip

Normally closed contact
NC (normally close) } 05
 } 06 opens during automatic trip








Technical data for auxiliary switch and signal contact


	Signal contact SK400	Auxiliary switch HK400
Rated voltage U_n :	400 V	400 V
Rated impulse withstand voltage:	4 kV	4 kV
Rated current:		
- I_{th} :	6 A	6 A
- AC15	2 A/230 V / 1 A/400 V	2 A/230 V / 1 A/400 V
- DC13	0.55 A/125 V=	0.55 A/125 V=
- DC15	0.27 A/250 V=	0.27 A/250 V=
Minimum current/voltage:	10 mA 12 V=	10 mA 12 V= (to ensure reliable electrical operation)
Connection cross-sections:	2x1.5 mm ² strand with sleeve	2x1.5 mm ² strand with sleeve
Plastic parts:	Free of halogen und cadmium	Free of halogen und cadmium
Internal resistance R_i :	0.0065 Ω	0.0065 Ω
Power loss at rated current P_v :	0.24 W	0.24 W
Ambient temperature:	$T_{max.} +55^\circ\text{C}$ $T_{min.} -25^\circ\text{C}$	$T_{max.} +55^\circ\text{C}$ $T_{min.} -25^\circ\text{C}$
Tightening torque:	1 Nm	1 Nm

SMISLINE TP technical details




Accessory mounting






On each protective device can be mounted:
 or 1 auxiliary switch
 or 1 signal contact
 or 2 auxiliary contact switches
 or 1 auxiliary switch and 1 signal contact



Contact description signal contact



Contact description auxiliary switch




① If you use an auxiliary switch and a signal contact you must connect first the signal contact on the MS325

SMISLINE TP technical details


Auxiliary switches and signal contacts

1. Wiring without auxiliary busbars LA, LB

Wiring of auxiliary switch and signal contact blocks without contact to the auxiliary busbars LA and LB.




2. Input contacts the auxiliary busbars LA, LB. Standard output wiring.




3. Collective alarm, signal contact contacts the auxiliary busbars LA, LB


A cost-effective collective alarm solution can be implemented without additional wiring by using this arrangement.



Contact description signal contact




Contact description auxiliary contact



SMISLINE TP technical details

Auxiliary switches and signal contacts
Contact arrangements to auxiliary busbars



Left/right mounting of auxiliary switch/signal contact for miniature circuit breaker Space-saving on the socket system

By mounting the auxiliary switches/signal contacts alternately on the left and right, the installation width on the SMISLINE socket system can be reduced. A dummy housing is therefore not needed when just using auxiliary switches or signal contacts.


S400 miniature circuit breakers with auxiliary switches mounted on left and right:
25% space saving



S400 miniature circuit breakers with NT40163 9mm on the right and S400 with auxiliary switch on the left:
20% space saving



Supply options for auxiliary busbars LA and LB



Supply option for auxiliary busbars using incoming terminal block.




Supply option for auxiliary busbars using incoming terminal block.

Positioning of contacting piece ZLS632 on auxiliary switch and signal contact

The small auxiliary switch/signal contact contacting piece can be simply and quickly changed from the position of the LA to the LB auxiliary busbar by reversing it by 180 degree.

HK/SK 1NO, 1NC



Signal or auxiliary contact Collective alarm

