Data Sheet DS/264GS/AS-EN Rev. F

# Model 264GS Gauge Model 264AS Absolute

# ABB 2600T Series Engineered solutions for all applications



Base accuracy: ±0.075%

## Span limits

- -0.2 to 60000kPa; 0.8inH<sub>2</sub>O to 8700psi
- 0.3 to 3000kPa abs; 2.25mmHg to 435psia

# Reliable sensing system coupled with very latest digital technologies

- provides large turn down ratio up to 100:1

## Comprehensive sensor choice

- optimize in-use total performance and stability

5-year stability

## Flexible configuration facilities

 provided locally via local keys combined with LCD indicator or via hand held terminal or PC configuration platform

## Multiple protocol availability

 provides integration with HART®, PROFIBUS PA and FOUNDATION Fieldbus platforms offering interchangeability and transmitter upgrade capabilities

Full compliance with PED Category III



## **Functional Specifications**

#### Range and span limits

Sensor	Upper Range	Lower Range Limit (LRL)	Minimu	ım span
Code	Limit (URL)	for 264GS	264GS abso 0.2kPa 0.3kPa 2mbar 0.8inH <sub>2</sub> O 2.25mn 0.4kPa 2kPa 4mbar 20mbar 1.6inH <sub>2</sub> O 15mmh 2.5kPa 12.5kPa 25mbar 125mbar 10inH <sub>2</sub> O 93.8mn 30kPa 1.50kPa 0.3bar 1.5bar	264AS absolute
С	6kPa 60mbar 24inH <sub>2</sub> O	-6kPa -60mbar -24inH₂O	2mbar	
F	40kPa 400mbar 160inH <sub>2</sub> O	–40kPa –400mbar –160inH2O	4mbar	2kPa 20mbar 15mmHg
L	250kPa 2500mbar 1000inH <sub>2</sub> O	0 abs	25mbar	12.5kPa 125mbar 93.8mmHg
U	3000kPa 30bar 435psi	0 abs	0.3bar	150kPa 1.5bar 21.7psi
R	10000kPa 100bar 1450psi	0 abs	1bar	
V	60000kPa 600bar 8700psi	0 abs	6bar	

Note: Lower Range Limit (LRL) for 264AS is 0 abs for all ranges

#### Span limits

Maximum span = URL

IT IS RECOMMENDED TO SELECT THE TRANSMITTER SENSOR CODE PROVIDING THE TURNDOWN VALUE AS LOWEST AS POSSIBLE TO OPTIMIZE PERFORMANCE CHARACTERISTICS.

## Zero suppression and elevation

Zero and span can be adjusted to any value within the range limits detailed in the table as long as:

- calibrated span ≥ minimum span

## **Damping**

Selectable time constant: 0, 0.25, 0.5, 1, 2, 4, 8 or 16s. This is in addition to sensor response time

## Turn on time

Operation within specification in less than 1s with minimum damping.

#### Insulation resistance

 $> 100M\Omega$  at 1000VDC (terminals to earth)

## **Operative limits**

## Temperature limits °C (°F):

## Ambient (is the operating temperature)

Silicone oil filling: -40°C and +85°C (-40°F and +185°F)

Inert filling and white oil: -20°C and +85°C (-4°F and +185°F)

Lower limit for LCD indicators and Viton gasket: -20°C (-4°F)

Lower limit for perfluoroelastomer gasket: -15°C (+5°F)

Upper limit for LCD indicators: +70°C (+158°F)

Note: For Hazardous Atmosphere applications see the temperature range specified on the certificate/approval relevant to the aimed type of protection

#### **Process**

Lower limit

- --50°C (-58°F); -20°C (-4°F) for Viton gasket.
- --15°C (+5°F) for perfluoroelastomer gasket

Upper limit

- Silicone oil, inert fluid and white oil: 121°C (250°F)

#### Storage

Lower limit: -50°C (-58°F); -40°C (-40°F) for LCD indicators

Upper limit: +85°C (+185°F)

#### **Pressure limits**

## Overpressure limits (without damage to the transmitter)

- 1MPa, 10bar, 145psi for sensor codes C, F
- 0.5MPa, 5bar, 72.5psi for sensor code L
- 6MPa, 60bar, 870psi for sensor code U
- 20MPa, 200bar, 2900psi for sensor code R
- 90MPa, 900bar, 13050psi for sensor code V
- 0.6MPa, 6bar, 87psi for perfluoroelastomer gasket

## **Proof pressure**

The transmitter can be exposed without leaking to line pressure of up to

- 1MPa, 10bar, 145psi for sensor codes C, F
- 0.5MPa, 5bar, 72.5psi for sensor code L
- 6MPa, 60bar, 870psi for sensor code U
- 20MPa, 200bar, 2900psi for sensor code R
- 90MPa, 900bar, 13050psi for sensor code V
- 0.6MPa, 6bar, 87psi for perfluoroelastomer gasket

## **Environmental limits**

### Electromagnetic compatibility (EMC)

Comply with EN 61000-6-3 for emission and EN 61000-6-2 for immunity requirements and test;

Radiated electromagnetic immunity level: 30V/m

(according to IEC 1000-4-3, EN61000-4-3)

Conducted electromagnetic immunity level: 30V

(according to IEC 1000-4-6, EN 61000-4-6)

Surge immunity level (with surge protector): 4kV

(according to IEC 1000-4-5 EN 61000-4-5)

Fast transient (Burst) immunity level: 4kV

(according to IEC 1000-4-4 EN 61000-4-4)

## Pressure equipment directive (PED)

Comply with 97/23/EEC Category III Module H.

up to 100% annual average Relative humidity:

Condensing, icing: admissible

#### Vibration resistance

Accelerations up to 2g at frequency up to 1000Hz

(according to IEC 60068-2-6)

#### Shock resistance

Acceleration: 50g Duration: 11ms (according to IEC 60068-2-27)

#### Wet and dust-laden atmospheres

The transmitter is dust and sand tight and protected against immersion effects as defined by EN60529 (1989) to IP 67 (IP 68 on request) or by NEMA to 4X or by JIS to C0920. IP65 with Harting Han connector.

## Hazardous atmospheres

With or without output meter/integral display

- COMBINED ATEX (Intrinsic safety and flameproof), FM and CSA ZELM approval. See below detailed classifications.
- COMBINED INTRINSIC SAFETY and FLAMEPROOF/EUROPE: ATEX/ZELM approval

II 1 GD T50°C, EEx ia IIC T6 (-40°C  $\leq$  Ta  $\leq$ +40°C)

T95°C, EEx ia IIC T4 (-40°C  $\leq$  Ta  $\leq$ +85°C)

II 1/2 GD T85°C, EEx d IIC T6 (-40°C  $\leq$  Ta  $\leq$  +75°C)

- INTRINSIC SAFETY/EUROPE:

ATEX/ZELM approval

II 1 GD T50°C, EEx ia IIC T6 (-40°C  $\leq$  Ta  $\leq$ +40°C)

T95°C, EEx ia IIC T4 (-40°C ≤ Ta ≤+85°C)

- TYPE "N"/EUROPE:

ATEX/ZELM type examination (for HART)

II 3 GD T50°C, EEx nL IIC T6 (-40°C  $\leq$  Ta  $\leq$ +40°C) T95°C, EEx nL IIC T4 (-40°C ≤ Ta ≤+85°C)

- FLAMEPROOF/EUROPE:

ATEX/CESI approval

II 1/2 GD T85°C, EEx d IIC T6 (-40°C  $\leq$  Ta  $\leq$  +75°C)

- CANADIAN STANDARDS ASSOCIATION and FACTORY MUTUAL:
  - Explosionproof: Class I, Div. 1, Groups A, B, C, D
  - Dust ignitionproof: Class II, Div. 1, Groups E, F, G
  - Suitable for : Class II, Div. 2, Groups F, G; Class III, Div. 1, 2
  - Nonincendive: Class I, Div. 2, Groups A, B, C, D
  - Intrinsically safe: Class I, II, III, Div. 1, Groups A, B, C, D, E, F, G AEx ia IIC T6/T4, Zone 0 (FM)
- STANDARDS AUSTRALIA (SAA): TS Approval
  - Intrinsically safe Ex ia IIC T4/T5 (-20°C ≤ Ta ≤+80°C) only HART
  - No sparking Ex n IIC T4/T6 (-20°C  $\leq$  Ta  $\leq$ +80°C) only HART
  - Flameproof Ex d IIC T4/T6 (-20°C ≤ Ta ≤+80°C)
- Dust ignitionproof DIP A21 Ta T6 (-20°C ≤ Ta ≤+80°C)
- INTRINSIC SAFETY/CHINA

NEPSI approval Ex ia IIC T4-T6

- FLAMEPROOF/CHINA

NEPSI approval Ex d IIC T6

- GOST (Russia), GOST (Kazakhstan), Inmetro (Brazil)

based on ATEX

## **Electrical Characteristics and Options**

## HART digital communication and 4 to 20mA output

#### **Power Supply**


The transmitter operates from 10.5 to 42VDC with no load and is protected against reverse polarity connection (additional load allows operations over 42VDC).

For EEx ia and other intrinsically safe approval power supply must not exceed 30VDC.

#### **Ripple**

20mV max on a  $250\Omega$  load as per HART specifications

#### **MINIMUM OPERATING VOLTAGES**



#### **Load limitations**

4 to 20mA and HART total loop resistance :

$$R(k\Omega) = \frac{\text{Supply voltage - min. operating voltage (VDC)}}{22.5}$$

A minimum of  $250\Omega$  is required for HART communication.

## Optional indicators

#### **Output meter**

CoMeter and Prometer LCD:

5-digit (±99999 counts) programmable with 7.6mm. high (3in), 7-segment numeric characters plus sign and digital point for digital indication of output value in percentage, current or engineer unit;

10-segment bargraph display (10% per segment) for analog indication of output in percentage;

7-digit with 6mm. high (2.3in), 14-segment alphanumeric characters, for engineer units and configuration display

Analog: 36mm (1.4in) scale on 90°.

#### Integral display

LCD, 15 lines x 56 column dot matrix providing 2 lines indication as

- top: 5-digit (numeric) plus sign or 7-digit alphanumeric
- bottom: 7-digit alphanumeric

and additional 50-segment bargraph for indication of analog output in percentage.

User-definable matrix display mode with HART communication:

- process variable in pressure unit or
- output signal as percentage, current or engineering units

Display also indicates in/out transfer function, static pressure, sensor temperature and diagnostic messages and provides configuration facilities.

#### Optional surge protection

Up to 4kV

- voltage 1.2 μs rise time / 50 μs delay time to half value
- current 8 µs rise time / 20 µs delay time to half value

## **Output signal**

Two-wire 4 to 20mA, user-selectable for linear or 5th order or two 2nd order switching point selectable programmable polynomial output.

HART® communication provides digital process variable (%, mA or engineering units) superimposed on 4 to 20mA signal, with protocol based on Bell 202 FSK standard.

## **Output current limits (to NAMUR standard)**

Overload condition

- Lower limit: 3.8mA- Upper limit: 20.5mA

### Transmitter failure mode (to NAMUR standard)

The output signal can be user-selected to a value of 3.7 or 22mA on gross transmitter failure condition, detected by self-diagnostics.

In case of CPU failure the output is driven <3.7mA or >22mA.

## **PROFIBUS PA output**

## Device type

Pressure transmitter compliant to Profiles 3.0 Class A & B; ident. number 052B HEX.

#### Power supply

The transmitter operates from 9 to 32VDC, polarity independent.

For EEx ia approval power supply must not exceed 17.5VDC. Intrinsic safety installation according to FISCO model.

#### **Current consumption**

operating (quiescent): 10.5mA fault current limiting: 20mA max.

#### **Output signal**

Physical layer in compliance to IEC 1158-2/EN 61158-2 with transmission to Manchester II modulation, at 31.25kbit/sec.

#### **Output interface**

PROFIBUS PA communication according to Profibus DP50170 Part 2/DIN 19245 part 1–3.

## Output update time

25ms

#### **Function blocks**

2 analog input, 1 transducer, 1 physical

## Integral display

LCD, 15 lines x 56 column dot matrix providing 2 lines indication as

- top: 5-digit (numeric) plus sign or 7-digit alphanumeric
- bottom: 7-digit alphanumeric

and additional 50-segment bargraph for indication of output in percentage of the analog input function block assigned to the primary variable.

User-definable matrix display mode:

- process variable in pressure units or
- primary variable in engineering units (output of transducer block) or
- output as percentage or engineering units of analog input function blocks

Display also indicates diagnostic messages and provides configuration facilities.

Secondary variable, static pressure and sensor temperature can be read.

#### Transmitter failure mode

On gross transmitter failure condition, detected by self-diagnostics, the output signal can be driven to defined conditions, selectable by the user as safe, last valid or calculated value. If electronic failure or short circuit occur the transmitter consumption is electronically limited at a defined value (20mA approx), for safety of the network.

## **FOUNDATION Fieldbus output**

#### Device type

LINK MASTER DEVICE

Link Active Scheduler (LAS) capability implemented.

## Power supply

The transmitter operates from 9 to 32VDC, polarity independent.

For EEx ia approval power supply must not exceed 24VDC (entity certification) or 17.5VDC (FISCO certification), according to FF-816.

#### **Current consumption**

operating (quiescent): 10.5mA fault current limiting: 20mA max.

#### **Output signal**

Physical layer in compliance to IEC 1158-2/EN 61158-2 with transmission to Manchester II modulation, at 31.25kbit/sec.

#### Function blocks/execution period

2 enhanced Analog Input blocks/25ms max (each)

- 1 enhanced PID block/40ms max.
- 1 standard ARitmetic block/25ms
- 1 standard Input Selector block/25ms
- 1 standard Control Selector block/25ms
- 1 standard Signal Characterization block/25ms
- 1 standard Integrator/Totalizer block/25ms

#### Additional blocks

- 1 enhanced Resource block
- 1 custom Pressure with calibration transducer block
- 1 custom Advanced Diagnostics transducer block including Plugged Input Line Detection
- 1 custom Local Display transducer block

## Number of link objects

35

## Number of VCRs

35

## Output interface

FOUNDATION fieldbus digital communication protocol to standard H1, compliant to specification V. 1.6; FF registration in progress.

## Integral display

LCD, 15 lines  $\times$  56 column dot matrix providing 2 lines indication as

- top: 5-digit (numeric) plus sign or 7-digit alphanumeric
- bottom: 7-digit alphanumeric

and additional 50-segment bargraph for percentage indication of the analog input function block output, assigned to the primary variable.

User-definable matrix display mode:

- process variable in pressure units or
- primary variable in engineering units (output of transducer block) or
- output as percentage or engineering units of one or more selected function blocks

Display also indicates diagnostic messages. Secondary variable, static pressure and sensor temperature can be read.

## Transmitter failure mode

The output signal is "frozen" to the last valid value on gross transmitter failure condition, detected by self-diagnostics which also indicate a BAD conditions. If electronic failure or short circuit occur the transmitter consumption is electronically limited at a defined value (20mA approx), for safety of the network.

## **Performance specifications**

Stated at reference condition to IEC 60770 ambient temperature of 20°C (68°F), relative humidity of 65%, atmospheric pressure of 1013hPa (1013mbar), zero based range for transmitter with isolating diaphragms ceramic or Hastelloy and silicone oil fill and HART digital trim values equal to 4–20mA span end points, in linear mode.

Unless otherwise specified, errors are quoted as % of span.

Some performance data are affected by the actual turndown (TD) as ratio between Upper Range Limit (URL) and calibrated span.

IT IS RECOMMENDED TO SELECT THE TRANSMITTER SENSOR CODE PROVIDING THE TURNDOWN VALUE AS LOWEST AS POSSIBLE TO OPTIMIZE PERFORMANCE CHARACTERISTICS.

## Dynamic performance (according to IEC 61298-1 definition)

Dead time: 40ms

Time constant (63.2% of total step change):

- 150 ms for all sensors

Response time (total) = dead time + time constant.

## **Accuracy rating**

% of calibrated span, including combined effects of terminal based linearity, hysteresis and repeatability.

For fieldbus versions SPAN refer to analog input function block outscale range  $\,$ 

Model 264GS

- ±0.075% for TD from 1:1 to 15:1 (10:1 for sensor C)

$$-\pm0.005\%$$
 x  $\frac{URL}{Span}$  for TD from 15:1 to 60:1

$$-\pm0.0075\%$$
 x  $\frac{\text{URL}}{\text{Span}}$  for TD from 10:1 to 30:1 for sensor C

Model 264AS

- ±0.075% for TD from 1:1 to 10:1

$$-\pm 0.0075\% \times \frac{URL}{Span}$$
 for TD from 10:1 to 20:1

## **Operating influences**

#### Ambient temperature

per 20K (36°F) change between the limits of –20°C to +65°C (–4 to +150°F) :

Model	Sensor Code	for TD up to	
264GS	F to V	15:1	± (0.04% URL + 0.065% span)
20403	С	10:1	± (0.06% URL + 0.10% span)
264AS	F to U	10:1	± (0.04% URL + 0.065% span)
204AS	С	10:1	± (0.065% URL + 0.10% span)

## **Optional CoMeter and ProMeter ambient temperature**

Total reading error per 20K (36°F) change between the ambient limits of -20 and +70°C (-4 and +158°F) :

±0.15% of max span (16mA).

## Supply voltage

Within voltage/load specified limits the total effect is less than 0.005% of URL per volt.

#### Load

Within load/voltage specified limits the total effect is negligible.

#### Electromagnetic field

Total effect: less than 0.10% of span from 20 to 1000MHz and for field strengths up to 30V/m when tested with shielded conduit and grounding, with or without meter.

#### Common mode interference

No effect from 100Vrms @ 50Hz, or 50VDC

## Mounting position

No effect

## Stability

±0.15% of URL over a five years period

## Vibration effect

±0.10% of URL (according to IEC 61298-3)

## **Physical Specification**

(Refer to ordering information sheets for variant availability related to specific model or versions code)

#### **Materials**

#### Process isolating diaphragms (\*)

Ceramic (Al203) gold-plated; Hastelloy C276™; Hastelloy C276™ gold-plated.

## Process connection (\*)

AISI 316 L ss; Hastelloy C276™.

## Gasket (only for sensor codes C, F) (\*)

Viton™, Perfluoroelastomer, Perbunan (NBR).

#### Sensor fill fluid

Silicone oil; inert fill (Carbon fluoride); white oil (FDA).

#### Mounting bracket (\*\*)

Zinc plated carbon steel with chrome passivation;

AISI 316 L ss.

## Sensor housing

AISI 316 L ss.

#### **Electronic housing and covers**

Barrel version

- Aluminium alloy with baked epoxy finish;
- Copper-free content aluminium alloy with baked epoxy finish;
- AISI 316 L ss.

## **Covers O-ring**

Buna N.

#### Local zero and span adjustments:

Glass filled polycarbonate plastic (removable).

#### **Tagging**

AISI 316ss data plate attached to the electronics housing.

## Calibration

Standard: at maximum span, zero based range, ambient temperature and pressure:

Optional: at specified range and ambient conditions; or at operating temperature.

## **Optional extras**

## Mounting brackets

For 60mm. (2in) pipes or wall mounting.

#### **Output indicator**

plug-in rotatable type, LCD or analog.

## Supplemental customer tag

AISI 316 ss tag screwed/fastened to the transmitter for customer's tag data up to a maximum of 20 characters and spaces on one line for tag number and tag name, and up to a maximum of 3 spaced strings of 10 characters each for calibration details (lower and upper values plus unit). Special typing evaluated on request for charges.

## Surge protection (only as external unit for PROFIBUS PA and FF)

Cleaning procedure for oxygen service (not for sensor V)

Test Certificates (test, design, calibration, material traceability)

Tag and manual language

**Communication connectors** 

## **Process connections**

 $^{1}/_{2}$  – 14 NPT female or male; DIN EN837–1 G  $^{1}/_{2}$  B.

#### Electrical connections

Two  $^{1}/_{2}$  – 14 NPT or M20x1.5 or PG 13.5 or  $^{1}/_{2}$  GK threaded conduit entries, direct on housing.

Special communication connector (on request)

- HART: straight or angle Harting Han connector and one plug.
- FOUNDATION Fieldbus, PROFIBUS PA: M12x1 or 7/8.

## **Terminal block**

HART version: three terminals for signal/external meter wiring up to 2.5mm² (14AWG) and three connection points for test and communication purposes.

Fieldbus versions: two terminals for signal wiring (bus connection) up to 2.5mm² (14AWG)

## Grounding

Internal and external 6mm² (10AWG) ground termination points are provided.

## Mounting position

Transmitter can be mounted in any position. Electronics housing may be rotated to any position. A positive stop prevents over travel.

## Mass (without options)

1.2kg approx (3lb); add 1.5kg (3.4lb) for AISI housing. Add 650g (1.5lb) for packing.

## **Packing**

Carton 26 x 26 x 18cm approx (10 x 10 x 7in).

<sup>™</sup> Hastelloy is a Cabot Corporation trademark

<sup>(\*)</sup> Wetted parts of the transmitter.

<sup>(\*\*)</sup> U-bolt material: AISI 400 ss; screws material: high-strength alloy steel or AISI 316 ss.

## Configuration

#### Transmitter with HART communication and 4 to 20 mA

#### Standard configuration

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and configured as follows:

Engineering Unit kPa 4 mA Zero

20 mA Upper Range Limit (URL)

Output Linear
Damping 1 sec.
Transmitter failure mode Upscale
Software tag (8 characters max) Blank

Optional LCD indicator/display 0 to 100.0% linear

Any or all the above configurable parameters, including Lower range–value and Upper range-value which must be the same unit of measure, can be easily changed using the HART hand–held communicator or by a PC running the configuration software SMART VISION with DTM for 2600T. The transmitter database is customized with specified flange type and material, O–ring and drain/vent materials and meter code option. Custom configuration (option)

The following data may be specified in addition to the standard configuration parameters:

Descriptor 16 alphanumeric characters Message 32 alphanumeric characters

Date Day, month, year

## **Transmitter with PROFIBUS PA communication**

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and configured as follows:

Measure Profile Pressure Engineering Unit kPa

Output scale 0% Lower Range Limit (LRL)
Output scale 100% Upper Range Limit (URL)

Output Linear

Hi-Hi Limit Upper Range Limit (URL)
Hi Limit Upper Range Limit (URL)
Low Limit Lower Range Limit (LRL)
Low-Low Limit Lower Range Limit (LRL)
Limits hysteresis 0.5% of output scale

PV filter 0 sec.
Address (settable by local key) 126

ag 32 alphanumeric characters

Any or all the above configurable parameters, including Lower range-value and Upper range-value which must be the same unit of measure, can be easily changed by a PC running the configuration software SMART VISION with DTM for 2600T

The transmitter database is customized with specified flange type and material, O-ring and drain/vent materials and meter code option. Custom configuration (option)

The following data may be specified in addition to the standard configuration parameters:

Descriptor 32 alphanumeric characters
Message 32 alphanumeric characters

Date Day, month, year

# Transmitter with FOUNDATION Fieldbus communication

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and the analog input function block FB1 is configured as follows:

Measure Profile Pressure Engineering Unit kPa

Output scale 0% Lower Range Limit (LRL)
Output scale 100% Upper Range Limit (URL)

Output Linear

Hi-Hi Limit Upper Range Limit (URL)
Hi Limit : Upper Range Limit (URL)
Low Limit Lower Range Limit (LRL)
Low-Low Limit Lower Range Limit (LRL)
Limits hysteresis 0.5% of output scale

PV filter time 0 sec.

Tag 32 alphanumeric characters

The analog input function block FB2 is configured for the sensor temperature measured in °C. Any or all the above configurable parameters, including the range values, can be changed using any host compliant to FOUNDATION fieldbus. The transmitter database is customized with specified flange type and material, O–ring and drain/vent materials and meter code option.

For any protocol available engineering units of pressure measure are :

Pa, kPa, MPa

inH<sub>2</sub>O@4°C, mmH<sub>2</sub>O@4°C, psi


inH2O@20°C, ftH2O@20°C, mmH2O@20°C

inHg, mmHg, Torr g/cm<sup>2</sup>, kg/cm<sup>2</sup>, atm mbar, bar


8

## $\textbf{MOUNTING DIMENSIONS} \ (\text{not for construction unless certified}) \ - \ dimensions \ \text{in mm} \ \ (\text{in} \ \ )$


## Transmitter with barrel housing on bracket for 60mm (2in) pipe mounting



<sup>1</sup>/<sub>2</sub> – 14 NPT female connection




DIN-EN837-1 G 1/2 B connection




<sup>1</sup>/<sub>2</sub> – 14 NPT male connection

## **Electrical connections**

## **HART Version**



## **FIELDBUS Versions**



## **BASIC ORDERING INFORMATION model 264GS Gauge Pressure Transmitter**

Select one character or set of characters from each category and specify complete catalog number.

Refer to additional ordering information code and specify one or more codes for each transmitter if additional options are required.

BASE MODEL - 1st to 5th cl	haracters			2	6 4	G	S	Х	X	Х	X	Х	Х
Gauge Pressure Transmitt	ter - BASE ACCURACY 0.	.075%											
SENSOR - Span limits - 6	5 <sup>th</sup> character							'					
0.2 and 6kPa	2 and 60mbar	0.8 and 24inH2O						С					
0.4 and 40kPa	4 and 400mbar	1.6 and 160inH <sub>2</sub> O						F					
2.5 and 250kPa	25 and 2500mbar	10 and 1000inH2O						L					
30 and 3000kPa	0.3 and 30bar	4.35 and 435psi						U					
100 and 10000kPa	1 and 100bar	14.5 and 1450psi						R					
600 and 60000 kPa	6 and 600bar	87 and 8700psi						V					
Diaphragm material / Fill 1	fluid (wetted parts) – 7th		(11.1.0)										
Hastelloy C276™		Silicone oil	(Note 2)				NAC		K				
Hastelloy C276™ gold-pla	ated	Silicone oil	(Note 2)				NAC		G				
Hastelloy C276™		Inert fluid	(Notes 1, 2)				NAC		F				
Hastelloy C276 <sup>™</sup> gold-pla Hastelloy C276 <sup>™</sup>	itea	Inert fluid	(Notes 1, 2)				NAC NAC		E Z				
Hastelloy C276™ gold-pla	atod	White oil (FDA) White oil (FDA)	(Note 2) (Note 2)				NAC		1				
Ceramic	ileu	No filling	(Note 3)				NAC		J				
Process connection mate	rial (wetted parts) - 8th o		(Note 3)				NAC	<u>/</u>	J				
AISI 316 L ss		<sup>1</sup> / <sub>2</sub> – 14 NPT female					NAC	:F		В			
AISI 316 L ss		1/2 - 14 NPT male					NAC			T			
AISI 316 L ss		DIN EN837–1 G 1/2 B					NAC			P			
Hastelloy C276™		1/2 – 14 NPT female					NAC			E			
Hastelloy C276™		1/2 - 14 NPT male					NAC			K			
Hastelloy C276™		DIN EN837-1 G <sup>1</sup> / <sub>2</sub> B					NAC			D			
Gasket - 9th character											1		
Viton™			(Notes 1, 3)				NAC	Έ			5		
Perfluoroelastomer (MWP:	=0.6MPa)		(Note 3)				NAC				6		
Perbunan	-0.0ivii <i>a</i> ,		(Note 3)				NAC				8		
None			(Note 2)				NAC				N		
Housing material and elec	ctrical connection - 10h	character	,										
Aluminium alloy (Barrel ver	rsion)	1/2 - 14 NPT										Α	
Aluminium alloy (Barrel ver		M20 x 1.5 (CM 20)										В	
Aluminium alloy (Barrel ver		Pg 13.5										D	
Aluminium alloy (Barrel ver	rsion)	1/2 GK										С	
Aluminium alloy (Barrel ver	rsion)	Harting Han connector	(general purpose only)			(N	Note 4	4)				Ε	
Aluminium alloy (Barrel ver	rsion)	Fieldbus connector	(general purpose only)			(N	Note 4	4)				G	
Aluminium alloy copper-fre		1/2 – 14 NPT										Н	
Aluminium alloy copper-fre		M20 x 1.5 (CM 20)										L	
Aluminium alloy copper-fre	ee (Barrel version)	Pg 13.5										Ν	
Aluminium alloy copper-fre		1/2 GK										M	
Aluminium alloy copper-fre		Harting Han connector	(general purpose only)			,	Note 4	,				Ρ	
Aluminium alloy copper-fre		Fieldbus connector	(general purpose only)			(1)	Vote 4	4)				R	
AISI 316 L ss (Barrel version	,	1/2 – 14 NPT										S	
AISI 316 L ss (Barrel versi		M20 x 1.5 (CM20)										Τ	
AISI 316 L ss (Barrel version		Pg 13.5										V	
AISI 316 L ss (Barrel version		1/2 GK	(managed managed 11)			/*	1-4	4)				U	
AISI 316 L ss (Barrel versions		Fieldbus connector	(general purpose only)			(1)	Vote 4	4)				Z	]
Output/Additional options		NI			/N I	<b>1</b> - C	0)						
HART digital communicati		No additional options	ardered by "Additional and	olo"\		te 5,							Н
HART digital communicati	ion and 4 to 20mA		ordered by "Additional ordering coo	ue")		te 5)							1
PROFIBUS PA		No additional options	ordered by "Additional andering -	do"\		te 5,							P 2
PROFIBUS PA			ordered by "Additional ordering coo	ue')		te 6)							F
FOUNDATION Fieldbus		No additional options	ordered by "Additional ordering ass	do"\		te 5,							3
FOUNDATION Fieldbus		Options requested (to be	ordered by "Additional ordering coo	ue')	(IVC	te 6)							3

## **ADDITIONAL ORDERING INFORMATION for model 264GS**

Add one or more 2-digit code(s) after the basic ordering information to select all required options

	xx	ХX	XX	ХX	хх	хх	ХX	хх	ХX	хx	хx	хx	хx
Electrical certification	٦٠٠٠						,,,,,						
ATEX Group II Category 1 GD – Intrinsic Safety EEx ia ATEX Group II Category 1/2 GD – Flameproof EEx d (Note 2) ATEX Group II Category 3 GD – Type of protection "N" EEx nL design compliance (Note 7) Canadian Standard Association (CSA) (only 1/2–14NPT, M20 and Pg 13.5 electrical connection) - (Note 8 Standards Australia SAA (Not Ex d; Not Ex ia and Ex n for PROFIBUS PA and FOUNDATION Fieldbus)	E5												
Factory Mutual (FM) approval (only with ½-14NPT, M20 and Pg 13.5 electrical connection) - (Note 8) Combined ATEX - Intrinsic Safety and Flameproof (Note 2) Combined ATEX, FM and CSA (only with ½-14NPT, M20 and Pg 13.5 electrical connection) (Notes 7,8) NEPSI (China) - Intrinsic Safety Ex ia NEPSI (China) - Flameproof Ex d (Note 2) GOST (Russia) EEx ia GOST (Russia) EEx d (Note 2)	EY EZ W1 W2												
GOST (Kazakhstan) EEx ia GOST (Kazakhstan) EEx d (Note 2) Inmetro (Brazil) EEx ia Inmetro (Brazil) EEx d (Note 2) Inmetro (Brazil) EEx nL Metrologic (Russia)	W3 W4 W5 W6 W7												
Metrologic (Kazakhstan)  Output meter	WD												
ProMeter, Standard calibration (Note 7) ProMeter, Special calibration (Note 7) Analog output indicator linear 0–100% scale (Note 7) Analog output indicator, special graduation (to be specified for linear scale) (Note 7) Programmable signal meter and HART configurator (CoMeter) (Note 7) Programmable signal meter and HART configurator (CoMeter – customer configuration) (Note 7)		D1 D2 D3 D5 D7 D8											
Integral LCD			•										
Digital LCD integral display			L1										
Mounting bracket (shape and material)													
For pipe mounting (Not suitable for AISI housing) Carbon steel For pipe mounting AISI 316 L ss				B1 B2									
Surge Surge/Transjent Protector/leternal for HART / 4 20mA													
Surge/Transient Protector (Internal for HART / 4-20mA) Surge/Transient Protector (External supplied loose for PROFIBUS PA and FOUNDATION Fieldbus only suitable with 1/2-14NPT and M20 electrical connection and with ATEX, FM and CSA certifications, no DI	JST)				S1								
Operating manual													
German Italian Spanish French						M1 M2 M3 M4							
Labels & tag language						IVI4							
German Italian Spanish							T1 T2 T3						
French Additional tag plate							T4						
Laser printing of tag on stainless steel plate								12					
Configuration									l				
Standard – Pressure = inH <sub>2</sub> O/psi at 20° C; Temperature = deg. F Standard – Pressure = inH <sub>2</sub> O/psi at 4° C; Temperature = deg. F Standard – Pressure = inH <sub>2</sub> O/psi at 20° C; Temperature = deg.C Standard – Pressure = inH <sub>2</sub> O/psi at 4° C; Temperature = deg. C Custom									N2 N3 N4 N5 N6				
Preparation procedure										•			
Oxygen service cleaning (only available with inert fill and Viton gasket) - Pmax =21MPa/210bar/3045psi;	max =	60°	C/14	∙0° F						P1			
Certificates Inspection certificate EN 10204–3.1 of calibration (9-point)													
Certificate of compliance with the order EN 10204–2.1 of instrument design											C1 C6		
Material traceability													
Certificate of compliance with the order EN 10204–2.1 of process wetted parts Inspection certificate EN 10204–3.1 of process wetted parts												H1 H3	
Connector												5	1
Fieldbus 7/8 (Recommended for FOUNDATION Fieldbus) - (supplied loose without mating female plug) Fieldbus M12x1 (Recommended for PROFIBUS PA) - (supplied loose without mating female plug) Harting Han – straight entry Harting Han – angle entry						(Not	es 6, es 6, es 5,	9)					U1 U2 U3

- Note 1: Suitable for oxygen service
- Note 2: Not available with Sensor code C, F
- Note 3: Not available with Sensor code L, U, R, V
- Note 4: Select type in additional ordering code
- Note 5: Not available with Electronic Housing code Z, R, G
- Note 6: Not available with Electronic Housing code P, E
- Note 7: Not available with PROFIBUS PA and FF output code 2 or 3
- Note 8: Not Ex d for sensor code C, F
- Note 9: Not available with Electronic housing code U, S, T, V, H, M, L, N, D, C, A, B
- ™ Hastelloy is a Cabot Corporation trademark
- ™ Viton is a Dupont de Nemour trademark

## Standard delivery items (can be differently specified by additional ordering code)

- General purpose (no electrical certification)
- No meter/display, no mounting bracket, no surge protection
- English manual and labels
- Configuration with kPa and deg. C units
- No test, inspection or material traceability certificates

THE SELECTION OF SUITABLE WETTED PARTS AND FILLING FLUID FOR COMPATIBILITY WITH THE PROCESS MEDIA IS A CUSTOMER'S RESPONSIBILITY, IF NOT OTHERWISE NOTIFIED BEFORE MANUFACTURING.

## **BASIC ORDERING INFORMATION model 264AS Absolute Pressure Transmitter**

Select one character or set of characters from each category and specify complete catalog number.

Refer to additional ordering information code and specify one or more codes for each transmitter if additional options are required.

BASE MODEL - 1st to 5th o	characters		2 6	6 4 A S X	Х	Х		Χ	Х
	mitter – BASE ACCURACY	0.075%							
SENSOR - Span limits -	6 <sup>th</sup> character								
0.3 and 6kPa	3 and 60mbar	2.25 and 45mmHg		С					
2 and 40kPa	20 and 400mbar	15 and 300mmHg		F					
12.5 and 250kPa	125 and 2500mbar	93.8 and 1875mmHg		Ĺ					
150 and 3000kPa	1.5 and 30bar	21.7 and 435psi		Ū					
	fluid (wetted parts) - 7th (				_				
Hastellov C276™	mana (montos parto)	Silicone oil	(Note 2)	NACE	Κ				
Hastelloy C276™ gold-pla	ated	Silicone oil	(Note 2)	NACE					
Hastelloy C276™		Inert fluid	(Notes 1, 2)	NACE	F				
Hastelloy C276™ gold-pla	ated	Inert fluid	(Notes 1, 2)	NACE	Е				
Hastelloy C276™		White oil (FDA)	(Note 2)	NACE	Z				
Hastelloy C276™ gold-pla	ated	White oil (FDA)	(Note 2)	NACE	1				
Ceramic		No filling `	(Note 3)	NACE	J				
Process connection mate	erial (wetted parts) - 8th c	haracter				-			
AISI 316 L ss		1/2 - 14 NPT female		NACE		В			
AISI 316 L ss		1/2 - 14 NPT male		NACE		Τ			
AISI 316 L ss		DIN EN837-1 G <sup>1</sup> / <sub>2</sub> B		NACE		Р			
Hastelloy C276™		1/2 - 14 NPT female		NACE		Ε			
Hastelloy C276™		1/2 - 14 NPT male		NACE		Κ			
Hastelloy C276™		DIN EN837-1 G 1/2 B		NACE		D			
Gasket - 9th character							1		
Viton™			(Notes 1, 3)	NACE			5		
Perfluoroelastomer (MWF	P=0.6MPa)		(Note 3)	NACE			6		
Perbunan	•		(Note 3)	NACE			8		
None			(Note 2)	NACE			Ν		
Housing material and ele	ctrical connection – 10th of	character							
Aluminium alloy (Barrel ve	ersion)	1/2 - 14 NPT						Α	
Aluminium alloy (Barrel ve	ersion)	M20 x 1.5 (CM 20)						В	
Aluminium alloy (Barrel ve	ersion)	Pg 13.5						D	
Aluminium alloy (Barrel ve		¹/₂ GK						С	
Aluminium alloy (Barrel ve		Harting Han connector	(general purpose only)	(Note				Ε	
Aluminium alloy (Barrel ve		Fieldbus connector	(general purpose only)	(Note	4)			G	
Aluminium alloy copper-fi		<sup>1</sup> / <sub>2</sub> – 14 NPT						Н	
Aluminium alloy copper-fr		M20 x 1.5 (CM 20)						L	
Aluminium alloy copper-fi		Pg 13.5						Ν	
Aluminium alloy copper-fr		1/2 GK						M	
Aluminium alloy copper-fr		Harting Han connector	(general purpose only)	(Note				Ρ	
Aluminium alloy copper-fr		Fieldbus connector	(general purpose only)	(Note	4)			R	
AISI 316 L ss (Barrel vers		1/2 - 14 NPT						S	
AISI 316 L ss (Barrel vers		M20 x 1.5 (CM20)						T	
AISI 316 L ss (Barrel vers		Pg 13.5						V	
AISI 316 L ss (Barrel vers		1/2 GK		/h · ·	4)			U	
AISI 316 L ss (Barrel vers	· · · · · · · · · · · · · · · · · · ·	Fieldbus connector	(general purpose only)	(Note	4)			Z	
Output/Additional options		NI		(NI=+== F O)					
HART digital communicat		No additional options	rdorod by II Additional analysis and III	(Notes 5, 6)					Н
HART digital communicat	tion and 4 to 20mA		rdered by "Additional ordering code")	(Note 5)					1
PROFIBUS PA		No additional options	und a und a la l	(Notes 5, 6)					Р
PROFIBUS PA			rdered by "Additional ordering code")	(Note 6)					2
FOUNDATION Fieldbus		No additional options	understand to a HA et altation of the state	(Notes 5, 6)					F
FOUNDATION Fieldbus		Options requested (to be or	rdered by "Additional ordering code")	(Note 6)					3

## **ADDITIONAL ORDERING INFORMATION for model 264AS**

Add one or more 2-digit code(s) after the basic ordering information to select all required options

	1												
lastrical cartification	_ xx	XX	XX	XX	XX	XX	XX	XX	XX	XX	XX	XX	XX
Combined ATEX   Condition	E5 E6 E7												
Output meter	***	1											
ProMeter, Standard calibration (Note 7) ProMeter, Special calibration (Note 7) Analog output indicator linear 0–100% scale (Note 7) Analog output indicator, special graduation (to be specified for linear scale) (Note 7) Programmable signal meter and HART configurator (CoMeter) (Note 7) Programmable signal meter and HART configurator (CoMeter – customer configuration) (Note 7)  **Integral LCD**		D1 D2 D3 D5 D7 D8											
Digital LCD integral display			L1										
founting bracket (shape and material)				ı									
For pipe mounting (Not suitable for AISI housing) Carbon steel				В1									
For pipe mounting AISI 316 L ss				B2									
Surge/Transient Protector (Internal for HART / 4-20mA) Surge/Transient Protector (External supplied loose for PROFIBUS PA and FOUNDATION Fieldbus only suitable with 1/2-14NPT and M20 electrical connection and with ATEX, FM and CSA certifications, no DU	JST)				S1								
perating manual													
German Italian Spanish French						M1 M2 M3 M4							
abels & tag language													
German Italian Spanish French							T1 T2 T3 T4						
dditional tag plate								•					
Laser printing of tag on stainless steel plate								12					
Standard – Pressure = inH2O/psi at 20° C; Temperature = deg. F Standard – Pressure = inH2O/psi at 4° C; Temperature = deg. F Standard – Pressure = inH2O/psi at 20° C; Temperature = deg. C Standard – Pressure = inH2O/psi at 4° C; Temperature = deg. C Custom									N2 N3 N4 N5 N6				
reparation procedure													
Oxygen service cleaning (only available with inert fill and Viton gasket) - Pmax =21MPa/210bar/3045psi; T	max =	60°	C/14	0° F						P1			
Certificates Inspection certificate EN 10204-3.1 of calibration (9-point)											C1		
Certificate of compliance with the order EN 10204–2.1 of instrument design											C6		
Asterial traceability  Certificate of compliance with the order EN 10204–2.1 of process wetted parts Inspection certificate EN 10204–3.1 of process wetted parts												H1 H3	
Connector													
Fieldbus 7/8 (Recommended for FOUNDATION Fieldbus) - (supplied loose without mating female plug) Fieldbus M12x1 (Recommended for PROFIBUS PA) - (supplied loose without mating female plug) Harting Han – straight entry						(Note (Note (Note	es 6, es 5,	9)					U1 U2 U3
						(Note		9)					U

- Note 1: Suitable for oxygen service
- Note 2: Not available with Sensor code C, F
- Note 3: Not available with Sensor code L, U
- Note 4: Select type in additional ordering code
- Note 5: Not available with Electronic Housing code Z, R, G
- Note 6: Not available with Electronic Housing code P, E
- Note 7: Not available with PROFIBUS PA and FF output code 2 or 3
- Note 8: Not Ex d for sensor code C, F
- Note 9: Not available with Electronic housing code U, S, T, V, H, M, L, N, D, C, A, B
- ™ Hastelloy is a Cabot Corporation trademark
- ™ Viton is a Dupont de Nemour trademark

## Standard delivery items (can be differently specified by additional ordering code)

- General purpose (no electrical certification)
- No meter/display, no mounting bracket, no surge protection
- English manual and labels
- Configuration with kPa and deg. C units
- No test, inspection or material traceability certificates

THE SELECTION OF SUITABLE WETTED PARTS AND FILLING FLUID FOR COMPATIBILITY WITH THE PROCESS MEDIA IS A CUSTOMER'S RESPONSIBILITY, IF NOT OTHERWISE NOTIFIED BEFORE MANUFACTURING.

## Contact us

## ABB Ltd.

## **Process Automation**

Howard Road St. Neots Cambridgeshire PE19 8EU UK

Tel: +44 (0)1480 475321 Fax: +44 (0)1480 217948

## ABB Inc.

## **Process Automation**

125 E. County Line Road Warminster PA 18974 USA

Tel: +1 215 674 6000 Fax: +1 215 674 7183

# ABB Automation Products GmbH

## **Process Automation**

Schillerstr. 72 32425 Minden Germany

Tel: +49 551 905 534 Fax: +49 551 905 555

## ABB S.p.A.

## **Process Automation**

Via Statale 113 22016 Lenno (CO) Italy

Tel: +39 0344 58111 Fax: +39 0344 56278

www.abb.com

#### Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents - in whole or in parts - is forbidden without prior written consent of ABB.

Copyright© 2010 ABB All rights reserved

™ Hastelloy is a Cabot Corporation trademark ™ Viton is a Dupont de Nemour trademark