

## Model 266DHH Differential flange mounted

Engineered solutions for all applications

Measurement made easy



**Base accuracy**

- from 0.06 % of calibrated span

**Reliable sensing system coupled with very latest digital technologies**

- provides large turn down ratio up to 100:1

**Comprehensive sensor choice**

- optimize in-use total performance and stability

**10-year stability**

- 0.15 % of URL

**Flexible configuration facilities**

- provided locally via local LCD keypad

**New TTG (Through-The-Glass) keypad technology**

- allows quick and easy local configuration without opening the cover, even in explosion proof environments

**IEC 61508 certification**

- for SIL2 (1oo1) and SIL3 (1oo2) applications

**PED compliance to Sound Engineering Practice (SEP)**

**WirelessHART version**

- the battery powered solution compliant to IEC 62591

**Best-in-class battery life**

- up to 10 years @ 32 s update time
- in-field replaceable

# Model 266DHH Differential flange mounted

## Functional Specifications

### Range and span limits

Sensor Code	Upper Range Limit (URL)	Lower Range Limit (LRL)	Minimum span
E	16 kPa	–16 kPa	0.54 kPa
	160 mbar	–160 mbar	5.4 mbar
	64 inH <sub>2</sub> O	–64 inH <sub>2</sub> O	2.16 inH <sub>2</sub> O
F	40 kPa	–40 kPa	0.4 kPa
	400 mbar	–400 mbar	4 mbar
	160 inH <sub>2</sub> O	–160 inH <sub>2</sub> O	1.6 inH <sub>2</sub> O
H	160 kPa	–160 kPa	1.6 kPa
	1600 mbar	–1600 mbar	16 mbar
	642 inH <sub>2</sub> O	–642 inH <sub>2</sub> O	6.4 inH <sub>2</sub> O
M	600 kPa	–600 kPa	6 kPa
	6 bar	–6 bar	0.06 bar
	87 psi	–87 psi	0.87 psi
P	2400 kPa	–2400 kPa	24 kPa
	24 bar	–24 bar	0.24 bar
	348 psi	–348 psi	3.5 psi

### Span limits

Maximum span = URL (can be further adjusted up to  $\pm$  URL (TD = 0.5) for differential models, within the range limits)  
IT IS RECOMMENDED TO SELECT THE TRANSMITTER SENSOR CODE PROVIDING THE TURNDOWN VALUE AS LOWEST AS POSSIBLE TO OPTIMIZE PERFORMANCE CHARACTERISTICS.

### Zero suppression and elevation

Zero and span can be adjusted to any value within the range limits detailed in the table as long as:  
– calibrated span  $\geq$  minimum span

### Damping (feature not available for WirelessHART version)

Selectable time constant : between 0 and 60 s  
This is in addition to sensor response time.

### Turn on time

Operation within specification in less than 10 s with minimum damping.

### Insulation resistance

> 100 M $\Omega$  at 500 V DC (terminals to earth)

## Operative limits

### Pressure limits:

#### Overpressure limits

Without damage to the transmitter

Flange	Fill fluid	Overpressure limits
ASME B16.5 Class 150	Silicone oil	0.07 kPa abs, 0.7 mbar abs, 0.5 mmHg and 230 psi
ASME B16.5 Class 300	Silicone oil	0.07 kPa abs, 0.7 mbar abs, 0.5 mmHg and 600 psi
EN 1092-1 PN 16	Silicone oil	0.07 kPa abs, 0.7 mbar abs, 0.5 mmHg and 13.5 bar
EN 1092-1 PN 40	Silicone oil	0.07 kPa abs, 0.7 mbar abs, 0.5 mmHg and 33.8 bar
ASME B16.5 Class 150	Inert (Galden)	0.135 kPa abs, 1.35 mbar abs, 1 mmHg and 230 psi
ASME B16.5 Class 300	Inert (Galden)	0.135 kPa abs, 1.35 mbar abs, 1 mmHg and 600 psi
EN 1092-1 PN 16	Inert (Galden)	0.135 kPa abs, 1.35 mbar abs, 1 mmHg and 13.5 bar
EN 1092-1 PN 40	Inert (Galden)	0.135 kPa abs, 1.35 mbar abs, 1 mmHg and 33.8 bar
ASME B16.5 Class 150	Inert (Halocarbon)	0.4 kPa abs, 4 mbar abs, 3 mmHg and 230 psi
ASME B16.5 Class 300	Inert (Halocarbon)	0.4 kPa abs, 4 mbar abs, 3 mmHg and 600 psi
EN 1092-1 PN 16	Inert (Halocarbon)	0.4 kPa abs, 4 mbar abs, 3 mmHg and 13.5 bar
EN 1092-1 PN 40	Inert (Halocarbon)	0.4 kPa abs, 4 mbar abs, 3 mmHg and 33.8 bar

### Static pressure limits

Transmitters for differential pressure model 266DHH operates within specifications between the following limits:

Flange	Static pressure limits
ASME B16.5 Class 150	1.3 kPa abs, 13 mbar abs, 0.2 psia and 230 psi
ASME B16.5 Class 300	1.3 kPa abs, 13 mbar abs, 0.2 psia and 600 psi
EN 1092-1 PN 16	1.3 kPa abs, 13 mbar abs, 0.2 psia and 13.5 bar
EN 1092-1 PN 40	1.3 kPa abs, 13 mbar abs, 0.2 psia and 33.8 bar

The pressure limit decreases with increasing temperature above 100°F (38°C), according to ASME B16.5 standards or above 50°C according to EN 1092-1 standards.

### Proof pressure

The transmitter can be exposed without leaking to line pressure of up to two times the flange rating.  
Meet ANSI/ISA–S 82.03 hydrostatic test requirements.

## Temperature limits °C ( °F) :

### Ambient

is the operating temperature

Model 266DHH	Ambient temperature limits
Silicone oil for sensor F to P	–40 and 85 °C (–40 and 185 °F)
Silicone oil for sensor E	–25 and 85 °C (–13 and 185 °F)
Inert (Galden) for sensor F to P	–20 and 85 °C (–4 and 185 °F)
Inert (Galden) for sensor E	–10 and 85 °C (14 and 185 °F)
Inert (Halocarbon) for sensor F to P	–20 and 85 °C (–4 and 185 °F)
Inert (Halocarbon) for sensor E	–10 and 85 °C (14 and 185 °F)

Model 266DHH	Ambient temperature limits
LCD integral display	–40 and 85 °C (–40 and 185 °F)
LCD display may not be clearly readable below –20 °C (–4 °F) or above +70 °C (+158 °F)	

Model 266DHH	Ambient temperature limit
Painted AISI 316 L ss housing	max 70 °C (158 °F) continuous

### IMPORTANT

For Hazardous Atmosphere applications see the temperature range specified on the certificate/approval relevant to the aimed type of protection.

### Process

Model 266DHH	Process temperature limits
Silicone oil for sensor F to P	–40 and 121 °C (–40 and 250 °F) <sup>(1)</sup>
Silicone oil for sensor E	–25 and 121 °C (–13 and 250 °F) <sup>(1)</sup>
Inert (Galden) for sensor F to P	–20 and 100 °C (–4 and 212 °F) <sup>(2)</sup>
Inert (Galden) for sensor E	–10 and 100 °C (14 and 212 °F) <sup>(2)</sup>
Inert (Halocarbon) for sensor F to P	–20 and 100 °C (–4 and 212 °F) <sup>(2)</sup>
Inert (Halocarbon) for sensor E	–10 and 100 °C (14 and 212 °F) <sup>(2)</sup>

Model 266DHH	Process temperature limits
Viton gasket	–20 and 121 °C (–4 and 250 °F)

### Storage

Model 266DHH	Storage temperature limits
Storage limits	–50 and 85 °C (–58 and 185 °F)
LCD integral display	–40 and 85 °C (–40 and 185 °F)

# Model 266DHH Differential flange mounted

## Environmental limits

### Electromagnetic compatibility (EMC)

Comply with EN 61326-1 and NAMUR NE 021 (2004) (option).  
Surge immunity level (with surge protector): 4 kV  
(according to IEC 1000-4-5 EN 61000-4-5)

### Pressure equipment directive (PED)

Comply with 97/23/EC following Sound Engineering Practice (SEP).

### Humidity

Relative humidity: up to 100 %  
Condensing, icing: admissible

### Vibration resistance

Accelerations up to 2 g at frequency up to 1000 Hz  
(according to IEC 60068-2-6)

### Shock resistance

Acceleration: 50 g  
Duration: 11 ms  
(according to IEC 60068-2-27)

### Wet and dust-laden atmospheres

The transmitter is dust and sand tight and protected against immersion effects as defined by IEC 60529 (2001) to IP 67 (IP 68 on request) or by NEMA Type 4X.  
IP65 with Harting Han connector.  
Aluminium and AISI housings as barrel version also comply to IP 66 as defined by IEC 60529 (2001).

### Hazardous atmospheres

#### (FOR ALL VERSIONS EXCEPT WirelessHART)

With or without integral display

#### INTRINSIC SAFETY:

ATEX Europe (code E1) approval

II 1 G Ex ia IIC T6/T5/T4 and II 1/2 G Ex ia IIC T6/T5/T4 and

II 1 D Ex iaD 20 T85 °C and II 1/2 D Ex iaD 21 T85 °C; IP67.

IECEx (code E8) approval

Ex ia IIC T6/T5/T4 and Ex iaD 20 T85 °C and Ex iaD 21 T85 °C; IP67.

NEPSI China (code EY)

Ex ia IIC T4~T6, DIP A20TA, T4~T6.

#### EXPLOSION PROOF:

ATEX Europe (code E2) approval

II 1/2 G Ex d IIC T6 and II 1/2 D Ex tD A21 IP67 T85 °C (Ta = -50 to +75 °C).

IECEx (code E9) approval

Ex d IIC T6 and Ex tD A21 IP67 T85 °C (Ta = -50 to +75 °C).

NEPSI China (code EZ)

Ex d IIC T6, DIP A21TA, T6.

#### TYPE "N":

ATEX Europe (code E3 ) type examination

II 3 G Ex nL IIC T6/T5/T4 and II 3 D Ex tD A22 IP67 T85 °C; IP67.

IECEx (code ER) type examination

Ex nL IIC T6/T5/T4; IP67.

NEPSI China (code ES) type examination

Ex nL IIC T4~T6, DIP A22TA, T6.

FM Approvals US (code E6) and FM Approvals Canada (code E4):

— Explosionproof (US): Class I, Div. 1, Groups A, B, C, D

— Explosionproof (Canada): Class I, Div. 1, Groups B, C, D

— Dust ignitionproof : Class II, Div. 1, Groups E, F, G

— Suitable for: Class II, Div. 2, Groups F, G; Class III, Div.1, 2

— Nonincendive: Class I, Div. 2, Groups A, B, C, D

— Intrinsically safe: Class I, II, III, Div. 1, Groups A, B, C, D, E, F, G

Class I, Zone 0 AEx ia IIC T6/T4, Zone 0 (FM US)

Class I, Zone 0 Ex ia IIC T6/T4, Zone 0 (FM Canada)

COMBINED ATEX (code EW = E1 + E2 + E3), (code E7 = E1 + E2)

COMBINED ATEX, FM and IECEx Approvals (code EN = EW + E4 + E6+ E1)

COMBINED FM Approvals US and Canada

— Intrinsically safe (code EA)

— Explosionproof (code EB)

— Nonincendive (code EC)

COMBINED IEC (code EH = E8 + E9), (code EI = E8 + E9 + ER)

COMBINED NEPSI (code EP = EY + EZ), (code EQ = EY + EZ + ES)

Technical Regulations Customs Union EAC (Russia, Kazakhstan, Belarus),

Inmetro (Brazil), Kosha (Korea).

REFER TO CERTIFICATES FOR AMBIENT TEMPERATURE RANGES (WITHIN THE LIMITS OF -50 TO 85°C) RELATED TO THE DIFFERENT TEMPERATURE CLASSES

## Hazardous atmospheres

### (ONLY FOR WirelessHART VERSION)

With or without integral display

---

#### INTRINSIC SAFETY:

ATEX Europe (code E1) approval

II 1 G Ex ia IIC T4 and II 1/2 G Ex ia IIC T4.

IECEX (code E8) approval

Ex ia IIC T4.

---

FM Approvals US and FM Approvals Canada:

— Intrinsically safe: Class I, Div. 1, Groups A, B, C, D (code EA)

Class I, Zone 0 AEx ia IIC T4 (FM US)

Class I, Zone 0 Ex ia IIC T4 (FM Canada)

---

COMBINED ATEX, IECEX and FM Approvals US and Canada

(Code EF = E1 + E8 + EA)

---

REFER TO CERTIFICATES FOR AMBIENT TEMPERATURE  
RANGES (WITHIN THE LIMITS OF -50 TO 70°C) RELATED TO  
THE DIFFERENT TEMPERATURE CLASSES

# Model 266DHH Differential flange mounted

## Electrical Characteristics and Options

### Optional indicators

#### Integrated digital display

(code LS; only with HART standard functionality)

Wide screen LCD, 128 x 64 pixel, 52.5 x 27.2 mm (2.06 x 1.07 in.) dot matrix. Two keys for zero/span or without keypad. User selectable application-specific visualizations. Display may also indicate static pressure, sensor temperature and diagnostic messages.



#### Integral display with integral keypad

(code L1; not with HART standard functionality)

Wide screen LCD, 128 x 64 pixel, 52.5 x 27.2 mm (2.06 x 1.07 in.) dot matrix. Multilanguage. Four keys for configuration and management of device. Easy setup for quick commissioning. User selectable application-specific visualizations. Totalized and instantaneous flow indication. Display may also indicate static pressure, sensor temperature and diagnostic messages and provides configuration facilities.



#### Integral display with Through-The-Glass (TTG) activated keypad (code L5; not with HART standard functionality)

As above integral display but equipped with the innovative TTG keypad allowing the activation of the configuration and management menus of the device without the need of removing the transmitter housing cover. TTG keypad is protected against accidental activations.



### Optional surge protection

Up to 4kV

- voltage 1.2  $\mu$ s rise time / 50  $\mu$ s delay time to half value
- current 8  $\mu$ s rise time / 20  $\mu$ s delay time to half value

### Process diagnostics (PILD)

Plugged impulse line detection (PILD) generates a warning via communication (HART, PA, FF). The device can be configured to drive the output to “Alarm current” or set a status “BAD”.

### HART® digital communication and 4 to 20 mA output Standard and Advanced functionality

Device type: 1a07<sub>hex</sub> (listed with HCF)

### Power supply

The transmitter operates from 10.5 to 42 V DC with no load and is protected against reverse polarity connection (additional load allows operations over 42 V DC). For Ex ia and other intrinsically safe approval power supply must not exceed 30 V DC. Minimum operating voltage increases to 12.3 V DC with optional surge protector

### Ripple

20 mV max on a 250  $\Omega$  load as per HART specifications.

### Load limitations

4 to 20 mA and HART total loop resistance :

$$R \text{ (k}\Omega\text{)} = \frac{\text{Supply voltage} - \text{min. operating voltage (V DC)}}{22 \text{ mA}}$$

A minimum of 250  $\Omega$  is required for HART communication.

### Output signal

Two-wire 4 to 20 mA, user-selectable for linear or square root output, power of  $3/2$  or  $5/2$ , square root for bidirectional flow, 22 points linearization table (i.e. for horizontal or spherical tank level measurement). HART® communication provides digital process variable superimposed on 4 to 20 mA signal, with protocol based on Bell 202 FSK standard. HART revision 5 is the default HART output. HART revision 7 is available on request.

### Output current limits (to NAMUR NE 43 standard)

Overload condition

- Lower limit: 3.8 mA (configurable from 3.8 to 4 mA)
- Upper limit: 20.5 mA (configurable from 20 to 21 mA)

Alarm current

- Lower limit: 3.6 mA (configurable from 3.6 to 4 mA)
- Upper limit: 21 mA (configurable from 20 to 23 mA, limited to 22 mA for HART Safety; apply for electronics release 7.1.15 or later)

Factory setting: high alarm current

### IEC 62591 WirelessHART® output

Device type: 1a06<sub>hex</sub> (listed with HCF)

Network ID: ABB<sub>hex</sub> [2747<sub>dec</sub>]

Join keys: 57495245<sub>hex</sub> [1464422981] 4c455353<sub>hex</sub> [1279611731]  
4649454c<sub>hex</sub> [1179206988] 444b4559<sub>hex</sub> [1145783641]

### Power Supply

1x D-cell size lithium-thionyl chloride battery.

Battery life: 10 years at 32 sec. update time, 8 years at 16 sec. update time or 5 years at 8 sec. update time.

(at reference conditions of 25 ± 2 °C ambient temperature, data routed from 3 additional devices, LCD off).

THE BATTERY CAN BE REPLACED IN FIELD, ALSO IN HAZARDOUS CLASSIFIED AREA.

### Output signal

IEC 62591 WirelessHART Version 7.5 (IEEE 802.15.4-2006);

Frequency band: 2.4 GHz DSSS

Update rate: user selectable from 1 sec. to 60 min.

### Integrated adjustable omnidirectional antenna

— Output radio frequency: maximum 10 mW (10 dBm) EIRP

— Range: up to 300 m. (328 yds.)

Minimum distance between antenna and person is 0.2 m. (8 in.)

### Telecommunications directive

Every wireless measuring device must be certified in accordance with the telecommunications directive, in this case the frequency range. This certification is country-specific.

### European directives

Radio Equipment and Telecommunications Terminal

Equipment Directive 99/5/EC R&TTE

ETSI EN 300 328 V1.7.1 in accordance with Article 3.2

ETSI EN 301 489-17

In Europe, use of the 2400 - 2483.5 MHz frequency band is not harmonized. Country-specific regulations must be observed.

### Restrictions for Norway

Operation not permitted within a radius of 20 km around Ny-Alesund in Svalbard. For more information, see [www.npt.no](http://www.npt.no) Norway Posts and Telecommunications site

### USA / Canadian directives

FCC Part 15.247:2009 (USA)

IC RSS-210 and ICES-003 (Canada)

### PROFIBUS® PA output

#### Device type

Pressure transmitter compliant to Profiles 3.0.1

Identification number: 3450<sub>hex</sub>

#### Power supply

The transmitter operates from 9 to 32 V DC , polarity independent, with or without surge protector.

For Ex ia approval power supply must not exceed 17.5 V DC.

Intrinsic safety installation according to FISCO model.

#### Current consumption

operating (quiescent): 15 mA

fault current limiting: 20 mA max.

#### Output signal

Physical layer in compliance to IEC 1158-2/EN 61158-2 with transmission to Manchester II modulation, at 31.25 kbit/s.

#### Output interface

PROFIBUS PA communication according to Profibus DP50170 Part 2/DIN 19245 part 1-3.

#### Output update time

25 ms

#### Data blocks

3 analog input, 1 physical.

#### Additional blocks

1 Pressure with calibration transducer block

1 Advanced Diagnostics transducer block including Plugged Input Line Detection

1 Local Display transducer block

#### Transmitter failure mode

On gross transmitter failure condition, detected by self-diagnostics, the output signal can be driven to defined conditions, selectable by the user as safe, last valid or calculated value.

If electronic failure or short circuit occur the transmitter consumption is electronically limited at a defined value (20 mA approx), for safety of the network.

# Model 266DHH Differential flange mounted

## FOUNDATION Fieldbus™ output

### Device type

LINK MASTER DEVICE

Link Active Scheduler (LAS) capability implemented.

Manufacturer code: 000320<sub>hex</sub>

Device type code: 0007<sub>hex</sub>

### Power supply

The transmitter operates from 9 to 32 V DC, polarity independent, with or without surge protector.

For Ex ia approval power supply must not exceed 24 V DC (entity certification) or 17.5 V DC (FISCO certification), according to FF-816.

### Current consumption

operating (quiescent): 15 mA

fault current limiting: 20 mA max.

### Output signal

Physical layer in compliance to IEC 1158-2/EN 61158-2 with transmission to Manchester II modulation, at 31.25 kbit/s.

### Function blocks/execution period

3 enhanced Analog Input blocks/25 ms max (each)

1 enhanced PID block/40 ms max.

1 standard ARithmetic block/25 ms

1 standard Input Selector block/25 ms

1 standard Control Selector block/25 ms

1 standard Signal Characterization block/25 ms

1 standard Integrator/Totalizer block/25 ms

### Additional blocks

1 enhanced Resource block,

1 custom Pressure with calibration transducer block

1 custom Advanced Diagnostics transducer block including Plugged Input Line Detection

1 custom Local Display transducer block

### Number of link objects

35

### Number of VCRs

35

## Output interface

FOUNDATION fieldbus digital communication protocol to standard H1, compliant to specification V. 1.7.

## Transmitter failure mode

The output signal is “frozen” to the last valid value on gross transmitter failure condition, detected by self-diagnostics which also indicate a BAD conditions. If electronic failure or short circuit occur the transmitter consumption is electronically limited at a defined value (20 mA approx), for safety of the network.



## Performance specifications

Stated at reference condition to IEC 60770 ambient temperature of 20 °C (68 °F), relative humidity of 65 %, atmospheric pressure of 1013 hPa (1013 mbar), mounting position with vertical diaphragm and zero based range for transmitter with isolating diaphragms in AISI 316 L ss or Hastelloy and silicone oil fill and HART digital trim values equal to 4 mA and to 20 mA span end points, in linear mode. Unless otherwise specified, errors are quoted as % of span. Some performance referring to the Upper Range Limit are affected by the actual turndown (TD) as ratio between Upper Range Limit (URL) and calibrated span.

IT IS RECOMMENDED TO SELECT THE TRANSMITTER SENSOR CODE PROVIDING THE TURNDOWN VALUE AS LOWEST AS POSSIBLE TO OPTIMIZE PERFORMANCE CHARACTERISTICS.

### Dynamic performance (according to IEC 61298–1 definition)

Sensors	Time constant (63.2 % of total step change)
Sensor M and P	≤ 70 ms
Sensor H	100 ms
Sensor F	180 ms
Dead time for all sensors	30 ms

Response time (total) = dead time + time constant.

See "Update Rate" for WirelessHART version.

### Accuracy rating

% of calibrated span, including combined effects of terminal based linearity, hysteresis and repeatability.

For fieldbus versions SPAN refer to analog input function block outscale range

Model	Sensor	for TD	
266DHH	F	from 1:1 to 10:1	± 0.06 %
	F	from 10:1 to 100:1	± 0.025 + (0.0035 x TD) %
	H to P	from 1:1 to 10:1	± 0.075 %
	H to P	from 10:1 to 100:1	± (0.0075 x TD) %
	E	from 1:1 to 10:1	± 0.075 %
	E	from 10:1 to 30:1	± (0.0075 x TD) %

### Ambient temperature

per 20K change between the limits of –40 °C to +85 °C (per 36 °F change between the limits of –40 to +185 °F):

Model	Sensor	for TD up to	
266DHH	F to P	10:1	± (0.03 % URL + 0.045 % span)
	E	10:1	± (0.04 % URL + 0.065 % span)

for an ambient temperature change from –10 °C to +60 °C (+14 to +140 °F):

Model	Sensor	for TD up to	
266DHH	F to P	10:1	± (0.055 % URL + 0.08 % span)
	E	10:1	± (0.075 % URL + 0.11 % span)

per 10K change between the limits of –40 °C to –10 °C or +60° to +85 °C (per 18 °F change between the limits of –40 to +14 °F or +140° to +185 °F):

Model	Sensor	for TD up to	
266DHH	F to P	10:1	± (0.03 % URL + 0.04 % span)
	E	10:1	± (0.04 % URL + 0.055 % span)

### Static pressure

(zero errors can be calibrated out at line pressure)

per 2 MPa, 20 bar or 290 psi

- zero error: ±0.05 % of URL for sensor F to P  
±0.08 % of URL for sensor E
- span error: ±0.08 % of reading.

### Supply voltage

Within voltage/load specified limits the total effect is less than 0.005 % of URL per volt.

### Load

Within load/voltage specified limits the total effect is negligible.

### Electromagnetic field

Meets all the requirements of EN 61326 for surge immunity level (of NAMUR NE 21 on request).

### Common mode interference

No effect from 100Vrms @ 50Hz, or 50 V DC

### Mounting position

No effect for rotation on diaphragm plane. A tilt up to 90° from vertical causes a zero shifts up to 0.5 kPa, 5 mbar or 2 inH<sub>2</sub>O, which can be corrected with zero adjustment. No span effect.

### Stability

±0.15 % of URL over a ten years period

# Model 266DHH Differential flange mounted

## Physical Specification

(Refer to ordering information sheets for variant availability related to specific model or versions code)

### Materials

#### Process isolating diaphragms (\*)

AISI 316 L ss; Monel 400®; Tantalum; Hastelloy® C-276.

#### High pressure side process mounting flange

AISI 316 L ss with flushing connections

#### Low pressure side process flange, adapter, plug and drain/vent valve (\*\*)

AISI 316 L ss <sup>(1)</sup>; Hastelloy® C-276 <sup>(2)</sup>; Monel 400® <sup>(3)</sup>.

#### Sensor fill fluid

Silicone oil; Inert fill (Halocarbon® 4.2 or Galden®).

#### Mounting bracket (\*\*)

Zinc plated carbon steel with chrome passivation; AISI 316 L ss.

#### Gaskets (\*)

Viton®; PTFE.

#### Sensor housing

AISI 316 L ss.

### Bolts and nuts

AISI 316 ss bolts and nuts Class A4–50 per UNI 7323 (ISO 3506), in compliance with NACE MR0175 Class II.

### Electronic housing and covers

Aluminium alloy (copper content  $\leq 0.3$  %) with baked epoxy finish (colour RAL9002); AISI 316 L ss;  
AISI 316 L ss with two components epoxy mastic coated with acrylic epoxy finish (colour aluminium grey), with antistatic agents according to CEI EN 60079.

### Covers O-ring

Buna N.

### Local adjustments (zero, span and write protect)

For Standard HART version:

- Internal for zero and span (on communication board)
- External non-intrusive for zero, span and write protect in glass filled polyphenylene oxyde, removable (code R1).

For all other versions:

- External non-intrusive for zero, span and write protect in glass filled polyphenylene oxyde, removable.

(\*) Wetted parts of the transmitter.

(\*\*) Bolts and nuts, gasket and mating flange supplied by customer.

<sup>(1)</sup> Supplied as AISI 316 L or as ASTM A351 Grade CF-3M

<sup>(2)</sup> Supplied as Hastelloy C-276 or as ASTM A494 alloy CW-12MW

<sup>(3)</sup> Supplied as Monel 400 or as ASTM A494 Grade M-35-1

## Plates

Transmitter nameplate: AISI 316 ss screwed to the electronics housing.

Certification plate and optional tag/calibration plate : self-adhesive attached to the electronics housing or AISI 316 ss fastened to the electronics housing with rivets or screws.

Optional wired-on customer data plate: AISI 316 ss.

Laser printing on metal or thermal printing on self-adhesive. For AISI 316 L ss housing it is mandatory to select option I2 or I3 for plates in AISI 316 ss.

## Calibration

Standard: at maximum span, zero based range, ambient temperature and pressure;

Optional: at specified range and ambient conditions.

## Optional extras

### Display (code Lx)

4-position (at 90°) user orientable.

### Optional plates (code Ix)

Code I2: AISI 316 ss plate with laser printed tag (up to 31 characters) and calibration details (up to 31 characters: lower and upper range values and engineering unit) fixed onto transmitter housing.

Code I1: AISI 316 ss wired-on plate with laser printed customized data (4 lines of 32 characters with 4 mm/0.16 in. height).

### Surge protection (code S2)

### Test Certificates (test, design, calibration, material traceability) (codes Cx and Hx)

### Tag and manual language (codes Tx and Mx)

### Communication connectors (code Ux)

## Process connections

Low pressure side :

on flanges :  $\frac{1}{4}$  in. – 18 NPT on process axis

on adapters :  $\frac{1}{2}$  in. – 14 NPT on process axis

fixing threads:  $\frac{7}{16}$  in. – 20 UNF at 41.3 mm centre distance

High pressure side (\*\*):

2 in. or 3 in., ASME Class 150 or Class 300 RF;

DN 50 or DN 80, PN 16 or PN 40 to EN 1092-1 Type B1

## Electrical connections

Two  $\frac{1}{2}$  in. – 14 NPT or M20x1.5 threaded conduit entries, direct on housing. Only M20x1.5 for WirelessHART with one port used for antenna.

Special communication connector (on request)

– HART : straight or angle Harting Han 8D connector and one plug.

– FOUNDATION Fieldbus, PROFIBUS PA: M12x1 or 7/8 in.

## Terminal block

HART version: three terminals for signal/external meter wiring up to 2.5 mm<sup>2</sup> (14 AWG), also connection points for test and communication purposes.

WirelessHART version: connection points for test and communication purposes; additional fast connection for external harvesting unit.

Fieldbus versions: two terminals for signal wiring (bus connection) up to 2.5 mm<sup>2</sup> (14 AWG)

## Grounding

Internal and external 6 mm<sup>2</sup> (10 AWG) ground termination points are provided.

## Mounting position

Transmitter can be mounted in any position.

Electronics housing may be rotated to any position. A positive stop prevents over travel.

## Mass (without options)

7 to 11 kg approx (16 to 24 lb); add 1.5 kg (3.3 lb) for AISI housing.

Add 650 g (1.5 lb) for packing.

## Packing

Carton 35 x 33 x 35 cm approx (14 x 13 x 14 in).

# Model 266DHH Differential flange mounted

## Configuration

### Transmitter with HART communication and 4 to 20 mA Standard configuration

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and configured as follows:

Engineering Unit	kPa
4 mA	Zero
20 mA	Upper Range Limit (URL)
Output	Linear
Damping	1 s
Transmitter failure mode	Upscale
Software tag (8 characters max)	Blank
Optional LCD display	PV in kPa; output in mA and in percentage on bargraph

Any or all the above configurable parameters, including Lower range-value and Upper range-value which must be the same unit of measure, can be easily changed using the HART hand-held communicator or by a PC running the configuration software with DTM for 266 models. The transmitter database is customized with specified flange type and material, O-ring and drain/vent materials and meter code option.

### Custom configuration (option N6)

The following data may be specified in addition to the standard configuration parameters:

Descriptor	16 alphanumeric characters
Message	32 alphanumeric characters
Date	Day, month, year

For HART protocol available engineering units of pressure measure are :

Pa, kPa, MPa  
inH2O@4 °C, mmH2O@4 °C, psi  
inH2O@20 °C, ftH2O@20 °C, mmH2O@20 °C  
inHg, mmHg, Torr  
g/cm<sup>2</sup>, kg/cm<sup>2</sup>, atm  
mbar, bar

These and others are available for PROFIBUS and FOUNDATION Fieldbus.

### Transmitter with WirelessHART communication Standard configuration

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and configured as follows:

Engineering Unit	kPa
Output scale 0 %	Lower Range Limit (LRL)
Output scale 100 %	Upper Range Limit (URL)
Output	Linear
Update rate	16 s
Software tag (8 characters max)	Blank
Optional LCD display	PV in kPa; output in percentage on bargraph

Any or all the above configurable parameters, including Lower range-value and Upper range-value which must be the same unit of measure, can be easily changed using the HART hand-held communicator or by a PC running the configuration software with DTM for 266 models. The transmitter database is customized with specified flange type and material, O-ring and drain/vent materials and meter code option.

### Custom configuration (option N6)

The following data may be specified in addition to the standard configuration parameters:

Descriptor	16 alphanumeric characters
Message	32 alphanumeric characters
Date	Day, month, year

## Transmitter with PROFIBUS PA communication

### Standard configuration

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and configured as follows:

Measure Profile	Pressure
Engineering Unit	kPa
Output scale 0 %	Lower Range Limit (LRL)
Output scale 100 %	Upper Range Limit (URL)
Output	Linear
Hi-Hi Limit	Upper Range Limit (URL)
Hi Limit	Upper Range Limit (URL)
Low Limit	Lower Range Limit (LRL)
Low-Low Limit	Lower Range Limit (LRL)
Limits hysteresis	0.5 % of output scale
PV filter	0 s
Address (set by local key)	126
Tag	32 alphanumeric characters
Optional LCD display	PV in kPa; output in percentage on bargraph

Any or all the above configurable parameters, including the range values which must be the same unit of measure, can be easily changed by a PC running the configuration software with DTM for 266 models. The transmitter database is customized with specified flange type and material, O-ring and drain/vent materials and meter code option.

### Custom configuration (option N6)

The following data may be specified in addition to the standard configuration parameters:

Descriptor	32 alphanumeric characters
Message	32 alphanumeric characters
Date	Day, month, year

## Transmitter with FOUNDATION Fieldbus communication

### Standard configuration

Transmitters are factory calibrated to customer's specified range. Calibrated range and tag number are stamped on the tag plate. If a calibration range and tag data are not specified, the transmitter will be supplied with the plate left blank and the analog input function block FB1 is configured as follows:

Measure Profile	Pressure
Engineering Unit	kPa
Output scale 0 %	Lower Range Limit (LRL)
Output scale 100 %	Upper Range Limit (URL)
Output	Linear
Hi-Hi Limit	Upper Range Limit (URL)
Hi Limit :	Upper Range Limit (URL)
Low Limit	Lower Range Limit (LRL)
Low-Low Limit	Lower Range Limit (LRL)
Limits hysteresis	0.5 % of output scale
PV filter time	0 s
Tag	32 alphanumeric characters
Optional LCD display	PV in kPa; output in percentage on bargraph

The analog input function block FB2 and FB3 are configured respectively for the sensor temperature measured in °C and for the static pressure measured in MPa.

Any or all the above configurable parameters, including the range values, can be changed using any host compliant to FOUNDATION fieldbus. The transmitter database is customized with specified flange type and material, O-ring and drain/vent materials and meter code option.

### Custom configuration (option N6)


The following data may be specified in addition to the standard configuration parameters:

Descriptor	32 alphanumeric characters
Message	32 alphanumeric characters
Date	Day, month, year

# Model 266DHH Differential flange mounted

## MOUNTING DIMENSIONS (not for construction unless certified) – dimensions in mm. (in.)

### Transmitter with barrel housing




NOTE : Process connection, gasket groove and gaskets are in accordance with IEC 61518.

Bolting threads for fixing adapter or other devices (i.e. manifold etc.) on process flange is  $\frac{7}{16}$  in. – 20 UNF.

- ① Adjustments | ② Identification plate | ③ Certification plate | ④ Drain/vent valve | ⑤ Process connections | ⑥ Terminal side |
- ⑦ L1 and L5 integral display housing | ⑧ Electronic side | ⑨ Adapter | ⑩ Space for cover removal | ⑪ Battery housing of WirelessHART version |
- ⑫ Antenna of WirelessHART version

## Transmitter with DIN aluminium housing



Rating	Size	Dimensions mm (in.)							N° of holes
		A (dia)	B (dia)	C (dia)	D (dia)	E (dia)	F (Note)	G	
ASME Class 150 R.F.	2 in.	53 (2.09)	92 (3.62)	120.5 (4.74)	152.5 (6)	20 (0.79)	19.5 (0.77)	1.6 (0.07)	4
ASME Class 150 R.F.	3 in.	77 (3.04)	127 (5)	152.5 (6)	190.5 (7.5)	20 (0.79)	24 (0.94)	1.6 (0.07)	4
ASME Class 300 R.F.	2 in.	53 (2.09)	92 (3.62)	127 (5)	165 (6.5)	20 (0.79)	22.5 (0.89)	1.6 (0.07)	8
ASME Class 300 R.F.	3 in.	77 (3.04)	127 (5)	168.5 (6.63)	210 (8.26)	22 (0.86)	28.5 (1.12)	1.6 (0.07)	8
EN PN 16 Type B1	DN 50	53 (2.09)	102 (4.02)	125 (4.92)	165 (6.5)	18 (0.71)	20 (0.79)	3 (0.12)	4
EN PN 16 Type B1	DN 80	77 (3.04)	138 (5.43)	160 (6.3)	200 (7.87)	18 (0.71)	20 (0.79)	2 (0.08)	8
EN PN 40 Type B1	DN 50	53 (2.09)	102 (4.02)	125 (4.92)	165 (6.5)	18 (0.71)	20 (0.79)	3 (0.12)	4
EN PN 40 Type B1	DN 80	77 (3.04)	138 (5.43)	160 (6.3)	200 (7.87)	18 (0.71)	24 (0.94)	2 (0.08)	8

### Note


For ASME, flange thickness tolerance is +3.0 / -0.0 mm (+0.12 / 0.0 in.).

For EN, flange thickness tolerance is +1.0 / -1.3 mm (+0.04 / 0.05 in.) up to 18 mm or ±1.5 mm (±0.06 in.) from 18 to 50 mm from 18 to 50 mm.

# Model 266DHH Differential flange mounted


## Electrical connections

### HART Version




HART hand-held communicator may be connected at any wiring termination point in the loop, providing the minimum resistance is 250 ohm. If this is less than 250 ohm, additional resistance should be added to allow communications. Maximum voltage drop on external remote indicator is 0.7 V DC.

### FIELDBUS Versions



PIN (male) IDENTIFICATION		
	FOUNDATION Fieldbus	PROFIBUS PA
1	DATA -	DATA +
2	DATA +	GROUND
3	SHIELD	DATA -
4	GROUND	SHIELD


CONNECTOR IS SUPPLIED LOOSE  
WITHOUT MATING FEMALE PLUG



- (1) Power source | (2) Remote indicator | (3) Handheld communicator | (4) External ground termination point | (5) Internal ground termination point | (6) Line load | (7) Harting Han 8D socket insert for mating plug (supplied loose) | (8) Fieldbus line (polarity independent)



## WirelessHART version



① Handheld communicator | ② External ground termination point | ③ Battery | ④ Fast connection for harvesting unit

# Model 266DHH Differential flange mounted

## Ordering information

### BASIC ORDERING INFORMATION model 266DHH Flange Mounted Differential Pressure Transmitter

Select one character or set of characters from each category and specify complete catalog number.

Refer to additional ordering information and specify one or more codes for each transmitter if additional options are required.

<b>BASE MODEL</b> - 1 <sup>st</sup> to 6 <sup>th</sup> characters				<b>2 6 6 D H H</b>	<b>X</b>	<b>S</b>	<b>X</b>	<b>X</b>	<b>X</b>	<b>X</b>	<b>X</b>	<b>X</b>	<b>X</b>
Differential Pressure Transmitter – BASE ACCURACY 0.06 %													
<b>SENSOR - Span limits</b> - 7 <sup>th</sup> characters													
0.54 and 16 kPa	5.4 and 160 mbar	2.16 and 64 inH2O			E								
0.4 and 40 kPa	4 and 400 mbar	1.6 and 160 inH2O			F								
1.6 and 160 kPa	16 and 1600 mbar	6.4 and 642 inH2O			H								
6 and 600 kPa	0.06 and 6 bar	0.87 and 87 psi			M								
24 and 2400 kPa	0.24 and 24 bar	3.5 and 348 psi			P								
<b>Use code</b> - 8 <sup>th</sup> characters						S							
<b>HIGH PRESSURE SIDE - Process mounting flange rating / Size</b> - 9 <sup>th</sup> characters													
ASME Class 150	2 in.						A						
ASME Class 150	3 in.						B						
ASME Class 300	2 in.						D						
ASME Class 300	3 in.						E						
EN PN 16 / 40	DN 50						M						
EN PN 16	DN 80						N						
EN PN 40	DN 80						L						
<b>HIGH PRESSURE SIDE - Mounting flange material/seat form</b> - 10 <sup>th</sup> characters													
AISI 316 L ss	Form RF (raised face) - serrated finish	(Note 1)		NACE				D					
AISI 316 L ss	EN 1092-1 Type B1 - serrated finish	(Note 2)		NACE				L					
<b>Diaphragm material / Fill fluid (wetted parts)</b> - 11 <sup>th</sup> characters													
AISI 316 L ss	Silicone oil			NACE				S					
Hastelloy® C-276	Silicone oil			NACE				K					
Monel 400®	Silicone oil			NACE				M					
Tantalum	Silicone oil			NACE				T					
AISI 316 L ss	Inert fluid - Galden	(Note 3)		NACE				A					
Hastelloy® C-276	Inert fluid - Galden	(Note 3)		NACE				F					
Monel 400®	Inert fluid - Galden	(Note 3)		NACE				C					
Tantalum	Inert fluid - Galden	(Note 3)		NACE				D					
AISI 316 L ss	Inert fluid - Halocarbon	(Note 3)		NACE				L					
Hastelloy® C-276	Inert fluid - Halocarbon	(Note 3)		NACE				P					
Monel 400®	Inert fluid - Halocarbon	(Note 3)		NACE				4					
Tantalum	Inert fluid - Halocarbon	(Note 3)		NACE				5					

continued  
see next page

BASIC ORDERING INFORMATION model 266DHH Flange Mounted Differential Pres. Transmitter				2	6	D	H	H	X	S	X	X	X	X	X	X	X
Low side process flanges/adapters material and connection (wetted parts) - 12 <sup>th</sup> characters																	
AISI 316 L ss (Horizontal connection)	1/4 in. – 18 NPT-f direct		NACE											A			
AISI 316 L ss (Horizontal connection)	1/2 in. – 14 NPT-f through adapter		NACE											B			
Hastelloy® C-276 (Horizontal connection)	1/4 in. – 18 NPT-f direct		(Note 4) NACE											D			
Hastelloy® C-276 (Horizontal connection)	1/2 in. – 14 NPT-f through adapter		(Note 4) NACE											E			
Monel 400® (Horizontal connection)	1/4 in. – 18 NPT-f direct		(Note 4) NACE											G			
Monel 400® (Horizontal connection)	1/2 in. – 14 NPT-f through adapter		(Note 4) NACE											H			
Bolts/Gasket (wetted parts) - 13 <sup>th</sup> characters																	
AISI 316 ss (NACE) – (MWP = 16 MPa)	Viton®		NACE												3		
AISI 316 ss (NACE) – (MWP = 16 MPa)	PTFE	(Note 3)	NACE												4		
Housing material and electrical connection - 14 <sup>th</sup> characters																	
Aluminium alloy (barrel version)	1/2 in. – 14 NPT												(Note 15)			A	
Aluminium alloy (barrel version)	M20 x 1.5 (CM 20)	(TO BE USED for WirelessHART)														B	
Aluminium alloy (barrel version)	Harting Han 8D connector	(general purpose only)											(Notes 5,15)			E	
Aluminium alloy (barrel version)	Fieldbus connector	(general purpose only)											(Notes 5,15)			G	
AISI 316 L ss (barrel version) (I2 or I3 required)	1/2 in. – 14 NPT												(Note 15)			S	
AISI 316 L ss (barrel version) (I2 or I3 required)	M20 x 1.5 (CM20)	(TO BE USED for WirelessHART)														T	
AISI 316 L ss (barrel version) (I2 or I3 required)	Fieldbus connector	(general purpose only)											(Notes 5,15)			Z	
AISI 316 L ss painted (barrel version) (I2 or I3 required)	1/2 in. – 14 NPT												(Note 15)			C	
AISI 316 L ss painted (barrel version) (I2 or I3 required)	M20 x 1.5 (CM20)	(TO BE USED for WirelessHART)														D	
AISI 316 L ss painted (barrel version) (I2 or I3 required)	Fieldbus connector	(general purpose only)											(Notes 5,15)			F	
Aluminium alloy (DIN version)	M20 x 1.5 (CM20)	(not Ex d or XP)											(Note 15)			J	
Aluminium alloy (DIN version)	Harting Han 8D connector	(general purpose only)											(Notes 5,15)			K	
Aluminium alloy (DIN version)	Fieldbus connector	(general purpose only)											(Notes 5,15)			W	
Output/Additional options - 15 <sup>th</sup> characters																	
HART and 4 to 20 mA - Standard functionality	No additional options												(Notes 6, 7)			L	
HART and 4 to 20 mA - Standard functionality	Options requested by "Additional ordering code"												(Note 6)			7	
HART and 4 to 20 mA - Advanced functionality (includes option R1)	No additional options												(Notes 6, 7)			H	
HART and 4 to 20 mA - Advanced functionality (includes option R1)	Options requested by "Additional ordering code"												(Note 6)			1	
PROFIBUS PA (includes option R1)	No additional options												(Notes 6, 7)			P	
PROFIBUS PA (includes option R1)	Options requested by "Additional ordering code"												(Note 7)			2	
FOUNDATION Fieldbus (includes option R1)	No additional options												(Notes 6, 7)			F	
FOUNDATION Fieldbus (includes option R1)	Options requested by "Additional ordering code"												(Note 7)			3	
HART and 4 to 20 mA Safety, certified to IEC 61508 (includes option R1)	No additional options												(Notes 6, 7)			T	
HART and 4 to 20 mA Safety, certified to IEC 61508 (includes option R1)	Options requested by "Additional ordering code"												(Note 6)			8	
WirelessHART (includes option R1)	No additional options												(Note 14)			W	
WirelessHART (includes option R1)	Options requested by "Additional ordering code"												(Note 14)			9	

NOTE - Option R1 represents the external pushbuttons

# Model 266DHH Differential flange mounted

## ADDITIONAL ORDERING INFORMATION for model 266DHH

Add one or more 2-digit code(s) after the basic ordering information to select all required options

				XX	XX
<b>Drain/vent valve (material and low side position) (wetted parts)</b>					
AISI 316 L ss	on process axis	(Note 8)	NACE	V1	
AISI 316 L ss	on flange side top	(Note 8)	NACE	V2	
AISI 316 L ss	on flange side bottom	(Note 8)	NACE	V3	
Hastelloy® C-276	on process axis	(Note 9)	NACE	V4	
Hastelloy® C-276	on flange side top	(Note 9)	NACE	V5	
Hastelloy® C-276	on flange side bottom	(Note 9)	NACE	V6	
Monel 400®	on process axis	(Note 10)	NACE	V7	
Monel 400®	on flange side top	(Note 10)	NACE	V8	
Monel 400®	on flange side bottom	(Note 10)	NACE	V9	
<b>Hazardous area certifications</b>					
ATEX Intrinsic Safety Ex ia			(Notes 6, 7)	E1	
ATEX Explosion Proof Ex d			(Notes 6, 7, 11, 15)	E2	
ATEX Type „N“			(Notes 6, 7, 15)	E3	
Combined ATEX - Intrinsic Safety, Explosion Proof and Type „N“			(Notes 6, 7, 11, 15)	EW	
Combined ATEX - Intrinsic Safety and Explosion Proof			(Notes 6, 7, 11, 15)	E7	
Combined ATEX, IECEx, FM Approvals (USA) and FM Approvals (Canada)			(Notes 6, 7, 11, 15)	EN	
FM Approvals (Canada) approval			(Notes 6, 7, 11, 15)	E4	
FM Approvals (USA) approval			(Notes 6, 7, 11, 15)	E6	
FM Approvals (USA and Canada) Intrinsic Safety			(Notes 6, 7)	EA	
FM Approvals (USA and Canada) Explosion Proof			(Notes 6, 7, 11, 15)	EB	
FM Approvals (USA and Canada) Nonincendive			(Notes 6, 7, 15)	EC	
IECEx Intrinsic Safety Ex ia			(Notes 6, 7)	E8	
IECEx Explosion Proof Ex d			(Notes 6, 7, 11, 15)	E9	
IECEx Type „N“ Ex nL			(Notes 6, 7, 15)	ER	
Combined IECEx - Intrinsic Safety, Explosion Proof and Type „N“			(Notes 6, 7, 11, 15)	EI	
Combined IECEx - Intrinsic Safety and Explosion Proof			(Notes 6, 7, 11, 15)	EH	
NEPSI Intrinsic Safety Ex ia			(Notes 6, 7, 15)	EY	
NEPSI Explosion Proof Ex d			(Notes 6, 7, 11, 15)	EZ	
NEPSI Type „N“			(Notes 6, 7, 15)	ES	
Combined NEPSI - Intrinsic Safety, Explosion Proof and Type „N“			(Notes 6, 7, 11, 15)	EQ	
Combined NEPSI - Intrinsic Safety and Explosion Proof			(Notes 6, 7, 11, 15)	EP	
Combined Intrinsic Safety - ATEX, IECEx and FM Approvals (USA and Canada)			(Note 16)	EF	

ADDITIONAL ORDERING INFORMATION for model 266DHH		XX	XX	XX	XX	XX	XX
<b>Other hazardous area certifications (ONLY AS ALTERNATIVE TO BASIC CERTIFICATION CODE Ex)</b>							
Technical Regulations Customs Union (EAC) Intrinsic Safety Ex ia for Russia	(Notes 6, 7, 15)	W1					
Technical Regulations Customs Union (EAC) Explosion Proof Ex d for Russia	(Notes 6, 7, 11, 15)	W2					
Technical Regulations Customs Union (EAC) combined Ex ia and Ex d for Russia	(Notes 6, 7, 11, 15)	WC					
Technical Regulations Customs Union (EAC) Intrinsic Safety Ex ia for Kazakhstan	(Notes 6, 7, 15)	W3					
Technical Regulations Customs Union (EAC) Explosion Proof Ex d for Kazakhstan	(Notes 6, 7, 11, 15)	W4					
Technical Regulations Customs Union (EAC) combined Ex ia and Ex d for Kazakhstan	(Notes 6, 7, 11, 15)	WD					
Inmetro (Brazil) Ex ia	(Notes 6, 7, 15)	W5					
Inmetro (Brazil) Ex d	(Notes 6, 7, 11, 15)	W6					
Inmetro (Brazil) Ex nL	(Notes 6, 7, 15)	W7					
Combined Inmetro (Brazil) - Intrinsic Safety, Explosion Proof and Type „N“	(Notes 6, 7, 11, 15)	W8					
Technical Regulations Customs Union (EAC) Intrinsic Safety Ex ia for Belarus	(Notes 6, 7, 15)	WF					
Technical Regulations Customs Union (EAC) Explosion Proof Ex d for Belarus	(Notes 6, 7, 11, 15)	WG					
Technical Regulations Customs Union (EAC) combined Ex ia and Ex d for Belarus	(Notes 6, 7, 11, 15)	WH					
Kosha (Korea) Intrinsic Safety Ex ia IIC T6, IP67	(Notes 6, 7, 13, 15)	WM					
Kosha (Korea) Explosion Proof Ex d IIC T6, IP67	(Notes 6, 7, 11, 13, 15)	WN					
Combined Kosha (Korea) - Intrinsic Safety and Explosion Proof	(Notes 6, 7, 11, 13, 15)	WP					
<b>Integral LCD</b>							
Digital LCD integral display with integrated keypad	(Note 13)	L1					
Digital LCD integral display with TTG (Through-The-Glass) activated keypad	(Note 13)	L5					
Integrated digital LCD display (ONLY SELECTABLE WITH OUTPUT CODE 7)	(Note 18)	LS					
<b>External non intrusive Z, S and WP pushbuttons</b>							
Transmitters with external pushbutton (ONLY SELECTABLE WITH OUTPUT CODE 7)						R1	
<b>Surge</b>							
Surge/Transient Protector	(Note 15)					S2	
<b>Operating manual (multiple selection allowed)</b>							
German (FOR HART, WirelessHART and PROFIBUS VERSIONS)							M1
Italian (ONLY FOR HART VERSIONS)							M2
Spanish (FOR HART, WirelessHART and FOUNDATION Fieldbus VERSIONS)							M3
French (ONLY FOR HART VERSIONS)							M4
English							M5
Chinese (ONLY FOR HART VERSIONS)							M6
Swedish (ONLY FOR HART VERSIONS)							M7
Polish (ONLY FOR HART VERSIONS)							M9
Portuguese (ONLY FOR HART VERSIONS)							MA
Russian (ONLY FOR HART VERSIONS)							MB
Dutch (ONLY FOR HART VERSIONS)							MD
Danish (ONLY FOR HART VERSIONS)							MF
Japanese (ONLY FOR HART VERSIONS)							MJ
Romenian (ONLY FOR HART VERSIONS)							MR
Turkish (ONLY FOR HART VERSIONS)							MT
<b>Plates language</b>							
German							T1
Italian							T2
Spanish							T3
French							T4

# Model 266DHH Differential flange mounted

ADDITIONAL ORDERING INFORMATION FOR MODEL 266DHH							XX	XX	XX	XX	XX	XX	XX
<b>Additional tag plate</b>													
Supplemental wired-on stainless steel plate							I1						
Tag and certification stainless steel plates and laser printing of tag							I2						
Tag, certification and supplemental wired-on stainless steel plates and laser printing of tag							I3						
<b>Configuration</b>													
Standard – Pressure = inH2O/ psi at 68 °F; Temperature = deg. F							N2						
Standard – Pressure = inH2O/ psi at 39.2 °F; Temperature = deg. F							N3						
Standard – Pressure = inH2O/ psi at 20 °C; Temperature = deg. C							N4						
Standard – Pressure = inH2O/ psi at 4 °C; Temperature = deg. C							N5						
Custom							N6						
<b>Certificates (multiple selection allowed)</b>													
Inspection certificate EN 10204–3.1 of calibration (9-point)									C1				
Inspection certificate EN 10204–3.1 of helium leakage test of the sensor module									C4				
Inspection certificate EN 10204–3.1 of the pressure test									C5				
Certificate of compliance with the order EN 10204–2.1 of instrument design									C6				
Printed record of configured data of transmitter									CG				
PMI test of wetted parts									CT				
<b>Approvals</b>													
GOST (Russia) Metrologic Pattern (NOT APPLICABLE WITH ANY HAZARDOUS AREA CERTIFICATION)									Y1				
GOST (Kazakhstan) Metrologic Pattern (NOT APPLICABLE WITH ANY HAZARDOUS AREA CERTIFICATION)									Y2				
GOST (Belarus) Metrologic Pattern (NOT APPLICABLE WITH ANY HAZARDOUS AREA CERTIFICATION)									Y4				
Chinese pattern (NOT APPLICABLE WITH ANY HAZARDOUS AREA CERTIFICATION)									Y5				
DNV approval (Notes 13, 15)										YA			
Approval for Custody transfer (PENDING)										YC			
Conformity to NAMUR NE 021 (2004) (NOT APPLICABLE WITH SURGE PROTECTOR CODE "S2") (Notes 13, 15, 17, 19)										YE			
<b>Material traceability</b>													
Certificate of compliance with the order EN 10204–2.1 of process wetted parts											H1		
Inspection certificate EN 10204–3.1 of process wetted parts											H3		
Test report EN 10204–2.2 of pressure bearing and process wetted parts											H4		
<b>Connector</b>													
Fieldbus 7/8 in. (Recommended for FOUNDATION Fieldbus) - (supplied loose without mating female plug)									(Notes 7, 12, 15)		U1		
Fieldbus M12x1 (Recommended for PROFIBUS PA) - (supplied loose without mating female plug)									(Notes 7, 12, 15)		U2		
Harting Han 8D – straight entry - (supplied loose)									(Notes 6, 12, 15)		U3		
Harting Han 8D – angle entry - (supplied loose)									(Notes 6, 12, 15)		U4		

Note 1: Not available with EN mounting flange code M, N, L

Note 2: Not available with ASME mounting flange code A, B, D, E

Note 3: Suitable for oxygen service

Note 4: Not available with diaphragm material/fill fluid code S, A, L

Note 5: Select type in additional ordering code

Note 6: Not available with Housing code G, Z, W, F

Note 7: Not available with Housing code E, K

Note 8: Not available with Process flanges/adapters code D, E, G, H

Note 9: Not available with Process flanges/adapters code A, B, G, H

Note 10: Not available with Process flanges/adapters code A, B, D, E

Note 11: Not available with Housing code J, K, W

Note 12: Not available with Housing code A, B, S, T, J

Note 13: Not available with Output code 7

Note 14: Not available with Housing code A, E, G, S, Z, C, F, J, K, W

Note 15: Not available with Output code 9, W

Note 16: Not available with Output code 1, 2, 3, 7, 8

Note 17: Not available with Output code 2, 3

Note 18: Not available with Hazardous area certification code EY, EZ, ES, EQ, EP, W1, W2, WC, W3, W4, WD, W5, W6, W7, W8, WF, WG, WH, WM, WN, WP

Note 19: Not available with Hazardous area certification code EW, EN, E4, E6, EA, EB, EC, EY, EZ, ES, EQ, EP, W1, W2, WC, W3, W4, WD, W5, W6, W7, W8, WF, WG, WH, WM, WN, WP

### **Standard delivery items (can be differently specified by additional ordering code)**

- Adapters supplied loose
- Plug on axis of horizontal connection flange;
- General purpose (no electrical certification)
- No display, no mounting bracket, no surge protection
- Multilanguage short-form operating instruction manual and labels in english (metal nameplate; self-adhesive certification and tag)
- Configuration with kPa and deg. C units
- No test, inspection or material traceability certificates

### **IMPORTANT REMARK FOR ALL MODELS**

THE SELECTION OF SUITABLE WETTED PARTS AND FILLING FLUID FOR COMPATIBILITY WITH THE PROCESS MEDIA IS A CUSTOMER'S RESPONSIBILITY, IF NOT OTHERWISE NOTIFIED BEFORE MANUFACTURING.

### **NACE COMPLIANCE INFORMATION**

- (1) The materials of constructions comply with metallurgical recommendations of NACE MR0175/ISO 15156 for sour oil field production environments. As specific environmental limits may apply to certain materials, please consult latest standard for further details. AISI 316/316 L, Hastelloy C-276, Monel 400 also conform to NACE MR0103 for sour refining environments.
  - (2) NACE MR-01-75 addresses bolting requirements in two classes:
    - Exposed bolts: bolts directly exposed to the sour environment or buried, encapsulated or anyway not exposed to atmosphere
    - Non exposed bolts: the bolting must not be directly exposed to sour environments and must be directly exposed to the atmosphere at all times.
- 266DHH bolting identified by "NACE" are in compliance with requirements of NACE MR0175 when considered "exposed bolting".

® Hastelloy is a registered trademark of Haynes International  
® Monel is a registered trademark of Special Metals Corporation  
® Viton is a registered trademark of E.I. DuPont de Nemour  
® Galden is a registered trademark of Solvay Group  
® Halocarbon is a registered trademark of Halocarbon Products Co.  
® HART and WirelessHART are registered trademarks of HART Communication Foundation  
® PROFIBUS is a registered trademark of Profibus International  
™ FOUNDATION Fieldbus is a trademark of Fieldbus Foundation

# Contact us

## **ABB Ltd.**

### **Process Automation**

Howard Road  
St. Neots  
Cambridgeshire PE19 8EU  
UK  
Tel: +44 (0)1480 475321  
Fax: +44 (0)1480 217948

## **ABB Inc.**

### **Process Automation**

125 E. County Line Road  
Warminster  
PA 18974  
USA  
Tel: +1 215 674 6000  
Fax: +1 215 674 7183

## **ABB Automation Products GmbH**

### **Process Automation**

Schillerstr. 72  
32425 Minden  
Germany  
Tel: +49 551 905 534  
Fax: +49 551 905 555

## **ABB S.p.A.**

### **Process Automation**

Via Luigi Vaccani 4  
22016 Tremezzina (CO)  
Italy  
Tel: +39 0344 58111

**[www.abb.com](http://www.abb.com)**

## **Note**

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents - in whole or in parts - is forbidden without prior written consent of ABB.

Copyright© 2016 ABB  
All rights reserved

3KXP300009R1001



Sales



Service



Software