

ABB MEASUREMENT & ANALYTICS | DATA SHEET

SensyTemp TSP300-W WirelessHART

Temperature sensor with Energy Harvester



Measurement made easy

Autonomous wireless temperature measurement

Powered by process temperature

Backup via standard lithium battery with long service life

Fast and easy commissioning

No battery replacement necessary with optimum operation

Intuitive and intelligent operating concept

**Configuration on the temperature sensor itself
Without external power supply**

Heavy duty model for harsh process operation

WirelessHART (IEC 62591)

Approvals

- ATEX
- IECEx

Introduction

Autonomous temperature measurement

In the past, temperature measurement devices always required cables to supply power and transmit signals. The cabling was often very laborious, taking up a lot of time and incurring high costs, particularly if larger distances had to be covered, disturbances circumvented, and safety aspects considered.

The costs for the cabling often exceeded the costs of the measuring device itself, which ultimately led to temperatures not being measured at all. This meant accepting compromises in terms of optimum process control.

The introduction of wireless signal transmission brought about a reduction in the costs of cabling. Nevertheless, a cable connection was still required to supply power to the measuring device.

Battery operation is a possible alternative. However, maintenance intervals for battery replacement must be strictly observed to guarantee fully functioning measurement.

The SensyTemp TSP300-W temperature sensors enable completely independent temperature measurement. There is no longer any need for cabling or battery replacement, and installation and maintenance costs are drastically reduced or even eliminated completely. No additional external energy is needed, and ensuring compliance with safety requirements is much easier. The result is an increase in system performance, improved effectiveness, and increased safety.



Figure 1: SensyTemp TSP300-W Temperature sensor

System structure

TSP temperature sensors are contact thermometers which, through contact with the measuring medium, are brought to the temperature of the medium.

The sensor is made up of modular components. The centerpiece is the measuring inset, which houses the actual sensor element for temperature measurement in its tip.

The thermowell surrounds the measuring inset and establishes the contact to the measuring medium. It ensures that the measuring inset can be replaced in a self-contained process and protects the inset against mechanical and corrosive influences of the process. The material and geometry of the thermowell must meet the process requirements (e.g. medium composition, measuring temperature, pressure).

The process connection is the mechanical interface between the process and the temperature sensor. The extension tube mounted on this interface creates the required distance to the connection head to protect it against overheating. The temperature gradient between the process temperature and the ambient temperature in the extension tube is converted into electrical energy by an Energy Harvester. An integrated micro-thermal generator (micro TEG) supplies the power for this. The electrical energy required is generated from the temperature difference between the process pipe and the ambient temperature by applying the Peltier effect. The micro TEG is therefore the ideal solution for using wireless WirelessHART temperature sensors as completely autonomous units in most processes.- Many processes involve sufficient process heat to enable a "complete power supply" by the micro TEG. A built-in high-performance battery buffers potential process-driven power failures of the micro TEG.

The adjustable connection head houses the transmitter electronics that convert the small output signal from the sensor elements into a WirelessHART signal.

... Introduction

Operating principle

Resistance thermometers and thermocouples are used as sensor elements.

Platinum has established itself as the resistance material in resistance thermometers due to its excellent chemical resistance and its characteristic curve quality.

Pt100 is used in most cases; a platinum resistance with 100 Ω at 0° C. The temperature coefficient α is 0.003851/K. Measuring ranges and accuracy classes are defined in IEC 60751.

There are two different Pt100 sensor element designs. Wire wound resistors (WW) consist of a bifilar wound platinum wire embedded in a ceramic capillary in ceramic powder. As the platinum wire is embedded flexibly in this design, there is almost no mechanical tension to restrict the measuring range. Measurements of -196 to 600 °C (-320.8 to 1112 °F) are possible, although this design is relatively sensitive to external mechanical influences.




Figure 2: Wire wound resistor (WW)

In thin film resistors (TF), a ceramic substrate is sputtered with platinum. The resistance wire is then sealed with a glass coating. As the platinum layer is permanently bonded with the substrate here, the measuring range for the most common types is -50 to 400 °C (-58 to 752 °F) due to material tensions. Thin film sensors are very small and light. They are particularly resistant to external mechanical influences and can be installed in very short temperature-sensitive lengths.



Figure 3: Thin film resistor (TF)

Thermocouples use the Seebeck effect. This creates thermal voltages dependent on two different, conductive alloys at different temperatures.

The level of the thermal voltage depends on the alloy combination and the temperature difference of the connection points.

Various types of thermocouples cover a measuring range of 0 to 1100 °C (32 to 2012 °F) for industrial thermocouples.

IEC 60584 describes both the characteristic curves and the accuracy classes of the most common types. In the USA, ANSI MC96.1, which is very similar, is used.

Thermocouples are extremely stable from a mechanical perspective and in an optimized design, have very short response times. However, resistance sensors provide greater accuracy.



Figure 4: Thermocouple

General information

As contact thermometers have to be brought to the temperature of the measuring medium, correct installation is particularly important for the quality of the measurement. The best results with regard to accuracy and response time are achieved when the sensor element is located at the point of the greatest medium velocity, i.e. the center of the pipe. To eliminate heat conduction errors to the greatest extent possible, the immersion depth must be 10 to 15 times the thermowell diameter.- Heat conduction errors arise when the ambient temperature reaches the sensor element via the thermowell.

The sensor built in to the tip of the thermowell should be as evenly bathed in medium as possible.

Installation positions 2 and 3: The thermowells are therefore usually installed at a 90° angle.- The thermowell tip, i.e. the sensor, should be in the middle of the pipe.

Installation positions 1 and 5: To meet the requirement for central installation of the sensor, thermowells can also be installed in elbow pipes vertically or at an obtuse angle to the flow direction.

Installation position 4: Indirect measurement of the medium temperature via the pipe surface is a further option in addition to immersion measurement. Indirect measurement is somewhat less accurate than measurement in the pipe. Pipe wall thickness, pipe material and other parameters can influence the measuring result.

For surface measurement, ensure optimum contact between the sensor element and the surface and that the sensor element is insulated against the ambient temperature by means of suitable insulating material.

In conjunction with an Energy Harvester, the temperature sensor is completely location-independent within its range in this measuring method as neither wiring nor difficult to install welded spuds are required.





Figure 5: Installation positions

Types of temperature sensor – overview

| Type | TSP311-W | TSP321-W | TSP331-W | TSP341-W |
|--------------------|--|---|---|---|
| |  |  |  |  |
| Energy Harvester | ● | — | ● | ● |
| LCD indicator | ● | ● | ● | ● |
| Design | Measuring inset, thermowell, extension tube with thermowell connection, process connection, connection head, WirelessHART electronics- | | | |
| Process connection | For installation in an existing thermowell | Screw-in thread, flange, weld-in socket, compression fitting | Screw-in thread, flange, weld-in socket | Surface mounting |
| Thermowell | without | Welded | Drilled | without |

Built-in sensors – specifications

Temperature ranges and pressure limits

| Designs, materials, ranges, limit values | | |
|--|--|---|
| Storage / transportation temperature | -50 bis 85 °C (-58 bis 185 °F) | |
| Process | In the process, the values specified generally deviate significantly downwards due to the influence of viscosity, medium velocity, pressure and temperature. | |
| Resistance thermometer Pt100 | Thin film resistor (TF) | -50 to 400 °C (-58 to 752 °F) |
| | Wire wound resistor (WW) | -196 to 600 °C (-320.8 to 1112 °F) |
| Thermocouples | Type K | -40 to 1200 °C (-40 to 2192 °F) |
| | Type N | -40 to 1200 °C (-40 to 2192 °F) |
| | Type J | -40 to 750 °C (-40 to 1382 °F) |
| | Type E | -40 to 950 °C (-40 to 1742 °F) |
| Thermowell materials | 1.4404 / 316L | -196 to 600 °C (-320.8 to 1112 °F) |
| | 1.4571 / 316Ti | -196 to 800 °C (-320.8 to 1472 °F) |
| | 2.4819 / Hastelloy C 276 | 0 to 1100 °C (32 to 2012 °F) |
| | 2.4816 / Inconel 600 | 0 to 1100 °C (32 to 2012 °F) |
| | 2.4360 / Monel 400 | 0 to 550 °C (32 to 1022 °F) |
| | 1.0460 / C22.8 | 0 to 1100 °C (32 to 2012 °F) |
| | 1.4876 / Incoloy 800 | 0 to 1100 °C (32 to 2012 °F) |
| | 1.4539 | 0 to 1100 °C (32 to 2012 °F) |
| | 1.7335 | 0 to 540 °C (32 to 1004 °F) |
| | 1.7380 | 0 to 570 °C (32 to 1058 °F) |
| for stainless steel thermowells with coating | ECTFE coating | 0 to 120 °C (32 to 248 °F) |
| | Tantalum coating | 0 to 200 °C (32 to 392 °F) |
| Designation of gas connections | Tubular thermowells | 40 bar (4 MPa) (580 psi) |
| | Drilled thermowells | 700 bar (70 MPa) (10152 psi) or in accordance with calculation by ABB* |

* ABB performs thermowell calculations in accordance with ASME PTC 19.3 / TW 2010 or in accordance with the calculation method (Dittrich / Kohler) often required in central Europe. This requires the specification of the maximum flow velocity of the measuring medium (m/s), the density (kg/m³), the process temperature (°C), and the process pressure (bar). The thermowell dimensions (mm) required are the installation length, tip diameter, bore diameter and the desired material.

... Built-in sensors – specifications

Measuring inset




Figure 6: Measuring inset

| Design | |
|-------------------------|---|
| Dimensions*** | for type 311-W: $M = U + K + 25 \text{ mm}$ (0.984 in)* for type 321-W: $M = N + 25 \text{ mm}$ (0.984 in) for type 331-W: $M = L + K + 25 \text{ mm}$ (0.984 in)* |
| Outer diameter | 3 mm, 6 mm** |
| Design | Open connection wires; Single or double sensor |
| Mineral-insulated cable | Bendable and vibration-resistant ABB mineral insulated cable. Sheath material for resistance thermometers made from stainless steel 1.4571 / 316Ti or highly heat-resistant steel 2.4816 / Inconel 600 for thermocouples.- |

* With Energy Harvester: $K = 241 \text{ mm}$ (9.488 in)

** Not with the Energy Harvester

*** The dimensions K, L, N and U are described on the following pages (thermowells, extension tubes)

Response times

The thermowell used in each application and the thermal contact between the thermowell and measuring inset have an impact on the response times of TSP temperature sensors. In the case of TSP321-W and TSP331-W temperature sensors, the design of the thermowell tip has been adapted to the measuring inset.

This maximizes heat transmission. The following table shows typical response times for types TSP321-W and TSP331-W measured in accordance with IEC 60751 in water at 0.4 m/s and temperature increase from 25 °C (77 °F) to 35 °C (95 °F).

| Sensor element | Exterior Ø [mm] | $t_{0.5}$ [s] | $t_{0.9}$ [s] |
|---|-----------------|---------------|---------------|
| Single Pt100 / 4 L resistance thermometer-- | 6 | 4 | 10 |
| Double type K thermocouple- | 3 | 0.8 | 2.1 |

Sensor element – resistance thermometer

Specifications and designs

| Measuring insets with resistance thermometers | | | | | Single Pt100 | | | | Double Pt100 | | | | | |
|---|-------------------------------|------------|------------|-------|--------------|-----|-----|-----|--------------|-----|-----|-----|-----|-----|
| Sensor | Maximum vibration sensitivity | TSL | nBL | Class | 2-W | | 3-W | | 4-W | | 2-W | | 3-W | |
| | | | | | Ø 3 | Ø 6 | Ø 3 | Ø 6 | Ø 3 | Ø 6 | Ø 3 | Ø 6 | Ø 3 | Ø 6 |
| TF | 100 m/sec ² (10 g) | 7 (0.276) | 30 (1.181) | B | . | . | . | . | . | . | . | . | . | . |
| | | | | A | . | . | . | . | . | . | . | . | . | . |
| | | | | AA | . | . | . | . | . | . | . | . | . | . |
| | 600 m/sec ² (60 g) | 10 (0.394) | 40 (1.575) | B | . | . | . | . | . | . | . | . | . | |
| | | | | A | . | . | . | . | . | . | . | . | . | |
| WW | 30 m/sec ² (3 g) | 50 (1.968) | 60 (2.362) | B | . | . | . | . | . | . | . | . | . | |
| | | | | A | . | . | . | . | . | . | . | . | . | |
| | 100 m/sec ² (10 g) | B | . | . | . | . | . | . | . | . | . | . | . | |
| | | A | . | . | . | . | . | . | . | . | . | . | | |

TSL = temperature-sensitive length in mm (in)

nBL = non-bendable length in mm (in)

Ø 3 / Ø 6 = measuring inset diameter in mm (in)

TF = thin film resistor

WW = wire wound resistor

2-W / 3-W / 4-W = two-, three-, or four-wire circuit

Accuracy classes in accordance with IEC 60751

| Resistance thermometer | Class | Measuring range | Calculation of the measuring error |
|---|-------|------------------------------------|-------------------------------------|
| In accordance Thin film resistor (TF) with IEC 60751 | B | -50 to 400 °C (-58 to 752 °F) | $\Delta t = \pm (0.30 + 0.0050 t)$ |
| | A | -30 to 300 °C (-22 to 572 °F) | $\Delta t = \pm (0.15 + 0.0020 t)$ |
| | AA | 0 to 100 °C (32 to 212 °F) | $\Delta t = \pm (0.10 + 0.0017 t)$ |
| Wire wound resistor (WW) | B | -196 to 600 °C (-320.8 to 1112 °F) | $\Delta t = \pm (0.30 + 0.0050 t)$ |
| | A | -196 to 500 °C (-320.8 to 932 °F) | $\Delta t = \pm (0.15 + 0.0020 t)$ |

|t| = insert required temperature value as an amount

Thermocouples

Specifications and designs

| Measuring insets with thermocouples | | | | | Single thermocouple | | | | Double thermocouple | | | | | | | |
|-------------------------------------|-------------------------------|-----------|------------|----------|---------------------|-----|-----|-----|---------------------|-----|-----|-----|-----|-----|-----|-----|
| Standard | Maximum vibration sensitivity | TSL | nBL | Class | K | | J | | N | | K | | J | | N | |
| | | | | | Ø 3 | Ø 6 | Ø 3 | Ø 6 | Ø 3 | Ø 6 | Ø 3 | Ø 6 | Ø 3 | Ø 6 | Ø 3 | Ø 6 |
| IEC 60584 | 600 m/sec ² (60 g) | 7 (0,276) | 30 (1,181) | 2 | . | . | . | . | . | . | . | . | . | . | . | . |
| | | | | 1 | . | . | . | . | . | . | . | . | . | . | . | . |
| ANSI MC 96.1 | | | | Standard | . | . | . | . | . | . | . | . | . | . | . | . |
| | | | | Special | . | . | . | . | . | . | . | . | . | . | . | . |

TSL = temperature-sensitive length in mm (in)

nBL = non-bendable length in mm (in)

Ø 3 (0.118) / Ø 6 (0.236) = measuring inset diameter in mm (in)

... Built-in sensors – specifications





Accuracy classes in accordance with IEC 60584 and ANSI MC 96.1





| Thermocouple | Class | Measuring range | Calculation of the measuring error | |
|---------------------------------|----------------------|----------------------------------|------------------------------------|-----------------|
| In accordance with IEC 60584 | Type K (NiCr–Ni) | 2 | –40 to 333 °C (–40 to 631.4 °F) | ±2.5 °C (77 °F) |
| | | | 333 to 1200 °C (–631.4 to 2192 °F) | ±0.0075 x t |
| | 1 | | –40 to 375 °C (–40 to 707 °F) | ±1.5 °C |
| | | | 375 to 1000 °C (–707 to 1832 °F) | ±0.0040 x t |
| | Type J (Fe–CuNi) | 2 | –40 to 333 °C (–40 to 631.4 °F) | ±2.5 °C |
| | | | 333 to 700 °C (–631.4 to 1292 °F) | ±0.0075 x t |
| | 1 | | –40 to 375 °C (–40 to 707 °F) | ±1.5 °C |
| | | | 375 to 750 °C (–707 to 1382 °F) | ±0.0040 x t |
| | Type N (NiCrSi–NiSi) | 2 | –40 to 333 °C (–40 to 631.4 °F) | ±2.5 °C |
| | | | 333 to 1200 °C (631.4 to 2192 °F) | ±0.0075 x t |
| | 1 | | –40 to 375 °C (–40 to 707 °F) | ±1.5 °C |
| | | | 375 to 1200 °C (–707 to 2192 °F) | ±0.0040 x t |
| Type E (NiCr–CuNi) | 2 | –40 to 333 °C (–40 to 631.4 °F) | ±2.5 °C | |
| | | 333 to 900 °C (631.4 to 1652 °F) | ±0.0075 x t | |
| 1 | | –40 to 375 °C (–40 to 707 °F) | ±1.5 °C | |
| | | 375 to 800 °C (–707 to 1472 °F) | ±0.0040 x t | |
| In accordance with ANSI MC 96.1 | Type K (NiCr–Ni) | Standard | 0 to 293 °C (32 to 559.4 °F) | ±2.2 °C |
| | | | 293 to 1250 °C (559.4 to 2282 °F) | ±0.0075 x t |
| | Special | | 0 to 275 °C (32 to 527 °F) | ±1.1 °C |
| | | | 275 to 1250 °C (527 to 2282 °F) | ±0.0040 x t |
| | Type J (Fe–CuNi) | Standard | 0 to 293 °C (32 to 559.4 °F) | ±2.2 °C |
| | | | 293 to 750 °C (559.4 to 1382 °F) | ±0.0075 x t |
| | Special | | 0 to 275 °C (32 to 527 °F) | ±1.1 °C |
| | | | 275 to 750 °C (527 to 1382 °F) | ±0.0040 x t |
| | Type N (NiCrSi–NiSi) | Standard | 0 to 293 °C (32 to 559.4 °F) | ±2.2 °C |
| | | | 293 to 1250 °C (559.4 to 2282 °F) | ±0.0075 x t |
| | Special | | 0 to 275 °C (32 to 527 °F) | ±1.1 °C |
| | | | 275 to 1250 °C (527 to 2282 °F) | ±0.0040 x t |
| Type E (NiCr–CuNi) | Standard | 0 to 293 °C (32 to 559.4 °F) | ±2.2 °C | |
| | | 293 to 900 °C (559.4 to 1652 °F) | ±0.0075 x t | |
| Special | | 0 to 275 °C (32 to 527 °F) | ±1.1 °C | |
| | | 275 to 800 °C (527 to 1472 °F) | ±0.0040 x t | |

|t| = insert required temperature value as a value




Thermowells

Type TSP321-W welded thermowells

| Straight shaft | DIN 43772 – form 2 | DIN 43772 – form 2G | DIN 43772 – form 2F |
|---|---|--|---|
| | M24 x 1.5 head connection | | |
|  |  |  |  |
| 1.4571/316Ti | F1 = 12, 14 mm | F1 = 12, 14 mm | F1 = 12, 14 mm |
| 1.4404/316L | F1 = 12, 14 mm | F1 = 12, 14 mm | F1 = 12, 14 mm |
| 2.4819/C-276 | - | F1 = 13.7 mm* | F1 = 13.7 mm* |
| Measuring inset | Ø 6 mm, tip 8 | Ø 6 mm, tip 8 | Ø 6 mm, tip 8 |

| Tapered tip* | DIN 43772 – form 3 | DIN 43772 – form 3G | DIN 43772 – form 3F |
|---|---|--|---|
| | M24 x 1.5 head connection | | |
|  |  |  |  |
| 1.4571/316Ti | F1/F3 = 12/9 mm | F1/F3 = 12/9 mm | F1/F3 = 12/9 mm |
| 1.4404/316L | F1/F3 = 12/9 mm | F1/F3 = 12/9 mm | F1/F3 = 12/9 mm |
| Measuring inset | Ø 6 mm | Ø 6 mm | Ø 6 mm |

... Built-in sensors – specifications




| Stepped tip | ABB – form 2S | ABB – form 2GS | ABB – form 2FS |
|---|---|--|---|
| M24 x 1.5 head connection | | | |
|  |  |  |  |
| 1.4571/316Ti | F1/F3 = 14/6 mm | F1/F3 = 14/6 mm | F1/F3 = 14/6 mm |
| 1.4404/316L | F1/F3 = 12/6 mm | F1/F3 = 12/6 mm | F1/F3 = 12/6 mm |
| 2.4819/C-276 | - | F1/F3 = 13.7/6 mm* | F1/F3 = 13.7/6 mm** |
| Measuring inset | Ø 3 mm | Ø 3 mm | Ø 3 mm |




* Only with G½ in A, ½ in NPT thread

** Flange 1.4571/316Ti, flange disc 2.4819/C-276

Other diameters and materials available on request.




Type TSP321-W drilled thermowells

| Weld-in thermowell | DIN 43772 – form 4 | DIN 43772 – form 4 | ABB – form PW | | | | |
|---------------------------|---|--|---|-----------|--------|---------------|------|
| Extension tube connection | M18 x 1.5 | M14 x 1.5 | ½ in NPT | | | | |
| |  |  |  | | | | |
| Material | 1.4404/316L; 1.4571/316Ti; 1.7335/13CrMo4-5; 1.5415/15Mo3 1.4876/Incoloy® 800; 2.4360/Monel® 400 2.4816/Inconel® 600; 2.4819/C-276 | | | | | | |
| F3/F2/F1 | d1 | 24h7/12.5 mm | 7 mm | 18h7/9 mm | 3.5 mm | 32/23/13.5 mm | 7 mm |
| Measuring inset | | Ø 6 mm | | Ø 3 mm | | Ø 6 mm | |

| Flange thermowell | DIN 43772 – form 4F | DIN 43772 – form 4FS | ABB – form PF | | | | |
|---------------------------|---|--|---|---------|--------|---------------|------|
| Extension tube connection | M18 x 1.5 | M14 x 1.5 | ½ in NPT | | | | |
| |  |  |  | | | | |
| Material | 1.4404/316L; 1.4571/316Ti 1.4404/316L; 1.4571/316Ti 1.4876/Incoloy® 800; 2.4360/Monel® 400* 2.4816/Inconel® 600; 2.4819/C-276* | | | | | | |
| F3/F2/F1 | d1 | 24/12.5 mm | 7 mm | 18/9 mm | 3.5 mm | 32/23/13.5 mm | 7 mm |
| Measuring inset | | Ø 6 mm | | Ø 3 mm | | Ø 6 mm | |

* 1.4876/Incoloy® 800; 2.4360/Monel® 400; 2.4816/Inconel® 600; 2.4819/C-276 with flange in 1.4571/316Ti and flange disc

... Built-in sensors – specifications

| Screw-in thermowell | ABB – form PS | ABB – form PS | ABB – form PS | | | | |
|---------------------------|--|--|---|------------|------|------------|------|
| Extension tube connection | ½ in NPT; WAF 36 | ½ in NPT; WAF 27 | ½ in NPT; WAF 27 | | | | |
| |  |  |  | | | | |
| Material | 1.4404/316L; 1.4571/316Ti; 1.4876/Incoloy® 800; 2.4360/Monel® 400; 2.4816/Inconel® 600; 2.4819/C-276 | | | | | | |
| F3/F1 | d1 | 25/16 mm | 7 mm | 20/13.5 mm | 7 mm | 17/13.5 mm | 7 mm |
| Measuring inset | | Ø 6 mm | | Ø 6 mm | | Ø 6 mm | |

Other diameters and materials available on request.

Standard lengths

| Welded thermowells mm (in.) | | |
|------------------------------|---|-------------------|
| Form | N = 230 (9.055) | U = 100 (3.94) |
| 2; 2G; 2F, | N = 290 (11.42) | U = 160 (6.30) |
| 3; 3G; 3F; | N = 380 (14.96) | U = 250 (9.84) |
| 2S; 2GS; 2FS | N = 530 (20.87) | U = 400 (15.75) |
| Drilled thermowells mm (in.) | | |
| Form 4 | L = 140 (5.51) | C = 65 (2.56) |
| | L = 200 (7.87) | C = 65 (2.56) |
| | L = 200 (7.87) | C = 125 (4.92) |
| | L = 260 (10.24) | C = 125 (4.92) |
| | L = 410 (16.14) | C = 275 (10.83) |
| Form 4S | L = 110 (4.33) | C = 65 (2.65) |
| | L = 140 (5.51) | C = 65 (2.65) |
| Form PW; | U = 100 (3.94), 150 (5.91), | L = U + 65 (2.56) |
| PF; PS | 200 (7.87), 250 (9.84), 300 (11.81), 350 (13.78) | |
| Form 4F | U = 130 (5.12), L = 200 (7.87) | C = 65 (2.56) |
| | U = 190 (7.48), L = 260 (10.24) | C = 125 (4.92) |
| | U = 340 (13.39), L = 410 (16.14) | C = 275 (10.83) |
| Form 4FS | U = 130 (5.12), L = 200 (7.87) | C = 65 (2.65) |

Special installation conditions for thermowells

For aggressive media, a flange thermowell made from stainless steel can be provided with an effective coating, for example ECTFE 0.5 mm.--

For highly corrosive measuring media, additional protection can also be provided in the form of a tantalum coating for flange thermowells Form 2F or 3F, outside diameter 12 mm, material 1.4571/316Ti or 1.4404/316L.

If required, contact your ABB partner.

Process connections

For welded and drilled thermowells

| Design | Sliding connection | |
|--|---|---|
| TSP321-W, plug-in thermowells, welded | G½ in A, ½ in NPT | |
| DIN 43772 – form 2, straight shaft | | |
| DIN 43772 – form 3, tapered tip | | |
| ABB – form 2S, stepped tip | | |
| Design | Fixed connection | |
| TSP321-W, screw-in thermowells, welded | G½ in A, G¾ in A, G1 in A, ½ in NPT, ¾ in NPT, 1 in NPT | |
| DIN 43772 – form 2G, straight shaft | M20 × 1,5, M27 × 1,5 | |
| DIN 43772 – form 3G, tapered tip | | |
| ABB – form 2GS, stepped tip | | |
| TSP331-W, screw-in thermowells, drilled | ½ in NPT, ¾ in NPT, 1 in NPT | |
| ABB – form PS | | |
| Design | Flange in accordance with EN 1092-1 | Flange in accordance with ASME B16.5 TW |
| TSP321-W, flange thermowells, welded | Form B1 sealing surface, | Form RF sealing surface, |
| DIN 43772 – form 2F, straight shaft | Form C or D optional | Form RTJ optional |
| DIN 43772 – form 3F, tapered tip | DN 15, DN 20, DN 25, DN 40, DN 50 | Nominal diameter 1 in, 1 ½ in, 2 in |
| ABB – form 2FS, stepped tip | each PN 10 to PN 40 | Nominal pressure 150 #, 300 #, 600 # |
| TSP331-W, flange thermowells, drilled | | |
| DIN 43772 – form 4F, F3 = 24 mm and 18 mm | | |
| ABB – form PF | | |

... Built-in sensors – specifications


Extension tubes

For types TSP311, TSP331

The extension tube is the component between thermowell and connection head. It is used to bridge any existing insulation or serves as a cooling section between the temperature-sensitive electronics in the connection head and the actual process. Extension tubes for thermometers without a harvester have a standard length K of 150 mm (5.906 in). For extension tubes with an Energy Harvester, the extension tube length K = 241 mm (9.488 in).

Extension tube spacer

Extension tube spacers (maximum 4 spacers, 25 mm in length) enable the device to be used at higher process temperatures. The spacers reduce the overtemperature of the connection head and the temperature at the micro TEG (see also the specifications for the Energy Harvester).



- (A) Overtemperature at the connection head compared to the ambient temperature
- (B) Extension tube length
- (T) Flange temperature

Figure 7: Flange temperature

Specifications

| | Cylindrical screw-in thread | Conical screw-in thread | ½ in NPT – ½ in NPT separable (nipple-union) | ½ in NPT – ½ in NPT separable (nipple-union-nipple) | Energy Harvester |
|-----------------------|---------------------------------------|-------------------------|--|---|-----------------------------|
| Head connection | M24 × 1.5 | M24 × 1.5 | ½ in NPT | ½ in NPT | M24 × 1.5 |
| | | | | | |
| Thermowell connection | M14 × 1.5; M18 × 1.5; M20 × 1.5; G1/2 | ½ in NPT | ½ in NPT | ½ in NPT | ½ in NPT; M18 × 1.5 |
| Material | | | | 1.4571/316Ti | 1.4404/316L 1.4571/316Ti |

Surface sensors

TSP341-W type design

Sensor mounting 90° to the piping

Design for simple surface mounting. A retaining board is mounted on the process side of the extension tube. The SensyTemp TSP341-W can be fastened to the surface using two tension clips.

With Energy Harvester

Adapters for fastening between the extension tube and retaining board can be selected to enable the Energy Harvester to be used at high surface temperatures. Minimum temperature difference of +35 K between the temperature at the process pipe and the environment.

Specification

Thermal insulation of the sensor at the tube surface is mandatory.

Stainless steel clamp collars for DN 150 to DN 500 (6 to 20 in)

Measuring range: -196 to 600 °C (-320 to 1112 °F)

Limited temperature range if the Energy Harvester is used (see also the Energy Harvester specifications).

Sensor elements: see Built-in temperature sensors

Sensor mounting alongside the piping

Design for surface mounting with adjustable and vibration-resistant fastening. A retaining board is welded to the surface of the pipe or tank conveying the medium. The attachment is screwed on using a 60° angle plate fixed to the thermometer. This tilts the temperature sensor by 30°. The tip of the measuring inset with the sensor is fastened to the process pipe using two clamp collars.

Specification

Thermal insulation of the sensor at the tube surface is mandatory.

Stainless steel clamp collars for DN 150 to DN 500 (6 to 20 in)

Measuring range: -196 to 600 °C (-320 to 1112 °F)

Limited temperature range if the Energy Harvester is used (see also the Energy Harvester specifications).

Sensor elements: see Built-in temperature sensors

Measuring inset length M: 400 mm (15.748 in)

Retaining board material: 1.4571/316Ti, 1.4404/316L or process-specific material

Dimensions mm (in)




Figure 8: Sensor fastening 90° to piping / alongside piping

Connection head

The connection head holds and protects the measurement and sender electronics and the battery required for these electronics. An LCD indicator can be installed as an option. The antenna and head can be rotated. This enables optimum transmission characteristics to be set.

Specification

- Ambient temperature -40 to 85 °C (-40 to 185 °F)
- optional -50 to 85 °C (-58 to 185 °F)
(restricted range during operation with LCD indicator or with explosion-proof design)

Electrical connections

- Spring cage terminals
- Connection leads up to max. 1.5 mm² (AWG 16)

Material

- Aluminum, epoxy-coated
- Stainless steel

Color

- gray RAL 9002

IP rating

- IP 66 / IP 67

Dimensions





Figure 9: Dimensions mm (in)

Electrical connections



- ① - ⑥ Sensor connection (of the measuring inset)
- Ⓐ DIP switch, hardware write protection
- Ⓑ DIP switch standby mode
- Ⓒ LCD indicator connection

- Ⓓ HART Maintenance Port (handheld terminal)
- Ⓔ Sensor 1
- Ⓕ Sensor 2

Figure 10: Electrical connections (opened connection head)

Transmitter

Specification

Electromagnetic compatibility

Interference immunity in accordance with IEC/EN 61326-1 (industrial environment, influence < 1%)

Vibration resistance in accordance with IEC 60068-2-6

10 to 60 Hz 0.21 mm / 60 to 2000 Hz 3g

Humidity in accordance with IEC 60068-2-30

95 %

With integrated adjustable omnidirectional antenna

Coverage:

up to 300 m (328 yds)

Wireless refresh rate

- Standard 16 seconds
- Can be configured between 4 seconds and 60 minutes

Transmission protocol

WirelessHART® Version 7 (IEEE 802.15.4-2006)

Frequency band

2.4 GHz (ISM-band, license-free)

Transmission power: max. 10 mW (10 dBm) EIRP

Minimum distance between antenna and persons

0.2 m (8 in)

User-defined configuration of Network ID & Join Key through LCD indicator with button operation or through EDD or DTM.

Resistance thermometer input

Resistance thermometer

- Pt100 in accordance with IEC 60751

Sensor connection type

- Two-wire, three-wire, and four-wire circuits

Connection lead

- Maximum sensor line resistance of 50 Ω per line in accordance with NE 89
- Three-wire circuit: Symmetrical sensor line resistances
- Two-wire circuit: Compensation up to 100 Ω total lead resistance

Measurement current

< 300 μ A

Sensor short circuit

< 5 Ω (for resistance thermometer)

Sensor wire break

- Measuring range: 0 to 500 Ω > 0.6 to 10 k Ω

Corrosion detection in accordance with NE 89

- Three-wire resistance measurement > 50 Ω
- Four-wire resistance measurement > 50 Ω

Sensor error signaling

- Resistance thermometer: short-circuit and wire break

Thermocouple input

Types

K, J, N, E in accordance with IEC 60584, ANSI MC 96.1

Connection lead

- Maximum sensor line resistance 1.5 k Ω per lead

Sensor wire break monitoring in accordance with NE 89

- Pulsed with 1 μ A outside measurement interval
- Thermocouple measurement 5.3 to 10 k Ω

Input resistance

> 10 M Ω

Internal reference junction Pt1000, IEC 60751 Class B

Sensor error signaling

- Thermocouple: Wire break

Freestyle characteristic / 32-points-sampling point table

- Resistance measurement up to a maximum of 5 k Ω
- Voltages up to maximum 1.1 V

Sensor error adjustment

- Through Callendar-Van Dusen coefficients
- Through value table, 32 support points
- Through single-point adjustment (offset adjustment)
- Through two-point adjustment

Input functionality

- 1 Sensor
- 2 Sensors: mean measurement, differential measurement, sensor redundancy, Sensor drift monitoring

... Transmitter

Measuring accuracy

includes linearity error, repeatability / hysteresis at 23 °C (73.4 °F) ±5 K ambient temperature.
Information on measuring accuracy corresponds to 3 σ (Gaussian distribution).

| Sensor element | Measuring range limit | Minimum span | Digital measuring accuracy (24 bit AD conversion) |
|------------------------|-----------------------------------|---------------|--|
| Resistance thermometer | | | |
| Pt100 (a=0.003850) | -196 to 600 °C (-320 to 1112 °F) | 10 °C (18 °F) | ±0.08 °C (±0.14 °F) |
| Thermocouples | | | |
| Type K (Ni10Cr-Ni5) | -270 to 1372 °C (-454 to 2502 °F) | 50 °C (90 °F) | ±0.35 °C (±0.63 °F) |
| Type J (Fe-Cu45Ni) | -210 to 1200 °C (-346 to 2192 °F) | | |
| Type N (Ni14CrSi-NiSi) | -270 to 1300 °C (-454 to 2372 °F) | | |
| Type E (Ni10Cr-Cu45Ni) | -270 to 1000 °C (-454 to 1832 °F) | | |

Operating influence

| Sensor element | Ambient temperature effect* |
|----------------------------------|--|
| Pt100 (all connection types) | ±0.004 °C (±0.007 °F) |
| Thermocouple (all defined types) | $\pm[(0.001 \% \times (ME[mV] / MS[mv]) + (100 \% \times (0.009 \text{ °C} / MS [\text{°C}]))]^{**}, ^{***}$ |

* Per 1 °C (1.8 °F) deviation to 23 °C (73.4 °F) based on the digital measured value

** The percentages refer to the already set measuring span

*** ME = voltage value of the sensor at the upper range value in accordance with the standard

MA = voltage value of the sensor at lower range value in accordance with the standard

MS = voltage value of the thermocouple over the measuring span in accordance with the standard. MS = (ME - MA)

LCD indicator

In the connection head

For displaying measurement and status information

For on-site configuration

Automatic shutdown after 1 minute without activating the buttons (can be configured)

Manual reactivation via push buttons



Figure 11: LCD indicator

Communication

Configuration parameters

- Sensor type, activation type
- Error signaling
- Measuring range
- General information, e.g. TAG number
- Damping
- Warning and alarm thresholds
- Output signal simulation
- Burst refresh rate
- Burst commands
- Network ID
- Join key
- Software write protection

Diagnostic information in accordance with NE 107

Standard:

- Sensor error signalling
(wire break or short circuit)
- Device error
- Limit value up-scale / down-scale
- Measuring range up-scale / down-scale
- Simulation active

Advanced:

- Sensor redundancy / sensor backup active
(sensor failure)
- Drift monitoring
- Sensor / Sensor connection lead corrosion
- Drag indicator for Sensor 1, Sensor 2 and ambient temperature
- Ambient temperature up-scaled
- Ambient temperature down-scaled
- Operating hours counter
- Wireless interface error
- Connection status
- Battery status

WirelessHART

The device is listed with the FieldComm Group.

| | |
|-----------------|--|
| Manufacturer-ID | 0x1A |
| Device-ID | 0x9B |
| Profile | HART® 7.5 |
| Network ID | 0xABB (2747 dec.) |
| Join Key | 0x57495245 0x4c455353 0x4649454c 0x444b4559 |
| Configuration | On device using LCD indicator DTM EDD |

0x = hexadecimal

NOTICE

For data security reasons, we highly recommend that you change parameters Network ID and Join Key during commissioning.

Standard Burst Configuration

Burst message 1

| | |
|---------------|---|
| HART® command | 9 'device variables with status' PV, SV, TV, QV, battery life (days) |
| Update rate | 16 seconds |

Burst message 2

| | |
|---------------|-----------------------------|
| HART® command | 48 'extended device status' |
| Update rate | 32 seconds |

Power supply

Energy Harvester

Specification

The Energy Harvester is based on the thermoelectrical effect (Seebeck effect) and requires a temperature difference of 35 K between the process pipe surface and the ambient temperature in order to provide all the energy required for the transmitter and sender electronics.

However, an integrated power management system provides energy

if the temperature difference is less than 35 K. Only the remaining energy needed is taken from the integrated battery, thereby increasing its availability. The energy withdrawal is provided as a percentage value.

Operating temperature at the process connection


- -40 to 150 °C (-40 to 302 °F)
Adapters for fastening between the extension tube and thermowell can be selected to enable the Energy Harvester to be used at high process temperatures.

Threaded connection to the process

- M18 × 1.5 or ½ in NPT

Material

- 1.4404/316L



Battery

Standard lithium battery (lithium content 5 g)
Service life 5 years (without Energy Harvester) under the following

reference conditions:

25 °C (77 °F) ambient temperature

Update rate 16 s

3 additional network participants

LCD off

Wireless operation approvals

Telecommunications directive

Any device used for wireless applications must be certified in accordance with the telecommunications directives applicable for the operating location. This certification is country-specific. Before commissioning, you must make sure that local restrictions are complied with.

European directives

Radio Equipment Directive 2014/53/EU

Within Europe, use of the 2400 - 2483.5 MHz frequency band is not harmonized. Country-specific regulations must therefore be observed.

Restrictions for Norway

Operation not permitted within a radius of 20 km around Ny-Alesund in Svalbard. For more information, see www.npt.no, the Norway Posts and Telecommunications website.

USA / Canada directives

FCC Part 15.247:2009 (USA)

IC RSS-210 and ICES-003 (Canada)

Use in potentially explosive atmospheres in accordance with ATEX and IECEx

Note

- Further information on the approval of devices for use in potentially explosive atmospheres can be found in the explosion protection test certificates (at www.abb.com/wirelessmeasurement).
- Depending on the design, a specific marking in accordance with ATEX or IECEx applies.

Ex marking

Transmitter

Model TSP3x1-W-A6..., TSP3x1-W-H6...

(Temperature sensor with transmitter in zone 0, 1 or 2)

| ATEX | IECEx |
|---------------------------------------|----------------------------------|
| II 1 G Ex ia IIC T4...T1 Ga | Ex ia IIC T4...T1 Ga |
| Certificate no.: PTB 14 ATEX 2010X | Certificate no.: PTB 15.0009X |

- The transmitter and the connected temperature sensor may be used fully in zone 0, zone 1 or zone 2.
- The temperature range corresponds to the information in **Temperature data**

LCD indicator

The device is supplied with or without an LCD indicator (order option "Housing / Indicators").

The LCD indicator has the following certificates:

| ATEX | IECEx |
|---------------------------------------|--|
| Certificate no.: PTB 05 ATEX 2079X | Certificate no.: IECEx PTB 12.0028X |

Temperature data

For all TSP3x1-W versions there are two relevant parts of the Sensor with different temperature ranges:

- The permissible temperature range on the housing of the transmitter is -40 to 70 °C (-40 to 158 °F).
- The process temperature at the measuring point could be different, but the influence of the self-heating from the sensor, the temperature rise in the electronic and the temperature class/zone has to be taken into account.

Model TSP341-W-A6 / H6-Y22 and Y23

Models TSP341-W xx Y22 and Y23 (...) are designed for ambient temperatures of -40 to 70 °C (-40 to 158 °F) on the transmitter housing. The maximum process temperature must be specified for the respective temperature class and the respective design with consideration of a maximum temperature of 70 °C (158 °F) for the electronics and self-heating of the temperature sensor components mentioned above.




Figure 12: Temperature sensor fastening alongside the piping

| Number | Temperature |
|--------|---|
| (A) | T_{ambient} : -40 to 70 °C (-40 to 158 °F) |
| (B) | Surfacetemperature: Temperature class reduced by selfheating of the Sensor |

... Use in potentially explosive atmospheres in accordance with ATEX and IECEx

TSP3x1-W (X=1-3) and TSP341-W-Y11 with Energy Harvester





Figure 13: Temperature sensor fastening 90° to the piping with Energy Harvester

| Number | Temperature |
|--------|--|
| (A) | T_{ambient} : -40 °C to 70 °C (-40 to 158 °F) |
| (B) | <ul style="list-style-type: none"> The Energy Harvester is designed for a temperature range from -40 to 150 °C (-40 to 302°F). To guarantee intrinsic safety, a maximum temperature difference of 150 K is allowed at the Energy Harvester |
| (C) | TEG unit used: Maximum surface temperature 150 °C (302 °F) |
| (D) | T_{process} : -40 °C to 150 °C (-40 to 302°F) |

TSP3x1-W (X=1-3) and TSP341-W-Y11 without Energy Harvester



K Extension tube length

Figure 14: Temperature sensor with extension tube

| Number | Temperature |
|--------|---|
| (A) | Temperature region for the electronic: -40 °C to 70 °C (-40 to 158 °F) Maximum T_{ambient} : 70 °C (158 °F) – heating due the process temperature |
| (B) | Maximum T_{process} : Temperature class reduced by selfheating of the Sensor |

For TSP3x1-W (X=1-3) and TSP341-W-Y11 without Energy Harvester the use for the different temperature classes depends on the process temperature and the zone definition. The transmitter housing may not heat up to more than 70 °C (158 °F). The transmitter housing heats up depending on the extension tube length 'K' and the process temperature. Therefore, the ambient temperature must be appropriately reduced in such cases.

The following table shows the maximum ambient temperature T_{ambient} for the TSP3x1-W at different process temperatures. A protection against radiation heat has to be realized. (For example: isolation with 25mm thickness around the process enclosure.)

| T_{process} | T_{ambient} for extension tube length K = 150 mm (5.9 in) | T_{ambient} for extension tube length K = 250 mm (9.8 in) |
|----------------------|--|--|
| 100 °C | max. 65 °C (149 °F) | max. 70 °C (158 °F) |
| 200 °C | max. 60 °C (140 °F) | max. 70 °C (158 °F) |
| 300 °C | max. 60 °C (140 °F) | max. 70 °C (158 °F) |
| 400 °C | max. 55 °C (131 °F) | max. 65 °C (149 °F) |

Self heating of the temperature sensor

The self heating of the sensor is generally defined. The corresponding values are considered in the following tables. For each configuration of the TSP3x1-W, the maximum process temperature for the various temperature classes is provided.

| Ex-Zone | T4 135 °C (-5K) | T3 200 °C (-5 K) | T2 300 °C (-10K) | T1 400 °C (-10K) |
|---------|-----------------|------------------|------------------|------------------|
| Zone 1 | 123 °C | 188 °C | 283 °C | 383 °C |
| Zone 0 | 96 °C | 148 °C | 223 °C | 303 °C |

Zone 0 in conformity with EN1127-1.

Electrical data

HART Maintenance Port

| | HART Maintenance Port on TTF300-W | Maximum external connection values |
|-----------------------|-----------------------------------|------------------------------------|
| Maximum voltage | $U_o = 5,4 \text{ V}$ | $U_i = 2,6 \text{ V}$ |
| Short-circuit current | $I_o = 25 \text{ mA}$ | $I_i = 18 \text{ mA}$ |
| Maximum power | $P_o = 34 \text{ mW}$ | — |
| Inductance | $L_i = 0 \text{ mH}$ | $L_o = 1 \text{ mH (IIC)}$ |
| Capacitance | $C_i = 1,2 \mu\text{F}$ | $C_o = 0,4 \mu\text{F (IIC)}$ |

| Main ordering information SensyTemp TSP311-W | XX |
|--|----|----|----|----|----|----|-------------------------|
| Thermowell Connection | | | | | | | Continued see next page |
| No extension / Connection head with thread M24 × 1,5 | W1 | | | | | | |
| No extension / Connection head with thread ½ in NPT | W2 | | | | | | |
| No extension / Connection head with lock nut M24 × 1,5 | W3 | | | | | | |
| Double nipple / G ½ A / G ½ A | W4 | | | | | | |
| Double nipple / ½ in NPT / ½ in NPT | W5 | | | | | | |
| Extension tube with Cylindrical thread G ½ A | G1 | | | | | | |
| Extension tube with Cylindrical thread G ¾ A | G2 | | | | | | |
| Extension tube with Cylindrical thread M14 × 1,5 | M1 | | | | | | |
| Extension tube with Cylindrical thread M18 × 1,5 | M2 | | | | | | |
| Extension tube with Cylindrical thread M20 × 1,5 | M3 | | | | | | |
| Extension tube with Cylindrical thread M24 × 1,5 | M4 | | | | | | |
| Extension tube with Cylindrical thread M27 × 2 | M5 | | | | | | |
| Extension tube with conygal thread ½ in NPT | N1 | | | | | | |
| Extension with Male nut, thread G ½ in | U6 | | | | | | |
| Extension tube with adjustable compression fitting G ½ A | A1 | | | | | | |
| Extension tube with adjustable compression fitting ½ in NPT | A2 | | | | | | |
| Nipple / ½ in NPT / ½ in NPT | N2 | | | | | | |
| Nipple-Union / ½ in NPT / Union ½ in NPT | N3 | | | | | | |
| Nipple - Union - Nipple / ½ in NPT / ½ in NPT | N4 | | | | | | |
| Others | Z9 | | | | | | |
| Immersion Length | | | | | | | |
| U = 140 mm (5.6 in) | U2 | | | | | | |
| U = 200 mm (8 in) | U4 | | | | | | |
| U = 260 mm (10.3 in) | U6 | | | | | | |
| Customer specific length < 150 mm (< 5.9 in) | W1 | | | | | | |
| Customer specific length 150 to < 300 mm (5.9 to < 11.8 in) | W2 | | | | | | |
| Customer specific length 300 to < 400 mm (11.8 to < 15.7 in) | W4 | | | | | | |
| Customer specific length 400 to < 500 mm (15.7 to < 19.7 in) | W5 | | | | | | |
| Customer specific length 500 to < 600 mm (19.7 to < 23.6 in) | W6 | | | | | | |
| Customer specific length 600 to < 750 mm (23.6 to < 29.5 in) | W7 | | | | | | |
| Customer specific length 750 to < 1000 mm (29.5 to < 39.4 in) | W8 | | | | | | |
| Customer specific length 1000 to < 1500 mm (39.4 to < 59 in) | Y1 | | | | | | |
| Customer specific length 1500 to < 2000 mm (59 to < 78.7 in) | Y3 | | | | | | |
| Customer specific length 2000 to < 3000 mm (78.7 to < 118 in) | Y5 | | | | | | |
| Customer specific length 3000 to < 5000 mm (118 to < 196.8 in) | Y7 | | | | | | |
| Customer specific length 5000 to < 10000 mm (196.8 to < 393.7 in) | Z1 | | | | | | |
| Customer specific length 10000 to < 15000 mm (393.7 to < 590.5 in) | Z3 | | | | | | |
| Customer specific length 15000 to < 20000 mm (590.5 to < 787.4 in) | Z4 | | | | | | |

... Ordering Information

| Main ordering information SensyTemp TSP311-W | XX | XX | XX | XX | XX | XX |
|---|----|----|----|----|----|-------------------------------|
| Measuring Inset Type | | | | | | Continued see next page |
| RTD, Basic application, TF, measuring range -50 to 400 °C (-58 to 752 °F), 10 g | S1 | | | | | |
| RTD, Extended vibration resistance, TF, measuring range -50 to 400 °C (-58 to 752 °F), 60 g | S2 | | | | | |
| RTD, Extended measuring range, WW, measuring range -196 to 600 °C (-321 to 1112 °F), 10 g | D1 | | | | | |
| RTD, Extended measuring range, WW, measuring range -196 to 600 °C (-321 to 1112 °F), 3 g | D2 | | | | | |
| Thermocouple | T1 | | | | | |
| Others | Z9 | | | | | |
| Measuring Inset Diameter | | | | | | |
| 3 mm (0,12 in) | | | D3 | | | |
| 6 mm (0,24 in) | | | D6 | | | |
| Others | | | Z9 | | | |
| Sensor Type and Wiring | | | | | | |
| 1 × Pt100, 2-wire | | | | | P1 | |
| 1 × Pt100, 3-wire | | | | | P2 | |
| 1 × Pt100, 4-wire | | | | | P3 | |
| 2 × Pt100, 2-wire | | | | | P4 | |
| 2 × Pt100, 3-wire | | | | | P5 | |
| 1 × Type K (NiCr-NiAl) | | | | | K1 | |
| 2 × Type K (NiCr-NiAl) | | | | | K2 | |
| 1 × Type J (Fe-CoNi) | | | | | J1 | |
| 2 × Type J (Fe-CoNi) | | | | | J2 | |
| 1 × Type N (NiCrSi-NiSi) | | | | | N1 | |
| 2 × Type N (NiCrSi-NiSi) | | | | | N2 | |
| 1 × Type T (Co-CoNi) | | | | | T1 | |
| 2 × Type T (Co-CoNi) | | | | | T2 | |
| 1 × Type E (NiCr-CoNi) | | | | | E1 | |
| 2 × Type E (NiCr-CoNi) | | | | | E2 | |
| Sensor Accuracy | | | | | | |
| RTD, Accuracy Class B, IEC 60751 | | | | | B2 | |
| Thin Film, Accuracy Class A, IEC 60751, Range -30 to 350 °C (-22 to 662 °F) | | | | | S1 | |
| Wire Wound, Accuracy Class A, IEC 60751, Range -196 to 500 °C (-321 to 932 °F) | | | | | D1 | |
| Wire Wound, Double, Accuracy Class A, IEC 60751, Range 0 to 250 °C (32 to 482 °F) | | | | | D2 | |
| TC, Accuracy Class 2, IEC 60584 | | | | | T2 | |
| TC, Accuracy Class 1, IEC 60584 | | | | | T1 | |
| TF, Accuracy Class AA, IEC 60751, Range 0 to 100 °C (32 to 212 °F) | | | | | S3 | |
| TC, Standard Accuracy ANSI MC96.1 | | | | | T4 | |
| TC, Special Accuracy ANSI MC96.1 | | | | | T3 | |
| Others | | | | | Z9 | |

| Main ordering information SensyTemp TSP311-W | | XX | XX |
|--|--|----|----|
| Connection Head Type / Material | | | |
| AGLH / Aluminium, high cover, screwed | | L2 | |
| AGLD / Aluminium, screwed cover with LCD indicator | | L4 | |
| AGSH / Stainless steel, high cover, screwed | | S2 | |
| AGSD / Stainless steel, screwed cover with LCD indicator | | S4 | |
| Others | | Z9 | |
| Transmitter | | | |
| WirelessHART | | | W1 |
| WirelessHART + Harvester | | | W3 |

Additional ordering information SensyTemp TSP311-W

| | XX |
|--|----|----|----|----|----|----|----|
| Declaration of Compliance: 2.1 | | | | | | | |
| Declaration of compliance according EN 10204-2.1, with the order | C4 | | | | | | |
| Test report: 2.2, Batch Values | | | | | | | |
| Test report according EN 10204-2.2 for batch values, MIC-TC | | C5 | | | | | |
| Inspection Certificate: 3.1, Visual, Dimensional and Functional Test | | | | | | | |
| Inspection certificate according EN 10204-3.1, visual, dimensional and functional test | | | C6 | | | | |
| Inspection Certificate: 3.1, Sensor Tolerance | | | | | | | |
| Inspection certificate according EN 10204-3.1, sensor tolerance | | | | CC | | | |
| Certificate: Sensor Calibration | | | | | | | |
| Inspection certificate according EN 10204-3.1, sensor calibration, single RTD | | | | | | CD | |
| Inspection certificate according EN 10204-3.1, sensor calibration, double RTD | | | | | | CE | |
| Inspection certificate according EN 10204-3.1, sensor calibration, single thermocouple | | | | | | CF | |
| Inspection certificate according EN 10204-3.1, sensor calibration, double thermocouple | | | | | | CG | |
| DAkKS sensor calibration, single RTD, calibration certificate per thermometer | | | | | | CH | |
| DAkKS sensor calibration, double RTD, calibration certificate per thermometer | | | | | | CJ | |
| DAkKS sensor calibration, single thermocouple, calibration certificate per thermometer | | | | | | CK | |
| DAkKS sensor calibration, double thermocouple, calibration certificate per thermometer | | | | | | CL | |
| Certificate: Other | | | | | | | |
| Other | | | | | | | CZ |
| Number of Calibration Test Points | | | | | | | |
| 1 point | | | | | | | P1 |
| 2 points | | | | | | | P2 |
| 3 points | | | | | | | P3 |
| 4 points | | | | | | | P4 |
| 5 points | | | | | | | P5 |

... Ordering Information

| Additional ordering information SensyTemp TSP311-W | XX | XX | XX |
|--|----|----|----|
| Temperatures for Sensor Calibration | | | |
| Standard calibration: 0 °C (32 °F) | V1 | | |
| Standard calibration: 100 °C (212 °F) | V2 | | |
| Standard calibration: 400 °C (752 °F) | V3 | | |
| Standard calibration: 0 °C and 100 °C (32 °F and 212 °F) | V4 | | |
| Standard calibration: 0 °C and 400 °C (32 °F and 752 °F) | V5 | | |
| Standard calibration: 0 °C, 100 °C and 200 °C (32 °F, 212 °F and 392 °F) | V7 | | |
| Standard calibration: 0 °C, 200 °C and 400 °C (32 °F, 392 °F and 752 °F) | V8 | | |
| Standard calibration: Customer specific temperatures | V6 | | |
| DAkKS calibration: 0 °C (32 °F) | D1 | | |
| DAkKS calibration: 100 °C (212 °F) | D2 | | |
| DAkKS calibration: 400 °C (752 °F) | D3 | | |
| DAkKS calibration: 0 °C and 100 °C (32 °F and 212 °F) | D4 | | |
| DAkKS calibration: 0 °C and 400 °C (32 °F and 752 °F) | D5 | | |
| DAkKS calibration: 0 °C, 100 °C and 200 °C (32 °F, 212 °F and 392 °F) | D7 | | |
| DAkKS calibration: 0 °C, 200 °C and 400 °C (32 °F, 392 °F and 752 °F) | D8 | | |
| DAkKS calibration: Customer specific temperatures | D6 | | |
| Documentation Language | | | |
| German | | M1 | |
| English | | M5 | |
| Name Plate | | | |
| Stainless steel plate with TAG no. | | | T1 |

Main ordering information SensyTemp TSP321-W

| Base model | TSP321-W | XX | XX | XX | XX | XX | XX | XX | XX | XX | XX | XX | XX |
|---|----------|----|----|-------------------------|----|----|----|----|----|----|----|----|----|
| SensyTemp TSP321-W Temperature Sensor, with tubular thermowell, WirelessHART | | | | | | | | | | | | | |
| Explosion Protection / Approvals | | | | Continued see next page | | | | | | | | | |
| Without | | | | Y0 | | | | | | | | | |
| Intrinsic Safety: ATEX II 1 G Ex ia IIC T4 | | | | A6 | | | | | | | | | |
| Intrinsic Safety: IECEx ia IIC T4 | | | | H6 | | | | | | | | | |
| Wetted Thermowell Material | | | | | | | | | | | | | |
| Stainless Steel ASTM 316L (1.4404) | | | | S1 | | | | | | | | | |
| Stainless Steel ASTM 316Ti (1.4571) | | | | S2 | | | | | | | | | |
| Heat Resistent Steel 1.4762 | | | | H2 | | | | | | | | | |
| Stainless Steel AISI 314 (1.4841) | | | | H3 | | | | | | | | | |
| Stainless Steel ASTM 904L (1.4539) | | | | S4 | | | | | | | | | |
| Ni-Alloy Hastelloy C-276 (2.4819) | | | | N1 | | | | | | | | | |
| Ni-Alloy Hastelloy C-4 (2.4610) | | | | N2 | | | | | | | | | |
| Others | | | | Z9 | | | | | | | | | |
| Thermowell Type | | | | | | | | | | | | | |
| Tubular thermowell with straight shaft (DIN 43772, Form 2) | | | | A1 | | | | | | | | | |
| Flanged tubular thermowell with straight shaft (DIN 43772, Form 2F) | | | | A2 | | | | | | | | | |
| Screwed tubular thermowell with straight shaft (DIN 43772, Form 2G) | | | | A3 | | | | | | | | | |
| Tubular thermowell, stepped tip (ABB Form 2S) | | | | B1 | | | | | | | | | |
| Flanged tubular thermowell, stepped tip (ABB Form 2FS) | | | | B2 | | | | | | | | | |
| Screwed tubular thermowell, stepped tip (ABB Form 2GS) | | | | B3 | | | | | | | | | |
| Tubular thermowell, tapered (DIN 43772, Form 3) | | | | C1 | | | | | | | | | |
| Flanged tubular thermowell, tapered (DIN 43772, Form 3F) | | | | C2 | | | | | | | | | |
| Screwed tubular thermowell, tapered (DIN 43772, Form 3G) | | | | C3 | | | | | | | | | |
| Screwed tubular thermowell without extension, straight shaft (ABB Form 2G0) | | | | A4 | | | | | | | | | |
| Screwed tubular thermowell without extension, stepped tip (ABB Form 2GS0) | | | | B4 | | | | | | | | | |
| Tubular thermowell, stepped tip 9 mm (0.36 in) (ABB Form 2S/9) | | | | K1 | | | | | | | | | |
| Flanged tubular thermowell, stepped tip 9 mm (0.36 in) (ABB Form 2FS/9) | | | | K2 | | | | | | | | | |
| Screwed tubular thermowell, stepped tip 9 mm (0.36 in) (ABB Form 2GS/9) | | | | K3 | | | | | | | | | |

| Main ordering information SensyTemp TSP321-W | XX | XX | XX | XX | XX | XX | XX |
|---|----|----|----|-------------------------|----|----|----|
| Immersion Length | | | | Continued see next page | | | |
| Without fixed immersion length | Y0 | | | | | | |
| U = 100 mm (4 in) | U1 | | | | | | |
| U = 160 mm (6.3 in) | U3 | | | | | | |
| U = 250 mm (10 in) | U5 | | | | | | |
| U = 400 mm (16 in) | U7 | | | | | | |
| Customer specific length < 150 mm (< 5.9 in) | W1 | | | | | | |
| Customer specific length 150 to < 300 mm (5.9 to < 11.8 in) | W2 | | | | | | |
| Customer specific length 300 to < 400 mm (11.8 to < 15.7 in) | W4 | | | | | | |
| Customer specific length 400 to < 500 mm (15.7 to < 19.7 in) | W5 | | | | | | |
| Customer specific length 500 to < 600 mm (19.7 to < 23.6 in) | W6 | | | | | | |
| Customer specific length 600 to < 750 mm (23.6 to < 29.5 in) | W7 | | | | | | |
| Customer specific length 750 to < 1000 mm (29.5 to < 39.4 in) | W8 | | | | | | |
| Customer specific length 1000 to < 1500 mm (39.4 to < 59 in) | Y1 | | | | | | |
| Customer specific length 1500 to < 2000 mm (59 to < 78.7 in) | Y3 | | | | | | |
| Customer specific length 2000 to < 3000 mm (78.7 to < 118 in) | Y5 | | | | | | |
| Customer specific length 3000 to < 5000 mm (118 to < 196.8 in) | Y7 | | | | | | |
| Customer specific length 5000 to < 10000 mm (196.8 to < 393.7 in) | Z1 | | | | | | |
| Nominal Length | | | | | | | |
| N = 230 mm (9.1 in) | | N1 | | | | | |
| N = 290 mm (11.42 in) | | N3 | | | | | |
| N = 380 mm (15 in) | | N5 | | | | | |
| N = 530 mm (20.9 in) | | N7 | | | | | |
| Customer specific length < 150 mm (< 5.9 in) | | W1 | | | | | |
| Customer specific length 150 to < 300 mm (5.9 to < 11.8 in) | | W2 | | | | | |
| Customer specific length 300 to < 400 mm (11.8 to < 15.7 in) | | W4 | | | | | |
| Customer specific length 400 to < 500 mm (15.7 to < 19.7 in) | | W5 | | | | | |
| Customer specific length 500 to < 600 mm (19.7 to < 23.6 in) | | W6 | | | | | |
| Customer specific length 600 to < 750 mm (23.6 to < 29.5 in) | | W7 | | | | | |
| Customer specific length 750 to < 1000 mm (29.5 to < 39.4 in) | | W8 | | | | | |
| Customer specific length 1000 to < 1500 mm (39.4 to < 59 in) | | Y1 | | | | | |
| Customer specific length 1500 to < 2000 mm (59 to < 78.7 in) | | Y3 | | | | | |
| Customer specific length 2000 to < 3000 mm (78.7 to < 118 in) | | Y5 | | | | | |
| Customer specific length 3000 to < 5000 mm (118 to < 196.8 in) | | Y7 | | | | | |
| Measuring Inset Type | | | | | | | |
| Without measuring inset | | Y0 | | | | | |
| RTD, Basic application, measuring range -50 to 400 °C (-58 to 752 °F), 10 g | | S1 | | | | | |
| RTD, Extended vibration resistance, measuring range -50 to 400 °C (-58 to 752 °F), 60 g | | S2 | | | | | |
| RTD, Extended measuring range, WW, measuring range -196 to 600 °C (-321 to 1112 °F), 10 g | | D1 | | | | | |
| RTD, Extended measuring range, WW, measuring range -196 to 600 °C (-321 to 1112 °F), 3 g | | D2 | | | | | |
| RTD, adjustable to German calibration regulations, sign of app. 000/308 - without calibration | | E1 | | | | | |
| Thermocouple | | T1 | | | | | |
| Others | | Z9 | | | | | |

... Ordering Information

| Main ordering information SensyTemp TSP321-W | XX | XX | XX | XX |
|---|----|----|----|----|
| Sensor Type and Wiring | | | | |
| 1 × Pt100, 2-wire | P1 | | | |
| 1 × Pt100, 3-wire | P2 | | | |
| 1 × Pt100, 4-wire | P3 | | | |
| 2 × Pt100, 2-wire | P4 | | | |
| 2 × Pt100, 3-wire | P5 | | | |
| 1 × Type K (NiCr-NiAl) | K1 | | | |
| 2 × Type K (NiCr-NiAl) | K2 | | | |
| 1 × Type J (Fe-CoNi) | J1 | | | |
| 2 × Type J (Fe-CoNi) | J2 | | | |
| 1 × Type N (NiCrSi-NiSi) | N1 | | | |
| 2 × Type N (NiCrSi-NiSi) | N2 | | | |
| 1 × Type T (Co-CoNi) | T1 | | | |
| 2 × Type T (Co-CoNi) | T2 | | | |
| 1 × Type E (NiCr-CoNi) | E1 | | | |
| 2 × Type E (NiCr-CoNi) | E2 | | | |
| Sensor Accuracy | | | | |
| RTD, Accuracy Class B, IEC 60751 | | | B2 | |
| Thin Film, Accuracy Class A, IEC 60751, Range -30 to 350 °C (-22 to 662 °F) | | | S1 | |
| Wire Wound, Accuracy Class A, IEC 60751, Range -196 to 500 °C (-321 to 932 °F) | | | D1 | |
| Wire Wound, Double, Accuracy Class A, IEC 60751, Range 0 to 250 °C (32 to 482 °F) | | | D2 | |
| TC, Accuracy Class 2, IEC 60584 | | | T2 | |
| TC, Accuracy Class 1, IEC 60584 | | | T1 | |
| TF, Accuracy Class AA, IEC 60751, Range 0 to 100 °C (0 to 212 °F) | | | S3 | |
| TC, Standard Accuracy ANSI MC96.1 | | | T4 | |
| TC, Special Accuracy ANSI MC96.1 | | | T3 | |
| Others | | | Z9 | |
| Connection Head Type / Material | | | | |
| AGLH / Aluminium, high cover, screwed | | | L2 | |
| AGLD / Aluminium, screwed cover with LCD indicator | | | L4 | |
| AGSH / Stainless steel, high cover, screwed | | | S2 | |
| AGSD / Stainless steel, screwed cover with LCD indicator | | | S4 | |
| Others | | | Z9 | |
| Transmitter | | | | |
| WirelessHART | | | | W1 |

... Ordering Information

| Additional ordering information SensyTemp TSP321-W | XX | XX | XX | XX |
|--|----|----|----|----|
| Certificate: Sensor Calibration | | | | |
| Inspection certificate according EN 10204-3.1, sensor calibration, single RTD | CD | | | |
| Inspection certificate according EN 10204-3.1, sensor calibration, double RTD | CE | | | |
| Inspection certificate according EN 10204-3.1, sensor calibration, single thermocouple | CF | | | |
| Inspection certificate according EN 10204-3.1, sensor calibration, double thermocouple | CG | | | |
| DAkKS sensor calibration, single RTD, calibration certificate per thermometer | CH | | | |
| DAkKS sensor calibration, double RTD, calibration certificate per thermometer | CJ | | | |
| DAkKS sensor calibration, single thermocouple, calibration certificate per thermometer | CK | | | |
| DAkKS sensor calibration, double thermocouple, calibration certificate per thermometer | CL | | | |
| Certificate: Other | | | | |
| Other | | | CZ | |
| Number of Calibration Test Points | | | | |
| 1 point | | | | P1 |
| 2 points | | | | P2 |
| 3 points | | | | P3 |
| 4 points | | | | P4 |
| 5 points | | | | P5 |
| Temperatures for Sensor Calibration | | | | |
| Standard calibration: 0 °C (32 °F) | | | | V1 |
| Standard calibration: 100 °C (212 °F) | | | | V2 |
| Standard calibration: 400 °C (752 °F) | | | | V3 |
| Standard calibration: 0 °C and 100 °C (32 °F and 212 °F) | | | | V4 |
| Standard calibration: 0 °C and 400 °C (32 °F and 752 °F) | | | | V5 |
| Standard calibration: 0 °C, 100 °C and 200 °C (32 °F, 212 °F and 392 °F) | | | | V7 |
| Standard calibration: 0 °C, 200 °C and 400 °C (32 °F, 392 °F and 752 °F) | | | | V8 |
| Standard calibration: Customer specific temperatures | | | | V6 |
| DAkKS calibration: 0 °C (32 °F) | | | | D1 |
| DAkKS calibration: 100 °C (212 °F) | | | | D2 |
| DAkKS calibration: 400 °C (752 °F) | | | | D3 |
| DAkKS calibration: 0 °C and 100 °C (32 °F and 212 °F) | | | | D4 |
| DAkKS calibration: 0 °C and 400 °C (32 °F and 752 °F) | | | | D5 |
| DAkKS calibration: 0 °C, 100 °C and 200 °C (32 °F, 212 °F and 392 °F) | | | | D7 |
| DAkKS calibration: 0 °C, 200 °C and 400 °C (32 °F, 392 °F and 752 °F) | | | | D8 |
| DAkKS calibration: Customer specific temperatures | | | | D6 |

| Additional ordering information SensyTemp TSP321-W | XX | XX | XX | XX | XX |
|--|-----------|-----------|-----------|-----------|-----------|
| Thermowell Options | | | | | |
| Thermowell stainless steel with additional tantalum sleeve | S1 | | | | |
| Thermowell coated with 0.5 mm (0.02 in) E-CTFE / Halar, wetted parts incl. flange surface | S2 | | | | |
| Thermowell coated with 0.5 mm (0.02 in) PFA, wetted parts incl. flange surface | S3 | | | | |
| Thermowell coated with 1 mm (0.04 in) NiCrB / META 43 (specify length from thermowell tip in mm) | S4 | | | | |
| Thermowell coated with 0.5 mm (0.02 in) NiZrO2 / PL1312 (specify length from thermowell tip in mm) | S5 | | | | |
| Thermowell clean for oxygen service | S9 | | | | |
| Others | SZ | | | | |
| Flange Connection Options | | | | | |
| Flange facing with groove form C EN 1092-1 | | F1 | | | |
| Flange facing with tongue form D EN 1092-1 | | F2 | | | |
| Flange facing with RTJ surface ASME B16.5 | | F3 | | | |
| Others | | FZ | | | |
| Thermometer single packed | | | | | |
| Each Thermometer single packed - Polyethylen | | | | PN | |
| Documentation Language | | | | | |
| German | | | | | M1 |
| English | | | | | M5 |
| Name Plate | | | | | |
| Stainless steel plate with TAG no. | | | | | T1 |

| Main ordering information SensyTemp TSP331-W | XX | XX | XX | XX | XX | XX |
|---|----|----|----|----|----|----------------------------|
| Thermowell Length | | | | | | Continued see next page |
| L = 110 mm (4.4 in), C = 65 mm (2.5 in) | D1 | | | | | |
| L = 115 mm (4.6 in), C = 40 mm (1.5 in) | D2 | | | | | |
| L = 140 mm (5.6 in), C = 65 mm (2.5 in) | D3 | | | | | |
| L = 200 mm (8 in), C = 65 mm (2.5 in) | D4 | | | | | |
| L = 200 mm (8 in), C = 125 mm (5 in) | D5 | | | | | |
| L = 260 mm (10.3 in), C = 125 mm (5 in) | D6 | | | | | |
| L = 410 mm (16.2 in), C = 275 mm (10.9 in) | D7 | | | | | |
| L = 146 mm (5.8 in) | R1 | | | | | |
| L = 175 mm (6.9 in) | R2 | | | | | |
| L = 265 mm (10.5 in) | R3 | | | | | |
| L = 415 mm (16.4 in) | R4 | | | | | |
| L = U + 65 mm (2.5 in) - European standard | P1 | | | | | |
| Custom specification | D9 | | | | | |
| Others | Z9 | | | | | |
| Measuring Inset Type | | | | | | |
| Without measuring inset | | Y0 | | | | |
| RTD, Basic application, measuring range -50 to 400 °C (-58 to 752 °F), 10 g | | S1 | | | | |
| RTD, Extended vibration resistance, measuring range -50 to 400 °C (-58 to 752 °F), 60 g | | S2 | | | | |
| RTD, Extended measuring range, WW, measuring range -196 to 600 °C (-321 to 1112 °F), 10 g | | D1 | | | | |
| RTD, Extended measuring range, WW, measuring range -196 to 600 °C (-321 to 1112 °F), 3 g | | D2 | | | | |
| RTD, adjustable to German calibration regulations, sign of app. 000/308 - without calibration | | E1 | | | | |
| Thermocouple | | T1 | | | | |
| Others | | Z9 | | | | |
| Sensor Type and Wiring | | | | | | |
| 1 × Pt100, 2-wire | | | P1 | | | |
| 1 × Pt100, 3-wire | | | P2 | | | |
| 1 × Pt100, 4-wire | | | P3 | | | |
| 2 × Pt100, 2-wire | | | P4 | | | |
| 2 × Pt100, 3-wire | | | P5 | | | |
| 1 × Type K (NiCr-NiAl) | | | K1 | | | |
| 2 × Type K (NiCr-NiAl) | | | K2 | | | |
| 1 × Type J (Fe-CoNi) | | | J1 | | | |
| 2 × Type J (Fe-CoNi) | | | J2 | | | |
| 1 × Type N (NiCrSi-NiSi) | | | N1 | | | |
| 2 × Type N (NiCrSi-NiSi) | | | N2 | | | |
| 1 × Type T (Co-CoNi) | | | T1 | | | |
| 2 × Type T (Co-CoNi) | | | T2 | | | |
| 1 × Type E (NiCr-CoNi) | | | E1 | | | |
| 2 × Type E (NiCr-CoNi) | | | E2 | | | |

... Ordering Information

| Main ordering information SensyTemp TSP331-W | XX | XX | XX |
|---|----|----|----|
| Sensor Accuracy | | | |
| RTD, Accuracy Class B, IEC 60751 | B2 | | |
| Thin Film, Accuracy Class A, IEC 60751, Range -30 to 350 °C (-22 to 662 °F) | S1 | | |
| Wire Wound, Accuracy Class A, IEC 60751, Range -196 to 500 °C (-321 to 932 °F) | D1 | | |
| Wire Wound, Double, Accuracy Class A, IEC 60751, Range 0 to 250 °C (32 to 482 °F) | D2 | | |
| TC, Accuracy Class 2, IEC 60584 | T2 | | |
| TC, Accuracy Class 1, IEC 60584 | T1 | | |
| TF, Accuracy Class AA, IEC 60751, Range 0 to 100 °C (0 to 212 °F) | S3 | | |
| TC, Standard Accuracy ANSI MC96.1 | T4 | | |
| TC, Special Accuracy ANSI MC96.1 | T3 | | |
| Others | Z9 | | |
| Connection Head Type / Material | | | |
| AGLH / Aluminium, high cover, screwed | | L2 | |
| AGLD / Aluminium, screwed cover with LCD indicator | | L4 | |
| AGSH / Stainless steel, high cover, screwed | | S2 | |
| AGSD / Stainless steel, screwed cover with LCD indicator | | S4 | |
| Transmitter | | | |
| WirelessHART | | | W1 |
| WirelessHART + Harvester | | | W3 |

... Ordering Information

| Additional ordering information SensyTemp TSP331-W | XX | XX | XX | XX |
|--|----|----|----|----|
| Certificate: Sensor Calibration | | | | |
| Inspection certificate according EN 10204-3.1, sensor calibration, single RTD | CD | | | |
| Inspection certificate according EN 10204-3.1, sensor calibration, double RTD | CE | | | |
| Inspection certificate according EN 10204-3.1, sensor calibration, single thermocouple | CF | | | |
| Inspection certificate according EN 10204-3.1, sensor calibration, double thermocouple | CG | | | |
| DAkKS sensor calibration, single RTD, calibration certificate per thermometer | CH | | | |
| DAkKS sensor calibration, double RTD, calibration certificate per thermometer | CJ | | | |
| DAkKS sensor calibration, single thermocouple, calibration certificate per thermometer | CK | | | |
| DAkKS sensor calibration, double thermocouple, calibration certificate per thermometer | CL | | | |
| Certificate: Other | | | | |
| Other | | | CZ | |
| Number of Calibration Test Points | | | | |
| 1 point | | | | P1 |
| 2 points | | | | P2 |
| 3 points | | | | P3 |
| 4 points | | | | P4 |
| 5 points | | | | P5 |
| Temperatures for Sensor Calibration | | | | |
| Standard calibration: 0 °C (32 °F) | | | | V1 |
| Standard calibration: 100 °C (212 °F) | | | | V2 |
| Standard calibration: 400 °C (752 °F) | | | | V3 |
| Standard calibration: 0 °C and 100 °C (32 °F and 212 °F) | | | | V4 |
| Standard calibration: 0 °C and 400 °C (32 °F and 752 °F) | | | | V5 |
| Standard calibration: 0 °C, 100 °C and 200 °C (32 °F, 212 °F and 392 °F) | | | | V7 |
| Standard calibration: 0 °C, 200 °C and 400 °C (32 °F, 392 °F and 752 °F) | | | | V8 |
| Standard calibration: Customer specific temperatures | | | | V6 |
| DAkKS calibration: 0 °C (32 °F) | | | | D1 |
| DAkKS calibration: 100 °C (212 °F) | | | | D2 |
| DAkKS calibration: 400 °C (752 °F) | | | | D3 |
| DAkKS calibration: 0 °C and 100 °C (32 °F and 212 °F) | | | | D4 |
| DAkKS calibration: 0 °C and 400 °C (32 °F and 752 °F) | | | | D5 |
| DAkKS calibration: 0 °C, 100 °C and 200 °C (32 °F, 212 °F and 392 °F) | | | | D7 |
| DAkKS calibration: 0 °C, 200 °C and 400 °C (32 °F, 392 °F and 752 °F) | | | | D8 |
| DAkKS calibration: Customer specific temperatures | | | | D6 |

| Additional ordering information SensyTemp TSP331-W | XX | XX | XX | XX | XX | XX |
|--|----|----|----|----|----|----|
| Thermowell Options | | | | | | |
| Thermowell coated with 0.5 mm (0.02 in) E-CTFE / Halar, wetted parts incl. flange surface | S2 | | | | | |
| Thermowell coated with 0.5 mm (0.02 in) PFA, wetted parts incl. flange surface | S3 | | | | | |
| Thermowell coated with 1 mm (0.04 in) NiCrB / META 43 (specify length from thermowell tip in mm) | S4 | | | | | |
| Thermowell coated with 0.5 mm (0.02 in) NiZrO2 / PL1312 (specify length from thermowell tip in mm) | S5 | | | | | |
| Thermowell incl. tests and certificates AD-2000 standard for austenitic steel | S6 | | | | | |
| Thermowell incl. tests and certificates AD-2000 standard for high temperature steel | S7 | | | | | |
| Thermowell incl. tests and certificates NACE MR 01-75 | S8 | | | | | |
| Thermowell clean for oxygen service | S9 | | | | | |
| Others | SZ | | | | | |
| Thermowell Stress Calculations | | | | | | |
| Thermowell stress calculation according Dittrich / Kohler | | SD | | | | |
| Thermowell stress calculation according Murdock | | SM | | | | |
| Flange Connection Options | | | | | | |
| Flange facing with groove form C EN 1092-1 | | | F1 | | | |
| Flange facing with tongue form D EN 1092-1 | | | F2 | | | |
| Flange facing with RTJ surface ASME B16.5 | | | F3 | | | |
| Flange full penetration welded | | | F4 | | | |
| Others | | | FZ | | | |
| Thermometer single packed | | | | | | |
| Each Thermometer single packed - Polyethylen | | | | | PN | |
| Documentation Language | | | | | | |
| German | | | | | | M1 |
| English | | | | | | M5 |
| Name Plate | | | | | | |
| Stainless steel plate with TAG no. | | | | | | T1 |

| Main ordering information SensyTemp TSP341-W | XX | XX | XX | XX |
|---|-----------|-----------|-----------|-----------|
| Sensor Type and Wiring | | | | |
| 1 × Pt100, 2-wire | P1 | | | |
| 1 × Pt100, 3-wire | P2 | | | |
| 1 × Pt100, 4-wire | P3 | | | |
| 2 × Pt100, 2-wire | P4 | | | |
| 2 × Pt100, 3-wire | P5 | | | |
| 1 × Type K (NiCr-NiAl) | K1 | | | |
| 2 × Type K (NiCr-NiAl) | K2 | | | |
| 1 × Type J (Fe-CoNi) | J1 | | | |
| 2 × Type J (Fe-CoNi) | J2 | | | |
| 1 × Type N (NiCrSi-NiSi) | N1 | | | |
| 2 × Type N (NiCrSi-NiSi) | N2 | | | |
| 1 × Type T (Co-CoNi) | T1 | | | |
| 2 × Type T (Co-CoNi) | T2 | | | |
| 1 × Type E (NiCr-CoNi) | E1 | | | |
| 2 × Type E (NiCr-CoNi) | E2 | | | |
| Sensor Accuracy | | | | |
| RTD, Accuracy Class B, IEC 60751 | | | B2 | |
| Thin Film, Accuracy Class A, IEC 60751, Range -30 to 350 °C (-22 to 662 °F) | | | S1 | |
| Wire Wound, Accuracy Class A, IEC 60751, Range -196 to 500 °C (-321 to 932 °F) | | | D1 | |
| Wire Wound, Double, Accuracy Class A, IEC 60751, Range 0 to 250 °C (32 to 482 °F) | | | T2 | |
| TC, Accuracy Class 2, IEC 60584 | | | T1 | |
| TC, Accuracy Class 1, IEC 60584 | | | T4 | |
| TC, Standard Accuracy ANSI MC96.1 | | | T3 | |
| Connection Head Type / Material | | | | |
| AGLH / Aluminium, high cover, screwed | | | | L2 |
| AGLD / Aluminium, screwed cover with LCD indicator | | | | L4 |
| AGSH / Stainless steel, high cover, screwed | | | | S2 |
| AGSD / Stainless steel, screwed cover with LCD indicator | | | | S4 |
| Transmitter | | | | |
| WirelessHART | | | | W1 |
| WirelessHART + Harvester | | | | W3 |

... Ordering Information

Additional ordering information SensyTemp TSP341-W

| | XX |
|--|----|----|----|----|----|----|----|
| Declaration of Compliance: 2.1 | | | | | | | |
| Declaration of compliance according EN 10204-2.1, with the order | C4 | | | | | | |
| Test report: 2.2, Batch Values | | | | | | | |
| Test report according EN 10204-2.2 for batch values, MIC-TC | | C5 | | | | | |
| Inspection Certificate: 3.1, Visual, Dimensional and Functional Test | | | | | | | |
| Inspection certificate according EN 10204-3.1, visual, dimensional and functional test | | | C6 | | | | |
| Inspection Certificate: 3.1, Sensor Tolerance | | | | | | | |
| Inspection certificate according EN 10204-3.1, sensor tolerance | | | | | CC | | |
| Certificate: Sensor Calibration | | | | | | | |
| Inspection certificate according EN 10204-3.1, sensor calibration, single RTD | | | | | | CD | |
| Inspection certificate according EN 10204-3.1, sensor calibration, double RTD | | | | | | CE | |
| Inspection certificate according EN 10204-3.1, sensor calibration, single thermocouple | | | | | | CF | |
| Inspection certificate according EN 10204-3.1, sensor calibration, double thermocouple | | | | | | CG | |
| DAkkS sensor calibration, single RTD, calibration certificate per thermometer | | | | | | CH | |
| DAkkS sensor calibration, double RTD, calibration certificate per thermometer | | | | | | CJ | |
| DAkkS sensor calibration, single thermocouple, calibration certificate per thermometer | | | | | | CK | |
| DAkkS sensor calibration, double thermocouple, calibration certificate per thermometer | | | | | | CL | |
| Certificate: Other | | | | | | | |
| Other | | | | | | | CZ |
| Number of Calibration Test Points | | | | | | | |
| 1 point | | | | | | | P1 |
| 2 points | | | | | | | P2 |
| 3 points | | | | | | | P3 |
| 4 points | | | | | | | P4 |
| 5 points | | | | | | | P5 |

| Additional ordering information SensyTemp TSP341-W | XX | XX | XX |
|--|-----------|-----------|-----------|
| Temperatures for Sensor Calibration | | | |
| Standard calibration: 0 °C (32 °F) | V1 | | |
| Standard calibration: 100 °C (212 °F) | V2 | | |
| Standard calibration: 400 °C (752 °F) | V3 | | |
| Standard calibration: 0 °C and 100 °C (32 °F and 212 °F) | V4 | | |
| Standard calibration: 0 °C and 400 °C (32 °F and 752 °F) | V5 | | |
| Standard calibration: 0 °C, 100 °C and 200 °C (32 °F, 212 °F and 392 °F) | V7 | | |
| Standard calibration: 0 °C, 200 °C and 400 °C (32 °F, 392 °F and 752 °F) | V8 | | |
| Standard calibration: Customer specific temperatures | V6 | | |
| DAkKS calibration: 0 °C (32 °F) | D1 | | |
| DAkKS calibration: 100 °C (212 °F) | D2 | | |
| DAkKS calibration: 400 °C (752 °F) | D3 | | |
| DAkKS calibration: 0 °C and 100 °C (32 °F and 212 °F) | D4 | | |
| DAkKS calibration: 0 °C and 400 °C (32 °F and 752 °F) | D5 | | |
| DAkKS calibration: 0 °C, 100 °C and 200 °C (32 °F, 212 °F and 392 °F) | D7 | | |
| DAkKS calibration: 0 °C, 200 °C and 400 °C (32 °F, 392 °F and 752 °F) | D8 | | |
| DAkKS calibration: Customer specific temperatures | D6 | | |
| Documentation Language | | | |
| German | | M1 | |
| English | | M5 | |
| Name Plate | | | |
| Stainless steel plate with TAG no. | | | T1 |

| Accessories | Order code |
|---|-------------------|
| Lithium battery | 3KXT000029U0000 |
| TSP300-W Commissioning Instruction, German | 3KXT161300R4403 |
| TSP300-W Commissioning Instruction, English | 3KXT161300R4401 |
| TSP300-W Commissioning Instruction, Language package Western Europe / Scandinavia | 3KXT161300R4493 |
| TSP300-W Commissioning Instruction, Language package Eastern Europe | 3KXT161300R4494 |
| TSP300-W Documentation CD-ROM | 3KXT161300R0800 |

Order form configuration

| Configuration | Selection |
|---|--|
| Measurement type (for 2-sensor selection only) | <input type="checkbox"/> Sensor redundancy / sensor backup <input type="checkbox"/> Sensor drift monitoring ____ °C / K sensor drift difference ____s time limit for drift overshoot <input type="checkbox"/> Difference measurement <input type="checkbox"/> Average measurement |
| Software write protection | <input type="checkbox"/> Off (standard) <input type="checkbox"/> On |
| TAG number | <input type="checkbox"/> _____ |
| Long TAG number | <input type="checkbox"/> _____ |
| Network ID | <input type="checkbox"/> Hexadecimal value ABB standard or _____ |
| Join key | <input type="checkbox"/> Hexadecimal value ABB standard or _____ <input type="checkbox"/> Hexadecimal value ABB standard or _____ <input type="checkbox"/> Hexadecimal value ABB standard or _____ <input type="checkbox"/> Hexadecimal value ABB standard or _____ |
| Burst message 1 | <input type="checkbox"/> 3 'Dynamic HART variables' <input type="checkbox"/> 9 'Device variables with status' (ABB-Standard) |
| HART command | |
| Update rate | <input type="checkbox"/> 4 seconds <input type="checkbox"/> 8 seconds <input type="checkbox"/> 16 seconds <input type="checkbox"/> 32 seconds <input type="checkbox"/> 60 to 3600 seconds _____ |

Trademarks

WirelessHART is a registered trademark of FieldComm Group, Austin, Texas, USA

ABB Limited**Measurement & Analytics**

Howard Road, St. Neots
Cambridgeshire, PE19 8EU
UK

Tel: +44 (0)870 600 6122

Fax: +44 (0)1480 213 339

Email: enquiries.mp.uk@gb.abb.com

ABB Inc.**Measurement & Analytics**

125 E. County Line Road
Warminster, PA 18974
USA

Tel: +1 215 674 6000

Fax: +1 215 674 7183

ABB Automation Products GmbH**Measurement & Analytics**

Schillerstr. 72
32425 Minden
Germany

Tel: +49 571 830-0

Fax: +49 571 830-1806

abb.com/wirelessmeasurement

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.